




L1: TOP CONDUCTOR - COPPER 0.035 MM

* DIELECTRIC - FR-4 0.8 MM

L2: BOTTOM CONDUCTOR - COPPER 0.035 MM

DESIGN CROSS SECTION CHART

TOTAL THICKNESS 0.87 MM



DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	SIZE	PLATED	QTY
⊙	0.2	PLATED	62
.	0.5	PLATED	14