

N 沟道 NexFET™ 功率 MOSFET

1 特性


- 针对 5V 栅极驱动进行了优化
- 超低 Q_g 和 Q_{gd}
- 低热阻
- 具有雪崩能力
- 无铅引脚镀层
- 符合 RoHS 标准
- 无卤素
- SON 5mm × 6mm 塑料封装

2 应用


- 网络、电信和计算系统中的负载点同步降压转换器
- 同步或控制 FET 应用

3 说明

NexFET™ 功率 MOSFET 旨在更最大限度地减少功率转换应用中的损耗，并针对 5V 栅极驱动应用进行了优化。



顶视图



$R_{DS(on)}$ 与 V_{GS} 间的关系

产品概要

V_{DS}	漏源极电压	25	V
Q_g	总栅极电荷 (4.5V)	6.8	nC
Q_{gd}	栅漏栅极电荷	1.3	nC
$R_{DS(on)}$	漏源导通电阻	$V_{GS}=3V$	5.4 mΩ
		$V_{GS}=4.5V$	4.6 mΩ
		$V_{GS}=8V$	3.9 mΩ
$V_{GS(th)}$	阈值电压	1.1	V


订购信息

器件	封装	介质	数量	出货
CSD16322Q5	SON 5mm × 6mm 塑料封装	13 英寸卷带	2500	卷带包装

绝对最大额定值

$T_A = 25^\circ\text{C}$ 时测得，除非另外注明	值	单位
V_{DS}	漏源极电压	25 V
V_{GS}	栅源电压	+10 / -8 V
I_D	持续漏极电流, $T_C = 25^\circ\text{C}$	97 A
	持续漏极电流 ⁽¹⁾	21 A
I_{DM}	脉冲漏极电流, $T_A = 25^\circ\text{C}$ ⁽²⁾	136 A
P_D	功率耗散 ⁽¹⁾	3.1 W
T_J, T_{STG}	运行结温和储存温度范围	-55 至 150 $^\circ\text{C}$
E_{AS}	雪崩能量，单一脉冲 $I_D = 50\text{A}, L = 0.1\text{mH}, R_G = 25\Omega$	125 mJ

- (1) 典型 $R_{\theta JA} = 39^\circ\text{C/W}$ (在 0.06 英寸 (1.52mm) 厚的 FR4 PCB 上安装 1 平方英寸 (6.45cm²)、2oz、0.071mm 厚的铜焊盘时)。
- (2) 脉冲持续时间 $\leq 300\mu\text{s}$ ，占空比 $\leq 2\%$



栅极电荷



Table of Contents

1 特性.....	1	5 Electrical Characteristics.....	3
2 应用.....	1	6 Thermal Characteristics.....	3
3 说明.....	1	7 Typical MOSFET Characteristics.....	4
4 Revision History.....	2	8 Mechanical, Packaging, and Orderable Information....	7

4 Revision History

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision B (May 2010) to Revision C (October 2023) Page

- Updated the numbering format for tables, figures, and cross-references throughout the document.....7

Changes from Revision A (April 2010) to Revision B (May 2010) Page

- Changed $R_{DS(on)}$, $V_{GS} = 3\text{ V}$ in the Electrical Characteristics table From: 7 To: 7.2 in the max column.....3

Changes from Revision * (August 2009) to Revision A (April 2010) Page

- 将“绝对最大额定值”的注释 1 从“ $R_{\theta JA} = 39^\circ\text{C/W}$ ”更改为“典型 $R_{\theta JA} = 39^\circ\text{C/W}$ ”..... 1
- Changed 图 7-1 text From: $R_{\theta JA} = 99^\circ\text{C/W}$ To: Typical $R_{\theta JA} = 98^\circ\text{C/W}$ 4
- Changed 图 7-10 text From: $R_{\theta JA} = 99^\circ\text{C/W}$ To: Typical $R_{\theta JA} = 98^\circ\text{C/W}$ 4
- Changed 图 7-11 X-axis values..... 4

5 Electrical Characteristics

(T_A = 25°C unless otherwise stated)


PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT	
Static Characteristics							
BV _{DSS}	Drain to Source Voltage	V _{GS} = 0 V, I _D = 250 μA	25			V	
I _{DSS}	Drain to Source Leakage Current	V _{GS} = 0 V, V _{DS} = 20 V	1			μA	
I _{GSS}	Gate to Source Leakage Current	V _{DS} = 0 V, V _{GS} = +10/−8 V	100			nA	
V _{GS(th)}	Gate to Source Threshold Voltage	V _{DS} = V _{GS} , I _D = 250 μA	0.9	1.1	1.4	V	
R _{DS(on)}	Drain to Source On Resistance	V _{GS} = 3 V, I _D = 20 A	5.4			7.2	mΩ
		V _{GS} = 4.5 V, I _D = 20 A	4.6			5.8	mΩ
		V _{GS} = 8 V, I _D = 20 A	3.9			5	mΩ
g _{fs}	Transconductance	V _{DS} = 15 V, I _D = 20 A	106			S	
Dynamic Characteristics							
C _{iss}	Input Capacitance	V _{GS} = 0 V, V _{DS} = 12.5 V, f = 1 MHz	1050		1365	pF	
C _{oss}	Output Capacitance		740		950	pF	
C _{rss}	Reverse Transfer Capacitance		55		70	pF	
R _G	Series Gate Resistance		1.1		2.2	Ω	
Q _g	Gate Charge Total (4.5 V)	V _{DS} = 12.5 V, I _D = 20 A	6.8		9.7	nC	
Q _{gd}	Gate Charge Gate to Drain		1.3			nC	
Q _{gs}	Gate Charge Gate to Source		2.4			nC	
Q _{g(th)}	Gate Charge at V _{th}		1.3			nC	
Q _{oss}	Output Charge	V _{DS} = 13 V, V _{GS} = 0 V	17			nC	
t _{d(on)}	Turn On Delay Time	V _{DS} = 12.5 V, V _{GS} = 4.5 V, I _D = 20 A, R _G = 2 Ω	6.1			ns	
t _r	Rise Time		10.7			ns	
t _{d(off)}	Turn Off Delay Time		12.3			ns	
t _f	Fall Time		3.7			ns	
Diode Characteristics							
V _{SD}	Diode Forward Voltage	I _{SD} = 20 A, V _{GS} = 0 V	0.8		1	V	
Q _{rr}	Reverse Recovery Charge	V _{DD} = 13 V, I _F = 20 A, di/dt = 300 A/μs	19			nC	
t _{rr}	Reverse Recovery Time	V _{DD} = 13 V, I _F = 20 A, di/dt = 300 A/μs	21			ns	

6 Thermal Characteristics


(T_A = 25°C unless otherwise stated)

PARAMETER		MIN	TYP	MAX	UNIT
R _{θJC}	Thermal Resistance Junction to Case ⁽¹⁾			2.4	°C/W
R _{θJA}	Thermal Resistance Junction to Ambient ^{(1) (2)}			50	°C/W

- (1) R_{θJC} is determined with the device mounted on a 1-inch² (6.45-cm²), 2-oz. (0.071-mm thick) Cu pad on a 1.5-inch × 1.5-inch (3.81-cm × 3.81-cm), 0.06-inch (1.52-mm) thick FR4 PCB. R_{θJC} is specified by design, whereas R_{θJA} is determined by the user's board design.
- (2) Device mounted on FR4 material with 1-inch² (6.45-cm²), 2-oz. (0.071-mm thick) Cu.




Max $R_{\theta JA} = 50^{\circ}\text{C/W}$
 when mounted on 1 inch²
 (6.45 cm²) of 2-oz. (0.071-
 mm thick) Cu.



Max $R_{\theta JA} = 123^{\circ}\text{C/W}$ when
 mounted on minimum pad
 area of 2-oz. (0.071-mm
 thick) Cu.

7 Typical MOSFET Characteristics

($T_A = 25^{\circ}\text{C}$ unless otherwise stated)



7 Typical MOSFET Characteristics

($T_A = 25^\circ\text{C}$ unless otherwise stated)




图 7-2. Saturation Characteristics




图 7-3. Transfer Characteristics




图 7-4. Gate Charge




图 7-5. Capacitance




图 7-6. Threshold Voltage vs. Temperature




图 7-7. On-State Resistance vs. Gate to Source Voltage

7 Typical MOSFET Characteristics (continued)

($T_A = 25^\circ\text{C}$ unless otherwise stated)




图 7-8. Normalized On-State Resistance vs. Temperature




图 7-9. Typical Diode Forward Voltage




图 7-10. Maximum Safe Operating Area




图 7-11. Single Pulse Unclamped Inductive Switching




图 7-12. Maximum Drain Current vs. Temperature

8 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
CSD16322Q5	Active	Production	VSON-CLIP (DQH) 8	2500 LARGE T&R	ROHS Exempt	SN	Level-1-260C-UNLIM	-55 to 150	CSD16322
CSD16322Q5.B	Active	Production	VSON-CLIP (DQH) 8	2500 LARGE T&R	ROHS Exempt	SN	Level-1-260C-UNLIM	-55 to 150	CSD16322

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



VSON-CLIP - 1.05 mm max height

PLASTIC SMALL OUTLINE - NO LEAD




1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.

EXAMPLE BOARD LAYOUT

DQH0008A

VSON-CLIP - 1.05 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE
SOLDER MASK DEFINED
SCALE:15X

4223292/A 10/2016

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/sluea271).
5. Vias are optional depending on application, refer to device data sheet. If some or all are implemented, recommended via locations are shown.

EXAMPLE STENCIL DESIGN

DQH0008A

VSON-CLIP - 1.05 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD 9:
71% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE
SCALE:15X

4223292/A 10/2016

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2025，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月