

## CSD18503KCS 40V N 沟道 NexFET™ 功率 MOSFET

## 1 特性



- 超低  $Q_g$  和  $Q_{gd}$
- 低热阻
- 雪崩级
- 逻辑电平
- 无铅引脚镀层
- 符合 RoHS
- 无卤素
- TO-220 塑料封装

## 2 应用

- 直流/直流转换
- 次级侧同步整流器
- 电机控制

## 3 说明

这款 40V、 $3.6\text{m}\Omega$ 、TO-220 NexFET™ 功率 MOSFET 旨在用于更大限度地降低功率转换应用中的损耗。

 $R_{DS(on)}$  与  $V_{GS}$  之间的关系

## 产品概要

| $T_A = 25^\circ\text{C}$ |              | 典型值                    |     | 单位               |
|--------------------------|--------------|------------------------|-----|------------------|
| $V_{DS}$                 | 漏源电压         | 40                     |     | V                |
| $Q_g$                    | 栅极电荷总量 (10V) | 30                     |     | nC               |
| $Q_{gd}$                 | 栅极电荷 (栅极到漏极) | 4.6                    |     | nC               |
| $R_{DS(on)}$             | 漏源导通电阻       | $V_{GS} = 4.5\text{V}$ | 5.4 | $\text{m}\Omega$ |
|                          |              | $V_{GS} = 10\text{V}$  | 3.6 | $\text{m}\Omega$ |
| $V_{GS(th)}$             | 阈值电压         | 1.9                    |     | V                |

订购信息<sup>(1)</sup>


| 器件          | 封装          | 介质 | 数量 | 运输 |
|-------------|-------------|----|----|----|
| CSD18503KCS | TO-220 塑料封装 | 管装 | 50 | 管装 |

(1) 如需了解所有可用封装, 请参阅数据表末尾的可订购产品附录。

## 绝对最大额定值

| $T_A = 25^\circ\text{C}$ |                                                                         | 值         | 单位               |
|--------------------------|-------------------------------------------------------------------------|-----------|------------------|
| $V_{DS}$                 | 漏源电压                                                                    | 40        | V                |
| $V_{GS}$                 | 栅源电压                                                                    | $\pm 20$  | V                |
| $I_D$                    | 持续漏极电流 (受封装限制)                                                          | 100       | A                |
|                          | 持续漏极电流 (受芯片限制), $T_C = 25^\circ\text{C}$ 时测得                            | 142       |                  |
|                          | 持续漏极电流 (受芯片限制), $T_C = 100^\circ\text{C}$ 时测得                           | 100       |                  |
| $I_{DM}$                 | 脉冲漏极电流 <sup>(1)</sup>                                                   | 358       | A                |
| $P_D$                    | 功率耗散                                                                    | 188       | W                |
| $T_J$ 、 $T_{stg}$        | 工作结温和贮存温度范围                                                             | -55 至 175 | $^\circ\text{C}$ |
| $E_{AS}$                 | 雪崩能量, 单脉冲<br>$I_D = 57\text{A}$ , $L = 0.1\text{mH}$ , $R_G = 25\Omega$ | 162       | mJ               |

(1) 最大  $R_{\theta JC} = 0.8^\circ\text{C/W}$ , 脉冲持续时间  $\leq 100\mu\text{s}$ , 占空比  $\leq 1\%$



栅极电荷



Table of Contents

|                                         |   |                                                        |   |
|-----------------------------------------|---|--------------------------------------------------------|---|
| 1 特性.....                               | 1 | 5.1 接收文档更新通知.....                                      | 7 |
| 2 应用.....                               | 1 | 5.2 支持资源.....                                          | 7 |
| 3 说明.....                               | 1 | 5.3 Trademarks.....                                    | 7 |
| 4 Specifications.....                   | 3 | 5.4 静电放电警告.....                                        | 7 |
| 4.1 Electrical Characteristics.....     | 3 | 5.5 术语表.....                                           | 7 |
| 4.2 Thermal Information.....            | 3 | 6 Revision History.....                                | 7 |
| 4.3 Typical MOSFET Characteristics..... | 4 | 7 Mechanical, Packaging, and Orderable Information.... | 8 |
| 5 Device and Documentation Support..... | 7 |                                                        |   |

## 4 Specifications

### 4.1 Electrical Characteristics

(T<sub>A</sub> = 25°C unless otherwise stated)

| PARAMETER               |                                  | TEST CONDITIONS                                                                             | MIN | TYP  | MAX  | UNIT |
|-------------------------|----------------------------------|---------------------------------------------------------------------------------------------|-----|------|------|------|
| STATIC CHARACTERISTICS  |                                  |                                                                                             |     |      |      |      |
| BV <sub>DSS</sub>       | Drain-to-Source Voltage          | V <sub>GS</sub> = 0V, I <sub>D</sub> = 250 μ A                                              | 40  |      |      | V    |
| I <sub>DSS</sub>        | Drain-to-Source Leakage Current  | V <sub>GS</sub> = 0V, V <sub>DS</sub> = 32V                                                 |     |      | 1    | μ A  |
| I <sub>GSS</sub>        | Gate-to-Source Leakage Current   | V <sub>DS</sub> = 0V, V <sub>GS</sub> = 20V                                                 |     |      | 100  | nA   |
| V <sub>GS(th)</sub>     | Gate-to-Source Threshold Voltage | V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250 μ A                                | 1.5 | 1.9  | 2.3  | V    |
| R <sub>DS(on)</sub>     | Drain-to-Source On-Resistance    | V <sub>GS</sub> = 4.5V, I <sub>D</sub> = 75A                                                |     | 5.4  | 6.8  | mΩ   |
|                         |                                  | V <sub>GS</sub> = 10V, I <sub>D</sub> = 75A                                                 |     | 3.6  | 4.5  | mΩ   |
| g <sub>fs</sub>         | Transconductance                 | V <sub>DS</sub> = 20V, I <sub>D</sub> = 75A                                                 |     | 98   |      | S    |
| DYNAMIC CHARACTERISTICS |                                  |                                                                                             |     |      |      |      |
| C <sub>iss</sub>        | Input Capacitance                | V <sub>GS</sub> = 0V, V <sub>DS</sub> = 20V, f = 1MHz                                       |     | 2500 | 3150 | pF   |
| C <sub>oss</sub>        | Output Capacitance               |                                                                                             |     | 480  | 600  | pF   |
| C <sub>rss</sub>        | Reverse Transfer Capacitance     |                                                                                             |     | 12   | 16   | pF   |
| R <sub>G</sub>          | Series Gate Resistance           |                                                                                             |     | 1.4  | 2.8  | Ω    |
| Q <sub>g</sub>          | Gate Charge Total (4.5V)         | V <sub>DS</sub> = 20V, I <sub>D</sub> = 75A                                                 |     | 15   | 18   | nC   |
| Q <sub>g</sub>          | Gate Charge Total (10V)          |                                                                                             |     | 30   | 36   | nC   |
| Q <sub>gd</sub>         | Gate Charge Gate-to-Drain        |                                                                                             |     | 4.6  |      | nC   |
| Q <sub>gs</sub>         | Gate Charge Gate-to-Source       |                                                                                             |     | 7.7  |      | nC   |
| Q <sub>g(th)</sub>      | Gate Charge at V <sub>th</sub>   |                                                                                             |     | 4.7  |      | nC   |
| Q <sub>oss</sub>        | Output Charge                    | V <sub>DS</sub> = 20V, V <sub>GS</sub> = 0V                                                 |     | 30   |      | nC   |
| t <sub>d(on)</sub>      | Turn On Delay Time               | V <sub>DS</sub> = 20V, V <sub>GS</sub> = 10V,<br>I <sub>DS</sub> = 75A, R <sub>G</sub> = 0Ω |     | 5.7  |      | ns   |
| t <sub>r</sub>          | Rise Time                        |                                                                                             |     | 5.3  |      | ns   |
| t <sub>d(off)</sub>     | Turn Off Delay Time              |                                                                                             |     | 14   |      | ns   |
| t <sub>f</sub>          | Fall Time                        |                                                                                             |     | 6.8  |      | ns   |
| DIODE CHARACTERISTICS   |                                  |                                                                                             |     |      |      |      |
| V <sub>SD</sub>         | Diode Forward Voltage            | I <sub>SD</sub> = 75A, V <sub>GS</sub> = 0V                                                 |     | 0.8  | 1    | V    |
| Q <sub>rr</sub>         | Reverse Recovery Charge          | V <sub>DS</sub> = 20V, I <sub>F</sub> = 75A,                                                |     | 60   |      | nC   |
| t <sub>rr</sub>         | Reverse Recovery Time            | di/dt = 300A/ μ s                                                                           |     | 37   |      | ns   |

### 4.2 Thermal Information

(T<sub>A</sub> = 25°C unless otherwise stated)

| THERMAL METRIC   |                                        | MIN | TYP | MAX | UNIT |
|------------------|----------------------------------------|-----|-----|-----|------|
| R <sub>θJC</sub> | Junction-to-Case Thermal Resistance    |     |     | 0.8 | °C/W |
| R <sub>θJA</sub> | Junction-to-Ambient Thermal Resistance |     |     | 62  |      |

### 4.3 Typical MOSFET Characteristics

( $T_A = 25^\circ\text{C}$  unless otherwise stated)




图 4-1. Transient Thermal Impedance




图 4-2. Saturation Characteristics




图 4-3. Transfer Characteristics




图 4-4. Gate Charge




图 4-5. Capacitance




图 4-6. Threshold Voltage vs Temperature




图 4-7. On-State Resistance vs Gate-to-Source Voltage




图 4-8. Normalized On-State Resistance vs Temperature




图 4-9. Typical Diode Forward Voltage




图 4-10. Maximum Safe Operating Area




图 4-11. Single Pulse Unclamped Inductive Switching




图 4-12. Maximum Drain Current vs Temperature

## 5 Device and Documentation Support

### 5.1 接收文档更新通知

要接收文档更新通知，请导航至 [ti.com](https://www.ti.com) 上的器件产品文件夹。点击 [通知](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

### 5.2 支持资源

**TI E2E™ 中文支持论坛**是工程师的重要参考资料，可直接从专家处获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题，获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的[使用条款](#)。

### 5.3 Trademarks

NexFET™ is a trademark of Texas Instruments.

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

### 5.4 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

### 5.5 术语表

**TI 术语表** 本术语表列出并解释了术语、首字母缩略词和定义。

## 6 Revision History

注：以前版本的页码可能与当前版本的页码不同

| Changes from Revision A (October 2023) to Revision B (March 2024) | Page |
|-------------------------------------------------------------------|------|
| • 更新了整个文档中的表格、图和交叉参考的编号格式.....                                    | 1    |

| Changes from Revision * (September 2012) to Revision A (January 2015)                              | Page |
|----------------------------------------------------------------------------------------------------|------|
| • 向标题添加了器件型号.....                                                                                  | 1    |
| • $T_C = 25^{\circ}\text{C}$ 时的连续漏极电流增加至 142A.....                                                 | 1    |
| • $T_C = 125^{\circ}\text{C}$ 时的连续漏极电流增加至 100A.....                                                | 1    |
| • 脉冲漏极电流增加至 358A.....                                                                              | 1    |
| • 最大功耗增加至 188W.....                                                                                | 1    |
| • 最大工作结温和贮存温度增加至 $175^{\circ}\text{C}$ .....                                                       | 1    |
| • 更新了脉冲电流条件.....                                                                                   | 1    |
| • Updated <a href="#">图 4-1</a> from a normalized $R_{\theta JA}$ to an $R_{\theta JC}$ curve..... | 4    |
| • Updated <a href="#">图 4-6</a> to extend to $175^{\circ}\text{C}$ .....                           | 4    |
| • Updated <a href="#">图 4-8</a> to extend to $175^{\circ}\text{C}$ .....                           | 4    |
| • Updated the SOA in <a href="#">图 4-10</a> .....                                                  | 4    |
| • Updated <a href="#">图 4-12</a> to extend to $175^{\circ}\text{C}$ .....                          | 4    |

## 7 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number       | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-----------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">CSD18503KCS</a> | Active        | Production           | TO-220 (KCS)   3 | 50   TUBE             | ROHS Exempt | SN                                   | N/A for Pkg Type                  | -55 to 175   | CSD18503KCS         |
| CSD18503KCS.B               | Active        | Production           | TO-220 (KCS)   3 | 50   TUBE             | ROHS Exempt | SN                                   | N/A for Pkg Type                  | -55 to 175   | CSD18503KCS         |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TUBE



\*All dimensions are nominal

| Device        | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|---------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CSD18503KCS   | KCS          | TO-220       | 3    | 50  | 532    | 34.1   | 700    | 9.6    |
| CSD18503KCS   | KCS          | TO-220       | 3    | 50  | 532    | 34.1   | 700    | 9.6    |
| CSD18503KCS.B | KCS          | TO-220       | 3    | 50  | 532    | 34.1   | 700    | 9.6    |
| CSD18503KCS.B | KCS          | TO-220       | 3    | 50  | 532    | 34.1   | 700    | 9.6    |

## 重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 [TI 的销售条款](#) 或 [ti.com](#) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
版权所有 © 2025，德州仪器 (TI) 公司