

Sample &

Buy





ZHCSES6A - FEBRUARY 2016 - REVISED MARCH 2016

DRV10970 三相无刷直流电机驱动器

Technical

Documents

特性 1

- 宽电源电压范围: 5V 至 18V
- 集成场效应晶体管 (FET): 1A 均方根 (RMS)、 1.5A 峰值输出相位/绕组电流
- 总驱动器 H + L R_{DSON}: 400mΩ
- 内置 180° 正弦波形和梯形换向 .
- 休眠模式下的功耗超低 (35µA)
- 自适应驱动角度调整
- 三霍尔传感器或单霍尔传感器两个选项,最大程度 • 地降低系统成本
- 电机旋转方向控制
- 可配置为以 30° 或 0° 放置霍尔传感器 ٠
- 可调节的重试时间(电机锁定后)
- 可通过编程设定的电流限制功能
- 转速计 在开漏 FG 引脚上提供电机转速信息
- 在开漏 RD 引脚上提供电机锁定报告
- 保护 特性
 - 电源 (VM) 欠压锁定
 - 逐周期电流限制
 - 过流保护 (OCP)
 - 热关断
 - 电机锁定检测和报告

2 应用

- 冷却风扇
- 小型家用电器
- 通用无刷直流 (BLDC) 电机驱动器

3 说明

Tools &

Software

DRV10970 是一款集成式三相 BLDC 电机驱动器,适 用于家用电器、冷却风扇以及其他通用电机控制 应 用。该器件内置智能特性,并且拥有小巧外形和简单的 引脚分布结构,不仅降低了设计复杂度、节省了电路板 空间,而且还降低了系统成本。集成的保护功能提高了 系统的稳健性和可靠性。

Support &

Community

20

DRV10970 的输出级包含三个 R_{DSON} 为 400 mΩ (H+ L) 的半桥。每个半桥都能够驱动高达 1A RMS 和 1.5A 峰值的输出电流。当器件进入休眠模式时,电流消耗典 型值为 35µA。

该器件内置有高级的 180° 正弦波形换向算法,可实现 高效率、低转矩纹波和出色的声学性能。自适应驱动角 度调整功能可确保器件在任何电机参数和负载条件下获 得最优效率。

DRV10970 针对基于差分或单端霍尔传感器的应用而 设计。差分霍尔信号输入由集成的比较器检测。该器件 支持基于三个霍尔传感器和单个霍尔传感器的 应用; 单霍尔传感器模式通过减少两个霍尔传感器来降低系统 成本。

器件信息(1)

器件型号	封装	封装尺寸(标称值)
DRV10970	TSSOP (24)	7.80mm × 6.40mm

(1) 要了解所有可用封装,请见数据表末尾的可订购产品附录。

应用电路





版权 © 2016, Texas Instruments Incorporated

目录

1	特性	
2	应用	l1
3	说明	1
4	修订	历史记录
5	说明	(续)3
6	Pin	Configuration and Functions 3
7	Spe	cifications5
	7.1	Absolute Maximum Ratings 5
	7.2	ESD Ratings5
	7.3	Recommended Operating Conditions 5
	7.4	Thermal Information 6
	7.5	Electrical Characteristics 6
	7.6	Typical Characteristics 9
8	Deta	ailed Description 11
	8.1	Overview 11
	8.2	Functional Block Diagram 12

4 修订历史记录

注: 之前版本的页码可能与当前版本有所不同。

Changes from Original (February 2016) to Revision A

• i	已更改 器件状态至"量产数据	"且已发布完整数据表			
-----	----------------	------------	--	--	--

	8.3	Feature Description	13
	8.4	Device Functional Modes	16
9	App	lication and Implementation	21
	9.1	Application Information	21
	9.2	Typical Application	<mark>28</mark>
10	Pow	ver Supply Recommendations	30
11	Laye	out	30
	11.1	Layout Guidelines	30
	11.2	Layout Example	30
12	器件	和文档支持	31
	12.1	社区资源	31
	12.2	商标	31
	12.3	静电放电警告	31
	12.4	Glossary	31
13	机械	、封装和可订购信息	32

INSTRUMENTS

FEXAS

www.ti.com.cn

Page

1



5 说明 (续)

该器件实现了一个标准控制接口,其中包含脉宽调制 (PWM) 输入(速度命令)、FG 输出(速度反馈)、FR 输入 (正向和反向控制)以及 RD 输出(电机锁定指示)。

DRV10970 器件支持以 30° 和 0° 放置霍尔传感器(相对于对应相的 BEMF)。该器件实现了梯形驱动模式来满足 更高的功率需求。

DRV10970 器件根据霍尔传感器输入是否切换开关状态来确定转子锁定情况。该器件会在经过一段可调节的自动重 试时间(可通过连接至 RETRY 引脚的电容来配置)后重试旋转电机。

该器件包含多种保护 功能来提高系统稳健性: 过流保护、欠压保护、过热保护以及转子锁定检测与报告。

DRV10970 采用耐热增强型 24 引脚薄型小外形尺寸 (TSSOP) 封装(环境友好型:符合 RoHS 标准并且无 Sb/Br)。

6 Pin Configuration and Functions



Pin Functions

PIN		TYDE	DESCRIPTION			
NAME	NO.	ITPE		DESCRIPTION		
POWER AND	GROUND					
CPN	10	—	Charge nump quitching pade	Connect a 0.1-µF X7R capacitor rated for VM between CPN		
CPP	9	_	Charge pump switching hode	and CPP		
GND	12	PWR	Device ground Must be connected to board ground			
VCP	8	_	Charge pump output	Connect a 16-V, 1-µF ceramic capacitor to VM		
VINT	16	PWR	Integrated regulator output	Integrated regulator (typical voltage 5 V) mainly for internal circuits; Provide external power for less than 20 mA. Bypass to GND with a 10-V, 2.2 -µF ceramic capacitor		
VM	15	PWR	Power supply	Connect to motor supply voltage; bypass to GND with a 10- μF ceramic capacitor rated for VM		

DRV10970 ZHCSES6A – FEBRUARY 2016 – REVISED MARCH 2016

www.ti.com.cn

Pin Functions (continued)

PIN	1	TYPE	DECODIDITION		
NAME	NO.	IYPE	DESCRIPTION		
CONTROL		-	1		
CS	17	_	Current limit setting pin	Connect a resistor to adjust the current limit.	
DAA	1	I	Drive angle adjustment configuration pin	Low: 10° drive angle adjustment High: 5° drive angle adjustment Floating: adaptive drive angle adjustment	
FG	24	0	Frequency indication pin	Open drain Electrical Frequency Output pin. One toggle per electrical cycle. Requires an external pull-up of 3.3 -k Ω .	
FR	23	I	Motor direction control	Direction Control Input. When low, phase driving sequence is $U \rightarrow V \rightarrow W$ (U phase is leading V phase by 120°). When high, the phase driving sequence is $U \rightarrow W \rightarrow V$.	
BRKMOD	21	I	Brake mode setting	Low: Coasting mode (phases are tri-stated) High: Brake mode (phases are driven low)	
PWM	19	I	Variable duty cycle PWM input for speed control	Connect to PWM signal.	
RD	18	0	Lock indication pin	Pulled logic low with lock condition; open-drain output requires an external pull-up of 3.3-k Ω	
RETRY	22	I	Auto retry timing configure	Timing adjustable by capacitor	
CMTMOD	20	I	Commutation mode setting	Low: Sinusoidal operation mode with 0° Hall placement High: Sinusoidal operation mode with 30° Hall placement Floating: Trapezoidal operation mode with 30° Hall placement	
U_HN	3	I	U-phase negative Hall input	Differential Hall Sensor negative input for U-phase. Connect to hall sensor negative output. When logic level hall IC is used, tie this pin to VINT/2 level. In single Hall mode, the device uses U-phase hall inputs to drive the motor.	
U_HP	2	I	U-phase positive Hall input	Differential Hall Sensor positive input for U-phase. Connect to hall sensor positive output. When logic level hall IC is used, connect this to hall IC output. In single Hall mode, the device uses U-phase hall inputs to drive the motor.	
V_HN	5	I	V-phase negative Hall input	Differential Hall Sensor negative input for V-phase. Connect to hall sensor negative output. When logic level hall sensor is used, tie this pin to VINT/2 level. In single hall mode, ground this pin.	
V_HP	4	I	V-phase positive Hall input	Differential Hall Sensor positive input for V-phase. Connect to hall sensor positive output. When logic level hall IC is used, connect this to hall IC output. Leave this pin floating to enable single Hall operation.	
W_HN	7	I	W-phase negative Hall input	Differential Hall Sensor negative input for W-phase. Connect to hall sensor negative output. When logic level hall sensor is used, tie this pin to VINT/2 level. In single hall mode, ground this pin.	
W_HP	6	I	W-phase positive Hall input	Differential Hall Sensor positive input for W-phase. Connect to hall sensor positive output. When logic level hall IC is used, connect this to hall IC output. In single hall mode, ground this pin.	
OUTPUT STA	GE				
U	14	0	U phase output	Connect to motor terminal U	
V	13	0	V phase output	Connect to motor terminal V	
W	11	0	W phase output	Connect to motor terminal W	

External Components

COMPONENT	PIN 1	PIN 2	RECOMMENDED
C _{VM}	VM	GND	10- μ F ceramic capacitor rated for VM (if VM = 12 V, 25-V capacitor is suggested, if VM = 18 V, 35-V capacitor is suggested)
C _{VCP}	VCP	VM	16-V, 1-µF ceramic capacitor
C _{SW}	CPP	CPN	0.1-µF X7R capacitor rated for VM



External Components (continued)

COMPONENT	PIN 1	PIN 2	RECOMMENDED
C _{VINT}	VINT	GND	10-V, 2.2-µF ceramic capacitor Rotor Lock Detection and Retry
C _{RETRY}	RETRY	GND	See 公式 2 for capacitor value
R _{CS}	CS	GND	See Current Limit and OCP for resistor value
R _{RD}	VCC ⁽¹⁾	RD	>1 k Ω , RD is open-drain output. This component must be pulled up externally.
R _{FG}	VCC ⁽¹⁾	FG	>1 k Ω , FG is open-drain output. This component must be pulled up externally.

(1) VCC is not a pin on the DRV10970. It can be VINT or any other system voltage (for example the 3.3-V or 5-V supply voltage powering the microcontroller). A VCC supply voltage pull-up is required for open-drain outputs RD and FG

7 Specifications

7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) (1) (2)

	MIN	MAX	UNIT
Power supply voltage (VM)	-0.3	20	V
Power supply voltage ramp rate (VM)		2	V/µs
Charge pump voltage (VCP, CPP)	-0.3	25	V
Charge pump negative switching pin (CPN)	-0.3	20	V
Internal logic regulator voltage (VINT)	-0.3	5.5	V
Control pin voltage (PWM, FR, RETRY, CMTMOD, BRKMOD, DAA)	-0.3	VINT + 0.3	V
Open drain output current (RD, FG)	0	10	mA
Open drain output voltage (RD, FG)	-0.3	20	V
Output voltage (U,V,W)	-1	20	V
Output current (U,V,W)	0	2	А
Hall input voltage (U_HP, U_HN, V_HP, V_HN, W_HP, W_HN)	0	6	V
Current limit adjust pin voltage (CS)	-0.3	3.6	V
Operating junction temperature, T _{JMAX}	-40	150	°C
Storage temperature, T _{stg}	-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) Referenced with respect to GND.

7.2 ESD Ratings

			VALUE	UNIT
V	Electrostatio discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±2000	V
V _(ESD) Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±500	v	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
Power supply voltage VI	Μ	5	18	V
Logic level input voltage	WM, FR, CMTMOD, BRKMOD, DAA, RETRY	0	VINT	V
Open drain output pullup voltage F0	G, RD	0	18	V
Hall input	J_HP, U_HN, V_HP, V_HN, W_HP, V_HN	0	5	V
I _{OUT} Output current		0	1.5	А

Recommended Operating Conditions (continued)

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
f _{PWM}	Applied PWM signal	15	100	kHz
I _{VINT}	VINT external load current		20 ⁽¹⁾	mA
T _{JOPR}	Operating junction temperature	-40	125	°C

(1) VINT is mainly for internal use. For external, it is only suggested to provide bias current for hall circuit.

7.4 Thermal Information

		DRV10970	
	THERMAL METRIC ⁽¹⁾	PWP (TSSOP)	UNIT
		24 PINS	
R _{θJA}	Junction-to-ambient thermal resistance	36.1	°C/W
R _{0JC(top)}	Junction-to-case (top) thermal resistance	17.4	°C/W
$R_{ extsf{ heta}JB}$	Junction-to-board thermal resistance	14.8	°C/W
ΤιΨ	Junction-to-top characterization parameter	0.4	°C/W
Ψ _{JB}	Junction-to-board characterization parameter	14.5	°C/W
R _{0JC(bot)}	Junction-to-case (bottom) thermal resistance	1.1	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

7.5 Electrical Characteristics

 $T_A = 25^{\circ}C$, over recommended operating conditions unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
POWER SUP	PLIES (VM, VINT)					
VM	VM operating voltage		5		18	V
I _{VM}	VM operating supply current	VM = 12 V, no external load on VINT		3	5	mA
I _{VM_SLEEP}	VM supply current during sleep mode	VM = 5 and 12 V		35	50	μΑ
		VM = 12 V, 0-mA external load	4.5	5	5.5	V
VINT	Integrated regulator valtage	VM = 12 V, 20-mA external load	4.5	5	5.5	V
VIINT	integrated regulator voltage	VM = 5 V, 0-mA external load	4.5	4.8	5	V
		VM = 5 V, 20-mA external load	4.5	4.8	5	V
V _{GND-BGND}	Ground potential difference between GND pin to PCB ground			300	mV	
CHARGE PUI	MP (VCP, CPP, CPN)					
		VM = 5 V, less than 1-mA load	9	10	11	V
VCP	VCP operating voltage	VM = 12 V, less than 1-mA load	16	18	19.5	V
		VM = 18 V, less than 1-mA load	22	24	25.5	V
CONTROL IN	PUTS (PWM)					
V _{IL-PWM}	PWM Input logic low voltage	VM = 5 V and $VM = 12 V$	0		0.8	V
V _{IH-PWM}	PWM Input logic high voltage	VM = 5 V and $VM = 12 V$	2.4		5.3	V
V _{HYS-PWM}	PWM Input logic hysteresis	VM = 5 V and $VM = 12 V$	400			mV
R _{PU-PWM}	Internal pullup resistance	VM = 5 V and $VM = 12 V$	70	100	120	kΩ
R _{PU-PWM-SL}	Internal pullup resistance in sleep mode	VM = 5 V and $VM = 12 V$, sleep mode	1	2	2.5	MΩ
CONTROL IN	PUTS (RETRY)	-				
I _{RETRY-SINK}	Retry timing set sinking current	VM = 5 V and 12 V	9	10	11	μA



Electrical Characteristics (continued)

 $T_A = 25^{\circ}C$, over recommended operating conditions unless otherwise noted.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
I _{RETRY-} SOURCE	Retry timing set sourcing current	VM = 5 V and 12 V	9	10	11	μA
V _{RETRY_H}	Retry comparator high threshold	VM = 5 V and 12 V	1.1	1.2	1.3	V
V _{RETRY_L}	Retry comparator low threshold	VM = 5 V and 12 V	0.55	0.6	0.65	V
CONTROL IN	PUTS (FR, DAA, CMTMOD, BR	KMOD)				
VIL	Digital input logic low voltage	VM = 5 V and 12 V	0		0.8	V
V _{IH}	Digital input logic high voltage	VM = 5 V and 12 V	2.2		5.3	V
VIFLOATING	Digital input floating voltage	VM = 5 V and 12 V	24% × VINT		36% × VINT	V
R _{PD-FR}	FR pin Internal pulldown resistance	VM = 5 V and 12 V	160	200	240	kΩ
R _{PD-BRKMOD}	BRKMOD pin Internal pulldown resistance	VM = 5 V and 12 V	160	200	240	kΩ
CONTROL O	JTPUTS (RD, FG)					
I _{OSINK}	OD output pin sink current	VO = 0.3 V	3.5			mA
IOSHORT	OD output pin short current limit	VO = 12 V		10	25	mA
HALL INPUT	COMPARATOR	•	•			
V _{HR}	Hall input rising	Zero to positive peak including offset. $T_A = -40^{\circ}C$, 25°C, 125°C	0	5	10	mV
V _{HF}	Hall input falling	Zero to negative peak including offset $T_A = -40^{\circ}C$, 25°C, 125°C	-10	-5	0	mV
V _{HALL_HYS}	Hall input hysteresis	VHP-VHN T _A = –40°C, 25°C, 125°C	5		12	mV
Magaz	Common mode veltere	VM = 5.5 V - 18 V	0.3		4.3	V
vcom	Common mode voltage	VM = 5 V - 5.5 V	0.3		3.8	V
Finput	Input frequency range		0		1000	Hz
UVLO		-	-			
V _{UVLO-VM-THR}	UVLO threshold voltage on VM, rising		3.8	4	4.5	V
V _{UVLO-VM-THF}	UVLO threshold voltage on VM, falling		3.6	3.8	4.25	V
V _{UVLO-VM-HYS}	VM UVLO comparator hysteresis		40		200	mV
V _{UVLO-VINT-} THR	VINT UVLO rise threshold		4.1	4.2	4.5	V
V _{UVLO-VINT-} THF	VINT UVLO fall threshold		3.8	4	4.2	V
V _{UVLO-VINT-} HYS	VINT UVLO comparator hysteresis		100		300	mV
INTEGRATED	MOSFET					
R _{DSON}	Series resistance (H + L)	VM = 12 V, VCP = 19 V, I _{OUT} = 1.5 A		0.4	0.6	Ω
CURRENT LI	MIT AND OVER CURRENT PRO	DTECTION (OCP)				
I _{LIM}	Current limit threshold	VM = 12 V, Rcs = 20 kΩ	1.3	1.5	1.7	A
V _{ILIM_THR}	Current limit circuit comparator threshold	VM = 12 V	1.15	1.2	1.25	V
A _{CL}	Current limit attenuation factor	VM = 12 V	22000	25000	28000	A/A

Electrical Characteristics (continued)

 $T_A = 25^{\circ}C$, over recommended operating conditions unless otherwise noted.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
I _{OCP}	Over current protection threshold. Magnitude of phase current at which driver stage is disabled to protect the device.	VM = 5 V and 12 V	3		5	A
SLEEP MOD	E TIMING					
T _{SLEEP_EN}	Minimum PWM low time to recognize a sleep command.	VM = 12 V	1.2			ms
T _{SLEEP_EX}	Minimum PWM high to exit from sleep mode.	VM = 12 V	2			μs
THERMAL SI	HUTDOWN					
T _{SDN_TR}	Shut down temperature threshold	Shut down triggering temperature	150	160	170	°C
T _{SDN_RS}	Shut down resume temperature	Shut down resume temperature	140	150	160	°C
T _{SDN_HYS}	Shut down temperature hysteresis	Shut down temperature hysteresis	5	10	15	°C
LOCK DETEC	ст					
t _{LOCK_EN}	Lock detect time		0.6	0.7	0.8	S
t _{LOCK_EX}	Lock release time	Retry capacitor = 0.33 uF	4	5	6	S



7.6 Typical Characteristics



DRV10970

ZHCSES6A – FEBRUARY 2016 – REVISED MARCH 2016



www.ti.com.cn

Typical Characteristics (接下页)





8 Detailed Description

8.1 Overview

The DRV10970 device controls three-phase brushless DC motors using a speed command (PWM) and direction (FR) interface and Hall signals from the motor. The device is capable of driving up to 1-A RMS and 1.5-A peak current per phase.

When the DRV10970 powers up, it starts to drive the motor in trapezoidal communication mode based on the Hall sensor information. If all three Hall sensors are connected, commutation logic relies on all three Hall sensors. If only the U phase Hall sensor is connected (V_HP is floating), DRV10970 starts to drive the motor in single Hall sensor mode.

After 6 electrical cycles, the device switches to sinusoidal drive mode if the CMTMOD pin is not floating. If the motor has Hall sensor 0° placement (set on the CMTMOD pin accordingly), the DRV10970 device automatically adjusts the driving angle based on the feedback from the motor; it optimizes the efficiency regardless of the motor parameters and the load conditions.

The adaptive driving angle adjustment function can be disabled by the DAA pin, in which case, fixed driving angle is available for user to optimize the motor drive efficiency.

The steady-state motor speed is commanded by the PWM input duty cycle, which converts to an average output voltage of VM multiplied by the duty cycle. Floating PWM pin is considered as 100% speed command. Motor rotating direction can be controlled by FR input. Rotational direction can be changed while motor is spinning. The device takes $t_{LOCK EX}$ time before reversing the direction.

The FG output is aligned with U phase Hall sensor signal which indicates the motor speed. And if the motor is locked by external force for t_{LOCK_EN} , RD output will be asserted to indicate the rotor lock condition, and DRV10970 retries after t_{LOCK_EX} period which is determined by the capacitor on the RETRY pin.

When the motor is stopped, either in lock condition or PWM equals zero, the state of the phases is selected by BRKMOD pin; coasting (phases are floating) or braking (phases are pulled down to GND).

DRV10970 enters sleep mode when PWM is driven low for t_{SLEEP} time and motor comes to a standstill (no FG), internal circuits including regulators are turned off and the power consumption is less than $I_{VM SLEEP}$.

Overcurrent, current limit, thermal shutdown and undervoltage protection circuits prevent the system components from being damaged during extreme conditions.

DRV10970 ZHCSES6A – FEBRUARY 2016 – REVISED MARCH 2016 TEXAS INSTRUMENTS

www.ti.com.cn

8.2 Functional Block Diagram





8.3 Feature Description

8.3.1 Current Limit and OCP

DRV10970 provides two stages of current control, cycle-by-cycle current limit and OCP.

The current limit function limits the motor phase current during the motor operation: during startup, acceleration, sudden load change, and rotor lock condition while spinning. The application specific threshold is achieved by choosing the value of the external resistor connected to the CS pin. [8] 9 shows the simplified circuitry of the current limit circuit using the CS pin. The voltage generated on the CS pin is proportional to the value of the external resistor value is chosen based on the current limit to be achieved (see $\Delta \pm$ 1).



图 9. Current Limit Function Simplified Circuitry

Current limit threshold is set by 公式 1.

$$I_{\text{LIMIT}} = (V_{\text{ILIM}_{\text{THR}}} \times A_{\text{CL}}) / R_{\text{CS}}$$

(1)

In trapezoidal operation mode, motor phase current is restricted by means of cycle-by-cycle limit, as shown in 10. If the current limit is triggered, one of the conducting MOSFETs is disabled and the complementary side MOSFET is activated until the beginning of the next PWM cycle. In the example shown in 10, MOSFET 1 and MOSFET 5 are conducting MOSFETs, MOSFET 1 is disabled, and the complementary MOSFET 4 is activated when the current limit is triggered.

Feature Description (接下页)



图 10. Cycle-by-Cycle Current Limit in Trapezoidal Mode

If the current limit is triggered in sinusoidal operation mode, DRV10970 device switches to trapezoidal mode of operation to exercise cycle-by-cycle current limiting. If the current limit condition does not show up for 2 electrical cycles, the device will switch back to sinusoidal mode (shown in 🕅 11). The current limit threshold in sinusoidal mode is 1.5 times the current limit value in the trapezoidal mode. The current limit function can be disabled by connecting CS pin to GND.





OCP has a fixed threshold I_{OCP} , it can protect the device in catastrophic short-circuit conditions such as phase short to GND, phase short to VM and phase short to another phase. The I_{OCP} limit is similar to the current limit, except that when phase current crosses I_{OCP} threshold (positively or negatively), the device shuts down all the MOSFETs immediately. The device will wait for 2 ms before it starts driving the motor again. If the high current still exists, the device will shut down the MOSFETs and again wait for 2 ms. This process of checking overcurrent will continue until the OC event goes away. The device is capable of handling an OC event continuously for its lifetime. The OC protection feature cannot be disabled.



Feature Description (接下页)

8.3.2 Thermal Shutdown

If the junction temperature exceeds safe limits, the DRV10970 device places its outputs (U, V, W) in high-impedance mode. After the junction temperature has fallen to a safe level, operation automatically resumes.

8.3.3 Rotor Lock Detection and Retry

A locked rotor condition is detected if the Hall signal stops toggling for t_{LOCK_EN} . The device enters a motor parking state: coasting (if BRKMOD = 0) or braking state (if BRKMOD = 1). In the coasting state, the device places its outputs (U, V, W) in a high-impedance state. In the braking state, it keeps the low-side MOSFETs ON and high-side MOSFETs OFF. The RD pin is asserted to indicate the rotor lock condition. Operation resumes after t_{LOCK_EX} time at the same time RD is deasserted. This process repeats until the locked rotor condition is cleared. RD will be deasserted in sleep mode.

The t_{LOCK_EX} time is determined by the capacitor value connected to the RETRY pin. The accuracy of the capacitor and ground potential difference between the device ground and C_{RETRY} capacitor ground affects the accuracy of the time setting. After the DRV10970 device enters rotor locked state, I_{RETRY} , sourcing current starts to charge the capacitor, C_{RETRY} , until the voltage of the capacitor reaches V_{RETRY_H} , then I_{RETRY_H} sinking current starts to discharge the capacitor, C_{RETRY} , until the voltage of the capacitor falls below V_{RETRY_L} . This process repeats 128 times which determines the t_{LOCK_EX} , then DRV10970 retry starting the motor.

 $t_{LOCK_EX} = 15.36 \times 10^6 \times C_{RETRY}$ (in seconds)



图 13. Lock Release Timing Waveform

8.3.4 Supply Undervoltage Condition (UVLO)

When the supply voltage (VM) level falls below the undervoltage lockout threshold voltage ($V_{UVLO-Th-f}$), the DRV10970 will keep phases (U, V, W) in high-impedance mode. Operation resumes when VM rises above the $V_{UVLO-Th-r}$ threshold.

(2)



Feature Description (接下页)

8.3.5 Sleep Mode

The DRV10970 provides a sleep mode function to save power when the motor is not spinning. The device can be commanded to enter sleep mode by driving logic low on PWM pin for at least t_{SLEEP_EN} seconds. Before entering low-power state, the speed will be ramped down (by brake condition or by coasting) where rotor lock condition is detected. This sequence to bring the motor to a halt condition may take several seconds based on the motor. The device then enters sleep state where reset is asserted and supply is driven to low. Only a small portion of the logic is kept alive to detect the PWM pin high. The device will wake up after PWM goes high (PWM high signal needs to be longer than t_{SLEEP_EX}) and starts to drive the motor again.



图 14. Sleep Mode Sequence and Timing

The current consumption during sleep mode is less than I_{VM_SLEEP} .

In sleep mode, internal regulator VINT is shut down; if the Hall sensors are powered by VINT, the Hall sensors are also put into power off condition to further save power. The U, V, and W phase outputs are tri-stated, FG and RD pins are de-asserted while in the sleep mode. The device will not be able to perform OCP while in sleep mode.

8.4 Device Functional Modes

8.4.1 Operation in Trapezoidal Mode and Sinusoidal Mode

The DRV10970 device can operate in either trapezoidal mode or sinusoidal mode depending on the setting of CMTMOD pin. Sinusoidal operation mode provides better acoustic performance, which is more suitable for applications like refrigerator fans, HVAC fans, pumps, and other home appliances. Trapezoidal mode provides higher driving torque, which is more suitable for systems with heavy and unpredictable load conditions, such as power tools and actuators.



Device Functional Modes (接下页)

8.4.1.1 Trapezoidal Control Mode

Trapezoidal control is also called 120° control or 6-step control. In the trapezoidal control mode, the DRV10970 device drives standard six step commutation sequence based on the Hall input states and FR (direction) pin value. Trapezoidal (30° Hall placement) commutation is in accordance with 表 1. The startup scheme of sinusoidal control mode is also based on trapezoidal commutation. Trapezoidal mode does not support single Hall sensor operation; it may cause unpredictable motor operation.

OTATE	ЦА		ı (1)			PHASE C	UTPUT ⁽²⁾		
STATE	ПА	LL SIGNA	L.,		FR = 1		FR = 0		
	U	V	W	U	V	W	U	V	W
1	1	1	0	High	Hi-Z	Low	Low	Hi-Z	High
2	1	0	0	High	Low	Hi-Z	Low	High	Hi-Z
3	1	0	1	Hi-Z	Low	High	Hi-Z	High	Low
4	0	0	1	Low	Hi-Z	High	High	Hi-Z	Low
5	0	1	1	Low	High	Hi-Z	High	Low	Hi-Z
6	0	1	0	Hi-Z	High	Low	Hi-Z	Low	High
1x ⁽³⁾	0	0	0	Hi-Z	Hi-Z	Hi-Z	Hi-Z	Hi-Z	Hi-Z
2x ⁽³⁾	1	1	1	Hi-Z	Hi-Z	Hi-Z	Hi-Z	Hi-Z	Hi-Z

(1) Hall signal XHALL = 1 if the positive input terminal voltage (x_HP) is higher than the negative input terminal voltage (x_HN)

(2) Phase output = Hi-Z which means both the high-side and low-side MOSFETs are turned off.

(3) State 1x and 2x are invalid states, DRV10970 will output high impedance for all three phases in this condition. Hall sensor placement or connection needs to be changed.

表 2. Trapezoidal Commutation With 0° Hall Placement

8.4.1.2 Sinusoidal Pulse Wide Modulation (SPWM) Control Mode

If the sinusoidal operation mode is selected, the device will start the motor with trapezoidal operation (based on the commutation table shown in 表 1) and switch to sinusoidal after 6 electrical cycles. If current limit is triggered during trapezoidal startup, the transition will be delayed until current limit is cleared. If current limit is triggered in sinusoidal operation, the device will switch back to trapezoidal mode and will remain until the current limit event goes away (refer to *Current Limit and OCP*).

In sinusoidal control mode, the commutation will only rely on phase U Hall sensor input and ignore the phase V and W Hall sensor input.

The DRV10970 provides sinusoidal voltage shaping in the SPWM mode. The device generates 25-kHz PWM outputs on each phase, which have an average value of sinusoidal waveform on phase to phase. If the phase voltage is measured with respect to ground, the waveform is sinusoidal coupled with third-order harmonics. At any time among the three phases, one phase output equals to zero, as shown in 🛚 16.



图 15. PWM Output and the Average Value



LEFT: Sinusoidal voltage from phase to phase. RIGHT: Sinusoidal voltage with third-order harmonics from phase to GND

图 16. Sinusoidal Voltage With Third-Order Harmonics Output

The output amplitude is determined by the VM and the maximum PWM duty cycle among one electrical cycle. If VM is used to control the motor speed, the output maximum PWM duty cycle is 100%. The output amplitude is proportional to the VM amplitude.



图 17. Adjust VM to Control the Motor Speed

The PWM is used for controlling the motor speed. System calculates the duty cycle of the PWM input as DutyIN, which is converted into sinusoidal PWM output.

The maximum amplitude is when PWM input is 100% and maximum PWM output duty cycle is 100%, the output amplitude will be VM. A lower value such as VM / 2 could be achieved by driving the PWM duty to 50%. When the input duty cycle is less than 10% and greater than 0% DRV10970 keeps the input command at a 10% duty cycle (see 图 18).









图 19. Adjust PWM Input Duty Cycle to Control the Motor Speed

Note that the speed control PWM input frequency does not reflect to PWM output frequency on the phase outputs. The device supports input PWM frequency in the range of 15 to 100 kHz, the PWM output frequency on the phase is always 25 kHz.

8.4.2 Single Hall Sensor Operation

The DRV10970 device supports single Hall sensor operation to reduce system cost.

If only U phase Hall sensor is connected to the device and V and W phase Hall sensors are not installed in the system, the device automatically drives the motor in single Hall sensor mode. Single Hall sensor operation does not support trapezoidal operation, which may cause unpredictable motor behavior.

In single hall sensor mode, rotor is aligned to a known position for about 700 ms first and then motor is driven with 2-step DC current into the coil, which means instead of 6-step control, the device only outputs 2 steps based on the U phase Hall sensor signal. The direction of driving current is based on the FR input and the commutation mode setting. 表 3 shows the startup logic. For example, if 0° Hall placement is selected (CMTMOD pin equals to High), FR equals to high, and U phase Hall sensor signal is high, DRV10970 will drive U phase PWM and both V and W phase low.

		PHASE OUTPUT							
	HALL SIGNAL		FR = 1			FR = 0			
		U	v	w	U	V	w		
0°	1	PWM	LOW	LOW	LOW	PWM	PWM		
0°	0	LOW	PWM	PWM	PWM	LOW	LOW		
30°	1	PWM	LOW	Hi-Z	LOW	PWM	Hi-Z		
30°	0	LOW	PWM	Hi-Z	PWM	LOW	Hi-Z		
Single H	lall Align	Hi-Z	LOW	PWM	Hi-Z	LOW	PWM		

表 3. Single Hall Startup Commutation Table

Cycle-by-cycle current limit is effective during single Hall sensor startup. After 6 electrical cycles of startup, the device will switch to sinusoidal mode of operation. If current limit is triggered, sinusoidal control will transit back to 2-step drive mode, same as startup sequence. Refer to *Current Limit and OCP*.

Note that single Hall sensor operation mode may exhibit slight reverse spin of the rotor during startup. The reverse movement will be less than 180 electrical degrees.

The rotor locked condition is detected when no U-phase hall switching for about 700ms. For certain low inertia motors or no load condition, the rotor may continue to vibrate when the rotor is locked which may result in a hall signal switching. This condition is not detected by the device as the hall period may look like a normal motor spinning condition. In this scenario, the device may continue to drive the motor. Lowering the OC limit may help resolve this condition.

版权 © 2016, Texas Instruments Incorporated



8.4.3 Adaptive Drive Angle Adjustment (ADAA) Mode

In sinusoidal mode, the phase voltage vector is driven such that phase current and BEMF voltages are aligned (in-phase) in order to achieve the maximum motor efficiency possible. When Hall sensor is placed at 0°, the BEMF voltage will be in-phase with respective Hall signals. The ADAA logic takes advantage of this fact and aligns the U-phase current to the U-Hall sensor input.

If DAA pin is floating, the DRV10970 device will operate in the ADAA mode, in which case, the device continuously monitors the phase difference between the U-phase current and U-phase Hall signal while adjusting the phase voltage driving angle $\Delta\theta$ (with respect to the U-Hall sensor signal, same as U-BEMF zero crossing) to align the current and Hall signal (shown in \mathbb{Z} 20). ADAA mode is the recommended mode of operation where the motor efficiency is maximized irrespective of motor parameters, load conditions, and motor speeds. ADAA mode is only available in sinusoidal mode and 0° Hall sensor placement. The motors with 30° Hall placement may use the fixed drive angle feature to achieve maximum system efficiency for a given application.



图 20. Adaptive Drive Angle Adjustment

For sinusoidal mode and 0° Hall sensor placement, if DAA pin is connected to GND, voltage driving angle will be fixed at 10°. If DAA pin is connected to VINT, voltage driving angle will be fixed at 5°.

For sinusoidal mode and 30° Hall sensor placement, if DAA is floating, voltage drive angle will be fixed at 0°. DAA pin is connected to GND, voltage driving angle will be fixed at 10°. If the DAA pin is connected to VINT, voltage driving angle will be fixed at 5°.

In trapezoidal operation mode, DAA input is ignored and always control the output based on 表 2.

 $\frac{1}{8}$ 4 shows the DRV10970 operation modes with DAA and CMT_MOD configurations.

表	4.	DAA	and	CMT	MOD	Config	gurations
---	----	-----	-----	-----	-----	--------	-----------

MODE	MOTOR TYPE	HALL PLACEMENT	DAA = FLOATING	DAA = GND	DAA = VINT	COMMENTS
CMT_MOD = floating	Trapezoidal	30°	Trapezoidal mode, DAA signal is ignored.			The Trapezoidal motor with 0° Hall placement may use 30 degree Hall delay (OTP setting) to achieve optimum driving.
CMT_MOD = GND		0°	ADAA	10° drive angle	5° drive angle	BEMF zero crossing and Hall crossing will be in-sync.
CMT_MOD = VINT	Sinusoidal	30°	0° drive angle	10° drive angle	5° drive angle	The drive angle is specified with respect to BEMF zero crossing. When measured with respect to Hall-U signal, add 30°.



9 Application and Implementation

注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

9.1.1 Hall Sensor Configuration and Connections

Hall sensors must be connected to the DRV10970 to provide the feedback of the motor position. The DRV10970 Hall sensor input circuit is capable of interfacing with a variety of Hall sensors, and with two different ways of Hall sensor placement, which are 0° placement and 30° placement.

Typically, a Hall element is used, which outputs a differential signal on the order of 100 mV or higher. The VINT regulator can be used for powering the Hall sensors, which eliminates the need for an external regulator. The Hall elements can be connected in serial or parallel as shown in \mathbb{E} 21 and \mathbb{E} 22.



图 21. Serial Hall Element Connection



Application Information (接下页)



图 22. Parallel Hall Element Connection

Noise on the Hall signal degrades the commutation performance of the device. Therefore, take utmost care to minimize the noise while routing the Hall signals to the device inputs. The device internally has fixed time hall filtering of about 320 μ s. To further minimize the high-frequency noise, a noise filtering capacitor may be connected across x_HP and x_HN pins as shown in 21 and 22. The value of the capacitor can be selected such that the RC time constant is in the range of 0.1 to 2 μ s. For example, Hall sensor with internal impedance (between Hall output to ground) of 1 k Ω , C_H value is 1 μ F for 1- μ s time constant.

Some motors integrate Hall sensors that provide logic outputs with open-drain type. These sensors can also be used with the DRV10970, with circuits shown in \mathbb{R} 23. The negative (x_HN) inputs are biased to 2.5 V by a pair of resistors between VINT and ground. For open-drain type Hall sensors, an additional pullup resistor to supply is needed on the positive (x_HP) input, where VINT is used again. The VINT output may be used to supply power to the Hall sensors as well.



Application Information (接下页)



图 23. Hall IC Connection

The correspondence between the phase U, V, W and the Hall signal U, V, W needs to follow the DRV10970 definition, which is:

- 1. Phase U is leading phase W by 120°, phase W is leading phase V by 120°. The Hall signal positive output is aligned with respective phase BEMF. Choose FR = 1 and 0° placement option (see 图 24).
- 3. Phase U is leading phase W by 120°, phase W is leading phase V by 120°. The Hall signal positive output is 30° lagging of respective phase BEMF. Choose FR = 1 and 30° placement option (see 图 26).
- 4. Phase U is leading phase V by 120°, phase V is leading phase W by 120°. The Hall signal positive output is 30° leading of respective phase BEMF. Choose FR = 0 and 30° placement option (see 表 2 and 图 29).

The correspondence and sequency is also applied to applications using open-drain output Hall ICs. \boxtimes 28 is an example of FR = 0, and 30° placement condition.



Application Information (接下页)







FR = 0 Hall placement = 0 degree Differential output Hall element

图 25. Correspondence Between Motor BEMF and Hall Signal (FR = 0, 0° Placement)



Application Information (接下页)







图 27. Correspondence Between Motor BEMF and Hall Signal (FR = 0, 30° Placement)



Application Information (接下页)



图 28. Correspondence Between Motor BEMF and Hall Signal (FR = 1, 30° Placement, Hall IC)





If the motor terminal definition is different from the previous description, rename the motor phase U, V, W, or the Hall U, V, W, or swap the positive and negative of the Hall sensor output to make it match.

Use these tips to find the correct U, V, and W phases and the respective Hall sensors:

- 1. Assume motor phases and Hall outputs do not have labels. If named, remove them.
- 2. Label A, B, C to the motor terminals (phases). Label Da and Db, Ea and Eb, Fa and Fb to the Hall output pairs. If Hall ICs are used, just label the digital outputs as D, E, F.
- Use three 10-kΩ resistors, connect them to motor terminals A, B, C with star connection. The center is called COM.
- 4. Provide power to the Hall sensors.



Application Information (接下页)

- 5. Use 4 channel Scope to observe signals. Connect probe -1, 2, 3 to A, B, C terminals of the motor (phases), probe-4 connects to Hall Da (or D). Name the probe 1 (terminal-A) as U-phase. (see 🛚 30)
- 6. Turn the rotor manually in clock-wise direction. If the waveform on probe-1 (U-phase) is leading probe-2 (terminal-B) by 120°, name the terminal-B as phase W and terminal-C as phase V. Else if waveform on the probe-2 is leading probe 1 (U) by 120°, terminal-B as V, terminal-C as W. At this stage all three phases of the motor are identified.
- 7. Motor manufacturers have two popular Hall placement options. The first is 0° Hall placement (BEMF and Hall signals are in-phase) and the second is 30° Hall placement (BEMF leads Hall signal by 30°). If the probe-4 is in-phase (or lagging 30°) with phase-U, name Da as Hall U positive (U_HP), Db as Hall U negative (U_HN). If probe-4 is in-phase with phase U (or lagging 30°), but inverted polarity, name Da as U_HN, Db as U_HP. If the probe-4 is not in-phase (or lagging 30°) with respect to U but aligns with phase-V or W, name accordingly as V_HP/V_HN or W_HP/W_HN. Repeat this step to map Ea/Eb and Fa/Fb in the same way. By end of this step, all three sets of Hall signals are mapped to respective phase signals phase U & Hall U_HP/HN, phase V & Hall V_HP/V_HN and phase W and W_HP/W_HN. Care should be taken while judging 30° Hall placement, sometimes 30° and 60° look alike. If U phase is leading Hall Da by 60°, there will be another phase (V or W) with in-phase or lagging by 30° relationship. Hence it's important to check all three phases before concluding.
- 8. When Hall ICs are used, if the Hall D is in-phase or lagging 30° with respect to phase U but inverted polarity, name the Hall D output as U_HN, and 2.5-V reference voltage to U_HP. If Hall D is leading 30°, then turn the rotor in counter clock-wise direction and map remaining E & F Hall outputs.
- 9. After phase UVW and Hall UVW positive negative are identified, manually rotate the motor again, check if the result matches 🗟 24 and 🗟 25 (0° placement) or 🗟 26 and 🗟 25 (30° placement).
- 10. Connect U,V,W and Hall U,V,W to the DRV10970, with the FR = 1, it should rotate with direction you manually spun it. Connect FR = 0, the motor will spin in the other direction.



图 30. Motor Measurement

DRV10970 ZHCSES6A – FEBRUARY 2016 – REVISED MARCH 2016



www.ti.com.cn

9.2 Typical Application



图 31. Typical Application Schematic

9.2.1 Design Requirements

表 5 gives design input parameters for system design.

DESIGN PARAMETER	EXAMPLE VALUE
Supply voltage	5 to 18 V
Continuous operation current	0 to 1 A
Peak current	1.5 A
Hall sensor differential output peak	>40 mV
PWM input frequency	15 to 100 kHz
PWM duty cycle	0% to 100%

表 5. Design Parameters

9.2.2 Detailed Design Procedure

- Refer to *Design Requirements* and make sure the system meets the recommended application range.
- Refer to *Hall Sensor Configuration and Connections* and make sure correct phases and corresponding hall signals are identified.
- Refer to Hall Sensor Configuration and Connections and make sure hall signals are connected accurately.
- Build your hardware based on Layout Guidelines.
- Connect the device into system and validate your system.



9.2.3 Application Curves





10 Power Supply Recommendations

The DRV10970 is designed to operate from an input voltage supply (VM) range between 5 and 18 V. Place a 10- μ F ceramic capacitor rated for VM as close as possible to the DRV10970.

11 Layout

11.1 Layout Guidelines

The VM terminal should be bypassed to GND using a low-ESR ceramic bypass capacitor with a recommended value of $10-\mu$ F rated for VM. Place this capacitor as close as possible to the VM pin with a thick trace or ground plane connection to the device GND pin.

The C_{RETRY} capacitor should be placed as close to the RETRY pin as possible with a thick trace or ground plane connection to the device GND pin.

A low-ESR ceramic capacitor must be placed in between the CPN and CPP pins. TI recommends a value of 0.1- μ F rated for VM. Place this component as close as possible to the pins.

A low-ESR ceramic capacitor must be placed in between the VM and VCP pins. TI recommends a value of $1-\mu$ F rated for 16 V. Place this component as close as possible to the pins.

Bypass VINT to ground with 2.2-µF ceramic capacitors rated for 10 V. Place these bypassing capacitors as close to the pins as possible.

Because the GND pin carries motor current, take utmost care while planning grounding scheme, keep the ground potential difference between any two points less than 100 mV.

11.2 Layout Example



图 34. Layout Schematic



12 器件和文档支持

12.1 社区资源

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E[™] Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support TI's Design Support Quickly find helpful E2E forums along with design support tools and contact information for technical support.

12.2 商标

PowerPAD, E2E are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

12.3 静电放电警告



这些装置包含有限的内置 ESD 保护。存储或装卸时,应将导线一起截短或将装置放置于导电泡棉中,以防止 MOS 门极遭受静电损伤。

12.4 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

ZHCSES6A – FEBRUARY 2016 – REVISED MARCH 2016



www.ti.com.cn

13 机械、封装和可订购信息

以下页中包括机械、封装和可订购信息。这些信息是针对指定器件可提供的最新数据。这些数据会在无通知且不对 本文档进行修订的情况下发生改变。欲获得该数据表的浏览器版本,请查阅左侧的导航栏。



PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS	Lead finish/	MSL rating/	Op temp (°C)	Part marking
	(1)	(2)			(3)	Ball material	Peak reflow		(6)
						(4)	(5)		
DRV10970PWP	Active	Production	HTSSOP (PWP) 24	60 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV10970
DRV10970PWP.A	Active	Production	HTSSOP (PWP) 24	60 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV10970
DRV10970PWPR	Active	Production	HTSSOP (PWP) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV10970
DRV10970PWPR.A	Active	Production	HTSSOP (PWP) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	DRV10970

⁽¹⁾ **Status:** For more details on status, see our product life cycle.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions a	are nominal
-------------------	-------------

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DRV10970PWPR	HTSSOP	PWP	24	2000	330.0	16.4	6.95	8.3	1.6	8.0	16.0	Q1



www.ti.com

PACKAGE MATERIALS INFORMATION

23-May-2025



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
DRV10970PWPR	HTSSOP	PWP	24	2000	350.0	350.0	43.0

TEXAS INSTRUMENTS

www.ti.com

23-May-2025

TUBE



- B - Alignment groove width

*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
DRV10970PWP	PWP	HTSSOP	24	60	530	10.2	3600	3.5
DRV10970PWP.A	PWP	HTSSOP	24	60	530	10.2	3600	3.5

PWP 24

GENERIC PACKAGE VIEW

PowerPAD[™] TSSOP - 1.2 mm max height

PLASTIC SMALL OUTLINE

4.4 x 7.6, 0.65 mm pitch

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





PWP (R-PDSO-G24)

PowerPAD[™] PLASTIC SMALL OUTLINE



All linear dimensions are in millimeters. NOTES: Α.

- Β. This drawing is subject to change without notice.
- Body dimensions do not include mold flash or protrusions. Mold flash and protrusion shall not exceed 0.15 per side. C.
- This package is designed to be soldered to a thermal pad on the board. Refer to Technical Brief, PowerPad D. Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 for information regarding recommended board layout. This document is available at www.ti.com http://www.ti.com. E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.

E. Falls within JEDEC MO-153

PowerPAD is a trademark of Texas Instruments.

THERMAL INFORMATION

This PowerPAD[™] package incorporates an exposed thermal pad that is designed to be attached to a printed circuit board (PCB). The thermal pad must be soldered directly to the PCB. After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For additional information on the PowerPAD package and how to take advantage of its heat dissipating abilities, refer to Technical Brief, PowerPAD Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 and Application Brief, PowerPAD Made Easy, Texas Instruments Literature No. SLMA004. Both documents are available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.

B. Exposed tie strap features may not be present.

PowerPAD is a trademark of Texas Instruments

NOTES:

- This drawing is subject to change without notice. Β.
- Customers should place a note on the circuit board fabrication drawing not to alter the center solder mask defined pad. C.
- This package is designed to be soldered to a thermal pad on the board. Refer to Technical Brief, PowerPad D. Thermally Enhanced Package, Texas Instruments Literature No. SLMA002, SLMA004, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com <http://www.ti.com>. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.
- F. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.

重要通知和免责声明

TI"按原样"提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源, 不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担 保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验 证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。 严禁以其他方式对这些资源进行 复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索 赔、损害、成本、损失和债务,TI 对此概不负责。

TI 提供的产品受 TI 的销售条款或 ti.com 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址:Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 版权所有 © 2025,德州仪器 (TI) 公司