

# SN54BCT25244, SN74BCT25244 25-Ω OCTAL BUFFERS/DRIVERS WITH 3-STATE OUTPUTS

SCBS064A – JUNE 1990 – REVISED NOVEMBER 1993

- State-of-the-Art BiCMOS Design Significantly Reduces  $I_{CCZ}$
- ESD Protection Exceeds 2000 V Per MIL-STD-883C, Method 3015; Exceeds 200 V Using Machine Model ( $C = 200$  pF,  $R = 0$ )
- Designed to Facilitate Incident-Wave Switching for Line Impedances of 25 Ω or Greater
- Distributed  $V_{CC}$  and GND Pins Minimize Noise Generated by the Simultaneous Switching of Outputs
- Package Options Include Plastic Small-Outline (DW) Packages, Ceramic Chip Carriers (FK) and Flatpacs (W), and Standard Plastic and Ceramic 300-mil DIPs (JT, NT)

## description


These 25-Ω octal buffers and line drivers are designed specifically to improve both the performance and density of 3-state memory address drivers, clock drivers, and bus-oriented receivers and transmitters.

These buffers are capable of sinking 188-mA  $I_{OL}$ , which facilitates switching 25-Ω transmission lines on the incident wave. The distributed  $V_{CC}$  and GND pins minimize switching noise for more reliable system operation.


When the output-enable ( $1\overline{OE}$  and  $2\overline{OE}$ ) inputs are low, the device transmits data from the A inputs to the Y outputs. When  $1\overline{OE}$  and  $2\overline{OE}$  are high, the outputs are in the high-impedance state.

The SN54BCT25244 is characterized for operation over the full military temperature range of  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ . The SN74BCT25244 is characterized for operation from  $0^{\circ}\text{C}$  to  $70^{\circ}\text{C}$ .

SN54BCT25244 . . . JT OR W PACKAGE  
SN74BCT25244 . . . DW OR NT PACKAGE  
(TOP VIEW)



SN54BCT25244 . . . FK PACKAGE  
(TOP VIEW)



NC – No internal connection


FUNCTION TABLE  
(each buffer/driver)

| INPUTS          |   | OUTPUT |
|-----------------|---|--------|
| $\overline{OE}$ | A | Y      |
| L               | H | H      |
| L               | L | L      |
| H               | X | Z      |

# SN54BCT25244, SN74BCT25244 25-Ω OCTAL BUFFERS/DRIVERS WITH 3-STATE OUTPUTS


SCBS064A – JUNE 1990 – REVISED NOVEMBER 1993

## logic symbol†



† This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

## logic diagram (positive logic)



Pin numbers shown are for the DW, JT, NT, and W packages.

## absolute maximum ratings over operating free-air temperature range (unless otherwise noted)‡

|   |                    |
|---|--------------------|
| Supply voltage range, $V_{CC}$ .....  | -0.5 V to 7 V      |
| Input voltage range, $V_I$ (see Note 1) .....                                       | -0.5 V to 7 V      |
| Voltage range applied to any output in the disabled or power-off state, $V_O$ ..... | -0.5 V to 5.5 V    |
| Voltage range applied to any output in the high state, $V_O$ .....                  | -0.5 V to $V_{CC}$ |
| Input clamp current, $I_{IK}$ ( $V_I < 0$ ) .....                                   | -30 mA             |
| Current into any output in the low state, $I_O$ : SN54BCT25244 .....                | 250 mA             |
| SN74BCT25244 .....  | 376 mA             |
| Operating free-air temperature range: SN54BCT25244 .....                            | -55°C to 125°C     |
| SN74BCT25244 .....  | 0°C to 70°C        |
| Storage temperature range .....   | -65°C to 150°C     |

‡ Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

# SN54BCT25244, SN74BCT25244 25-Ω OCTAL BUFFERS/DRIVERS WITH 3-STATE OUTPUTS

SCBS064A – JUNE 1990 – REVISED NOVEMBER 1993

## recommended operating conditions (see Note 2)

|          |                                | SN54BCT25244 |     |     | SN74BCT25244 |     |     | UNIT |
|----------|--------------------------------|--------------|-----|-----|--------------|-----|-----|------|
|          |                                | MIN          | NOM | MAX | MIN          | NOM | MAX |      |
| $V_{CC}$ | Supply voltage                 | 4.5          | 5   | 5.5 | 4.5          | 5   | 5.5 | V    |
| $V_{IH}$ | High-level input voltage       | 2            |     |     | 2            |     |     | V    |
| $V_{IL}$ | Low-level input voltage        |              |     | 0.8 |              |     | 0.8 | V    |
| $I_{IK}$ | Input clamp current            |              |     | -18 |              |     | -18 | mA   |
| $I_{OH}$ | High-level output current      |              |     | -53 |              |     | -80 | mA   |
| $I_{OL}$ | Low-level output current       |              |     | 125 |              |     | 188 | mA   |
| $T_A$    | Operating free-air temperature | -55          |     | 125 | 0            |     | 70  | °C   |

NOTE 2: Unused or floating inputs must be held high or low.

## electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS            |  | SN54BCT25244 |      | SN74BCT25244 |     | UNIT |      |     |
|-----------|----------------------------|--|--------------|------|--------------|-----|------|------|-----|
|           |                            |  | MIN          | TYP† | MAX          | MIN |      | TYP† | MAX |
| $V_{IK}$  | $V_{CC} = 4.5\text{ V}$ ,  | $I_I = -18\text{ mA}$                  |              |      | -1.2         |     | -1.2 | V    |     |
| $V_{OH}$  | $V_{CC} = 4.75\text{ V}$ , | $I_{OH} = -3\text{ mA}$                |              |      |              | 2.7 |      | V    |     |
|           | $V_{CC} = 4.5\text{ V}$    | $I_{OH} = -53\text{ mA}$               | 2            |      |              |     |      |      |     |
|           |                            | $I_{OH} = -80\text{ mA}$               |              |      |              | 2   |      |      |     |
| $V_{OL}$  | $V_{CC} = 4.5\text{ V}$    | $I_{OL} = 94\text{ mA}$                |              | 0.38 | 0.55         |     | 0.42 | 0.55 | V   |
|           |                            | $I_{OL} = 125\text{ mA}$               |              |      | 0.8          |     |      |      |     |
|           |                            | $I_{OL} = 188\text{ mA}$               |              |      |              |     |      | 0.7  |     |
| $I_I$     | $V_{CC} = 5.5\text{ V}$ ,  | $V_I = 5.5\text{ V}$                   |              |      | 0.1          |     | 0.1  | mA   |     |
| $I_{IH}$  | $V_{CC} = 5.5\text{ V}$ ,  | $V_I = 2.7\text{ V}$                   |              |      | 20           |     | 20   | μA   |     |
| $I_{IL}$  | $V_{CC} = 5.5\text{ V}$ ,  | $V_I = 0.5\text{ V}$                   |              |      | -0.6         |     | -0.6 | mA   |     |
| $I_{OZH}$ | $V_{CC} = 5.5\text{ V}$ ,  | $V_O = 2.7\text{ V}$                   |              |      | 50           |     | 50   | μA   |     |
| $I_{OZL}$ | $V_{CC} = 5.5\text{ V}$ ,  | $V_O = 0.5\text{ V}$                   |              |      | -50          |     | -50  | μA   |     |
| $I_{CCL}$ | $V_{CC} = 5.5\text{ V}$ ,  | Outputs open                           |              |      | 90           | 119 | 90   | 119  | mA  |
| $I_{CCH}$ | $V_{CC} = 5.5\text{ V}$ ,  | Outputs open                           |              |      | 59           | 78  | 59   | 78   | mA  |
| $I_{CCZ}$ | $V_{CC} = 5.5\text{ V}$ ,  | Outputs open                           |              |      | 7            | 11  | 7    | 11   | mA  |
| $C_i$     | $V_{CC} = 5\text{ V}$ ,    | $V_I = 2.5\text{ V}$ or $0.5\text{ V}$ |              |      | 5.5          |     | 5.5  |      | pF  |
| $C_o$     | $V_{CC} = 5\text{ V}$ ,    | $V_O = 2.5\text{ V}$ or $0.5\text{ V}$ |              |      | 17           |     | 17   |      | pF  |

† All typical values are at  $V_{CC} = 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

## switching characteristics over recommended ranges of supply voltage and operating free-air temperature, $C_L = 50\text{ pF}$ (unless otherwise noted) (see Note 3)

| PARAMETER | FROM (INPUT)           | TO (OUTPUT) | $V_{CC} = 5\text{ V}$ ,<br>$T_A = 25^\circ\text{C}$ |     |     | SN54BCT25244 |      | SN74BCT25244 |      | UNIT |
|-----------|------------------------|-------------|---|-----|-----|--------------|------|--------------|------|------|
|           |                        |             | MIN   | TYP | MAX | MIN          | MAX  | MIN          | MAX  |      |
| $t_{PLH}$ | A                      | Y           | 1   | 3.2 | 4.9 | 1            | 5.6  | 1            | 5.5  | ns   |
| $t_{PHL}$ |                        |             | 2   | 4   | 5.6 | 2            | 6.3  | 2            | 6    |      |
| $t_{PZH}$ | OE                     | Y           | 3.2   | 5.6 | 8.5 | 3.2          | 9.7  | 3.2          | 9.3  | ns   |
| $t_{PZL}$ |                        |             | 3.7   | 6.3 | 9.2 | 3.7          | 10.4 | 3.7          | 10.2 |      |
| $t_{PHZ}$ | $\overline{\text{OE}}$ | Y           | 1.6   | 3.6 | 5.5 | 1.6          | 6.5  | 1.6          | 6.3  | ns   |
| $t_{PLZ}$ |                        |             | 3.1   | 5.3 | 7.8 | 3.1          | 9.5  | 3.1          | 8.4  |      |

NOTE 3: Load circuits and voltage waveforms are shown in Section 1.





## PACKAGING INFORMATION

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|---------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">SN74BCT25244DW</a>  | Obsolete      | Production           | SOIC (DW)   24 | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | BCT25244            |
| <a href="#">SN74BCT25244DWR</a> | Active        | Production           | SOIC (DW)   24 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | BCT25244            |
| SN74BCT25244DWR.A               | Active        | Production           | SOIC (DW)   24 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | BCT25244            |

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.


**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**TAPE AND REEL INFORMATION**

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74BCT25244DWR | SOIC         | DW              | 24   | 2000 | 330.0              | 24.4               | 10.75   | 15.7    | 2.7     | 12.0    | 24.0   | Q1            |


**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74BCT25244DWR | SOIC         | DW              | 24   | 2000 | 350.0       | 350.0      | 43.0        |

DW (R-PDSO-G24)

PLASTIC SMALL OUTLINE



- NOTES:
- All linear dimensions are in inches (millimeters). Dimensioning and tolerancing per ASME Y14.5M-1994.
  - This drawing is subject to change without notice.
  - Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
  - Falls within JEDEC MS-013 variation AD.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2025, Texas Instruments Incorporated