

TMUX9832 具有闩锁效应抑制的无高电压偏置、超出电源电压、220V 1:1、32 通道开关

1 特性

- 仅需要 +5V 辅助电源
 - 功耗极低：50kHz 时所有 32CH 开关的功耗为 9.5mW (典型值)
- 宽输入信号范围：
 - 高达 $\pm 110\text{V}$ 、 $220\text{V } V_{PP}$
 - 支持 $\pm 120\text{V}$ 、 $240\text{V } V_{PP}$ 电压过冲
- 低关断电容：10.6pF
- 低导通电阻
- 高达 100MHz 的数据移位时钟频率
- 逻辑电平：1.8V 至 5V
- 集成型 NDIN 可反转输入数据极性
- 快速导通时间：3 μs (最大值)
- 出色的 HD2PC 性能：在 5 MHz 时为 -65dB
- 具有优化引脚排列的小型 BGA 和 QFN 封装选项
- 集成热关断功能，可提高系统可靠性
- 输出端上集成泄漏电阻器
- 器件构造可实现闩锁效应抑制
- 工作温度范围：-40°C 至 125°C

2 应用

- 医疗超声成像
- 超声波智能探头
- 无损检验 (NDT) 金属探伤
- 压电式传感器驱动器
- 超声波流量变送器
- 打印机
- 光学 MEMS 模块

3 说明

TMUX9832 是一款具有闩锁效应抑制的 32 通道低谐波失真、低电阻、低电容、高电压模拟开关集成电路 (IC)。每个器件均具有 32 个独立可选的 1:1 单极单投 (SPST) 开关通道。该器件仅需要 +5V 电源，同时仍能支持 $\pm 110\text{V}$ 模拟信号。TMUX9832 还在漏极 (Dx) 引脚上集成了泄漏电阻器，以对容性负载进行放电，如压电式传感器。TMUX9832 专为医疗超声波成像和其他压电式传感器驱动器应用而设计。


TMUX9832 集成了可级联的 32 位移位寄存器和锁存器，用于控制 32 个开关中的每一个开关。菊花链功能允许控制许多 TMUX9832 器件，而无需为每个器件选择单独的芯片。为了减少信号路径中由潜在时钟馈通导致的噪声，低电平有效锁存使能可以在数据载入移位寄存器时保持高电平。32 位移位寄存器可在 1.8V 至 5V 电源下运行，并支持高达 100MHz 的时钟速度。

封装信息

器件型号	封装 ⁽¹⁾	封装尺寸 ⁽²⁾
TMUX9832	RWF (VQFN)	10mm × 10mm
	ZEH (NFBGA)	7.5 mm × 7.5 mm

(1) 如需了解所有可用封装，请参阅数据表末尾的可订购产品附录。

(2) 封装尺寸 (长 × 宽) 为标称值，并包括引脚 (如适用)。



简化原理图



Table of Contents

1 特性	1	5.3 Trademarks.....	3
2 应用	1	5.4 静电放电警告.....	3
3 说明	1	5.5 术语表.....	3
4 Revision History	2	6 Mechanical, Packaging, and Orderable Information	3
5 Device and Documentation Support	3	6.1 Mechanical Data.....	3
5.1 接收文档更新通知.....	3	6.2 Tape and Reel Information.....	4
5.2 支持资源.....	3		

4 Revision History

DATE	REVISION	NOTES
June 2023	*	Initial Release

5 Device and Documentation Support

5.1 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击 [订阅更新](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

5.2 支持资源

TI E2E™ 支持论坛 是工程师的重要参考资料，可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的《使用条款》。

5.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.
所有商标均为其各自所有者的财产。

5.4 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

5.5 术语表

TI 术语表 本术语表列出并解释了术语、首字母缩略词和定义。


6 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.


6.1 Mechanical Data

For package drawing information, request access to full data sheet at [myTI account](#).

6.2 Tape and Reel Information




QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TMUX9832ZEHR	NFBGA	ZEH	(1)	2000	330	16.4	7.85	7.85	2.25	12	16	Q3

(1) For pin count information, request access to full data sheet at [myTI account](#)

TAPE AND REEL BOX DIMENSIONS



Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TMUX9832ZEHR	NFBGA	ZEH	(1)	2000	336.6	336.6	31.8

(1) For pin count information, request access to full data sheet at [myTI account](#)

ADVANCE INFORMATION

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
PTMUX9832RWFR	Active	Preproduction	VQFN (RWF) 72	2500 LARGE T&R	-	Call TI	Call TI	-40 to 85	PTMUX9832
PTMUX9832RWFR.B	Active	Preproduction	VQFN (RWF) 72	2500 LARGE T&R	-	Call TI	Call TI	-40 to 85	PTMUX9832
PTMUX9832ZEHR	Active	Preproduction	NFBGA (ZEH) 83	2000 LARGE T&R	-	Call TI	Call TI	-40 to 85	
PTMUX9832ZEHR.B	Active	Preproduction	NFBGA (ZEH) 83	2000 LARGE T&R	-	Call TI	Call TI	-40 to 85	

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 [TI 的销售条款](#) 或 [ti.com](#) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
版权所有 © 2025，德州仪器 (TI) 公司