

Translate Voltages for a SIM Card



Subscriber Identity Modules, commonly called SIM cards, are used to store secure information in mobile devices for use in communications. This type of voltage translation applies to SIM, USIM, and UICC.




Figure 1. Example SIM Card Voltage Translation Block Diagram

Design Considerations

- Clock signals can be up to 5 MHz
- Translators enable communication when devices have mismatched logic voltage levels
- Prevent damage to devices that cannot support higher voltage inputs
- Improve data rates over discrete translation solutions
- Protect controller while peripheral is not connected
- [\[FAQ\] How does a slow or floating input affect a CMOS device?](#)
- Need additional assistance? Ask our engineers a question on the [TI E2E™ Logic Support Forum](#)

Table 1. Recommended Parts

Part Number	Automotive Qualified	Supported Card Types			Features
		Class A 5 V	Class B 3 V	Class C 1.8 V	
TXS0104E		✓	✓	✓	Auto-bidirectional voltage translation for all channels Supports all voltages and frequencies for SIM/UICC Increased ESD protection on B ports
TXS0104E-Q1	✓	✓	✓	✓	
TXS4555			✓	✓	Complete SIM/UICC translator solution Integrated LDO regulator Increased ESD protection on card-side
TXS02326A			✓	✓	Complete dual SIM/UICC translator and multiplexer solution Dual integrated LDO regulators I ² C communication with baseband processor Increased ESD protection on card-side

For more devices, browse through the [online parametric tool](#) where you can sort by desired voltage, channel numbers, and other features.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2022, Texas Instruments Incorporated