

Texas Instruments TUSB73x0 Configuration Options

Elias Villegas

Computer and Consumer Interface

ABSTRACT

This document outlines the options available to configure the Texas Instruments TUSB73x0 xHCI Host Controller.

Dynamic D3

This option is provided for customers to realize power savings by allowing the TUSB73x0 to dynamically transition between PCI D0 and PCI D3 depending on downstream port activity.

NOTE: Host platforms wishing to take advantage of DynamicD3 functionality must ensure that WAKE# events are properly supported by both the system BIOS and the system chipset.

XI_WAKE:

This option provides the ability for the TUSB73x0 controller to assert WAKE# in the absence of an external clock source by using the internal ring oscillator. When XI_WAKE functionality is enabled, the controller does not require a running USB clock to wake from device suspend states.

Without XI_WAKE functionality enabled, the TUSB73x0 requires a running USB clock at all times in order to assert WAKE#.

NOTE: Enabling XI_WAKE functionality (and as a result, the internal ring oscillator) increases device power consumption by 200 mW in devices suspend states. System designers should take this into consideration when deciding to implement this feature.

There are two methods to enable or disable the functionality described in [Table 1](#):

Table 1. Equalizer Control Register (PCI 0xE8 31:24)

Bit	Field Name	Description
31	DYNAMIC_D3_EN	Dynamic D3 Control -If this bit is set to '1', and PORT4_EQ_OV (PCI 0xEC, bit 26) is set to '0', the driver shall enable Dynamic D3 functionality.
30	XI_WAKE_EN	XI_WAKE Control -If this bit is set to '1', and PORT4_EQ_OV (PCI 0xEC, bit 26) is set to '0', the driver shall enable XI_WAKE functionality.
29	RFU	Reserved for future use. Must be '0'.
28	RFU	Reserved for future use. Must be '0'.
27	RFU	Reserved for future use. Must be '0'.
26	RFU	Reserved for future use. Must be '0'.
25	RFU	Reserved for future use. Must be '0'.
24	RFU	Reserved for future use. Must be '0'.

Method 1: BIOS

If the customer has control of the host BIOS, the relevant bits at PCI offset 0xE8 (see [Table 1](#)) can be set directly from the BIOS. No EEPROM or software modifications are required. This is the preferred method for most customers.

Method 2: EEPROM

For an add-in card, or in cases where the customer does not have control of the BIOS, the relevant bits can be programmed via an attached EEPROM (EEPROM Offset 0x15).

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2012, Texas Instruments Incorporated