

TPS63030EVM-658 User's Guide

This user's guide describes the characteristics, operation, and use of the TPS63030EVM-658 evaluation module (EVM). This EVM contains the Texas Instruments TPS63030 buck-boost converter, configured with external components to regulate current through a WLED. This user's guide includes EVM specifications, recommended test setup, test results, bill of materials, and a schematic diagram.

Contents

1	Introduction	2
	1.1 Performance Specification Summary	2
	1.2 Modifications.....	2
2	TPS63030EVM-658 Setup	2
	2.1 Input/Output Connections.....	2
3	Test Results	3
4	Design Procedure for Divider Network.....	3
5	Board Layout	4
6	Schematic and Bill of Materials	6
	6.1 TPS63030EVM-658 Schematic.....	6
	6.2 TPS63030EVM-658 Bill of Materials	7

List of Figures

1	Efficiency vs Input Voltage	3
2	Assembly Layer Including Silk Screen.....	4
3	Top Copper Layer	5
4	Bottom Copper Layer.....	5

List of Tables

1	Typical Performance Specification Summary	2
2	Bill of Materials.....	7

1 Introduction

The Texas Instruments TPS63030EVM-658 evaluation module contains a TPS63030 buck-boost converter integrated circuit (IC), supporting components, and one white light-emitting diode (WLED). The purpose of this EVM is to facilitate evaluation of the TPS63030 in a typical WLED application.

1.1 Performance Specification Summary

Table 1. Typical Performance Specification Summary

Parameter	Min	Typ	Max	Units
V_{IN}	1.8		5.5	V
V_{OUT}		3.2		V
I_{WLED}	325	350	375	mA
Overvoltage Protection Clamp Voltage		6		V

Table 1 provides a summary of the TPS63030EVM-658 performance specifications. All specifications are given for an ambient temperature of 25°C.

1.2 Modifications

To aid user customization of the EVM, the board was designed with devices having 0603 or larger footprints. Actual implementations may occupy less space. Resistor R6 may be removed to measure current through the LED.

2 TPS63030EVM-658 Setup

2.1 Input/Output Connections

The connection points and jumper positions are described in the following paragraphs.

2.1.1 J1 – V_{IN}

This header is the positive connection for the input power supply. Twist the leads to the input supply and keep them as short as possible. The input voltage must remain within the limits specified in [Table 1](#).

2.1.2 J2 – Sense + and -

This header is low current sense lines that monitor V_{in} at the input capacitor.

2.1.3 J3 – GND

This header is the return connection to the input power supply.

2.1.4 J4 – LED Out

This header is voltage out of the converter to the LED

2.1.5 JP1 – Enable

This jumper connects the enable pin of the TPS63030 to either ON (enabling the TPS63030) or OFF (disabling the TPS63030). The jumper must be installed in one position only. Do not leave JP1 open.

WARNING

This EVM WLED shines brightly. Protective eyewear and use of the diffuser cover is recommended.

3 Test Results




Figure 1. Efficiency vs Input Voltage

4 Design Procedure for Divider Network

The TPS63030 feedback voltage (FB) is set to 0.50 V. If this were used for current regulation, the power dissipation of the sense resistor will be high. To reduce power dissipation on the current sense resistor R3, a reference voltage of 2.5 V is summed with it, thereby reducing V_{sense} voltage and power dissipation in R3.

The first step is to choose the LED operating current and V_{sense} voltage, which determines the value for R3. There is a trade off between power dissipation on R3 and accuracy of regulation point. As V_{sense} is increased, the current regulation accuracy improves; the maximum voltage is 0.50 V. As V_{sense} is decreased, the power dissipation is reduced, but the error due to V_{ref} on resistors R1 and R2 increases.

The EVM I_{LED} is set to 350 mA with a V_{sense} voltage of 0.178 V.

$$V_{\text{sense}} = I_{\text{LED}} \times R3 = 350 \text{ mA} \times 510 \text{ m}\Omega = 0.178 \text{ V}$$

$$V_{\text{R1}} = V_{\text{FB}} - V_{\text{sense}} = 0.50 \text{ V} - 0.178 \text{ V} = 0.322 \text{ V}$$

$$V_{\text{R2}} = V_{\text{REF}} - V_{\text{FB}} = 2.5 \text{ V} - 0.50 \text{ V} = 2.00 \text{ V}$$

Choose divider current of 0.1 mA.

$$R1 = \frac{V_{\text{R1}}}{0.1 \text{ mA}} = \frac{0.322 \text{ V}}{0.1 \text{ mA}} = 3.22 \text{ k}\Omega$$

Standard value is 3.24 k Ω .

$$R2 = \frac{V_{\text{R2}}}{0.1 \text{ mA}} = \frac{2.00 \text{ V}}{0.1 \text{ mA}} = 20 \text{ k}\Omega$$

Standard value is 20 k Ω .

Output current can be increased or decreased by changing R3. For 700-mA output current, decrease R3 to 250 m Ω . Changes in the reference voltage, R1 or R2, also can be used to change the LED current.

5 Board Layout

This section provides the board layout of the TPS63030EVM-658. A 2-layer PCB with a number of vias near the LED was used to help with the thermal dissipation of the WLED. Users must carefully design their system to handle the thermal challenges raised by the WLEDs.

Board layout is critical for all switch-mode power supplies. See the data sheet ([SLVS893](#)) for specific layout and routing guidelines.




Figure 2. Assembly Layer Including Silk Screen




Figure 3. Top Copper Layer




Figure 4. Bottom Copper Layer

6.2 TPS63030EVM-658 Bill of Materials

Table 2. Bill of Materials

Count	RefDes	Value	Description	Size	Part Number	MFR
4	C1, C2, C3, C5	10uF	Capacitor, Ceramic, 6.3V, X5R, 20%	0603	GRM188R60J106ME47D	Murata
1	C4	1000pF	Capacitor, Ceramic, 50V, X7R, 10%	0603	Std	Std
1	D1	LUWCVBP	LED, 350mA	3.10 x 3.10 mm	LUW CVBP.CE-5L8L-GMKM-8E8G	Osram
1	L1	1.5 μ H	Inductor, Power, 3.1A, 22m Ω , \pm 20%	0.157 x 0.157 inch	XFL4020-152ME	Coilcraft
1	R1	3.24K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R2	20.0K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R3	0.51	Resistor, Chip, 1/10W, 1%	0805	Std	Std
2	R4, R7	1.00M	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R5	249	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R6	0	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	U1	TPS63030DSK	IC, DC-DC Converter	DSK	TPS63030DSK	TI
1	U2	TL431AIDBZ	IC, Precision Adjustable Shunt Regulator	SOT23-3	TL431AIDBZ	TI

Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Original (August 2010) to A Revision	Page
• Updated D1 in Section 6.1 from "D1 LUWCP7P" to "D1 LUWCVBP"	6
• Updated D1 line in Table 2	7

Evaluation Board/Kit Important Notice

Texas Instruments (TI) provides the enclosed product(s) under the following conditions:

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. Persons handling the product(s) must have electronics training and observe good engineering practice standards. As such, the goods being provided are not intended to be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including product safety and environmental measures typically found in end products that incorporate such semiconductor components or circuit boards. This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and therefore may not meet the technical requirements of these directives or other related directives.

Should this evaluation board/kit not meet the specifications indicated in the User's Guide, the board/kit may be returned within 30 days from the date of delivery for a full refund. **THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE.**

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge.

EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

TI currently deals with a variety of customers for products, and therefore our arrangement with the user **is not exclusive.**

TI assumes **no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein.**

Please read the User's Guide and, specifically, the Warnings and Restrictions notice in the User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For additional information on TI's environmental and/or safety programs, please contact the TI application engineer or visit www.ti.com/esh.

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used.

FCC Warning

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment in other environments may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

EVM Warnings and Restrictions

It is important to operate this EVM within the input voltage range of 1.8 V to 5.5 V and the output voltage range of 3 V to 5 V .

Exceeding the specified input range may cause unexpected operation and/or irreversible damage to the EVM. If there are questions concerning the input range, please contact a TI field representative prior to connecting the input power.

Applying loads outside of the specified output range may result in unintended operation and/or possible permanent damage to the EVM. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative.

During normal operation, some circuit components may have case temperatures greater than 80°C. The EVM is designed to operate properly with certain components above 80°C as long as the input and output ranges are maintained. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors. These types of devices can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during operation, please be aware that these devices may be very warm to the touch.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2019, Texas Instruments Incorporated

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2019, Texas Instruments Incorporated