Test Report: PMP41106

Universal Input, 500W Constant Current and Constant Voltage E-Bike Charger Reference Design



Description

This reference design is a universal input, 48V, 10.4A constant current (CC), constant voltage (CV) charger for e-bike applications. The reference design achieves 91.5% end-to-end peak efficiency with a 110Vac input, and 93.50% end-to-end peak efficiency with a 230Vac input. This design includes fan control and charging status indication based on output current. This reference design uses the UCC28180, UCC256603, UCC28910, and TL103W devices.

Features93.5% p

- 93.5% peak efficiency
- Power factor of greater than 0.9 for output power larger than 100W
- · Charging status indication
- · Automatic fan control
- 190mm × 100mm × 40mm

Applications


· Battery charger





Top

Bottom



Block Diagram

Test Prerequisites www.ti.com

1 Test Prerequisites

1.1 Voltage and Current Requirements

Table 1-1. Voltage and Current Requirements

| PARAMETER | SPECIFICATIONS |
|-----------------|-----------------|
| Input Voltage | 90Vac to 264Vac |
| Input Frequency | 50Hz to 60Hz |
| Output Voltage | 30Vdc to 48Vdc |
| Output Current | 10.4A |

1.2 Required Equipment

AC Source: Chroma 6590

E-Load: Chroma 63203A-600-210 Oscilloscope: Tektronix MDO3024 Mulitmeter: YOKOGAWA WT500

2 Testing and Results

2.1 Load Regulation

Load regulation is shown in Figure 2-1.




Figure 2-1. Load Regulation



2.2 Efficiency Graphs

Efficiency is shown in Figure 2-2 and Figure 2-3.




Figure 2-2. CV Mode Efficiency Graph




Figure 2-3. CC Mode Efficiency Graph



2.2.1 Power Factor (PF) and Input Current Total Harmonic Distortion (iTHD)

Graphs of PF and iTHD are shown in Figure 2-4 and Figure 2-5.




Figure 2-4. Graph of PF




Figure 2-5. Graph of iTHD

www.ti.com Testing and Results

2.3 Efficiency Data

Efficiency data, power factor and input current THD data is shown in Table 2-1.

Table 2-1. Efficiency, PF, and THD Data

| | Table 2-1. Efficiency, PF, and THD Data | | | | | | | |
|---------------------|---|--------|--------|----------------------|----------------------|---------------------|----------------------|----------------|
| V _{IN} (V) | I _{IN} (A) | PF | iTHD | V _{OUT} (V) | I _{OUT} (A) | P _{IN} (W) | P _{OUT} (W) | Efficiency (%) |
| 109.88 | 0.5708 | 0.9579 | 14.15% | 48.468 | 1 | 61.5 | 48.5 | 78.86% |
| 109.75 | 1.0391 | 0.997 | 4.32% | 48.466 | 1.998 | 113.4 | 96.85 | 85.41% |
| 109.62 | 1.5088 | 0.999 | 4.06% | 48.461 | 2.992 | 164.8 | 145 | 87.99% |
| 109.48 | 1.9884 | 0.999 | 3.75% | 48.456 | 4.013 | 216.9 | 194.45 | 89.65% |
| 109.34 | 2.4537 | 0.999 | 3.63% | 48.452 | 5.003 | 267.8 | 242.33 | 90.49% |
| 109.2 | 2.9311 | 0.999 | 3.63% | 48.446 | 6.01 | 320 | 291.16 | 90.99% |
| 109.02 | 3.4148 | 0.999 | 3.67% | 48.43 | 7.001 | 371.8 | 339.1 | 91.2% |
| 108.88 | 3.9 | 0.999 | 3.75% | 48.425 | 8 | 424.2 | 387.42 | 91.33% |
| 108.74 | 4.402 | 0.999 | 3.85% | 48.42 | 9.01 | 478 | 436.3 | 91.28% |
| 108.54 | 5.071 | 0.999 | 4% | 48.412 | 10.34 | 549.5 | 500.6 | 91.1% |
| 108.66 | 4.8166 | 0.999 | 3.975% | 46.06 | 10.347 | 522.7 | 476.57 | 91.17% |
| 108.77 | 4.383 | 0.999 | 3.885% | 42.018 | 10.347 | 476.1 | 434.8 | 91.33% |
| 108.92 | 3.9618 | 0.999 | 3.8% | 38.087 | 10.348 | 430.9 | 394.12 | 91.46% |
| 109.03 | 3.5496 | 0.999 | 3.72% | 34.052 | 10.348 | 386.5 | 352.4 | 91.18% |
| 109.14 | 3.1577 | 0.999 | 3.67% | 30.122 | 10.348 | 344 | 311.793 | 90.64% |
| 230.03 | 0.3117 | 0.8708 | 20.5% | 48.45 | 1.009 | 61.7 | 48.9 | 79.25% |
| 229.96 | 0.5192 | 0.9182 | 18.18% | 48.445 | 2.013 | 112.5 | 97.53 | 86.69% |
| 229.9 | 0.7312 | 0.935 | 15.92% | 48.441 | 3 | 162.4 | 145.3 | 89.47% |
| 229.83 | 0.9488 | 0.9511 | 11.5% | 48.436 | 4.02 | 213.6 | 194.7 | 91.15% |
| 229.77 | 1.167 | 0.96 | 9.43% | 48.431 | 5.02 | 264.2 | 243.1 | 92.01% |
| 229.71 | 1.3829 | 0.9725 | 7.15% | 48.426 | 6.016 | 314.4 | 291.33 | 92.66% |
| 229.64 | 1.5981 | 0.9882 | 4.33% | 48.422 | 7 | 364.4 | 338.86 | 92.99% |
| 229.54 | 1.8228 | 0.999 | 3.7% | 48.418 | 8.004 | 415.8 | 387.52 | 93.2% |
| 229.48 | 2.0476 | 0.999 | 4.16% | 48.414 | 9 | 467 | 435.72 | 93.3% |
| 229.4 | 2.3531 | 0.999 | 4.55% | 48.408 | 10.344 | 536.6 | 500.73 | 93.32% |
| 229.42 | 2.2397 | 0.99 | 4.5% | 46.055 | 10.35 | 510.8 | 476.7 | 93.32% |
| 229.48 | 2.0427 | 0.98 | 4.2% | 42.013 | 10.351 | 465.9 | 434.87 | 93.34% |
| 229.57 | 1.8504 | 0.98 | 3.8% | 38.082 | 10.351 | 422.2 | 394.18 | 93.36% |
| 229.63 | 1.6617 | 0.98 | 3.96% | 34.046 | 10.352 | 379 | 352.44 | 92.99% |
| 229.67 | 1.4822 | 0.98 | 5.73% | 30.117 | 10.353 | 337.6 | 311.78 | 92.35% |



2.4 Thermal Images

Thermal image is shown in Table 2-2.

Table 2-2. Component Temperature, 230V, 50Hz Input, Full Load

| LLC Inductor | 52°C | | | |
|----------------------|--------|--|--|--|
| LLC Transformer | 55°C | | | |
| LLC Rectifier Diodes | 51.3°C | | | |
| Rectifier Bridge | 50°C | | | |
| PFC Choke | 36°C | | | |




Figure 2-6. Thermal Image at 230Vac

Note
TA = 25.0°C, 230V, 50Hz Input, Full Load




Figure 2-7. Thermal Image at 230Vac




Figure 2-8. Thermal Image at 230Vac

Table 2-3. Component Temperature, 110V, 50Hz Input, Full Load

| LLC Inductor | 52.6°C |
|----------------------|--------|
| LLC Transformer | 55.4°C |
| LLC Rectifier Diodes | 51.3℃ |
| Rectifier Bridge | 67.9°C |
| PFC MOSFET | 45.9°C |




Figure 2-9. Thermal Image at 110Vac

Note

TA = 25.0°C, 110V, 50Hz Input, Full Load




Figure 2-10. Thermal Image at 110Vac

ww.ti.com Waveforms




Figure 2-11. Thermal Image at 110Vac

Note

Tested after 30 minutes operation, with 12V, 0.5A fan cooling

3 Waveforms

3.1 Switching

Switching behavior is shown in Figure 3-1 through Figure 3-10.




Figure 3-1. PFC, 90Vac Input, Full Load




Figure 3-2. PFC, 110Vac Input, Full Load

Waveforms INSTRUMENTS
www.ti.com




Figure 3-3. PFC, 230Vac Input, Full Load




Figure 3-4. PFC, 264Vac Input, Full Load




Figure 3-5. PFC, 90Vac Input, Full Load, Switch Node Waveform




Figure 3-6. PFC, 264Vac Input, Full Load, Switch Node Waveform




Figure 3-7. LLC, 48V, 10.4A Load





Figure 3-8. LLC, 48V, 0A Load

Note

CH1: Vgs CH2: Vds CH3: Resonant tank current

www.ti.com Waveforms






Figure 3-9. LLC, 40V, 10.4A Load

Figure 3-10. LLC, 30V, 10.4A Load

Note

CH2: Vds CH4: Resonant tank current

3.2 Output Voltage Ripple

Output voltage ripple is shown in Figure 3-11 and Figure 3-12.




Figure 3-11. 48V, No Load





Figure 3-12. 48V, 10.4A Load

Waveforms www.ti.com

3.3 Start-up Sequence

Start-up behavior is shown in Figure 3-13 and Figure 3-14.






Figure 3-13. 110Vac Input, No Load


Figure 3-14. 230Vac Input, No Load

Note

CH1: Output voltage, CH2: Input voltage

3.4 Dynamic Response

Dynamic response is shown in Figure 3-15 and Figure 3-16.






Figure 3-15. 110Vac Input, 48V, 5.2A to 10.4A

Figure 3-16. 230Vac Input, 48V, 5.2A to 10.4A

Note

The high-current level is full load for 20ms. The low-current level is ½ load for 20ms, with a slew rate of 2.5A/µs

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated