




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD085	REV: E1	SUN REV: Unknown revision
LAYER NAME = Top Overlay	TID #: N/A		
PLOT NAME = Top Overlay	GENERATED : 1/14/2025 1:38:05 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD085	REV: E1	SUN REV: Unknown revision
LAYER NAME = Top Solder	TID #: N/A		
PLOT NAME = Top Solder Mask	GENERATED : 1/14/2025 1:38:05 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD085	REV: E1	SUN REV: Unknown revision
LAYER NAME = Top Layer	TID #: N/A		
PLOT NAME = Top Layer	GENERATED : 1/14/2025 1:38:05 PM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD085	REV: E1	SUN REV: Unknown revision
LAYER NAME = Bottom Layer	TID #: N/A		
PLOT NAME = Bottom Layer	GENERATED : 1/14/2025 1:38:05 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD085	REV: E1	SUN REV: Unknown revision
LAYER NAME = Bottom Solder	TID #: N/A		
PLOT NAME = Bottom Solder Mask	GENERATED : 1/14/2025 1:38:05 PM	TEXAS INSTRUMENTS	



Symbol	Quantity	Finished Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
C	2	59.00mil (1.499mm)	NPTH	Round	Top Layer - Bottom Layer	
☆	1416	7.87mil (0.200mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	49	8.00mil (0.203mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	10	14.00mil (0.356mm)	PTH	Round	Top Layer - Bottom Layer	
◇	15	16.00mil (0.406mm)	PTH	Round	Top Layer - Bottom Layer	
B	1	17.72mil (0.450mm)	PTH	Round	Top Layer - Bottom Layer	
▼	2	35.43mil (0.900mm)	PTH	Round	Top Layer - Bottom Layer	
□	68	40.00mil (1.016mm)	PTH	Round	Top Layer - Bottom Layer	
○	6	51.18mil (1.300mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	16	59.06mil (1.500mm)	PTH	Round	Top Layer - Bottom Layer	
☆	4	62.99mil (1.600mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	28	63.00mil (1.600mm)	PTH	Round	Top Layer - Bottom Layer	
⌘	2	120.00mil (3.048mm)	PTH	Round	Top Layer - Bottom Layer	
○	3	169.29mil (4.300mm)	PTH	Round	Top Layer - Bottom Layer	
○	1	177.17mil (4.500mm)	PTH	Round	Top Layer - Bottom Layer	
▽	2	23.62mil (0.600mm)	PTH	Slot	Top Layer - Bottom Layer	
1625 Total						

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD085	REV: E1	SUN REV: Unknown revision
LAYER NAME = Drill Drawing	TID #: N/A		
PLOT NAME = Drill Drawing	GENERATED : 1/14/2025 1:38:05 PM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:	MD085	REV:	E1	SUN REV:	Unknown revision
LAYER NAME = M2 Board Dimensions	TID #:	N/A				
PLOT NAME = Board Dimensions	GENERATED	:	1/14/2025	1:38:07 PM	TEXAS INSTRUMENTS	