


Alternative:
Continuous mode
WURTH: 749196111
L=250uH
n1/n2 = 3/2
lin=0.15A
lin rms= 0.087A
lout max=0.238A
lout rms= 0.136A
l ripple= 0.065A



National Semiconductor and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. National and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. National and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.

Designed for: Public Release	Mod. Date: 5/27/2010
Project: NSCE0117	
Sheet Title: AC/DC Flyback	Sheet: 1 of 1
Size: A3	Schematic: 870 xxxxxx
Rev: X1	
Assembly Variant: -100A	
File: NSCE0117_SchDoc	
Contact: http://www.national.com/support	



<http://www.national.com>

© Copyright, National Semiconductor, 201