





Top Overlay










GND




Middle Signal









Bottom Signal








Symbol	Count	Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
✕	148	7.87mil (0.200mm)	PTH	Round	Top Signal - Bottom Signal	+/-1.97mil
⌒	916	8.00mil (0.203mm)	PTH	Round	Top Signal - Bottom Signal	
✕	8	25.00mil (0.635mm)	PTH	Round	Top Signal - Bottom Signal	
□	2	27.56mil (0.700mm)	PTH	Slot	Top Signal - Bottom Signal	
◎	2	35.43mil (0.900mm)	NPTH	Round	Top Signal - Bottom Signal	
◇	86	40.16mil (1.020mm)	PTH	Round	Top Signal - Bottom Signal	
⊕	10	43.31mil (1.100mm)	PTH	Round	Top Signal - Bottom Signal	
▽	10	43.31mil (1.100mm)	PTH	Round	Top Signal - Bottom Signal	
☆	32	45.28mil (1.150mm)	PTH	Round	Top Signal - Bottom Signal	
⬠	2	59.06mil (1.500mm)	PTH	Slot	Top Signal - Bottom Signal	
▽	2	74.80mil (1.900mm)	PTH	Slot	Top Signal - Bottom Signal	
✕	4	125.00mil (3.175mm)	NPTH	Round	Top Signal - Bottom Signal	
	1222 Total					

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout



M2 Board Dimensions