

# Bill of Materials

TI DESIGNS

TIDEP-0040 - SDR Industrial I/O Board

Quantity	Designator	Type	LibRef	Footprint	Comment	Value	Voltage	Description	Mfg	Mfg PN
3	C300, C400, C403	capacitor	B45196H2156K209	SMD TAN B	15uF	15uF	10V	CAP TANT 15UF 10V 10% 1411	Kemet	T491B156K010AT
4	R209, R210, R211, R212	resistor	RES 0603	R0603L	49.9	49.9		RES 49.9 OHM 1/10W 1% 0603 SMD	Vishay Dale	CRCW060349R9KFA
1	B100	general	BR1225-1VC	BR1225-1VC	BR1225-1VC			BATTERY LITH 12.5MM COIN PC PINS	Panasonic - BSG	BR-1225VCN
2	R804, R810	resistor	RES 1206	R1206N	270	270		RES 270 OHM 1/4W 1% 1206 SMD	Vishay Dale	CRCW1206270R9KFA
1	X100	general	CB3LV-3I-24M5760	CB3LV	CB3LV-3I-24M5760			OSC 24.5760 MHZ 3.3V SMD	CTS-Frequency Controls	CB3LV-3I-24M5760
1	C613	capacitor	CAP X7R 0603 16V	C0603N	0.22uF	0.22uF	16V	CAP CER 22UF 16V X7R 0603	Murata Electronics North America	GRM188R71C224KA01D
4	Q500, Q501, Q502, Q503	general	MMBT2222A	SOT-23-3	MMBT2222A			TRANSISTOR GP NPN AMP SOT-23	Fairchild Semiconductor	MMBT2222A
1	JP504	general	JUMPER HEADER	JUMPER	JUMPER			CONN HEADER 2POS 100 VERT GOLD	Molex Connector Corporation	22-28-4024
3	D600, D601, D602	general	B340A-13-F	SMA	B340A-13-F			DIODE SCHOTTKY 3A 40V SMA	Diodes Inc	B340A-13-F
3	U600, U601, U602	general	TP55430	S08(PWP)	TP55430			IC BUCK ADJ 3A 850	Texas Instruments	TP55430DDA
1	TP1	general	TP_BLK_5001	TP	5001			TEST POINT PC MINI .040"D BLACK	Keystone Electronics	5001
1	J104	general	87832-2420	87832-2420	87832-2420			CONN HEADER 24POS 2MM VERT SMD	Molex Connector Corporation	87832-2420
2	R222, R225, R305, R306, R310, R313	resistor	RES 0402	R0402L	130	130		RES 130 OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW0402130RFKED
4	R313, R302, R305, R309, R312	resistor	RES 0402	R0402L	680	680		RES 680 OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW0402680RFKED
5	R209, R210, R211, R212, R223, R224	resistor	RES 0402	R0402L	1.80k	1.80k		RES 1.80K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW04021K80FKED
1	R601	resistor	RES 0402	R0402L	3.24k	3.24k		RES 3.24K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW04023K24FKED
1	R301, R307, R308, R314	resistor	RES 0402	R0402L	3.30k	3.30k		RES 3.30K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW04023K30FKED
1	R214	resistor	RES 0402	R0402L	4.99K	4.99K		RES 4.99K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW04024K99FKED
1	R603	resistor	RES 0402	R0402L	5.90K	5.90K		RES 5.90K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW04025K90FKED
1	R606	resistor	RES 0402	R0402L	15.8K	15.8K		RES 15.8K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW040215K8FKED
1	R605	resistor	RES 0402	R0402L	20.0K	20.0K		RES 20.0K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW040220K0FKED
1	R607	resistor	RES 0402	R0402L	140k	140k		RES 140K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW0402140KFKED
1	R604	resistor	RES 0402	R0402L	348K	348K		RES 348K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW0402348KFKED
2	C907, C908	capacitor	CAP NPO 0402 50V	C0402L	12pF	12pF	50V	CAP CER 12PF 5% 50V NPO 0402	AVX Corporation	04025A12J0AT2A
1	Y200	general	ECS-250-18-5PX-F-TR	CSM-7	25.000 MHZ			CRYSTAL 25.000MHZ 18PF SMD	ECS Inc	ECS-250-18-5PX-F-TR
1	J103	general	67913-0002	67913-0002	1775059-1			CONN SD MEMORY SMD BOTTOM MNT	TE Connectivity	1775059-1
3	J700, J701, J702, C601, C602, C605, C606, C800, C805	capacitor	CAP X5R 1206X07 50V	CAPC3216X18N	4.7uF	4.7uF	50V	CAP CER 4.7UF 50V X5R 1206	Taiyo Yuden	UMK316H475KL-T
1	D603	general	MBRRA160T3G	403D-02-SMA	MBRRA160T3G			DIODE SCHOTTKY 60V 1A SMA	On Semiconductor	MBRRA160T3G
1	J300	general	SJ-3523-SMT	SJ-3523-SMT	SJ-3523-SMT			CONN AUDIO JACK 3.5MM STEREO SMD	CLUI Inc	SJ-3523-SMT-TR
2	S100, S101	general	KMR221GLF5	KMR221GLF5	KMR221GLF5			SWITCH TACTILE SPST-NO 0.05A 32V	C&K Components	KMR221GLF5
1	J503	general	67491-1032	67491-1032	67491-1032			CONN HEADER SATA 7POS PCB GOLD	Molex Connector Corporation	67491-1032
1	J400	general	74320-4004	74320-4004	74320-4004			CONN RECEPT RT ANG DIGITAL DVI	Molex Connector Corporation	74320-4004
2	C111, C112	capacitor	CAP X5R 1206X07 6.3V	CAPC3216X18N	100uF	100uF	6.3V	CAP CER 100UF 6.3V 20% X5R 1206	Murata Electronics North America	GRM31CR60J107ME39L
1	U300	general	DSDA1791D8	D828	DSDA1791D8			IC 34BIT STEREO A/D DAC 28-SSOP	Texas Instruments	DSDA1791D8
1	C600	general	F2S6681Z	SO-8	F2S6681Z			MOSFET P-CH 30V 20A SO-8	Fairchild Semiconductor	F2S6681Z
1	U900	general	MC92315JST	TSSOP20	MC92315JST			IC CAN CONTROLLER W/SR 20TSSOP	Microchip Technology	MC92315JST
3	L300, L400, L401, L301, L401, L401	general	MMZ1608R301A	L0603	MMZ1608R301A			FERRITE CHIP 300 OHM 500MA 0603	TDK Corporation	MMZ1608R301A
1	U301	general	OPA2134UA	SO-8	OPA2134UA			IC OPAMP ULTIDR STER AB 8SOIC	Texas Instruments	OPA2134UA
1	U400	general	TFPA10PAP	PAP64 N	TFPA10PAP			IC TRANSMITTER DIGITAL 64-HTQFP	Texas Instruments	TFPA10PAP
1	U200	general	TLK100PH	PHF48 N	TLK100PH			IC TXRX IND ETHERNET 48HTQFP	Texas Instruments	TLK100PH
2	U100, U101	general	TPS2041BDBVR	SOT-23-5	TPS2041BDBVR			IC PWR DIST SWITCH SNGL SOT23-5	Texas Instruments	TPS2041BDBVR
1	U502	general	TRS232ECPWR	TSSOP16	TRS232ECPWR			IC RS232 LINE DVR/RCVR 16-TSSOP	Texas Instruments	TRS232ECPWR
1	C307	capacitor	TCPCA105M8R	CAPC2012X12N	1.0uF	1.0uF	10V	CAP TANT 1.0UF 10V 20% SMD	Rohm Semiconductor	TCPCA105M8R
1	Y900	general	ABLS-20.000MHZ-L4Q-T	CSM-7	20.000MHz			CRYSTAL 20MHZ 18PF SMD	Abracon Corporation	ABLS-20.000MHZ-L4Q-T
1	U501	general	ISO1050DUBR	DUB08	ISO1050DUBR			IC TXRX CAN 5V 8SOP	Texas Instruments	ISO1050DUBR
3	C611, C612, C615	capacitor	CAP X5R 1210X11 25V	CAPC3225X27N	22uF	22uF	25V	CAP CER 22UF 25V X5R 1210	Taiyo Yuden	TMM325B226MM-T
2	C603, C607	capacitor	593D107X0010D2TE3	SMD TAN D	100uF	100uF	10V	CAP TANT 100UF 10V 20% 2917	Vishay Sprague	593D107X0010D2TE3
35	C105, C106, C107, C108, C109, C110, C113, C117, C119, C120, C200, C203, C204, C205, C206, C207, C208, C209, C210, C211, C212, C213, C214, C215, C216, C217, C301, C304, C305, C306, C301, J502, J504	capacitor	CAP X7R 0402 16V	C0402L	0.1uF	0.1uF	16V	CAP CER 0.1UF 16V 10% X7R 0402	TDK Corporation	C105X7R1C104K050BC
1	J100	general	5103308-1	IDC_D09	5103308-1			CONN HEADER LOPRO STR 10POS GOLD	TE Connectivity	5103308-1
1	J100	general	UX60-MB-558	UX60-MB-558	UX60-MB-558			CONN RECEPT MINI USB2.0 5POS	Hirsch Electric Co Ltd	UX60-MB-558
1	J200	general	JX0011D21BNL	JX0011	JX0011D21BNL			RJ-45 Jack with internal transformer and LED	Pulse	JX0011D21BNL
1	C610	capacitor	CAP X7R 0805X05 50V	CAPC2012X14N	1.0uF	1.0uF	50V	CAP CER 1UF 50V X7R 0805	Murata Electronics North America	GRM21BR71H105KA12L
1	J600	general	1711026	1711026	1711026			CONN TERM BLOCK 2POS SMM PCB	Phoenix Contact	1711026
4	F601, F602, F603, R604	general	MF-MSMF110-24	F1812N	MF-MSMF110/24X-2	1.1A	24V	FUSE PTC RESET 1.10A 5MD 1812	Bourns Inc	MF-MSMF110/24X-2
2	U102, U103	general	USBLC6-2P6	SOT-666	USBLC6-2P6			IC ESD PROTECTION FOR SMD SOT-666	STMicroelectronics	USBLC6-2P6
1	RV600	general	VC15MA0160KBA	2220	VC15MA0160KBA			VARIABLE TVS ESD 16VDC1200A 2220	AVX Corporation	VC15MA0160KBA
1	R208	resistor	RES 0402	R0402L	0.0	0.0		RES 0.0 OHM 1/16W 0402 SMD	Vishay	CRCW0402000Z0ED
1	R107, R109, R501, R502, R504, R505, R506, R507, R508, R509	resistor	RES 0402	R0402L	1.00K	1.00K		RES 1.00K OHM 1/16W 1% 0402 SMD	Vishay	CRCW04021K00FKED
2	R600, R602	resistor	RES 0402	R0402L	10.0k	10.0k		RES 10.0K OHM 1/16W 1% 0402 SMD	Vishay	CRCW040210K0FKED
2	R304, R311	resistor	RES 0402	R0402L	100	100		RES 100 OHM 1/16W 1% 0402 SMD	Vishay	CRCW0402100RFKED
2	C201, C202	capacitor	CAP NPO 0402 50V	C0402L	33pF	33pF	50V	CAP CER 33PF 50V 5% NPO 0402	TDK Corporation	C105COG1H330D050BA
4	C308, C311, C312, C314	capacitor	CAP X7R 0402 50V	C0402L	560pF	560pF	50V	CAP 560PF 50V CERAMIC X7R 0402	Kemet	C0402C561K5RACU
11	R217, R218, R219, R220, R226, R227, R228, R229	resistor	RES 0402	R0402L	33.0	33.0		RES 33.0 OHM 1/16W 1% 0402 SMD	Vishay	CRCW040233R0FKED
1	J101	general	MityOMAP Interface	I0033853-15ZFSLF	MityOMAP Interface			CONN SODIMM DDR2 200POS R/A SMD	FCI	I0033853-05ZFSLF
1	J102	general	USB-A-S-RA-TSMT	USB-A-S-RA-TSMT	USB-A-S-RA-TSMT			CONN RCPT USB RT ANG SMD	Multicomp	USB-A-S-RA-TSMT
2	U800, U801	general	VBLSD1-S12-55-SIP	VBLSD1	VBLSD1-S12-55-SIP			CONVERTER DC/DC 5V REG 0.75W	CLUI Inc	VBLSD1-S12-55-SIP
1	R409	resistor	RES 0402	R0402N	1.00k	1.00k		RES 1.00K OHM 1/16W 1% 0402 SMD	Vishay Dale	CRCW04021K00FKED
3	L600, L601, L602, C310, C401, C404, C406, C407, C408, C409, C410, C411, C502, C503, C608	capacitor	CAP X7R 0603 50V	C0603N	0.1uF	0.1uF	50V	CAP CER 0.1UF 50V 10% X7R 0603	AVX Corporation	06035C106KA7A
1	R500	resistor	RES 0603	R0603N	10.0k	10.0k		RES 10.0K OHM 1/10W 1% 0603 SMD	Yageo	RC0603F-0710K
3	C600, C604, C609	capacitor	CAP X7R 0603 50V	C0603N	0.01uF	0.01uF	50V	CAP CER 1000PF 50V 10% X7R 0603	Murata Electronics North America	GRM188R71H103KA01D

	C302, C402, C405, C505, C506, C507, C508, C614, C901	capacitor	CAP X7R 0603 25V	E0603N	1.0uF	1.0uF	25V	CAP CER 1UF 25V 10% X7R 0603	TDK Corporation	CGA3E1X7R1E105K080AC
1	U505	general	SM712TCT	SOT-23-3	SM712.TCT			IC TVS ASYMM RS-485V 7.12V SOT23	Semtech	SM712.TCT
1	R502	resistor	RES 1206	R1206N	120	120		RES 120 OHM 1/4W 1% 1206 SMD	Yageo	RC1206FR-07120RL
3	R400, R401, R402	resistor	RES 0603	R0603N	510	510		RES 510 OHM 1/10W 1% 0603 SMD	Vishay Dale	CRCW0603S10RKEA
2	C309, C313	capacitor	CAP X7R 0402 50V	C0402N	1800pF	1800pF	50V	CAP CER 1800PF 50V 10% X7R 0402	Murata Electronics North America	GRM155R71H182KA01D
1	O100	general	2N7002ET1G	SOT-23-3	2N7002ET1G			MOSFET N-CH 60V 260MA SOT-23	On Semiconductor	2N7002ET1G
1	U12	general	TLV803SD8ZR	SOT-23-3	TLV803SD8ZR			IC VOLT SUPERVISR 2.93V SOT23-3	Texas Instruments	TLV803SD8ZR
1	PN-PCB1	general	PN-PCB		90-000107R-4_RevA	90-000107R-4_RevA		PCB - MityOMAP Industrial IO	Critical Link LLC	90-000107R-4

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.