

About Test Results

Test results of the TIDA-00576 reference design are performed using the DLP® LightCrafter Display 4710 EVM which is the TI's implementation of the TIDA-00576 reference design. This EVM incorporates the DLP 0.47" 1080p chipset comprising of the DLP4710 DMD, DLPC3439 controller and DLPA3005 PMIC/Led Driver. The EVM and TI design enable faster development cycles for applications requiring full HD resolution and higher brightness projection display solutions. The entire test data contained below was measured from one DLP LightCrafter Display 4710 EVM to provide an example from a typical unit. Please note that performance will vary across EVMs due to variations in manufacturing. The performance data is not guaranteed

If You Need Assistance

Refer to the DLP and MEMS TI E2E Community support forums:

https://e2e.ti.com/support/dlp_mems_micro-electro-mechanical_systems

For specific questions on the DLP LightCrafter Display 4710 EVM refer to the DLP LightCrafter Display 4710 Development Platform Forum.

This test reports provides following test data:

1. Lumens measurement
2. Power Up and Power Down Sequence
3. Optical Engine Size
4. Optical Engine Throw Ratio

1 Lumens Measurement

This section provides the lumens measured for the EVM, which is the TI's implementation of this reference design.


White Point: 6600K

Lumens: 456 (ANSI)


2. Power Up and Power Down Timing Measurements

Power Up and Power Down timing requirements are described in detail in the DLP4710 datasheet. Key signals measured are PROJ_ON and the power supplies to the DMD- VBIAS, VOFFSET and VRESET. For more details on the timing requirements please refer the DLP4710 device datasheet.

Power Up Timing Measurements




Power down Timing Measurements



3. Optical engine size

DLP4710 is a key component of the 0.47" 1080p chipset and enables use of full HD resolution for projection display applications. The optical engine used in this DLPDLCR4710EVM is designed for +1000 Lumens applications:



Total volume of the optical engine is: 883.14 cc

4. Throw Ratio

An optical engine’s throw ratio is defined as the ratio of the distance measured from lens to screen and the width of the projected image.

$$\text{Throw Ratio} = \text{Distance/Width}$$

Throw ratio for the optical engine used in this ref design is 1.0

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated