

Why Use Sub-1 GHz in Your IoT Application



Dalia Youkhana

We continue to see tremendous growth within the [Internet of Things \(IoT\)](#) market with more devices than ever being connected to the cloud.

With applications such as home automation, which allow you to equip your home with lighting, heating, and alarm systems that give you the ability to turn on lights, set a desired temperature and receive notifications of any alarm activity right on your mobile device as soon as you approach the drive way.

The ability to connect low-power devices to the cloud is possible today with a number of different wireless connectivity technologies. The question often becomes which wireless technology is the right one for your application.

Communication over the [Sub-1 GHz band](#) has the unique ability of providing the longest range and lowest-power consumption with overall link robustness.

Long Range

- Half the frequency gives **twice** the range: The lower the frequency the longer the range. The attenuation is proportional to the wave length allowing lower frequencies, like Sub-1 GHz, to be able to travel further than higher frequencies.
- Provides **full house** and vicinity coverage: Sub-1 GHz has better penetration capabilities than 2.4 GHz as the attenuation through objects, such as walls, increases with frequency. Also, lower frequencies are better at “turning corners” providing increased indoor coverage.
- **Narrowband** capability: Sub-1 GHz solutions can operate in a narrowband mode, decreasing the probability of interference and increasing range due to improved link budget.

Robustness

- **Avoid crowded** bands: Compared to the 2.4 GHz band, which is crowded with *Bluetooth*®, *ZigBee*® and *Wi-Fi*®, the Sub-1 GHz ISM bands are mostly used for low duty-cycle links and are less likely to interfere with each other.
- **Less susceptible** to interference: Sub-1 GHz solutions can operate in a narrowband mode, decreasing the probability of interference.
- **Frequency hopping**: With the [TI 15.4-Stack software](#), you are able to achieve longer range in the FCC band and offer better protection against in-band interference by implementing [frequency hopping](#).

Ultra-low Power

- **Lower power** than other technologies: You can achieve the same range in Sub-1 GHz than 2.4 GHz with less transmit power. This enables Sub-1 GHz to be a very viable solution for battery-powered applications. For example, the [SimpleLink™ Sub-1 GHz CC1310 wireless microcontroller \(MCU\)](#) offers one of the lowest power consumptions in the industry.
- **Multi-year** operation on a coin cell battery: Sub-1 GHz operates in a quieter environment which means that the reception is less likely to be disturbed by other transmitters, resulting in less retries and hence improving the battery lifetime.
- **20 km** on a coin cell battery: Sub-1 GHz is the only technology capable of covering whole houses with simple software compared to *Bluetooth*®, *ZigBee*® and *Wi-Fi*® which results in overall lower power consumption.

[Figure 1](#) is an infographic highlighting the key benefits of using a Sub-1 GHz technology for your IoT network.

Why Sub-1 GHz

Facts about Sub-1 GHz

Long-range

Ultra-low power

Robust connection

Sub-1 GHz can span 20 km on a coin cell battery

Sub-1 GHz provides multi-year operation on a coin cell battery

Sub-1 GHz offers connectivity that reaches through walls and can turn corners

20 km on a coin cell

Connect, control and monitor the home and its vicinity with long range connectivity utilizing simple software, running on a coin cell battery for up to 10 years

Ultra-low power

Cover the entire retail floor of several hundreds of nodes to update information and manage data flow quickly all on battery powered devices

Robust and secure link

For dense urban environments, achieve a robust and reliable connection with integrated frequency hopping and built-in AES-based encryption

Long range on a single hop

Extend long-range connection in spread-out areas to monitor and track activity such as animal movement, crop growth, weather and more

TI provides the building blocks to develop ultra-low power, long-range and robust connectivity networks for IoT applications

Get started now:

- SimpleLink™ CC1310 LaunchPad™ development kit
- New! TI 15.4-Stack software

Figure 1. Reasons why you should use Sub-1 GHz in your IoT applications.

Get Started Developing Today!

- Order the [CC1310 wireless MCU LaunchPad™ development kit](#)

- Download the [TI 15.4-Stack software development kit](#)

Additionally Resources:

- Learn more about TI's Sub-1 GHz solutions: www.ti.com/sub1ghz
- Read more about our new TI 15.4-Stack software in this [blog post](#)
- Find out more about TI's role in the IoT: www.ti.com/iot
- Watch our 'Why Sub-1 GHz?' training video
- Download our latest [white paper](#) on frequency hopping
- Also, check out some of our CC1310 wireless mcu-based TI Design reference designs:
 - Humidity & Temp Sensor Node for Sub-1 GHz Star Networks Enabling 10+ Year Coin Cell Battery Life ([TIDA-00484](#))
 - Low Power Wireless PIR Motion Detector Reference Design Enabling 10 Year Coin Cell Battery Life ([TIDA-00489](#))
 - Energy Harvesting Ambient Light and Environment Sensor Node for Sub-1 GHz Networks Reference Design ([TIDA-00488](#))

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2023, Texas Instruments Incorporated