

AN-1870 LM26420 Evaluation Board

1 Introduction

The LM26420 evaluation board was designed to provide two 2A outputs, V_{OUT1} and V_{OUT2} . It is available in either the HTSSOP package option of the LM26420 for easier probing or the WQFN version for evaluating the smaller package. The design emphasizes on the compactness of the LM26420 PCB layout and is thermally optimized. The total solution size is less than 35mm by 40mm. The board supports the conversion from an input voltage ranging from 3V to 5.5V down to output voltages of 0.8V for each channel. V_{OUT1} and V_{OUT2} are set to 1.2V and 2.5V respectively. The feedback resistor can be changed to support output voltages as low as 0.8V or as high at 4.5V, assuming V_{IN} is high enough to support it. The EN pins are pulled up to V_{IN} by jumpers for easy evaluation but can also be easily controlled by external logic.

The board's specifications are:

- Input Voltage: 3V to 5.5V
- Output Voltages: 1.2V_{OUT1} and 2.5V_{OUT2}
- Maximum load current: 2A/output
- Minimum load current: 0A
- Size: 1.35 in. × 1.6 in.
- Peak Current Limit: $\approx 3.2A$ at 25°C
- Nominal Switching Frequency: 550 kHz or 2.2MHz

2 Powering Up the Board

Since the EN pins are directly tied to the input voltage via jumpers J_1 and J_2 , starting up the board is as simple as connecting a voltage supply from 3V to 5.5V between the V_{IN} and GND terminals. There should be 1.2V on V_{OUT1} and 2.5V on V_{OUT2} , assuming the jumpers connect V_{IN} to EN for each channel. Great care should be taken in powering up the supplies such that the input voltage, V_{IN} , does not exceed the Absolute Maximum Rating of 7V. If the part experiences voltages greater than 7V for a prolonged period of time, then damage to the part can occur and then the evaluation board may cease working.

The linear soft-start ramps for the two output voltages and should last about 600 μs . Load can be applied prior to power-up. If an output is shorted either before or after start-up, removal of the short-circuit condition should bring the corresponding output back to normal voltage.

3 Typical Application Circuit




Figure 1. LM26420 Demo Board Schematic

4 16-Pin WQFN Pin Out




Figure 2. 16-Pin WQFN (top view)

Table 1. Pin Descriptions 16-Pin WQFN

Pin	Name	Function
1,2	VIND ₁	Power Input supply for Buck1.
11, 12	VIND ₂	Power Input supply for Buck2.
15	VINC	Power Input supply for control circuitry.
4	PGND ₁	Power ground pin for Buck 1.
9	PGND ₂	Power ground pin for Buck 2.
14	AGND	Signal ground pin. Place the bottom resistor of the feedback network as close as possible to pin.
6	PG ₁	Power Good Indicator for Buck 1. Pin is connected through a resistor to an external supply (open collector output).
7	PG ₂	Power Good Indicator for Buck 2. Pin is connected through a resistor to an external supply (open collector output).
5	FB ₁	Feedback pin for Buck 1. Connect to external resistor divider to set output voltage.
8	FB ₂	Feedback pin for Buck 2. Connect to external resistor divider to set output voltage.
3	SW ₁	Output switch for Buck 1. Connect to the inductor.
10	SW ₂	Output switch for Buck 2. Connect to the inductor.
16	EN ₁	Enable control input. Logic high enable operation for Buck 1. Do not allow this pin to float or be greater than VIN + 0.3V.
13	EN ₂	Enable control input. Logic high enable operation for Buck 2. Do not allow this pin to float or be greater than VIN + 0.3V.
DAP	Die Attach Pad	Connect to system ground for low thermal impedance and as a primary electrical GND connection.

5 20-Pin HTSSOP Pin Out




Figure 3. 20-Pin HTSSOP (top view)

Table 2. Pin Descriptions 20-Pin HTSSOP

Pin	Name	Function
3, 4	VIND ₁	Power Input supply for Buck1.
17, 18	VIND ₂	Power Input supply for Buck2.
1	VINC	Power Input supply for control circuitry.
6,7	PGND ₁	Power ground pin for Buck 1.
14, 15	PGND ₂	Power ground pin for Buck 2.
20	AGND	Signal ground pin. Place the bottom resistor of the feedback network as close as possible to pin.
9	PG ₁	Power Good Indicator for Buck 1. Pin is connected through a resistor to an external supply (open drain output).
12	PG ₂	Power Good Indicator for Buck 2. Pin is connected through a resistor to an external supply (open drain output).
8	FB ₁	Feedback pin for Buck 1. Connect to external resistor divider to set output voltage.
13	FB ₂	Feedback pin for Buck 2. Connect to external resistor divider to set output voltage.
5	SW ₁	Output switch for Buck 1. Connect to the inductor.
16	SW ₂	Output switch for Buck 2. Connect to the inductor.
2	EN ₁	Enable control input. Logic high enable operation for Buck 1. Do not allow this pin to float or be greater than VIN + 0.3V.
19	EN ₂	Enable control input. Logic high enable operation for Buck 2. Do not allow this pin to float or be greater than VIN + 0.3V.
10,11	NC	No Connect.
DAP	Die Attach Pad	Connect to system ground for low thermal impedance, but it cannot be used as a primary GND connection.

6 Schematic - X Version





Figure 4. Schematic - X Version





Table 3. Bill of Materials - X Version

Item	Designator	Description	Manufacturer	Part No.	Qty.
1	C1, C2, C3, C4, C6, C7	22µF, 6.3V, X5R, 1206	TDK	C3216X5R0J226(M or K)	6
2	C5	0.47µF, 16V, X7R, 0603	TDK	C2012X7R1C474K	1
3	L1, L2	1µH, 6.4A	TDK	SPM6530T-1R0M120 or RLF7030T-1R0N6R4	2
4	R1	5.1k, 1%, 603	Vishay	CRCW06035K10F	1
5	R2	21.3k, 1%, 603	Vishay	CRCW060321K3F	1
6	R7, R8	49.9k, 1%, 603	Vishay	CRCW060349K9F	2
7	R3, R4, R5, R6	10k, 1%, 603	Vishay	CRCW060310K0F	4
8	R9	5.1 Ohm, 1%, 805	Vishay	CRCW06035R10F	1
9	J1, J2	Jumper for Enables	Sullins Connector Solutions	STC02SYAN	2
10	TP1-TP8	0.094" Diameter Solder Terminal	Keystone Electronics	5011	8
11	U1	Dual 2A, 2.2MHz PWM Switcher, HTSSOP-20 or WQFN-16	Texas Instruments	LM26420 or LM26420	1





7 Schematic - Y Version

Figure 5. Schematic - Y Version
Table 4. Bill of Materials - Y Version

Item	Designator	Description	Manufacturer	Part No.	Qty.
1	C1, C2, C3, C4, C6, C7	22 μ F, 6.3V, X5R, 1206	TDK	C3216X5R0J226(M or K)	6
2	C5	0.47 μ F, 16V, X7R, 0603	TDK	TMK105BJ104KV-F	1
3	L1, L2	3.3 μ H, 6.4A	TDK or Coilcraft	RLF7030T-3R3M4R1 or MSS7341-332NL_	2
4	R1	5.1k, 1%, 603	Vishay	CRCW06035K10F	1
5	R2	21.3k, 1%, 603	Vishay	CRCW060321K3F	1
6	R7, R8	49.9k, 1%, 603	Vishay	CRCW060349K9F	2
7	R3, R4, R5, R6	10k, 1%, 603	Vishay	CRCW060310K0F	4
8	R9	5.1 Ohm, 1%, 805	Vishay	CRCW06035R10F	1
9	J1, J2	Jumper for Enables	Sullins Connector Solutions	STC02SYAN	2
10	TP1-TP8	0.094" Diameter Solder Terminal	Keystone Electronics	5011	8
11	U1	Dual 2A, 550kHz PWM Switcher, HTSSOP-20 or WQFN-16	Texas Instruments	LM26420YMH or LM26420YSQ	1







8 HTSSOP-20 PCB Layout






9 WQFN-16 PCB Layout



10 Typical Performance Characteristics





IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com