


1 Startup


Input voltage = 85VAC
Load current = full load (3.84A)




PMP10100_RevA Test Results



Input voltage = 85VAC
Load current = no load




Input voltage = 265VAC
Load current = full load (3.84A)




2 Shutdown


Input voltage = 85VAC
Load current = full load (3.84A)




Input voltage = 265VAC
Load current = full load (3.84A)




3 Efficiency



4 Load regulation



5 Control Loop Frequency Response




Output power = 19.5V@3.84A
 Input voltage = 85VAC
 Phase margin = 56°
 Bandwidth = 1.1kHz

Output power = 19.5V@3.84A
 Input voltage = 230VAC
 Phase margin = 52°
 Bandwidth = 1.4kHz


Output power = 19.5V@3.84A
 Input voltage = 265VAC
 Phase margin = 51°
 Bandwidth = 1.5kHz

6 Switch Node

Input voltage = 265VAC
 Load current = full load (3.84A)




Input voltage = 85VAC
 Load current = full load (3.84A)



7 Output ripple voltage


Input voltage = 230VAC

Load current = full load (3.84A)




8 Load Transients

Input voltage = 230VAC
Load current = 1A to 4A



9 Thermal Analysis

The images below show the infrared images taken from the FlexCam after 15min at full load (19.5V@3.84A).



Name	Temperature
Transformer T2	64.3°C
Mosfet Q5	62.3°C
Snubber Network	83.3°C
Diode D6	52.8°C


IR20150511_0574 full load Vin=325VDC.is2

10 EMI Measurement

The graph below shows the conducted emission EMI noise and the EN55022 Class-B Quasi-Peak limits (measurement from the worst case line). The measurement is not certified. The load was connected to a LISN and an isolation transformer; the load was a power resistor. The receiver was set to Quasi-peak detector, 10 KHz bandwidth. The negative terminal of the converter has been connected to the ground of the LISN.

Input voltage = 230VAC

Load current = 3.84A



Date: 12.MAY.2015 13:14:52

PMP10100_RevA Test Results




Input voltage = 110VAC
Load current = 3.84A



Ref Lvl
90 dB μ V

RBW	10 kHz	RF Att	0 dB
VBW	100 kHz	Mixer	-20 dBm
SWT	60 s	Unit	dB μ V



Date: 12.MAY.2015 13:09:36

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated