

## CSD17308Q3 30-V N-Channel NexFET™ Power MOSFETs

### 1 Features

- Optimized for 5-V gate drive
- Ultra-low  $Q_g$  and  $Q_{gd}$
- Low thermal resistance
- Avalanche rated
- Lead-free terminal plating
- RoHS compliant
- Halogen free
- VSON 3.3 mm × 3.3 mm plastic package


### 2 Applications

- Notebook point of load
- Point-of-load synchronous buck in networking, telecom, and computing systems

### 3 Description

This 30-V, 8.2-m $\Omega$ , 3.3 mm × 3.3 mm VSON NexFET™ power MOSFET is designed to minimize losses in power conversion applications and optimized for 5-V gate drive applications.

Top View



### Product Summary

$T_A = 25^\circ\text{C}$		VALUE	UNIT
$V_{DS}$	Drain-to-source voltage	30	V
$Q_g$	Gate charge total (4.5 V)	3.9	nC
$Q_{gd}$	Gate charge gate-to-drain	0.8	nC
$R_{DS(on)}$	Drain-to-source on-resistance	$V_{GS} = 3\text{ V}$	12.5
		$V_{GS} = 4.5\text{ V}$	9.4
		$V_{GS} = 8\text{ V}$	8.2
$V_{GS(th)}$	Threshold voltage	1.3	V

### Device Information<sup>(1)</sup>

DEVICE	QTY	MEDIA	PACKAGE	SHIP
CSD17308Q3	2500	13-Inch Reel	SON 3.30 mm × 3.30 mm Plastic Package	Tape and Reel

(1) For all available packages, see the orderable addendum at the end of the data sheet.


### Absolute Maximum Ratings

$T_A = 25^\circ\text{C}$ unless otherwise stated		VALUE	UNIT
$V_{DS}$	Drain-to-source voltage	30	V
$V_{GS}$	Gate-to-source voltage	+10 / -8	V
$I_D$	Continuous drain current (package limited)	50	A
	Continuous drain current, $T_C = 25^\circ\text{C}$	44	
	Continuous drain current <sup>(1)</sup>	14	
$I_{DM}$	Pulsed drain current, $T_A = 25^\circ\text{C}$ <sup>(2)</sup>	167	A
$P_D$	Power dissipation <sup>(1)</sup>	2.7	W
	Power dissipation, $T_C = 25^\circ\text{C}$	28	
$T_J$ , $T_{stg}$	Operating junction and storage temperature	-55 to 150	$^\circ\text{C}$
$E_{AS}$	Avalanche energy, single pulse $I_D = 36\text{ A}$ , $L = 0.1\text{ mH}$ , $R_G = 25\ \Omega$	65	mJ


(1) Typical  $R_{\theta JA} = 46^\circ\text{C/W}$  when mounted on a 1-in<sup>2</sup> (6.45-cm<sup>2</sup>), 2-oz (0.071-mm) thick Cu pad on a 0.06-in (1.52-mm) thick FR4 PCB.

(2) Max  $R_{\theta JC} = 4.5^\circ\text{C/W}$ , pulse duration  $\leq 100\ \mu\text{s}$ , duty cycle  $\leq 1\%$ .

$R_{DS(on)}$  vs  $V_{GS}$



Gate Charge



## Table of Contents

<b>1 Features</b> .....	<b>1</b>	6.1 Support Resources .....	<b>8</b>
<b>2 Applications</b> .....	<b>1</b>	6.2 Trademarks .....	<b>8</b>
<b>3 Description</b> .....	<b>1</b>	6.3 Electrostatic Discharge Caution .....	<b>8</b>
<b>4 Revision History</b> .....	<b>2</b>	6.4 Glossary .....	<b>8</b>
<b>5 Specifications</b> .....	<b>3</b>	<b>7 Mechanical, Packaging, and Orderable Information</b> .....	<b>9</b>
5.1 Electrical Characteristics .....	<b>3</b>	7.1 Q3 Package Dimensions .....	<b>9</b>
5.2 Thermal Information .....	<b>3</b>	7.2 Recommended PCB Pattern .....	<b>10</b>
5.3 Typical MOSFET Characteristics .....	<b>5</b>	7.3 Recommended Stencil Opening .....	<b>10</b>
<b>6 Device and Documentation Support</b> .....	<b>8</b>	7.4 Q3 Tape and Reel Information .....	<b>11</b>

## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

### Changes from Revision B (October 2015) to Revision C Page

- Changed  $V_{GS(th)}$  MAX specification in the *Electrical Characteristics* table, From 1.8 V : To 1.6 V ..... **3**

### Changes from Revision A (February 2010) to Revision B Page

- Added part number to title ..... **1**
- Added Package Limited Continuous Drain Current ..... **1**
- Added line for Power Dissipation,  $T_C = 25^\circ\text{C}$  in *Absolute Maximum Ratings* table ..... **1**
- Updated pulsed current conditions ..... **1**
- Updated [Figure 1](#) to show  $R_{\theta JC}$  curves ..... **5**
- Added 4.5 V curve in [Figure 8](#) ..... **6**
- Updated [Figure 10](#) ..... **7**
- Added the *Device and Documentation Support* section ..... **8**
- Updated the [Mechanical, Packaging, and Orderable Information](#) section ..... **9**

### Changes from Original (February 2010) to Revision A Page

- Deleted the Package Marking Information section ..... **11**

## 5 Specifications

### 5.1 Electrical Characteristics

 $T_A = 25^\circ\text{C}$  unless otherwise stated

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
<b>STATIC CHARACTERISTICS</b>						
$BV_{DSS}$	Drain-to-source voltage	$V_{GS} = 0\text{ V}, I_D = 250\ \mu\text{A}$	30			V
$I_{DSS}$	Drain-to-source leakage current	$V_{GS} = 0\text{ V}, V_{DS} = 24\text{ V}$			1	$\mu\text{A}$
$I_{GSS}$	Gate-to-source leakage current	$V_{DS} = 0\text{ V}, V_{GS} = +10 / -8\text{ V}$			100	nA
$V_{GS(th)}$	Gate-to-source threshold voltage	$V_{DS} = V_{GS}, I_D = 250\ \mu\text{A}$	0.9	1.3	1.6	V
$R_{DS(on)}$	Drain-to-source on-resistance	$V_{GS} = 3\text{ V}, I_D = 10\text{ A}$		12.5	16.5	m $\Omega$
		$V_{GS} = 4.5\text{ V}, I_D = 10\text{ A}$		9.4	11.8	
		$V_{GS} = 8\text{ V}, I_D = 10\text{ A}$		8.2	10.3	
$g_{fs}$	Transconductance	$V_{DS} = 15\text{ V}, I_D = 10\text{ A}$		37		S
<b>DYNAMIC CHARACTERISTICS</b>						
$C_{ISS}$	Input capacitance	$V_{GS} = 0\text{ V}, V_{DS} = 15\text{ V}, f = 1\text{ MHz}$		540	700	pF
$C_{OSS}$	Output capacitance			280	365	pF
$C_{RSS}$	Reverse transfer capacitance			27	35	pF
$R_g$	Series gate resistance			0.9	1.8	$\Omega$
$Q_g$	Gate charge total (4.5 V)	$V_{DS} = 15\text{ V}, I_D = 10\text{ A}$		3.9	5.1	nC
$Q_{gd}$	Gate charge gate-to-drain			0.8		nC
$Q_{gs}$	Gate charge gate-to-source			1.3		nC
$Q_{g(th)}$	Gate charge at $V_{th}$			0.7		nC
$Q_{OSS}$	Output charge		$V_{DS} = 13\text{ V}, V_{GS} = 0\text{ V}$		7.4	
$t_{d(on)}$	Turnon delay time	$V_{DS} = 15\text{ V}, V_{GS} = 4.5\text{ V}, I_D = 10\text{ A}, R_G = 2\ \Omega$		4.5		ns
$t_r$	Rise time			5.7		ns
$t_{d(off)}$	Turnoff delay time			9.9		ns
$t_f$	Fall time			2.3		ns
<b>DIODE CHARACTERISTICS</b>						
$V_{SD}$	Diode forward voltage	$I_{DS} = 10\text{ A}, V_{GS} = 0\text{ V}$		0.85	1	V
$Q_{rr}$	Reverse recovery charge	$V_{DD} = 13\text{ V}, I_F = 10\text{ A}, di/dt = 300\text{ A}/\mu\text{s}$		9.3		nC
$t_{rr}$	Reverse recovery time			14.3		ns

### 5.2 Thermal Information

 $T_A = 25^\circ\text{C}$  unless otherwise stated


THERMAL METRIC		MIN	TYP	MAX	UNIT
$R_{\theta JC}$	Junction-to-case thermal resistance <sup>(1)</sup>			4.5	$^\circ\text{C}/\text{W}$
$R_{\theta JA}$	Junction-to-ambient thermal resistance <sup>(1)(2)</sup>			58	$^\circ\text{C}/\text{W}$

- (1)  $R_{\theta JC}$  is determined with the device mounted on a 1-in<sup>2</sup> (6.45-cm<sup>2</sup>), 2-oz (0.071-mm) thick Cu pad on a 1.5-in × 1.5-in (3.81-cm × 3.81-cm), 0.06-in (1.52-mm) thick FR4 PCB.  $R_{\theta JC}$  is specified by design, whereas  $R_{\theta JA}$  is determined by the user's board design.
- (2) Device mounted on FR4 material with 1-in<sup>2</sup> (6.45-cm<sup>2</sup>), 2-oz (0.071-mm) thick Cu.

**CSD17308Q3**


SLPS262C – FEBRUARY 2010 – REVISED DECEMBER 2019

[www.ti.com](http://www.ti.com)



M0161-01

Max  $R_{\theta JA} = 58^{\circ}\text{C/W}$   
 when mounted on 1 in<sup>2</sup>  
 (6.45 cm<sup>2</sup>) of  
 2-oz (0.071-mm) thick  
 Cu.



M0161-02

Max  $R_{\theta JA} = 165^{\circ}\text{C/W}$   
 when mounted on a  
 minimum pad area of  
 2-oz (0.071-mm) thick  
 Cu.

### 5.3 Typical MOSFET Characteristics

T<sub>A</sub> = 25°C unless otherwise stated




Figure 1. Transient Thermal Impedance




Figure 2. Saturation Characteristics










Figure 3. Transfer Characteristics

Typical MOSFET Characteristics (continued)

T<sub>A</sub> = 25°C unless otherwise stated



Typical MOSFET Characteristics (continued)

T<sub>A</sub> = 25°C unless otherwise stated




Figure 10. Maximum Safe Operating Area




Figure 11. Single Pulse Unclamped Inductive Switching




Figure 12. Maximum Drain Current vs Temperature

## 6 Device and Documentation Support

### 6.1 Support Resources

TI E2E™ [support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 6.2 Trademarks

NexFET, E2E are trademarks of Texas Instruments.  
All other trademarks are the property of their respective owners.

### 6.3 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

### 6.4 Glossary

[SLYZ022](#) — *TI Glossary*.


This glossary lists and explains terms, acronyms, and definitions.



## 7 Mechanical, Packaging, and Orderable Information


The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

### 7.1 Q3 Package Dimensions




DIM	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.950	1.000	1.100	0.037	0.039	0.043
A1	0.000	0.000	0.050	0.000	0.000	0.002
b	0.280	0.340	0.400	0.011	0.013	0.016
b1	0.310 NOM			0.012 NOM		
c	0.150	0.200	0.250	0.006	0.008	0.010
D	3.200	3.300	3.400	0.126	0.130	0.134
D2	1.650	1.750	1.800	0.065	0.069	0.071
d	0.150	0.200	0.250	0.006	0.008	0.010
d1	0.300	0.350	0.400	0.012	0.014	0.016
E	3.200	3.300	3.400	0.126	0.130	0.134
E2	2.350	2.450	2.550	0.093	0.096	0.100
e	0.650 TYP			0.026 TYP		
H	0.35	0.450	0.550	0.014	0.018	0.022
K	0.650 TYP			0.026 TYP		
L	0.35	0.450	0.550	0.014	0.018	0.022
L1	0	—	0	0	—	0
$\theta$	0	—	0	0	—	0

## 7.2 Recommended PCB Pattern




For recommended circuit layout for PCB designs, see application note [SLPA005](#) – *Reducing Ringing Through PCB Layout Techniques*.

## 7.3 Recommended Stencil Opening



All dimensions are in mm, unless otherwise specified.

## 7.4 Q3 Tape and Reel Information



M0144-01

### Notes:

1. 10 sprocket hole pitch cumulative tolerance  $\pm 0.2$
2. Camber not to exceed 1 mm in 100 mm, noncumulative over 250 mm
3. Material: black static dissipative polystyrene
4. All dimensions are in mm (unless otherwise specified).
5. Thickness:  $0.30 \pm 0.05$  mm
6. MSL1 260°C (IR and Convection) PbF-Reflow Compatible

**PACKAGING INFORMATION**

Orderable part number	Status (1)	Material type (2)	Package   Pins	Package qty   Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
<a href="#">CSD17308Q3</a>	Active	Production	VSON-CLIP (DQG)   8	2500   LARGE T&R	ROHS Exempt	SN	Level-1-260C-UNLIM	-55 to 150	CSD17308
CSD17308Q3.B	Active	Production	VSON-CLIP (DQG)   8	2500   LARGE T&R	ROHS Exempt	SN	Level-1-260C-UNLIM	-55 to 150	CSD17308
<a href="#">CSD17308Q3T</a>	Active	Production	VSON-CLIP (DQG)   8	250   SMALL T&R	ROHS Exempt	SN	Level-1-260C-UNLIM	-55 to 150	CSD17308
CSD17308Q3T.B	Active	Production	VSON-CLIP (DQG)   8	250   SMALL T&R	ROHS Exempt	SN	Level-1-260C-UNLIM	-55 to 150	CSD17308

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025