

LM654B0-Q1 Pin-Compatible 20A (25A Peak) ZEN 1 Stackable Automotive Buck Converter

1 Features

- AEC-Q100 qualified for automotive applications:
 - Temperature grade 1: –40°C to +125°C, T_A
- · Built in clocking for stacking of converters
- Internal or external compensation
- Pin selectable output voltage 3.3V and 5V fixed or adjustable from 0.8V to 0.9 × V_{IN}
- · Wide input voltage range: 3V to 36V
- ZEN 1 switcher technology
 - Optimized for low EMI requirements
 - Facilitates CISPR 25 Class 5 CISPR 11 Class B compliance
 - Enhanced HotRod[™] QFN package with symmetrical pinout
- Switching frequency from 300kHz to 2.2MHz
 - Pin-configurable AUTO or FPWM operation
 - Synchronizable with external clock
- Low minimum on time: 40ns (maximum)
 - Enables 36V to 3.3V conversion at 2.2MHz
- · High-efficiency and high power density

2 Applications

- Advanced driver assistance systems (ADAS)
- Automotive infotainment and cluster
- · Hybrid, electric, and powertrain systems
- Medical imaging systems
- · Test and measurement systems
- · Wireless infrastructure systems

3 Description

The LM654B0-Q1 is a buck converter designed for high efficiency, high power density, and low EMI performance with ZEN switcher technology for automotive applications. The converter operates over a wide input voltage range of 3V to 36V with pin selectable fixed output voltages of 3.3V and 5V or an adjustable output.


The low EMI operation is enabled with minimized loop inductance, optimized SW node slew-rate, and dual-random spread spectrum (DRSS). The DRSS significantly reduces peak emissions through a combination of triangular and pseudo-random modulation while keeping output voltage ripple very low.

The current-mode control architecture with 32ns typical minimum on-time allows high conversion ratios at high frequencies, fast transient response, and excellent load and line regulation.

Package Information

PART NUMBER	PACKAGE ⁽¹⁾	PACKAGE SIZE ⁽²⁾		
LM654B0-Q1	VDA (WQFN-FCRLF, 26)	4.5mm × 4.5mm		

- (1) For more information, see Section 7.
- (2) The package size (length × width) is a nominal value and includes pins, where applicable.



Simplified Schematic



Table of Contents

1 Features	5.3 Support Resources4
2 Applications1	5.4 Trademarks4
3 Description1	
4 Device Comparison Table3	
5 Device and Documentation Support4	
5.1 Device Support4	——————————————————————————————————————
	7.1 Tape and Reel Information5

Submit Document Feedback

Copyright © 2025 Texas Instruments Incorporated



4 Device Comparison Table

DEVICE	PART NUMBER PART NUMBER CI		RATED OUTPUT CURRENT	TOP-SIDE EXPOSED THERMAL PAD	BOTTOM EXPOSED THERMAL PAD	PACKAGE	JUNCTION TEMPERATURE RANGE
LM654B0-Q1	LM654B0VDARQ1	PLM654B0VDARQ1	20	YES	YES	VDA (26)	–40°C to 150°C

Product Folder Links: LM654B0-Q1



5 Device and Documentation Support

5.1 Device Support

5.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

5.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

5.3 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

5.4 Trademarks

HotRod[™] and TI E2E[™] are trademarks of Texas Instruments.

All trademarks are the property of their respective owners.

5.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

5.6 Glossary

TI Glossary

This glossary lists and explains terms, acronyms, and definitions.

6 Revision History

DATE REVISION		NOTES		
November 2025	*	Initial Release		


Product Folder Links: LM654B0-Q1




7 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

7.1 Tape and Reel Information




QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



Reel Width W1 Reel Pin1 Package Package K0 Device SPQ Pins Diameter Type Drawing (mm) (mm) (mm) (mm) (mm) Quadrant (mm) (mm) WQFN-PLM654B0VDARQ1 VDA 26 3000 12.4 1.4 8.0 12 Q2 FCRLF

Copyright © 2025 Texas Instruments Incorporated



Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
PLM654B0VDARQ1	WQFN-FCRLF	VDA0026A	26	3000	346	346	33

ADVANCE INFORMATION




VDA0026A

PACKAGE OUTLINE

WQFN-FCRLF - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



Product Folder Links: LM654B0-Q1




EXAMPLE BOARD LAYOUT

VDA0026A

WQFN-FCRLF - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
 5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations show on this view. It is recommended that vias under paste be filled, plugged or tented.






EXAMPLE STENCIL DESIGN

VDA0026A

WQFN-FCRLF - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



www.ti.com 10-Nov-2025

PACKAGING INFORMATION

Orderable part number	r Status	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
PLM654B0VDARQ1	Active	Preproduction	WQFN-FCRLF (VDA) 26	3000 LARGE T&R	-	Call TI	Call TI	-40 to 150	

⁽¹⁾ Status: For more details on status, see our product life cycle.

- (3) RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.
- (4) Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- (5) MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.
- (6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025