

www.ti.com

SCAS860B - OCTOBER 2008 - REVISED MARCH 2012

RAD-TOLERANT CLASS V, HEX SCHMITT-TRIGGER INVERTER

Check for Samples: SN54AC14-SP

FEATURES

•	2-V to 6-V V _{CC} Operation	J OR W PACKAGE (TOP VIEW)			
•	Inputs Accept Voltages to 6 V	, L		, –	
•	Max tpd of 9.5 ns at 5 V	1A [1 1	4 V _{CC}	
•	Rad-Tolerant: 50 kRad(Si) TID (1)	1Y []	2 1	3 🛛 6A	
	 TID Dose Rate < 2mRad/sec 	2A []	3 1	2 6 Y	
_	ONL V Qualified CND E002 07024	2Y []	4 1	1 🛛 5A	
•	QML-V Quaimed, SMD 5962-87624	ЗА [5 1	0] 5Y	
(1)	Radiation tolerance is a typical value based upon initial device	3Y [6	9 🛛 4A	
(-)	qualification. Radiation Lot Acceptance Testing is available - contact factory for details.		7	8 4Y	

DESCRIPTION/ORDERING INFORMATION

These Schmitt-trigger devices contain six independent inverters. They perform the Boolean function $Y = \overline{A}$. Because of the Schmitt action, they have different input threshold levels for positive-going (V_{T+}) and for negative-going (V_{T-}) signals.

These circuits are temperature compensated and can be triggered from the slowest of input ramps and still give clean, jitter-free output signals. They also have a greater noise margin than conventional inverters.

ORDERING INFORMATION⁽¹⁾

T _A	PACK	AGE ⁽²⁾	ORDERABLE PART NUMBER	TOP-SIDE MARKING
EE%C to 105%C	CDIP – J	Tube	5962-8762402VCA	5962-8762402VCA
-55°C 10 125°C	CFP – W	Tube	5962-8762402VDA	5962-8762402VDA

(1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at www.ti.com.

(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.

FUNCTION TABLE (EACH INVERTER)						
INPUT OUTPUT A Y						
Н	L					
L	н					

LOGIC DIAGRAM, EACH INVERTER (POSITIVE LOGIC)





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

SCAS860B-OCTOBER 2008-REVISED MARCH 2012

TEXAS INSTRUMENTS

www.ti.com

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
V _{CC}	Supply voltage range		-0.5	7	V
VI	Input voltage range ⁽²⁾	-0.5	V _{CC} + 0.5	V	
Vo	Output voltage range ⁽²⁾	-0.5	V _{CC} + 0.5	V	
I _{IK}	Input clamp current	$V_{I} < 0 \text{ or } V_{I} > V_{CC}$		±20	mA
I _{OK}	Output clamp current	V ₀ < 0		±20	mA
I _O	Continuous output current	$V_{O} = 0$ to V_{CC}		±50	mA
	Continuous current through V_{CC} or GND			±200	mA
T _{stg}	Storage temperature range		-65	150	°C

(1) Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input and output voltage ratings may be exceeded provided the input and output current ratings are observed.

RECOMMENDED OPERATING CONDITIONS⁽¹⁾

			MIN	MAX	UNIT
V_{CC}	Supply voltage		2	6	V
VI	Input voltage		0	V _{CC}	V
Vo	Output voltage		0	V _{CC}	V
		$V_{CC} = 3 V$		-12	
I _{OH}	High-level output current	$V_{CC} = 4.5 V$		-24	mA
	V _{CC} = 5.5 V			-24	
		$V_{CC} = 3 V$		12	
I _{OL}	Low-level output current	$V_{CC} = 4.5 V$		24	mA
		$V_{CC} = 5.5 V$		24	
T _A	Operating free-air temperature		-55	125	°C

 All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

Copyright © 2008–2012, Texas Instruments Incorporated



SCAS860B-OCTOBER 2008-REVISED MARCH 2012

www.ti.com

Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

DADAMETED	TEAT CONDITIONS	v	T _A = 25°	С	T _A = -55°C T	UNIT	
PARAMETER	TEST CONDITIONS	V _{CC}	MIN	MAX	MIN MAX		UNIT
V _T .		3 V		2.3		2.3	
Positive-going		4.5 V		3.2		3.2	V
threshold		5.5 V		3.9		3.9	
VT		3 V	0.5		0.5		
Negative-going		4.5 V	0.9		0.9		V
threshold		5.5 V	1.1		1.1		
۸V+		3 V	0.3	1.3	0.3	1.3	
Hysteresis		4.5 V	0.4	1.4	0.4	1.4	V
$(V_{T+} - V_{T-})$		5.5 V	0.5	1.6	0.5	1.6	
		3 V	2.9		2.9		
	I _{OH} = -50 μA	4.5 V	4.4		4.4		
		5.5 V	5.4		5.4		
V _{OH}	$I_{OH} = -12 \text{ mA}$	3 V	2.56		2.4		V
		4.5 V	3.86		3.7		
	$I_{OH} = -24 \text{ mA}$	5.5 V	4.86		4.7		
	$I_{OH} = -50 \text{ mA}^{(1)}$	5.5 V			3.85		
		3 V		0.1		0.1	
	I _{OL} = 50 μA	4.5 V		0.1		0.1	
		5.5 V		0.1		0.1	
V _{OL}	I _{OL} = 12 mA	3 V		0.5		0.5	V
	1 24 m 4	4.5 V		0.5		0.5	
	$I_{OL} = 24 \text{ IIIA}$	5.5 V		0.5		0.5	
	$I_{OL} = 50 \text{ mA}^{(1)}$	5.5 V				1.65	
I _I	$V_{I} = V_{CC} \text{ or } GND$	5.5 V		±0.1		±1	μA
I _{CC}	$V_{I} = V_{CC}$ or GND, $I_{O} = 0$	5.5 V		4		80	μA
I _{CCt}	$V_{I} = V_{CC}/2 V$ One input at V _I , other input at V _{CC} or GND ⁽²⁾	5.5 V		7.5		7.5	mA
Ci	$V_I = V_{CC}$ or GND	5 V		8		8	pF

(1) Not more than one output should be tested at a time, and the duration of the test should not exceed 10 ms.

(2) V_{I} is incremented in 0.1-V steps to 3.7 V.

www.ti.com

SCAS860B-OCTOBER 2008-REVISED MARCH 2012

SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range, V_{CC} = 3.3 V ± 0.3 V, C_L = 50 pF (unless otherwise noted) (see Figure 1)

DADAMETED	FROM	то	Τμ	_A = 25°C		T _A = –55°C T	O 125°C		
FARAMETER	(INPUT)	(OUTPUT)	MIN	TYP	MAX	MIN	MAX		
t _{PLH}	٨	V	1.5	6	13.5	1	16	2	
t _{PHL}	A	ř	1.5	6	11.5	1	14	ns	

SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range, V_{CC} = 5 V ± 0.5 V, C_L = 50 pF (unless otherwise noted) (see Figure 1)

	FROM	то	Т	_A = 25°C		T _A = -55°C	TO 125°C	
PARAMETER	(INPUT)	(OUTPUT)	MIN	TYP	MAX	MIN	MAX	UNIT
t _{PLH}		V	1.5	5	10	1.5	12	20
t _{PHL}	A	ř	1.5	5	8.5	1.5	10	ns

OPERATING CHARACTERISTICS

 $V_{CC} = 5 \text{ V}, \text{ } \text{T}_{\text{A}} = 25^{\circ}\text{C}$

PARAMETER	TEST CONDITIONS	TYP	UNIT
C _{pd} Power dissipation capacitance	$C_{L} = 50 \text{ pF}, \text{ f} = 1 \text{ MHz}$	25	pF



SCAS860B-OCTOBER 2008-REVISED MARCH 2012

www.ti.com

PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and jig capacitance.

- B. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, Z_O = 50 Ω , t_f \leq 2.5 ns, t_f \leq 2.5 ns.
- C. The outputs are measured one at a time with one input transition per measurement.

Figure 1. Load Circuit and Voltage Waveforms

SCAS860B - OCTOBER 2008 - REVISED MARCH 2012

6

REVISION HISTORY

Ch	anges from Revision A (March, 2010) to Revision B P	age	е
•	Added I _{CCt} parameter to Electrical Characteristics	;	3



www.ti.com



PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	(3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
5962-8762401VCA	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-8762401VC A SNV54AC14J
5962-8762401VCA.A	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-8762401VC A SNV54AC14J
5962-8762401VDA	Active	Production	CFP (W) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-8762401VD A SNV54AC14W
5962-8762401VDA.A	Active	Production	CFP (W) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-8762401VD A SNV54AC14W
5962-8762402VCA	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-8762402VC A SNV54AC14J
5962-8762402VCA.A	Active	Production	CDIP (J) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-8762402VC A SNV54AC14J
5962-8762402VDA	Active	Production	CFP (W) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-8762402VD A SNV54AC14W
5962-8762402VDA.A	Active	Production	CFP (W) 14	25 TUBE	No	SNPB	N/A for Pkg Type	-55 to 125	5962-8762402VD A SNV54AC14W

⁽¹⁾ Status: For more details on status, see our product life cycle.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



www.ti.com

29-May-2025

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN54AC14-SP :

• Catalog : SN54AC14

NOTE: Qualified Version Definitions:

• Catalog - TI's standard catalog product

TEXAS INSTRUMENTS

www.ti.com

23-May-2025

TUBE



- B - Alignment groove width

*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
5962-8762401VDA	W	CFP	14	25	506.98	26.16	6220	NA
5962-8762401VDA.A	W	CFP	14	25	506.98	26.16	6220	NA
5962-8762402VDA	W	CFP	14	25	506.98	26.16	6220	NA
5962-8762402VDA.A	W	CFP	14	25	506.98	26.16	6220	NA

W (R-GDFP-F14)

CERAMIC DUAL FLATPACK



- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. This package can be hermetically sealed with a ceramic lid using glass frit.
 - D. Index point is provided on cap for terminal identification only.
 - E. Falls within MIL STD 1835 GDFP1-F14



GENERIC PACKAGE VIEW

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



J0014A



PACKAGE OUTLINE

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



NOTES:

- 1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This package is hermitically sealed with a ceramic lid using glass frit.
- Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
 Falls within MIL-STD-1835 and GDIP1-T14.



J0014A

EXAMPLE BOARD LAYOUT

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE





IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025, Texas Instruments Incorporated