

www.ti.com _______SCDS319 – JUNE 2011


SINGLE FET BUS SWITCH 2.5-V/3.3-V LOW-VOLTAGE SWITCH WITH 5-V-TOLERANT LEVEL SHIFTER

Check for Samples: SN74CB3T1G125-Q1

FEATURES

- Qualified for Automotive Applications
- Output Voltage Translation Tracks V_{CC}
- Supports Mixed-Mode Signal Operation on All Data I/O Ports
 - 5-V Input Down to 3.3-V Output Level Shift With 3.3-V V_{CC}
 - 5-V/3.3-V Input Down to 2.5-V Output Level Shift With 2.5-V V_{CC}
- 5-V-Tolerant I/Os, With Device Powered Up or Powered Down
- Bidirectional Data Flow With Near-Zero Propagation Delay
- Low ON-State Resistance (r_{on}) Characteristics (r_{on} = 5 Ω Typ)
- Low Input/Output Capacitance Minimizes Loading (C_{io(OFF)} = 5 pF Typ)
- Data and Control Inputs Provide Undershoot Clamp Diodes
- Low Power Consumption (I_{CC} = 20 µA Max)

- V_{CC} Operating Range From 2.3 V to 3.6 V
- Data I/Os Support 0- to 5-V Signaling Levels (0.8 V, 1.2 V, 1.5 V, 1.8 V, 2.5 V, 3.3 V, 5 V)
- Control Inputs Can Be Driven by TTL or 5-V/3.3-V CMOS Outputs
- I_{off} Supports Partial-Power-Down Mode Operation
- Supports Digital Applications: Level Translation, USB Interface, Bus Isolation
- Ideal for Low-Power Portable Equipment



DESCRIPTION

The SN74CB3T1G125-Q1 is a high-speed TTL-compatible FET bus switch with low ON-state resistance (r_{on}), allowing for minimal propagation delay. The device fully supports mixed-mode signal operation on all data I/O ports by providing voltage translation that tracks V_{CC} . The SN74CB3T1G125-Q1 supports systems using 5-V TTL, 3.3-V LVTTL, and 2.5-V CMOS switching standards, as well as user-defined switching levels (see Figure 1).

The SN74CB3T1G125-Q1 is a 1-bit bus switch with a single ouput-enable (\overline{OE}) input. When \overline{OE} is low, the bus switch is ON, and the A port is connected to the B port, allowing bidirectional data flow between ports. When \overline{OE} is high, the bus switch is OFF, and a high-impedance state exists between the A and B ports.

This device is fully specified for partial-power-down applications using I_{off}. The I_{off} feature ensures that damaging current will not backflow through the device when it is powered down. The device has isolation during power off.


To ensure the high-impedance state during power up or power down, \overline{OE} should be tied to V_{CC} through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



SCDS319 – JUNE 2011 www.ti.com



NOTE A: If the input high voltage (V_{IH}) level is greater than or equal to $V_{CC} - 1$ V, and less than or equal to 5.5 V, then the output high voltage (V_{OH}) level will be equal to approximately the V_{CC} voltage level.

Figure 1. Typical DC Voltage Translation Characteristics

ORDERING INFORMATION


T _A	PACKA	GE ⁽¹⁾	ORDERABLE PART NUMBER	TOP-SIDE MARKING ⁽²⁾
-40°C to 125°C	SOT (SC-70) - DCK	Reel of 3000	CCB3T1G125QDCKRQ1	72_

- (1) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.
- (2) The actual top-side marking has one additional character that designates the assembly/test site.

FUNCTION TABLE

INPUT OE	INPUT/OUTPUT A	FUNCTION
L	В	A port = B port
Н	Z	Disconnect


LOGIC DIAGRAM (POSITIVE LOGIC)





www.ti.com SCDS319 – JUNE 2011

SIMPLIFIED SCHEMATIC, EACH FET SWITCH (SW)



- (1) Gate voltage (V_G) is equal to approximately V_{CC} + V_T when the switch is ON and V_I > V_{CC} + V_T.
- (2) EN is the internal enable signal applied to the switch.

ABSOLUTE MAXIMUM RATINGS(1)

over operating free-air temperature range (unless otherwise noted)

			MIM	I MAX	UNIT
V_{CC}	Supply voltage range		-0.5	5 7	V
V _{IN}	Control input voltage range (2) (3)		-0.5	5 7	V
V _{I/O}	Switch I/O voltage range ^{(2) (3) (4)}		-0.5	5 7	V
I _{IK}	Control input clamp current	V _{IN} < 0		-50	mA
I _{I/OK}	I/O port clamp current	V _{I/O} < 0		-50	mA
I _{IO}	ON-state switch current ⁽⁵⁾			±128	mA
	Continuous current through V _{CC} or GND			±100	mA
θ_{JA}	Package thermal impedance ⁽⁶⁾	DCK package		252	°C/W
T _{stg}	Storage temperature range	,	-65	150	°C

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltages are with respect to ground, unless otherwise specified.
- 3) The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.
- (4) V_I and V_O are used to denote specific conditions for $V_{I/O}$.
- (5) I_I and I_O are used to denote specific conditions for $I_{I/O}$.
- (6) The package thermal impedance is calculated in accordance with JESD 51-7.

RECOMMENDED OPERATING CONDITIONS(1)

			MIN	MAX	UNIT
V_{CC}	Supply voltage		2.3	3.6	V
	History I and the Property of the sec	V _{CC} = 2.3 V to 2.7 V	1.7	5.5	
V_{IH}	High-level control input voltage $V_{CC} = 2.7 \text{ V to}$		2	5.5	V
	Lava lava lava desli fare di valla es	V _{CC} = 2.3 V to 2.7 V	0	0.7	
V_{IL}	Low-level control input voltage	$V_{CC} = 2.7 \text{ V to } 3.6 \text{ V}$	0	0.8	V
V _{I/O}	Data input/output voltage		0	5.5	V
T _A	Operating free-air temperature		-40	125	°C

⁽¹⁾ All unused control inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.



SCDS319 - JUNE 2011 www.ti.com

ELECTRICAL CHARACTERISTICS(1)

over recommended operating free-air temperature range (unless otherwise noted)

PAR	RAMETER	TEST CONDITIONS		MIN	TYP ⁽²⁾	MAX	UNIT	
V _{IK}		$V_{CC} = 3 \text{ V}, I_{I} = -18 \text{ mA}$				-1.2	V	
V _{OH}		See Figure 3 and Figure 4						
I _{IN}	Control inputs	$V_{CC} = 3.6 \text{ V}, V_{IN} = 3.6 \text{ V} \text{ to } 5.5 \text{ V} \text{ or GND}$				±10	μΑ	
		V _{CC} = 3.6 V,	$V_1 = V_{CC} - 0.7 \text{ V to } 5.5 \text{ V}$			±20		
I		Switch ON,	$V_{I} = 0.7 \text{ V to } V_{CC} - 0.7 \text{ V}$			-40	μΑ	
		$V_{IN} = V_{CC}$ or GND	$V_{I} = 0 \text{ to } 0.7 \text{ V}$	±5				
I _{OZ} (3)		V_{CC} = 3.6 V, V_{O} = 0 to 5.5 V, V_{I} = 0, Switch OFF,	$V_{IN} = V_{CC}$ or GND			±10	μΑ	
I _{off}		$V_{CC} = 0$, $V_{O} = 0$ to 5.5 V, $V_{I} = 0$			10	μΑ		
		$V_{CC} = 3.6 \text{ V}, I_{VO} = 0,$	$V_I = V_{CC}$ or GND			20		
I _{CC}		Switch ON or OFF, $V_{IN} = V_{CC}$ or GND	V _I = 5.5 V			20	μΑ	
ΔI_{CC} (4)	Control inputs	V_{CC} = 3 V to 3.6 V, One input at V_{CC} - 0.6 V, One	ther inputs at V _{CC} or GND			300	μΑ	
C _{in}	Control inputs	$V_{CC} = 3.3 \text{ V}, V_{IN} = V_{CC} \text{ or GND}$			3		рF	
C _{io(OFF)}		V_{CC} = 3.3 V, $V_{I/O}$ = 5.5 V, 3.3 V, or GND, Switch	OFF, V _{IN} = V _{CC} or GND		5		pF	
		V _{CC} = 3.3 V, Switch ON,	V _{I/O} = 5.5 V or 3.3 V		4			
C _{io(ON)}	$V_{IN} = V_{CC}$ or GND		V _{I/O} = GND		12		pF	
		$V_{CC} = 2.3 \text{ V}$, TYP at $V_{CC} = 2.5 \text{ V}$,	I _O = 24 mA		5	10		
" (5)		$V_1 = 0$	I _O = 16 mA		5	10	0	
r _{on} ⁽⁵⁾		V 2V V 0	I _O = 24 mA		5	9	Ω	
		$V_{CC} = 3 \text{ V}, V_I = 0$	I _O = 16 mA		5	9		

- V_{IN} and I_{IN} refer to control inputs. V_{I} , V_{O} , I_{I} , and I_{O} refer to data pins. All typical values are at $V_{CC}=3.3$ V (unless otherwise noted), $T_{A}=25^{\circ}C$. For I/O ports, the parameter I_{OZ} includes the input leakage current. This is the increase in supply current for each input that is at the specified TTL voltage level, rather than V_{CC} or GND.
- Measured by the voltage drop between A and B terminals at the indicated current through the switch. ON-state resistance is determined by the lower of the voltages of the two (A or B) terminals.

SWITCHING CHARACTERISTICS


over recommended operating free-air temperature range (unless otherwise noted) (see Figure 2)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC} = ± 0.2		V _{CC} = 3 ± 0.3		UNIT
	(INPOT)	(001F01)	MIN	MAX	MIN	MAX	
t _{en}	ŌĒ	A or B	1	10.5	1	9.5	ns
t _{dis}	ŌĒ	A or B	1	8.5	1	9	ns




www.ti.com SCDS319 – JUNE 2011

PARAMETER MEASUREMENT INFORMATION



TEST	V _{cc}	S1	R _L	V,	C _L	V _^
t _{pd(s)}	2.5 V ± 0.2 V 3.3 V ± 0.3 V	Open Open	500 Ω 500 Ω	3.6 V or GND 5.5 V or GND	30 pF 50 pF	
t _{PLZ} /t _{PZL}	2.5 V ± 0.2 V	2 x V _{cc}	500 Ω	GND	30 pF	0.15 V
	3.3 V ± 0.3 V	2 x V _{cc}	500 Ω	GND	50 pF	0.15 V
t _{PHZ} /t _{PZH}	2.5 V ± 0.2 V	Open	500 Ω	3.6 V	30 pF	0.15 V
	3.3 V ± 0.3 V	Open	500 Ω	5.5 V	50 pF	0.15 V



NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, $Z_o = 50 \,\Omega$, $t_i \leq 2.5 \,\mathrm{ns}$, $t_i \leq 2.5 \,\mathrm{ns}$.
- D. The outputs are measured one at a time, with one transition per measurement.
- E. $t_{\mbox{\tiny PLZ}}$ and $t_{\mbox{\tiny PHZ}}$ are the same as $t_{\mbox{\tiny dis}}.$
- F. t_{PZL} and t_{PZH} are the same as t_{en} .
- G. t_{PLH} and t_{PHL} are the same as t_{pd(s)}. The tpd propagation delay is the calculated RC time constant of the typical ON-state resistance of the switch nd the specified load capacitance, when driven by an ideal voltage source (zero output impedance).
- H. All parameters and waveforms are not applicable to all devices.

Figure 2. Test Circuit and Voltage Waveforms



SCDS319 – JUNE 2011 www.ti.com

TYPICAL CHARACTERISTICS





Figure 3. Data Output Voltage vs Data Input Voltage



www.ti.com SCDS319 – JUNE 2011

TYPICAL CHARACTERISTICS



OUTPUT VOLTAGE HIGH




Figure 4. V_{OH} Values

www.ti.com 11-Nov-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
CCB3T1G125QDCKRQ1	Active	Production	SC70 (DCK) 5	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	72R
CCB3T1G125QDCKRQ1.B	Active	Production	SC70 (DCK) 5	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	72R

⁽¹⁾ Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN74CB3T1G125-Q1:

Catalog: SN74CB3T1G125

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



PACKAGE OPTION ADDENDUM

www.ti.com 11-Nov-2025

NOTE: Qualified Version Definitions:

 $_{\bullet}$ Catalog - TI's standard catalog product

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Aug-2017

TAPE AND REEL INFORMATION





A0	<u> </u>
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CCB3T1G125QDCKRQ1	SC70	DCK	5	3000	180.0	8.4	2.47	2.3	1.25	4.0	8.0	Q3

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Aug-2017



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CCB3T1G125QDCKRQ1	SC70	DCK	5	3000	202.0	201.0	28.0



SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.
 3. Reference JEDEC MO-203.

- 4. Support pin may differ or may not be present.5. Lead width does not comply with JEDEC.
- 6. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

7. Publication IPC-7351 may have alternate designs.8. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 10. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025