
- Member of Texas Instruments' Widebus™
   Family
- 5-Ω Switch Connection Between Two Ports
- TTL-Compatible Input Levels
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II

#### description

The SN74CBT16861 provides 20 bits of high-speed TTL-compatible bus switching. The low on-state resistance of the switch allows connections to be made with minimal propagation delay.

The device is organized as one dual 10-bit switch with separate output-enable ( $\overline{OE}$ ) input. When  $\overline{OE}$  is low, the switch is on, and port A is connected to port B. When  $\overline{OE}$  is high, the switch is open, and the high-impedance state exists between the two ports.

# DGG, DGV, OR DL PACKAGE (TOP VIEW)



NC - No internal connection

#### ORDERING INFORMATION

| TA            | PACK        | AGE <sup>†</sup> | ORDERABLE<br>PART NUMBER | TOP-SIDE<br>MARKING |
|---------------|-------------|------------------|--------------------------|---------------------|
|               | SSOP – DL   | Tube             | SN74CBT16861DL           | CBT16861            |
| –40°C to 85°C | 330F = DL   | Tape and reel    | SN74CBT16861DLR          | CB110001            |
|               | TSSOP – DGG | Tape and reel    | SN74CBT16861DGGR         | CBT16861            |
|               | TVSOP - DGV | Tape and reel    | SN74CBT16861DGVR         | CY861               |

<sup>†</sup> Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

# FUNCTION TABLE (each 10-bit bus switch)

| INPUT<br>OE | FUNCTION        |
|-------------|-----------------|
| L           | A port = B port |
| Н           | Disconnect      |




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Widebus is a trademark of Texas Instruments.



### logic diagram (positive logic)



## absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

| Supply voltage range, V <sub>CC</sub>                    |               | $-0.5 \text{ V to 7 V}$ |
|--|---------------|-------------------------|
| Input voltage range, V <sub>I</sub> (see Note 1)         |               | $-0.5 \text{ V to 7 V}$ |
| Continuous channel current                               |               | 128 mA                  |
| Input clamp current, $I_{IK}$ ( $V_{I/O} < 0$ )          |               | –50 mA                  |
| Package thermal impedance, θ <sub>JA</sub> (see Note 2): | : DGG package | 70°C/W                  |
|  | DGV package   | 58°C/W                  |
|  | DL package    | 63°C/W                  |
| Storage temperature range, T <sub>stg</sub>              |               | –65°C to 150°C          |

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

## recommended operating conditions (see Note 3)

|                |                                  | MIN | MAX | UNIT |
|----------------|----------------------------------|-----|-----|------|
| Vcc            | Supply voltage                   | 4   | 5.5 | V    |
| VIH            | High-level control input voltage | 2   |     | V    |
| VIL            | Low-level control input voltage  |     | 0.8 | V    |
| T <sub>A</sub> | Operating free-air temperature   | -40 | 85  | °C   |

NOTE 3: All unused control inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.



<sup>2.</sup> The package thermal impedance is calculated in accordance with JESD 51-7.

# electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PAF                  | RAMETER        |  | MIN                          | TYP†                                   | MAX | UNIT |      |    |
|----------------------|----------------|--|------------------------------|--|-----|------|------|----|
| VIK                  |                | $V_{CC} = 4.5 \text{ V},$                                | I <sub>I</sub> = -18 mA      |  |     |      | -1.2 | V  |
| 1.                   |                | $V_{CC} = 0$ ,   | V <sub>I</sub> = 5.5 V       |  |     |      | 10   |    |
| l <sub>I</sub>       |                | $V_{CC} = 5.5 \text{ V},$                                | $V_I = 5.5 \text{ V or GND}$ |  |     |      | ±1   | μΑ |
| Icc                  |                | $V_{CC} = 5.5 \text{ V},$                                | $I_{O} = 0$ ,                | $V_I = V_{CC}$ or GND                  |     |      | 3    | μΑ |
| ∆lcc <sup>‡</sup>    | Control inputs | $V_{CC} = 5.5 \text{ V},$                                | One input at 3.4 V,          | Other inputs at V <sub>CC</sub> or GND |     |      | 2.5  | mA |
| Ci                   | Control inputs | $V_I = 3 V \text{ or } 0$                                |                              |  |     | 3    |      | pF |
| C <sub>io(OFF)</sub> | ı              | $V_0 = 3 \text{ V or } 0,$                               | OE = V <sub>CC</sub>         |  |     | 5.5  |      | pF |
|                      |                | $V_{CC} = 4 \text{ V},$<br>TYP at $V_{CC} = 4 \text{ V}$ | V <sub>I</sub> = 2.4 V,      | I <sub>I</sub> = 15 mA                 |     | 14   | 22   |    |
| ron§                 |                |  | V <sub>1</sub> = 0           | I <sub>I</sub> = 64 mA                 |     | 5    | 7    | Ω  |
| J                    |                | V <sub>CC</sub> = 4.5 V                                  | V <sub>I</sub> = 0           | I <sub>I</sub> = 30 mA                 |     | 5    | 7    |    |
|                      |                |  | V <sub>I</sub> = 2.4 V,      | I <sub>I</sub> = 15 mA                 |     | 10   | 15   |    |

<sup>†</sup> All typical values are at  $V_{CC} = 5 \text{ V}$  (unless otherwise noted),  $T_A = 25^{\circ}C$ .

# switching characteristics over recommended operating free-air temperature range (unless otherwise noted) (see Figure 1)

| PARAMETER         | FROM<br>(INPUT) | TO<br>(OUTPUT) | V <sub>CC</sub> = 4 V |      | V <sub>CC</sub> = 5 V<br>± 0.5 V |      | UNIT |
|-------------------|-----------------|----------------|-----------------------|------|----------------------------------|------|------|
|                   | (INFOT)         | (001701)       | MIN                   | MAX  | MIN                              | MAX  |      |
| t <sub>pd</sub> ¶ | A or B          | B or A         |                       | 0.35 |                                  | 0.25 | ns   |
| t <sub>en</sub>   | ŌĒ              | A or B         | 2.7                   | 6.3  | 1.7                              | 6.5  | ns   |
| <sup>t</sup> dis  | ŌĒ              | A or B         | 1.5                   | 8    | 1.8                              | 7.1  | ns   |


The propagation delay is the calculated RC time constant of the typical on-state resistance of the switch and the specified load capacitance, when driven by an ideal voltage source (zero output impedance).



<sup>&</sup>lt;sup>‡</sup> This is the increase in supply current for each input that is at the specified TTL voltage level rather than V<sub>CC</sub> or GND.

<sup>§</sup> Measured by the voltage drop between the A and B terminals at the indicated current through the switch. On-state resistance is determined by the lowest voltage of the two (A or B) terminals.

#### PARAMETER MEASUREMENT INFORMATION



NOTES: A. C<sub>L</sub> includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_{O} = 50 \Omega$ ,  $t_{r} \leq$  2.5 ns,  $t_{f} \leq$  2.5 ns.
- D. The outputs are measured one at a time with one transition per measurement.
- E. tpLz and tpHz are the same as tdis.
- F. tpzL and tpzH are the same as ten.
- G.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .

Figure 1. Load Circuit and Voltage Waveforms



www.ti.com 11-Nov-2025

#### PACKAGING INFORMATION

| Orderable part number | Status | Material type | Package   Pins   | Package qty   Carrier | RoHS | Lead finish/  | MSL rating/        | Op temp (°C) | Part marking |
|-----------------------|--------|---------------|------------------|-----------------------|------|---------------|--------------------|--------------|--------------|
|                       | (1)    | (2)           |                  |                       | (3)  | Ball material | Peak reflow        |              | (6)          |
|                       |        |               |                  |                       |      | (4)           | (5)                |              |              |
| SN74CBT16861DGGR      | Active | Production    | TSSOP (DGG)   48 | 2000   LARGE T&R      | Yes  | NIPDAU        | Level-1-260C-UNLIM | -40 to 85    | CBT16861     |
| SN74CBT16861DGGR.A    | Active | Production    | TSSOP (DGG)   48 | 2000   LARGE T&R      | Yes  | NIPDAU        | Level-1-260C-UNLIM | -40 to 85    | CBT16861     |
| SN74CBT16861DGVR      | Active | Production    | TVSOP (DGV)   48 | 2000   LARGE T&R      | Yes  | NIPDAU        | Level-1-260C-UNLIM | -40 to 85    | CY861        |
| SN74CBT16861DGVR.A    | Active | Production    | TVSOP (DGV)   48 | 2000   LARGE T&R      | Yes  | NIPDAU        | Level-1-260C-UNLIM | -40 to 85    | CY861        |
| SN74CBT16861DLR       | Active | Production    | SSOP (DL)   48   | 1000   LARGE T&R      | Yes  | NIPDAU        | Level-1-260C-UNLIM | -40 to 85    | CBT16861     |
| SN74CBT16861DLR.A     | Active | Production    | SSOP (DL)   48   | 1000   LARGE T&R      | Yes  | NIPDAU        | Level-1-260C-UNLIM | -40 to 85    | CBT16861     |

<sup>(1)</sup> Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

<sup>(2)</sup> Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

<sup>(4)</sup> Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 11-Nov-2025

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 24-Jul-2025

## TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width     |
|----|---|
| В0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

| Device           | Package<br>Type | Package<br>Drawing |    | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
|------------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| SN74CBT16861DGGR | TSSOP           | DGG                | 48 | 2000 | 330.0                    | 24.4                     | 8.6        | 13.0       | 1.8        | 12.0       | 24.0      | Q1               |
| SN74CBT16861DGVR | TVSOP           | DGV                | 48 | 2000 | 330.0                    | 16.4                     | 7.1        | 10.2       | 1.6        | 12.0       | 16.0      | Q1               |
| SN74CBT16861DLR  | SSOP            | DL                 | 48 | 1000 | 330.0                    | 32.4                     | 11.35      | 16.2       | 3.1        | 16.0       | 32.0      | Q1               |

www.ti.com 24-Jul-2025



## \*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74CBT16861DGGR | TSSOP        | DGG             | 48   | 2000 | 367.0       | 367.0      | 45.0        |
| SN74CBT16861DGVR | TVSOP        | DGV             | 48   | 2000 | 353.0       | 353.0      | 32.0        |
| SN74CBT16861DLR  | SSOP         | DL              | 48   | 1000 | 356.0       | 356.0      | 53.0        |

# DGV (R-PDSO-G\*\*)

#### **24 PINS SHOWN**

#### **PLASTIC SMALL-OUTLINE**



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.

D. Falls within JEDEC: 24/48 Pins – MO-153 14/16/20/56 Pins – MO-194





SMALL OUTLINE PACKAGE



### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
  4. Reference JEDEC registration MO-153.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



# DGG (R-PDSO-G\*\*)

# PLASTIC SMALL-OUTLINE PACKAGE

#### **48 PINS SHOWN**



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold protrusion not to exceed 0,15.

D. Falls within JEDEC MO-153

# DL (R-PDSO-G48)

# PLASTIC SMALL-OUTLINE PACKAGE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
- D. Falls within JEDEC MO-118

PowerPAD is a trademark of Texas Instruments.



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025