

SELECTABLE GTL VOLTAGE REFERENCE

FEATURES

- V_{DD} Range: 3.0 V to 3.6 V
 V_{TT} Range: 1 V to 1.3 V
- Provides Selectable GTL V_{REF}
 - 0.615 \times V_{TT}
 - 0.63 \times V_{TT}
 - 0.65 \times V_{TT}
 - 0.67 \times V_{TT}
- ±1% Resistor Ratio Tolerance
- Ambient Temperature Range: –40°C to 85°C
- ESD Protection Exceeds the Following Levels Tests (Tested Per JESD-22):
 - 2500-V Human-Body Model (A114-B, Class II)
 - 250-V Machine Model (A115-A)
 - 1500-V Charged-Device Model (C101)

DESCRIPTION/ORDERING INFORMATION

The SN74GTL3004 provides for a selectable GTL Voltage Reference (GTL V_{REF}). The value of the GTL V_{REF} can be adjusted using S0 and S1 select pins.

The S0 and S1 pins contain glitch-suppression circuitry for excellent noise immunity. When left floating, the S0 and S1 control input pins have $100-k\Omega$ pullups that set the GTL V_{REF} default value to the $0.67 \times V_{TT}$ ratio (S0 = 1 and S1 =1).

ORDERING INFORMATION

T _A	PACKAGE ⁽¹⁾	(2)	ORDERABLE PART NUMBER	TOP-SIDE MARKING	
–40°C to 85°C	SOT (SC70) - DCK	Tape and reel	SN74GTL3004DCKR	2TK	


- (1) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.
- (2) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



LOGIC DIAGRAM



FUNCTION TABLE

S1	S0	RATIO SET
0	0	$0.615 \times V_{TT}$
0	1	$0.63 \times V_{TT}$
1	0	$0.65 \times V_{TT}$
1	1	$0.67 \times V_{TT}$



ABSOLUTE MINIMUM AND MAXIMUM RATINGS(1)

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
V_{DD}	Power supply voltage range	-0.3	4.6	V	
V _{TT}	Termination voltage range ⁽²⁾	-0.3	4.6	V	
V _{IN}	Control input voltage range (2)	-0.3	$V_{DD} + 0.3$	V	
V _{GTL_REF}	Resistor output voltage range (2)	output voltage range ⁽²⁾		$V_{DD} + 0.3$	V
I _{IK}	Input clamp current	V _{IN} < 0		-18	mA
I _{OK}	Output clamp current	V _O < 0		-18	mA
	Continuous current through V _{DD} or GND			100	mA
θ_{JA}	Package thermal impedance ⁽³⁾	DCK package		259	°C/W
T _{stg}	Storage temperature range	-65	150	°C	

⁽¹⁾ Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

RECOMMENDED OPERATING CONDITIONS(1)

	PARAMETER	MIN	TYP	MAX	UNIT
V_{DD}	Power supply voltage	3	3.3	3.6	V
V_{TT}	Termination voltage	1	1.1	1.3	V
V _{IH}	High-level control input voltage	$V_{DD} \times 0.65$			V
V _{IL}	Low-level control input voltage			$V_{DD} \times 0.35$	V
V_{I}	Control input voltage	0		V_{DD}	V
I _{OUT}	I _{GTL_REF} , GTL_REF output current		0	10	μΑ
PW	Control input pulse width	110			ns
T _A	Operating free-air temperature	-40		85	°C

⁽¹⁾ All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow of Floating CMOS Inputs, literature number SCBA004.

ELECTRICAL CHARACTERISTICS

over recommended operating free-air temperature range, $T_A = -40$ °C to 85°C, $V_{DD} = 3.3$ V ±10%, GND = 0 V (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
V_{IK}	Control	$V_{DD} = 3.6 \text{ V}, I_{IN} = -18 \text{ mA}$			-1.8	V
I_{IN}	Control	$V_{DD} = 3.6 \text{ V}, V_{IN} = \text{GND}$			43	μΑ
I_{DD}		$V_{DD} = 3.6 \text{ V}, V_{IN} = \text{GND}, I_{O} = 0 \text{ mA}$			85	μΑ
R	End-to-end resistance	$V_{DD} = 3.6 \text{ V}, V_{TT} = 1.1 \text{ V}, I_{O} = 0 \text{ mA}$	4.25	7.12	10.6	kΩ
	GTL V _{REF} accuracy ⁽¹⁾	I _O = 0 μA, See Figure 1	-1		1	%
	GIL VREF accuracy	$I_O = 10 \mu A$, See Figure 1	-7		7	-/0

⁽¹⁾ GTL V_{REF} accuracy is used to compare measured GTL_VREF voltage versus expected GTL_VREF voltage as determined by control inputs S0 and S1. The resistor ratio tolerance is incorporated into this parameter.

SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range,, $T_A = -40^{\circ}\text{C}$ to 85°C, $V_{DD} = 3.3 \text{ V} \pm 10\%$, GND = 0 V (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
PSR	Power supply rejection			-58		dB
	Pulse rejection				40	ns

Product Folder Link(s): SN74GTL3004

⁽²⁾ The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

⁽³⁾ The package thermal impedance is calculated in accordance with JESD 51-7.



PARAMETER MEASUREMENT INFORMATION




Figure 1. GTL_REF Accuracy

www.ti.com 11-Nov-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking (6)
						(4)	(5)		
SN74GTL3004DCKR	Active	Production	SC70 (DCK) 6	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	2TK
SN74GTL3004DCKR.B	Active	Production	SC70 (DCK) 6	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	2TK

⁽¹⁾ Status: For more details on status, see our product life cycle.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

PACKAGE MATERIALS INFORMATION

www.ti.com 30-May-2024

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device		Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74GTL3004DCKR	SC70	DCK	6	3000	180.0	8.4	2.3	2.55	1.2	4.0	8.0	Q3

PACKAGE MATERIALS INFORMATION

www.ti.com 30-May-2024



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74GTL3004DCKR	SC70	DCK	6	3000	205.0	200.0	33.0



SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.

 4. Falls within JEDEC MO-203 variation AB.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale, TI's General Quality Guidelines, or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025