
# AMC1333M10 Evaluation Module



#### **ABSTRACT**

This user's guide describes the characteristics, operation, and use of the AMC1333M10EVM. A complete circuit description as well as a schematic diagram and bill of materials are included.

Throughout this document, AMC1333M10EVM is shortened to AMC1333EVM and the abbreviation *EVM* and the term *evaluation module* are synonymous with the AMC1333EVM.



AMC1333EVM



# **Table of Contents**

| 1 EVM Overview   | 3 |
|--|---|
| 1.1 Features   | 3 |
| 1.2 Introduction                                       | 3 |
| 2 Analog Interface                                     | 4 |
| 2.1 Analog Inputs                                      |   |
| 3 Digital Interface                                    |   |
| 4 Power Supplies and Device Operation                  |   |
| 4.1 AVDD and DVDD Inputs: J2 and J3                    |   |
| 4.2 Device Operation.                                  |   |
| 5 Layout, Bill of Materials, and Schematic             |   |
| 5.1 Printed Circuit Board Layout                       |   |
| 5.2 Bill of Materials.                                 |   |
| 5.3 Schematic  |   |
|  |   |
| List of Figures  |   |
| Figure 2-1. AMC1333EVM Schematic: Analog Input Section | 4 |
| Figure 3-1. Digital I/O Schematic                      |   |
| Figure 4-1. AVDD and DVDD Inputs                       |   |
| Figure 5-1. AMC1333EVM Silkscreen                      |   |
| Figure 5-2. AMC1333EVM Schematic                       |   |
|  |   |
| List of Tables   |   |
| Table 1-1. Related Documentation                       | 3 |
| Table 2-1. J1: Analog Inputs                           | 4 |
| Table 3-1. J4: AMC1333EVM Digital Output               | 5 |
| Table 5-1. Bill of Materials                           | 8 |

# **Trademarks**

All trademarks are the property of their respective owners.

www.ti.com EVM Overview

#### 1 EVM Overview

#### 1.1 Features

This EVM supports the following features:

- Full-featured evaluation board for the AMC1333 single-channel, delta-sigma modulator
- Screw terminals for the external AVDD and DVDD supplies
- · Screw terminals for easy access to the analog inputs and digital outputs

#### 1.2 Introduction

The AMC1333 is a 1-bit modulator with an output buffer separated from the input interface circuitry by a silicon dioxide (SiO2) isolation barrier. The isolation barrier provides galvanic isolation of up to 8000 V<sub>PEAK</sub>. When used in combination with a digital filter, the AMC1333 can be used to achieve 16-bit, analog-to-digital (A/D) conversion with no missing codes.

For use in high-resolution measurement applications, an effective accuracy of 14 bits can be obtained with a digital filter bandwidth of 20 kHz at a modulator rate of 10 MHz.

Table 1-1 lists the related documents available through the Texas Instruments web site at www.ti.com.

**Table 1-1. Related Documentation** 

| Document  | Literature Number |
|---|-------------------|
| AMC1333 data sheet  | SBASA71           |
| Comparing Isolated Amplifiers and Isolated Modulators technical white paper | SBAA359           |



# 2 Analog Interface

The analog input to the AMC1333EVM is routed from a three-wire screw terminal screw at J1. This screw terminal provides access to the inverting and noninverting inputs of the AMC1333.

# 2.1 Analog Inputs

The analog input to the AMC1333EVM board allows connection to AINP and AINN through an R/C filter with  $10-\Omega$  resistors (R5 and R6) and a 10-nF capacitor (C2). If filtering is not required, the C2 capacitor can be removed and the R5 and R6 resistors can be replaced with  $0-\Omega$  resistors.

The user optional resistor divider network that consists of R1, R2, and R3 is not populated by default. Populating this resistor divider network allows the user to select values of R1, R2, and R3 to generate a voltage across R3 for voltage sensing. Figure 2-1 shows an input circuit schematic for the AMC1333EVM and Table 2-1 lists the screw terminal connections.




Figure 2-1. AMC1333EVM Schematic: Analog Input Section

Table 2-1, J1: Analog Inputs

| Pin Number | Signal | Description                              |  |
|------------|--------|--|--|
| J1.1       | AINP   | Noninverting analog input to the AMC1333 |  |
| J1.2       | AINN   | AINN Inverting input to the AMC1333      |  |
| J1.3       | AGND   | Analog ground reference                  |  |

#### **CAUTION**

Carefully review the AMC1333 product data sheet for the limitations of the analog input range, and ensure that the appropriate analog and digital voltages are applied prior to connecting any analog input to the EVM. The EVM uses ±1 V for the AMC1333 and is not certified for high-voltage operation.

www.ti.com Digital Interface

# 3 Digital Interface

The AMC1333EVM digital input/output is a simple three-terminal screw connector located at J4. J4.2 is the output data from the modulator installed in location U1. As shown in Figure 3-1, pin 7 of U1 is the modulator clock output. The clock output can be monitored at J4.3 relative to J4.1. Figure 3-1 shows the digital I/O circuitry for the AMC1333EVM. Table 3-1 lists the digital output signals relative to J4.




Figure 3-1. Digital I/O Schematic

Table 3-1. J4: AMC1333EVM Digital Output

| Pin Number | Signal | Description                      |
|------------|--------|----------------------------------|
| J4.1       | DGND   | Digital ground reference         |
| J4.2       | DOUT   | Modulator bit stream data output |
| J4.3       | CLOCK  | Modulator clock                  |



# 4 Power Supplies and Device Operation

The AMC1333EVM requires two separate external power rails, AVDD and DVDD. AVDD is on the high voltage side of the modulator and DVDD is on the user side of the modulator.

# 4.1 AVDD and DVDD Inputs: J2 and J3

There are two screw terminals that allow external supplies to be connected. The J2 screw terminal allows the user to externally provide power to AVDD and the screw terminal J3 allows the user to externally provide power to DVDD. The AVDD supply must be between 3  $V_{DC}$  and 5.5  $V_{DC}$  and the DVDD supply must be between 3  $V_{DC}$  and 5  $V_{DC}$ . Figure 4-1 shows the input power scheme.




Figure 4-1. AVDD and DVDD Inputs

# 4.2 Device Operation

When the analog power supplies are applied to the AMC1333EVM, the digital outputs become active. The AMC1333 uses its own internal modulator clock. Screw terminal J4 has the connections as listed in Table 3-1.

An analog input signal can be applied directly at screw terminal J1; see Figure 2-1 and Table 2-1 for details. The linear analog input range, (VIN+) - (VIN-), is  $\pm 1 \text{ V}$  for the AMC1333.

For the AMC1333, when the input voltage approaches the maximum input level of +1 V, the 1's density of the modulator output approaches 92%. Likewise, when the input voltage approaches the lower limit of –1 V, the 1's density is approximately 8%.



# 5 Layout, Bill of Materials, and Schematic

This section contains the printed circuit board (PCB) layout, complete bill of materials (BOM), and schematic diagram for the AMC1333EVM.

#### Note

Board layouts are not to scale and are intended to show how the board is laid out. These graphics are not intended to be used for manufacturing AMC1333EVM PCBs.

# **5.1 Printed Circuit Board Layout**

Figure 5-1 shows the PCB layout for the AMC1333EVM.




Figure 5-1. AMC1333EVM Silkscreen



# 5.2 Bill of Materials

Table 5-1 shows the AMC1333EVM bill of materials (BOM).


# Table 5-1. Bill of Materials

| Designator                              | Description  | Manufacturer        | Mfg. PartNumber  GCM219R71C105KA37D |
|---|--|---------------------|-------------------------------------|
| C1, C7                                  | CAP, CERM, 1 μF, 16 V,+/- 10%,<br>X7R, AEC-Q200 Grade 1, 0805  | MuRata              |                                     |
| C2                                      | CAP, CERM, 0.01 uF, 16 V, +/-<br>10%, X7R, 0603  | Kemet               | C0603C103K4RACTU                    |
| C4, C8                                  | CAP, CERM, 10 µF, 50 V,+/- 10%,<br>X7R, AEC-Q200 Grade 1, 1206   | TDK                 | CGA5L1X7R1H106K160AE                |
| C5, C9                                  | CAP, CERM, 0.1 uF, 50 V, +/-<br>10%, X7R, 1206   | Yageo America       | CC1206KRX7R9BB104                   |
| C10, C11                                | CAP, CERM, 10 pF, 50 V, +/- 1%, C0G/NP0, 0603  | Kemet               | C0603C100F5GAC7867                  |
| J1, J4                                  | Terminal Block, 3.5mm Pitch, 3x1, TH   | On-Shore Technology | ED555/3DS                           |
| J2, J3                                  | Terminal Block, 3.5mm Pitch, 2x1, TH   | On-Shore Technology | OSTTE020161                         |
| LBL1                                    | Thermal Transfer Printable<br>Labels, 0.650" W x 0.200" H -<br>10,000 per roll                                   | Brady               | THT-14-423-10                       |
| R4                                      | RES, 0, 5%, 0.1 W, AEC-Q200<br>Grade 0, 0603   | Panasonic           | ERJ-3GEY0R00V                       |
| R5, R6                                  | 6 RES, 10.0, 0.1%, 0.1 W, 0603   |                     | CRT0603-BY-10R0ELF                  |
| R7, R8, R9 RES, 20.0, 0.1%, 0.1 W, 0603 |  | Yageo America       | RT0603BRD0720RL                     |
| P2, TP3 Terminal, Turret, TH, Double    |  | Keystone            | 1573-2                              |
| U1                                      | Small, High-Precision, Reinforced<br>Isolated Delta-Sigma Modulator<br>for Voltage Sensing Applications<br>SOIC8 | Texas Instruments   | AMC1333M10DWVR                      |
| C3, C6                                  | C6 CAP, CERM, 1000 pF, 16 V, +/-<br>10%, X7R, 0603   |                     |                                     |
| R1, R2, R3                              | RES, 10.2 k, 1%, 0.25 W, 1206  | Not Installed       |                                     |
| TP1 Terminal, Turret, TH, Double        |  | Not Installed       |                                     |



# 5.3 Schematic

Figure 5-2 shows the AMC1333EVM schematic.






Figure 5-2. AMC1333EVM Schematic

# IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated