

SN74AXC8T245 Evaluation Module

This user's guide describes the characteristics, operation, and use of the SN74AXC8T245EVM Evaluation Module (EVM). A complete printed-circuit board layout, schematic diagrams, and bill of materials are included in this document.

Contents

1	Introduction	2
2	Board Layout	8
3	Schematic and Bill of Materials	9

List of Figures

1	SN74AXC8T245EVM: 8-Channel PW Package	3
2	SN74AXC8T245EVM: 8, 4, 2, 1 Channel versions	4
3	SN74AXC8T245EVM Layout	8
4	EVM Schematic	9
5	One Channel	10
6	Two Channel	10
7	Four Channel	10
8	Eight Channel	11

List of Tables

1	SN74AXC8T245 Functional Table	2
2	EVM Package Options	5
3	Supported Devices	5
4	Pullup and Pulldown Resistors	7
5	SN74AXC8T245EVM Bill of Materials	12

Trademarks

All trademarks are the property of their respective owners.

1 Introduction

The SN74AXC8T245EVM helps evaluate the operation of the SN74AXC8T245 device belonging to the AXC direction-controlled translation family. The board is setup to also accommodate the AVC and LVC family of direction-controlled translation devices.

1.1 Features

The SN74AXC8T245 is a dual-supply bus transceiver with configurable voltage translation and an operating range from 0.65 V to 3.6 V. The A port is designed to track V_{CCA} . V_{CCA} accepts any supply voltage from 0.65 V to 3.6 V. The B port is designed to track V_{CCB} . V_{CCB} accepts any supply voltage from 0.65 V to 3.60 V. This device is fully specified for partial-power-down applications using I_{OFF} . The I_{OFF} circuitry disables the outputs, thus preventing damaging current backflow through the device when it is powered down. The V_{CC} isolation feature ensures that if either V_{CC} input is at ground, both A and B data I/O ports are in the high-impedance state. There are two direction control pins, each controlling 4 data I/Os enabling independent and simultaneous up and down translation. The DIR1 pin controls the direction of data I/O channels 1 through 4, and the DIR2 pin controls the direction of data I/O channels 5 through 8. The functional table of the SN74AXC8T245 is listed in [Table 1](#).

Table 1. SN74AXC8T245 Functional Table

OE	DIR1	DIR2	Signal Direction
H	X	X	Hi-Z
L	L	L	B to A
L	L	H	B{1:4} to A{1:4} and A{5:8} to B{5:8}
L	H	L	A to B
L	H	H	A{1:4} to B{1:4} and B{5:8} to A{5:8}




Figure 1. SN74AXC8T245EVM: 8-Channel PW Package




Figure 2. SN74AXC8T245EVM: 8, 4, 2, 1 Channel versions

The SN74AXC8T245EVM has the TSSOP (PW) package footprint, however, the device is also available in QFN (RHL) and Micro-QFN (RKT) packages. The various packages which the EVM supports are listed in [Table 2](#).

Table 2. EVM Package Options

Version	Package	Device Populated
One Channel	DCK	No
Two Channel	DCT	No
Four Channel	PW	No
Eight Channel	PW	Yes

The EVM is generically built and therefore it supports various devices as listed in [Table 3](#).

Table 3. Supported Devices

Version	Supported Devices	Order Samples
One Channel	SN74AVC1T45	SN74AVC1T45 samples
	SN74AVCH1T45	SN74AVCH1T45 samples
	SN74LVC1T45	SN74LVC1T45 samples
	SN74LVC1T45-Q1	SN74LVC1T45-Q1 samples
Two Channel	SN74AVC2T45-Q1	SN74AVC2T45-Q1 samples
	SN74LVC2T45-Q1	SN74LVC2T45-Q1 samples
	SN74AVC2T45	SN74AVC2T45 samples
	SN74AVCH2T45	SN74AVCH2T45 samples
	SN74LVC2T45	SN74LVC2T45 samples
Four Channel	SN74AVC4T245	SN74AVC4T245 samples
	SN74AVCH4T245	SN74AVCH4T245 samples
	SN74AVC4T245-Q1	SN74AVC4T245-Q1 samples
Eight Channel	SN74AXC8T245 (Installed)	SN74AXC8T245
	SN74AXCH8T245	SN74AXCH8T245 samples
	SN74AVC8T245	SN74AVC8T245 samples
	SN74AVCH8T245	SN74AVCH8T245 samples
	SN74LVC8T245	SN74LVC8T245 samples
	SN74LVCH8T245	SN74LVCH8T245 samples
	SN74LVC8T245-Q1	SN74LVC8T245-Q1 samples
	SN74AVC8T245-Q1	SN74AVC8T245-Q1 samples

1.2 Hardware Description

1.2.1 Headers

The EVM has standard 100-mil headers with the side closer to the device connected to ground. The side farther away from the device is mapped to the device pinout for easier connection as seen in [Figure 1](#). The silkscreen indicates the pin function.

1.2.2 Bypass Capacitors

C1, C3, C5, and C7 are the bypass capacitors for V_{CCA} while C2, C4, C6, and C8 are the bypass capacitors for V_{CCB} with a value of 0.1 μ F.

1.2.3 Pullup and Pulldown Resistors

The direction control and output enable pins are the inputs for the devices and should never be left floating. The CMOS inputs must be held at a known state, either V_{CC} or ground, to ensure proper device operation. Refer to *Implications of Slow or Floating CMOS Inputs* (SCBA004). The default state in the EVM is referenced to V_{CCA} using a 10-k Ω pull-up resistor. There is also the option of connecting the inputs to ground using pull-down resistors, or directly to ground via jumper on the header pins. *In order to enable the SN74AXC8T245EVM, connect a jumper on the OE pin to ground as shown in Figure 1.* In order to use the eight-channel version devices other than the SN74AXC8T245 (i.e SN74AVC8T245 / SN74LVC8T245), the pull-up resistor R10 must be removed and the jumper to the ground needs to be connected on DIR_GND8T.

Table 4 lists the pullup and pulldown resistors.

Table 4. Pullup and Pulldown Resistors

Device	Pin	Pullup	Pulldown
One Channel ⁽¹⁾	DIR	R3	R7
Two Channel ⁽²⁾	DIR	R6	R8
Four Channel ⁽³⁾	DIR1	R13	R25
	DIR2	R14	R26
	1OEN	R15	R27
	2OEN	R16	R28
Eight Channel (SN74AXC8T245 OR SN74AXCH8T245)	DIR1	R11	R30
	DIR2	R10	R29
	OEN	R9	R12

⁽¹⁾ One channel considering SN74AVC1T45 or SN74LVC1T45

⁽²⁾ Two channel considering SN74AVC2T45 or SN74LVC2T45

⁽³⁾ Four channel considering SN74AVC4T245

1.2.4 SMB Connectors

The edge-mounted SMB connector option is provided for each of the channel versions on data I/O pins of A1 and B1, respectively, for high-speed operation. One pair of SMB connector is installed on the A1 and B1 data I/O pair of the SN74AXC8T245 while the corresponding header pin has an uninstalled 0-Ω resistor R18 and R17. The data I/O pins A8, B8 also have the uninstalled SMB connector option with 0-Ω resistors to headers.

2 Board Layout

Figure 3 illustrates the EVM layout. Increase zoom level for clarity.





Figure 3. SN74AXC8T245EVM Layout

3 Schematic and Bill of Materials


3.1 Schematic

Figure 4 illustrates the EVM schematic. Increase the zoom level for clarity.




Copyright © 2017, Texas Instruments Incorporated

Figure 4. EVM Schematic




Copyright © 2017, Texas Instruments Incorporated

Figure 5. One Channel



Copyright © 2017, Texas Instruments Incorporated


Figure 6. Two Channel



Copyright © 2017, Texas Instruments Incorporated

Figure 7. Four Channel

8-CHANNEL



Copyright © 2017, Texas Instruments Incorporated

Figure 8. Eight Channel

3.2 Bill of Materials

Table 5 lists the EVM bill of materials.

Table 5. SN74AXC8T245EVM Bill of Materials

Designator	Qty	Value	Description	Package Reference	Part Number	Manufacturer
!PCB1	1		Printed Circuit Board		6607340	Any
C1, C2, C3, C4, C5, C6, C7, C8	8	0.1uF	CAP, CERM, 0.1 μ F, 16 V, +/- 10%, X7R, 0402	0402	0402YC104KAT2A	AVX
J1, J2	2		Header, 100mil, 3x2, Gold, TH	3x2 Header	TSW-103-07-G-D	Samtec
J3, J4, J10, J11, J13, J14	6		Header, 100mil, 4x2, Gold, TH	4x2 Header	TSW-104-07-G-D	Samtec
J9, J12, J15, J17	4		Header, 100mil, 6x2, Gold, TH	6x2 Header	TSW-106-07-G-D	Samtec
J21, J22	2		Connector, SMB Jack, End launch, SMT	SMB End launch Jack, SMT	131-3701-801	Emerson Network Power
R1, R2, R4, R5, R21, R22, R23, R24	8	0	RES, 0, 5%, 0.063 W, 0402	0402	ERJ-2GE0R00X	Panasonic
R3, R6, R9, R10, R11, R13, R14, R15, R16	9	10k	RES, 10 k, 5%, 0.063 W, 0402	0402	CRCW040210K0JNED	Vishay-Dale
U4	1		Asynchronous Communication Between Data Buses, PW0024A (TSSOP-24)	PW0024A	SN74AXC8T245PWR	Texas Instruments
J5, J6, J7, J8, J16, J18, J19, J20	0		Connector, SMB Jack, End launch, SMT	SMB End launch Jack, SMT	131-3701-801	Emerson Network Power
R7, R8, R12, R25, R26, R27, R28, R29, R30	0	10k	RES, 10 k, 5%, 0.1 W, 0603	0603	CRCW060310K0JNEA	Vishay-Dale
R17, R18	0	0	RES, 0, 5%, 0.063 W, 0402	0402	ERJ-2GE0R00X	Panasonic
U1	0		Single-Bit Dual-Supply Bus Transceiver with Configurable Voltage-Level Shifting DCK0006A (SOT-6)	DCK0006A	SN74AVC1T45DCKR	Texas Instruments
U2	0		Dual-Bit Dual-Supply Bus Transceiver with Configurable Voltage Translation, DCT0008A (SSOP-8)	DCT0008A	SN74AVC2T45DCTR	Texas Instruments
U3	0		4-Bit Dual-Supply Bus Transceiver with Configurable Voltage-Level Shifting, PW0016A (TSSOP-16)	PW0016A	SN74AVC4T245PWR	Texas Instruments

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated