

ALM2402-Q1 Functional Safety FIT Rate, FMD and Pin FMA



Table of Contents

| | |
|--|----|
| 1 Overview | 2 |
| 2 Functional Safety Failure In Time (FIT) Rates | 3 |
| 2.1 HTSSOP Package..... | 3 |
| 2.2 WSON Package..... | 4 |
| 3 Failure Mode Distribution (FMD) | 5 |
| 4 Pin Failure Mode Analysis (Pin FMA) | 6 |
| 4.1 HTSSOP Package..... | 7 |
| 4.2 WSON Package..... | 11 |

Trademarks

All trademarks are the property of their respective owners.

1 Overview

This document contains information for the ALM2402-Q1 (HTSSOP and WSON packages) to aid in a functional safety system design. Information provided are:

- Functional safety failure in time (FIT) rates of the semiconductor component estimated by the application of industry reliability standards
- Component failure modes and their distribution (FMD) based on the primary function of the device
- Pin failure mode analysis (pin FMA)

Figure 1-1 shows the device functional block diagram for reference.




Figure 1-1. Functional Block Diagram

The ALM2402-Q1 was developed using a quality-managed development process, but was not developed in accordance with the IEC 61508 or ISO 26262 standards.

2 Functional Safety Failure In Time (FIT) Rates

2.1 HTSSOP Package

This section provides functional safety failure in time (FIT) rates for the HTSSOP package of the ALM2402-Q1 based on two different industry-wide used reliability standards:

- [Table 2-1](#) provides FIT rates based on IEC TR 62380 / ISO 26262 part 11
- [Table 2-2](#) provides FIT rates based on the Siemens Norm SN 29500-2

Table 2-1. Component Failure Rates per IEC TR 62380 / ISO 26262 Part 11

| FIT IEC TR 62380 / ISO 26262 | FIT (Failures Per 10 ⁹ Hours) |
|------------------------------|--|
| Total component FIT rate | 12 |
| Die FIT rate | 4 |
| Package FIT rate | 8 |

The failure rate and mission profile information in [Table 2-1](#) comes from the reliability data handbook IEC TR 62380 / ISO 26262 part 11:

- Mission profile: Motor control from table 11
- Power dissipation: 300 mW
- Climate type: World-wide table 8
- Package factor (lambda 3): Table 17b
- Substrate material: FR4
- EOS FIT rate assumed: 0 FIT

Table 2-2. Component Failure Rates per Siemens Norm SN 29500-2

| Table | Category | Reference FIT Rate | Reference Virtual T _J |
|-------|---|--------------------|----------------------------------|
| 5 | CMOS, BICMOS Digital, analog, or mixed | 20 FIT | 55°C |

The reference FIT rate and reference virtual T_J (junction temperature) in [Table 2-2](#) come from the Siemens Norm SN 29500-2 tables 1 through 5. Failure rates under operating conditions are calculated from the reference failure rate and virtual junction temperature using conversion information in SN 29500-2 section 4.

2.2 WSON Package

This section provides functional safety failure in time (FIT) rates for the WSON package of the ALM2402-Q1 based on two different industry-wide used reliability standards:

- [Table 2-3](#) provides FIT rates based on IEC TR 62380 / ISO 26262 part 11
- [Table 2-4](#) provides FIT rates based on the Siemens Norm SN 29500-2

Table 2-3. Component Failure Rates per IEC TR 62380 / ISO 26262 Part 11

| FIT IEC TR 62380 / ISO 26262 | FIT (Failures Per 10 ⁹ Hours) |
|------------------------------|--|
| Total component FIT rate | 8 |
| Die FIT rate | 4 |
| Package FIT rate | 4 |

The failure rate and mission profile information in [Table 2-3](#) comes from the reliability data handbook IEC TR 62380 / ISO 26262 part 11:

- Mission profile: Motor control from table 11
- Power dissipation: 300 mW
- Climate type: World-wide table 8
- Package factor (λ_3): Table 17b
- Substrate material: FR4
- EOS FIT rate assumed: 0 FIT

Table 2-4. Component Failure Rates per Siemens Norm SN 29500-2

| Table | Category | Reference FIT Rate | Reference Virtual T _J |
|-------|---|--------------------|----------------------------------|
| 5 | CMOS, BICMOS Digital, analog, or mixed | 20 FIT | 55°C |

The reference FIT rate and reference virtual T_J (junction temperature) in [Table 2-4](#) come from the Siemens Norm SN 29500-2 tables 1 through 5. Failure rates under operating conditions are calculated from the reference failure rate and virtual junction temperature using conversion information in SN 29500-2 section 4.

3 Failure Mode Distribution (FMD)

The failure mode distribution estimation for the ALM2402-Q1 in [Table 3-1](#) comes from the combination of common failure modes listed in standards such as IEC 61508 and ISO 26262, the ratio of sub-circuit function size and complexity, and from best engineering judgment.

The failure modes listed in this section reflect random failure events and do not include failures resulting from misuse or overstress.

Table 3-1. Die Failure Modes and Distribution

| Die Failure Modes | Failure Mode Distribution (%) |
|---|-------------------------------|
| Output open (Hi-Z) | 20% |
| Output saturated high | 25% |
| Output saturated low | 25% |
| Output functional, out of specification voltage or timing | 30% |

4 Pin Failure Mode Analysis (Pin FMA)

This section provides a failure mode analysis (FMA) for the pins of the ALM2402-Q1 (HTSSOP and WSON packages). The failure modes covered in this document include the typical pin-by-pin failure scenarios:

- Pin short-circuited to ground (see [Table 4-2](#) and [Table 4-6](#).)
- Pin open-circuited (see [Table 4-3](#) and [Table 4-7](#))
- Pin short-circuited to an adjacent pin (see [Table 4-4](#) and [Table 4-8](#))
- Pin short-circuited to supply (see [Table 4-5](#) and [Table 4-9](#))

[Table 4-2](#) through [Table 4-9](#) also indicate how these pin conditions can affect the device as per the failure effects classification in [Table 4-1](#).

Table 4-1. TI Classification of Failure Effects

| Class | Failure Effects |
|-------|---|
| A | Potential device damage that affects functionality |
| B | No device damage, but loss of functionality |
| C | No device damage, but performance degradation |
| D | No device damage, no impact to functionality or performance |

Following are the assumptions of use and the device configuration assumed for the pin FMA in this section:

- Short circuit to Supply or Power means short to VCC
- Short to GND means short to VEE
- VCC_01 and VCC_02 are equivalent to VCC and GND is equivalent to VEE
- OTF/SH_DN pin is configured in such a state as to enable the amplifier

4.1 HTSSOP Package

Figure 4-1 shows the ALM2402-Q1 pin diagram for the HTSSOP package. For a detailed description of the device pins, see the *Pin Configuration and Functions* section in the ALM2402-Q1 data sheet.




Figure 4-1. Pin Diagram (HTSSOP) Package

Table 4-2. Pin FMA for Device Pins Short-Circuited to Ground

| Pin Name | Pin No. | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|--|----------------------|
| IN1- | 1 | Negative feedback not present to device. Depending on circuit configuration, output will most likely move to negative supply. | B |
| IN+ | 2 | Device common-mode tied to negative rail. Depending on circuit configuration, output will likely not respond due to the device being put in an invalid common-mode condition. | C |
| OTF | 3 | GND pin will be likely be driven to OTF voltage. the device will turn off. No damage to device. | B |
| INA2+ | 4 | Device common-mode tied to negative rail. Depending on circuit configuration, output will likely not respond due to the device being put in an invalid common-mode condition. | C |
| IN2- | 5 | Negative feedback not present to device. Depending on circuit configuration, output will most likely move to negative supply. | B |
| NC | 7 | NC pin internally disconnected; no effect. | D |
| NC | 8 | NC pin internally disconnected; no effect. | D |
| OUT2 | 9 | Depending on circuit configuration, the device will likely be forced into short circuit condition with OUT2 voltage ultimately forced to GND voltage. Prolonged exposure to short circuit conditions can result in long term reliability issues. | A |
| VCC | 10 | Op amp supplies will be shorted together leaving VCC pin at some voltage between VCC and GND sources (depending on source impedance). | A |
| VCC | 11 | Op amp supplies will be shorted together leaving VCC pin at some voltage between VCC and GND sources (depending on source impedance). | A |
| VCC | 12 | Op amp supplies will be shorted together, which leaves the VCC pin at some voltage between VCC and GND sources (depending on source impedance). | A |
| OUT1 | 13 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT1 voltage ultimately forced to GND voltage. Prolonged exposure to short circuit conditions can result in long term reliability issues. | A |

Table 4-3. Pin FMA for Device Pins Open-Circuited

| Pin Name | Pin No. | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|--|----------------------|
| IN1– | 1 | Inverting pin of op amp left floating. Negative feedback will not be provided to device, likely resulting in device output moving between positive and negative rail. IN1– pin voltage will likely end up at positive or negative rail due to leakage on ESD diodes. | B |
| IN+ | 2 | Input common-mode left floating. Op amp will not be provided with common-mode bias, device output will likely end up at positive or negative rail. IN1+ pin voltage will likely end up at positive or negative rail due to leakage on ESD diodes. | B |
| OTF | 3 | No damage to device, but OTF pin will be vulnerable to capacitive coupling and potential switching between shutdown and non-shutdown states. | B |
| IN2+ | 4 | Input common-mode left floating. Op amp will not be provided with common-mode bias, device output will likely end up at positive or negative rail. IN2+ pin voltage will likely end up at positive or negative rail due to leakage on ESD diodes. | B |
| IN2– | 5 | Inverting pin of op amp left floating. Negative feedback will not be provided to device, likely resulting in device output moving between positive and negative rail. IN2– pin voltage will likely end up at positive or negative rail due to leakage on ESD diodes. | B |
| GND | 6 | Negative supply left floating. Op amp will cease to function as no current can source/sink to the device. | B |
| NC | 7 | NC pin internally disconnected; no effect. | D |
| NC | 8 | NC pin internally disconnected; no effect. | D |
| OUT2 | 9 | No negative feedback or ability for OUT2 to drive application. | B |
| VCC | 10 | Positive supply left floating. Op amp will cease to function as no current can source/sink to the device. | A |
| VCC | 11 | Positive supply left floating. Op amp will cease to function as no current can source/sink to the device. | A |
| VCC | 12 | Positive supply left floating. Op amp will cease to function as no current can source/sink to the device. | A |
| OUT1 | 13 | No negative feedback or ability for OUT1 to drive application. | B |
| GND | 14 | Negative supply left floating. Op amp will cease to function as no current can source/sink to the device. | A |

Table 4-4. Pin FMA for Device Pins Short-Circuited to Adjacent Pin

| Pin Name | Pin No. | Shorted to | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|------------|--|----------------------|
| IN1- | 1 | 2 | Both inputs will be tied together. Depending on the offset of the device, this will likely move the output voltage near mid supply. | D |
| IN1+ | 2 | 3 | Device will toggle between shutdown or non-shutdown depending on OTF voltage. This is a 3.3V logic gate, so exceeding the ABS max ratings for current or voltage can damage the device. | A |
| OTF | 3 | 4 | Device will toggle between shutdown or non-shutdown depending on OTF voltage. This is a 3.3V logic gate, so exceeding the ABS max ratings for current or voltage can damage the device. | A |
| IN2+ | 4 | 5 | Both inputs will be tied together. Depending on the offset of the device, this will likely move the output voltage near mid supply. | D |
| IN2- | 5 | 6 | Negative feedback not present to device. Depending on circuit configuration, output will most likely move to negative supply. | B |
| GND | 6 | 7 | NC pin internally disconnected; no effect. | D |
| NC | 8 | 9 | NC pin internally disconnected; no effect. | D |
| OUT2 | 9 | 10 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT2 voltage ultimately forced to VCC voltage. Prolonged exposure to short circuit conditions can result in long term reliability issues. | A |
| VCC | 12 | 13 | Depending on circuit configuration, device will likely be forced into short circuit condition with VCC voltage ultimately forced to OUT1 voltage. Prolonged exposure to short circuit conditions can result in long term reliability issues. | A |
| OUT1 | 13 | 14 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT1 voltage ultimately forced to GND voltage. Prolonged exposure to short circuit conditions can result in long term reliability issues. | A |
| GND | 14 | 1 | Negative feedback not present to device. Depending on circuit configuration, output will most likely move to negative supply. | B |

Table 4-5. Pin FMA for Device Pins Short-Circuited to supply

| Pin Name | Pin No. | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|--|----------------------|
| IN1- | 1 | Negative feedback not present to device. Depending on non-inverting input voltage and circuit configuration, output will most likely move to negative supply. | B |
| IN1+ | 2 | Depending on circuit configuration, application will likely not function due to the device common-mode being connected to IN1+. | B |
| OTF | 3 | Device will be likely be enabled. This is a 3.3V logic gate, so exceeding the absolute maximum ratings for current or voltage can damage the device. | A |
| IN2+ | 4 | Depending on circuit configuration, application will likely not function due to the device common-mode being connected to IN2+. | B |
| IN2- | 5 | Negative feedback not present to device. Depending on non-inverting input voltage and circuit configuration, output will most likely move to negative supply. | B |
| GND | 6 | Op amp supplies will be shorted together leaving GND pin at some voltage between GND and VCC sources (depending on source impedance). | A |
| NC | 7 | NC pin internally disconnected; no effect. | D |
| NC | 8 | NC pin internally disconnected; no effect. | D |
| OUT2 | 9 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT2 voltage ultimately forced to VCC voltage. Prolonged exposure to short circuit conditions can result in long term reliability issues. | A |
| OUT1 | 13 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT1 voltage ultimately forced to VCC voltage. Prolonged exposure to short circuit conditions can result in long term reliability issues. | A |
| GND | 14 | Op amp supplies will be shorted together leaving GND pin at some voltage between GND and VCC sources (depending on source impedance). | A |

4.2 WSON Package

Figure 4-2 shows the ALM2402-Q1 pin diagram for the WSON package. For a detailed description of the device pins, see the *Pin Configuration and Functions* section in the ALM2402-Q1 data sheet.




Figure 4-2. Pin Diagram (WSON Package)

Table 4-6. Pin FMA for Device Pins Short-Circuited to Ground

| Pin Name | Pin No. | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|--|----------------------|
| IN1- | 1 | Negative feedback not present to device. Depending on circuit configuration, output will most likely move to negative supply. | B |
| IN+ | 2 | Device common-mode tied to negative rail. Depending on circuit configuration, output will likely not respond due to the device being put in an invalid common-mode condition. | C |
| OTF | 3 | GND pin will be likely be driven to OTF voltage. the device will turn off. No damage to device. | B |
| INA2+ | 4 | Device common-mode tied to negative rail. Depending on circuit configuration, output will likely not respond due to the device being put in an invalid common-mode condition. | C |
| IN2- | 5 | Negative feedback not present to device. Depending on circuit configuration, output will most likely move to negative supply. | B |
| OUT2 | 7 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT2 voltage ultimately forced to GND voltage. Prolonged exposure to short circuit conditions could result in long term reliability issues. | A |
| VCC | 8 | Op amp supplies will be shorted together leaving VCC pin at some voltage between VCC and GND sources (depending on source impedance). | A |
| VCC | 9 | Op amp supplies will be shorted together leaving VCC pin at some voltage between VCC and GND sources (depending on source impedance). | A |
| VCC | 10 | Op amp supplies will be shorted together leaving VCC pin at some voltage between VCC and GND sources (depending on source impedance). | A |
| OUT1 | 11 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT1 voltage ultimately forced to GND voltage. Prolonged exposure to short circuit conditions could result in long term reliability issues. | A |

Table 4-7. Pin FMA for Device Pins Open-Circuited

| Pin Name | Pin No. | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|--|----------------------|
| IN1- | 1 | Inverting pin of op amp left floating. Negative feedback will not be provided to device, likely resulting in device output moving between positive and negative rail. IN1- pin voltage will likely end up at positive or negative rail due to leakage on ESD diodes. | B |
| IN+ | 2 | Input common-mode left floating. Op amp will not be provided with common-mode bias, device output will likely end up at positive or negative rail. IN1+ pin voltage will likely end up at positive or negative rail due to leakage on ESD diodes. | B |
| OTF | 3 | No damage to device, but OTF pin will be vulnerable to capacitive coupling and potential switching between shutdown and non-shutdown states. | B |
| IN2+ | 4 | Input common-mode left floating. Op amp will not be provided with common-mode bias, device output will likely end up at positive or negative rail. IN2+ pin voltage will likely end up at positive or negative rail due to leakage on ESD diodes. | B |
| IN2- | 5 | Inverting pin of op amp left floating. Negative feedback will not be provided to device, likely resulting in device output moving between positive and negative rail. IN2- pin voltage will likely end up at positive or negative rail due to leakage on ESD diodes. | B |
| GND | 6 | Negative supply left floating. Op amp will cease to function as no current can source/sink to the device. | B |
| OUT2 | 7 | No negative feedback or ability for OUT2 to drive application. | B |
| VCC | 8 | Positive supply left floating. Op amp will cease to function as no current can source/sink to the device. | A |
| VCC | 9 | Positive supply left floating. Op amp will cease to function as no current can source/sink to the device. | A |
| VCC | 10 | Positive supply left floating. Op amp will cease to function as no current can source/sink to the device. | A |
| OUT1 | 11 | No negative feedback or ability for OUT1 to drive application. | B |
| GND | 12 | Negative supply left floating. Op amp will cease to function as no current can source/sink to the device. | A |

Table 4-8. Pin FMA for Device Pins Short-Circuited to Adjacent Pin

| Pin Name | Pin No. | Shorted to | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|------------|--|----------------------|
| IN1- | 1 | 2 | Both inputs will be tied together. Depending on the offset of the device, this will likely move the output voltage near mid supply. | D |
| IN1+ | 2 | 3 | Device will toggle between shutdown or non-shutdown depending on OTF voltage. This is a 3.3V logic gate, so exceeding the ABS max ratings for current or voltage could damage the device. | A |
| OTF | 3 | 4 | Device will toggle between shutdown or non-shutdown depending on OTF voltage. This is a 3.3V logic gate, so exceeding the ABS max ratings for current or voltage could damage the device. | A |
| IN2+ | 4 | 5 | Both inputs will be tied together. Depending on the offset of the device, this will likely move the output voltage near mid supply. | D |
| IN2- | 5 | 6 | Negative feedback not present to device. Depending on circuit configuration, output will most likely move to negative supply. | B |
| GND | 6 | 7 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT2 voltage ultimately forced to GND voltage. Prolonged exposure to short circuit conditions could result in long term reliability issues. | A |
| OUT2 | 7 | 8 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT2 voltage ultimately forced to VCC voltage. Prolonged exposure to short circuit conditions could result in long term reliability issues. | A |
| VCC | 10 | 11 | Depending on circuit configuration, device will likely be forced into short circuit condition with VCC voltage ultimately forced to OUT1 voltage. Prolonged exposure to short circuit conditions could result in long term reliability issues. | A |
| OUT1 | 11 | 12 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT1 voltage ultimately forced to GND voltage. Prolonged exposure to short circuit conditions could result in long term reliability issues. | A |
| GND | 12 | 1 | Negative feedback not present to device. Depending on circuit configuration, output will most likely move to negative supply. | |

Table 4-9. Pin FMA for Device Pins Short-Circuited to supply

| Pin Name | Pin No. | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|--|----------------------|
| IN1- | 1 | Negative feedback not present to device. Depending on non-inverting input voltage and circuit configuration, output will most likely move to negative supply. | B |
| IN1+ | 2 | Depending on circuit configuration, application will likely not function due to the device common-mode being connected to IN1+. | B |
| OTF | 3 | Device will be likely be enabled. This is a 3.3V logic gate, so exceeding the ABS max ratings for current or voltage could damage the device. | A |
| IN2+ | 4 | Depending on circuit configuration, application will likely not function due to the device common-mode being connected to IN2+. | B |
| IN2- | 5 | Negative feedback not present to device. Depending on non-inverting input voltage and circuit configuration, output will most likely move to negative supply. | B |
| GND | 6 | Op amp supplies will be shorted together leaving GND pin at some voltage between GND and VCC sources (depending on source impedance). | A |
| OUT2 | 7 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT2 voltage ultimately forced to VCC voltage. Prolonged exposure to short circuit conditions could result in long term reliability issues. | A |
| OUT1 | 11 | Depending on circuit configuration, device will likely be forced into short circuit condition with OUT1 voltage ultimately forced to VCC voltage. Prolonged exposure to short circuit conditions could result in long term reliability issues. | A |
| GND | 12 | Op amp supplies will be shorted together leaving GND pin at some voltage between GND and VCC sources (depending on source impedance). | A |

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated