

Speech and Sound Compression and Decompression With MSP430™ MCUs

MSP430 Applications

ABSTRACT

This document describes an IMA adaptive differential pulse code modulation (ADPCM) compression and decompression algorithm and the steps to use the ADPCM library on MSP430™ microcontrollers (MCUs). This document describes the use of the ADPCM library for two voice recorder examples that use the signal-chain-on-chip feature of the MSP430 MCUs.

Source code and sample files are available for download from <http://www.ti.com/lit/zip/slaa361>.

Contents

1	Introduction	2
2	Compression and Decompression Algorithms	2
	2.1 Differential Pulse Code Modulation (DPCM)	2
	2.2 Adaptive Differential Pulse Code Modulation (ADPCM)	4
3	Signal Chain on Chip in MSP430 MCUs	5
	3.1 MSP430F169 Signal-Chain-on-Chip Solution	5
	3.2 MSP430FG4618 Signal-Chain-on-Chip Solution	6
4	Performance on the MSP430 MCUs	7
	4.1 Using the Associated Code	7
5	References	8

List of Figures

1	DPCM Encoder and Decoder Block Diagram	2
2	Comparison of 8-Bit Audio Data and Difference of Successive Samples	3
3	ADPCM Encoder and Decoder Block Diagram	4
4	Signal-Chain-on-Chip Solution With MSP430F169	5
5	Signal-Chain-on-Chip Solution Using MSP430FG4618	6

Trademarks

MSP430 is a trademark of Texas Instruments.
IAR Embedded Workbench is a registered trademark of IAR Systems.
All other trademarks are the property of their respective owners.

1 Introduction

Sound recorders are implemented with relative ease on microcontrollers (MCUs) that have an integrated analog-to-digital converter (ADC). A microphone followed by an amplifier captures the sound, which is fed to the analog input of the ADC. The recorded sound can then be stored in memory (flash or RAM). A button press can trigger the MCU to play the recorded sound. To play the sound, software moves the stored data to a digital-to-analog converter (DAC) followed by an audio power amplifier.

Such a sound recorder can be easily realized using the MSP430 MCUs. The MSP430 MCU takes advantage of the integrated peripherals to form an on-chip analog signal chain. In addition, the CPU of the MSP430 is powerful enough to perform compression of the recorded sound.

This application report and the accompanying code uses the [MSP430FG4618 microcontroller](#) and the [MSP430F169 microcontroller](#) for demonstration purposes. The concepts and code in this application report apply to any MSP430 MCU that has at least one ADC input and a DAC.

2 Compression and Decompression Algorithms

The simplest way to make a voice recorder is to store the analog-to-digital conversion results (for example, 12-bit samples) directly in the flash memory. Most of the time, the audio data does not use the complete ADC range, which means that redundant information is stored in the flash memory. Compression algorithms remove this redundant information and reduce the data that must be stored.

Adaptive differential pulse code modulation (ADPCM) is a compression algorithm. Various ADPCM algorithms exist, all of which use differential codes and adaptation of the step-size of the quantizer. [Section 2.1](#) describes differential pulse code modulation (DPCM), and [Section 2.2](#) describes the IMA ADPCM algorithm, which is used in the associated code.

2.1 Differential Pulse Code Modulation (DPCM)

DPCM encodes the analog audio input signal based on the difference between the current sample and the previous sample. [Figure 1](#) shows a DPCM encoder and decoder block diagram. In this example, the signal difference, $d(n)$, is determined using a signal estimate, $Se(n)$, rather than the previous input. This method makes sure that the encoder uses the same information available to the decoder. If the true previous input sample were used by the encoder, an accumulation of quantization errors could occur. This accumulation would lead to a drift of the reconstructed signal from the original input signal. Use of the signal estimate in [Figure 1](#) prevents drift from the original input signal in the reconstructed signal, $Sr(n)$. The reconstructed signal, $Sr(n)$, is the input to the predictor, which determines the next signal estimate, $Se(n+1)$.





Figure 1. DPCM Encoder and Decoder Block Diagram

Figure 2 shows a small part of a recorded audio stream. Analog audio input samples (PCM values) and the differences between successive samples (DPCM values) are compared in the two diagrams.

The range of the PCM values is between 26 and 203, with a delta of 177 steps. The encoded DPCM values are within a range of -44 to 46, with a delta of 90 steps. Despite a quantizer step size of one, this DPCM encoding already shows a compression of the input data. The range of the encoded DPCM values could be further decreased by selecting a higher quantizer step size.



NOTE: Differential PCM Step Size = 1

Figure 2. Comparison of 8-Bit Audio Data and Difference of Successive Samples

2.2 Adaptive Differential Pulse Code Modulation (ADPCM)

ADPCM is a variant of DPCM that varies the quantization step size. Amplitude variations of speech input signals are seen between different speakers or between voiced and unvoiced segments of the speech input signal. The adaptation of the quantizer step size takes place every sample and ensures equal encoding efficiency for both low and high input signal amplitudes. Figure 3 shows the modified DPCM block diagram including the step-size adaptation.




Figure 3. ADPCM Encoder and Decoder Block Diagram

The ADPCM encoder calculates the signal estimate, (Se), by decoding the ADPCM code. This means that the decoder is part of an ADPCM encoder. Hence, the encoded audio data stream can only be replayed using the decoder. This means that the decoder must track the encoder.

The initial encoder and decoder signal estimate level, as well as the step-size adaptation level, must be defined before starting encoding or decoding. Otherwise, the encoded or decoded value could exceed the scale.

3 Signal Chain on Chip in MSP430 MCUs

The MSP430 microcontrollers offers a variety of on-chip peripherals. To complete a signal-chain-on-chip solution, the MSP430 MCU must have at least one analog input to the ADC and a DAC. [Section 3.1](#) and [Section 3.2](#) introduce solutions with two different MSP430 MCUs.

3.1 MSP430F169 Signal-Chain-on-Chip Solution

The MSP430F169 has an integrated 12-bit SAR ADC, a hardware multiplier module that allows efficient realization of digital filters, and an integrated 12-bit DAC module. [Figure 4](#) shows a signal chain circuit in the MSP430F169.




Figure 4. Signal-Chain-on-Chip Solution With MSP430F169

This configuration also works with an external serial flash memory, which could be used for storage of the audio data. It is possible to connect an external flash memory through the I²C or SPI interface of the MSP430 MCU. The CPU loading could be greatly reduced by using the MSP430F169 DMA module for automatic transfers of received data to RAM.

3.2 MSP430FG4618 Signal-Chain-on-Chip Solution

Another signal-chain-on-chip solution is possible with an MSP430FG4618. While the MSP430F169 has 60KB of integrated flash memory, the MSP430FG4618 has 116KB of flash memory. Another advantage of the MSP430FG4618 is the integrated operational amplifier module. These operational amplifiers can be used to amplify the microphone input and the analog output of the DAC. [Figure 5](#) shows the signal chain of the MSP430FG4618 solution. This is the configuration of the [MSP430FG4618/F2013 Experimenter Board](#). This evaluation board can be used with the associated code example.




Figure 5. Signal-Chain-on-Chip Solution Using MSP430FG4618

The output signal of the microphone is small and must be amplified. The MSP430 operational amplifiers can be used in different operating modes. Using the amplifier in PGA mode allows a maximum amplification of 15, which is not enough for the microphone amplifier. Additional gain is provided using external components, and operational amplifier OA0 in [Figure 5](#) is used in general-purpose amplifier mode. There are eight performance settings for the amplifiers to allow performance (gain-bandwidth product and slew rate) to be traded with current consumption. The example code uses high-performance mode (fast mode) for all amplifiers (OA0, OA1, and OA2).

For more information about the operational amplifier, refer to the [MSP430FG4618/F2013 Experimenter Board User's Guide](#).

The universal serial communication interface (USCI) could be used to store the audio data in an external flash memory. The connection to the external memory could be done either through an I²C bus or an SPI bus.

4 Performance on the MSP430 MCUs

The [associated code](#) includes "*.wav" file examples that show the quality of a decoded ADPCM data. Play these example files on media player software on the PC to compare them and hear the quality that is possible with an ADPCM compression algorithm. To improve the quality, increase the audio sample rate and optimize the audio sample size (resolution).

4.1 Using the Associated Code

The [associated code](#) includes two software projects. These two versions are based on the descriptions in [Section 3](#), and both use the IMA ADPCM algorithm.

The use of the ADPCM functions is simple. First, ADPCM.h must be included in the application code. This header file declares the ADPCM functions of the ADPCM.c file. Before each sequence of recording or replaying audio data, the ADPCM_Init() function must be called. This function defines the start values for the signal estimate (Se) and the step size pointer that is used for the quantizer step size adaptation. The encoder and decoder are synchronized by these settings. Encoding is realized by calling the ADPCM_Encoder(int value) function, and playback is realized by calling ADPCM_Decoder() for each audio sample. The following code segment shows how this could be done.

```
#include "ADPCM.h"

void main(void)
{
    // initialization of application software

    while(1)    // Main Loop
    {
        // application software
        if (P1IN & 0x01)
            record();
        if (P1IN & 0x02)
            play();
    }
}

void record(void)
{
    // initialization for recording (ADC, timer, amplifier, ...)
    ADPCM_Init();    // this is done before recording is started

    // start recording
}

void play(void)
{
    // initialization for recording (DAC, timer, amplifier, ...)
    ADPCM_Init();    // this is done before playback is started

    // start playback
}
```

The following measurements of the ADPCM function execution times were made with IAR Embedded Workbench® KickStart version 3.42A. The default optimization settings were used for the measurements.

ADPCM_Encoder() function call requires between 114 and 126 cycles.

ADPCM_Decoder() function call requires between 99 and 109 cycles.

These measurements include only the compression and decompression algorithms. Algorithms to record and play require additional code.

5 References

1. [MSP430x4xx Family User's Guide](#)
2. [MSP430F15x, MSP430F16x, MSP430F161x Mixed-Signal Microcontrollers](#)
3. [MSP430FG461x, MSP430CG461x Mixed-Signal Microcontrollers](#)
4. [A Low-Cost 12-Bit Speech CODEC Design Using the MSP430F13x](#)
5. [MSP430FG4618/F2013 Experimenter Board User's Guide](#)

Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from July 6, 2007 to August 24, 2018	Page
• Editorial and format changes throughout document	1
• Added the paragraph that begins "This application report and the accompanying code..." in Section 1, Introduction	2
• Updated Section 5, References	8

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated