# Maximizing the Full Potential of NTC Using BQ25180 Linear Charger



Juan Ospina

#### **ABSTRACT**

The Temperature Sensing (TS) function is a vital function for providing batteries charge and to operate within a safe temperature range. The BQ25180 provides a TS design as a current source that biases a resistor network with an NTC thermistor. Although the TS is designed to work with NTC of particular characteristics, external resistors extend the NTCs which can be used with the BQ25180. The External NTC Monitoring Calculator, which is available on the TI-Charger GUI, provides an easy means to check the configured application's expected TS behavior.

# **Table of Contents**

1 Temperature Sensing	2
1 Temperature Sensing	2
1.2 Current Driven TS Function	2
1.3 Calculating R <sub>S</sub> and R <sub>P</sub>	
2 BQ25180 and NTC Monitoring Calculator	
3 Example of TS Circuit Design	
4 References	8
List of Figures	
Figure 1-1. JEITA Charging Parameters	2
Figure 1-2. Typical Current Driven TS Application	3
Figure 2-1. Menu Logo	4
Figure 2-2. External NTC Monitoring (TS) Calculator Page View	
Figure 3-1. TS Thresholds Without Compensating Resistors	
Figure 3-2. TS Threshold with Compensating Resistors	
List of Tables	
Table 3-1. Equation Constants	6
Table 3-2. Expected JEITA Threshold Temperatures	6

### **Trademarks**

All trademarks are the property of their respective owners.

Temperature Sensing www.ti.com

# 1 Temperature Sensing

# 1.1 Temperature Sensing and JEITA Standard

Temperature sensing of the battery is a precautionary measure to maintain the battery within safe temperatures during the course of charging. Temperature sensing feature makes use of temperature sensitive resistivity to approximate and respond to battery temperatures while charging. For this purpose, many battery manufacturers incorporate a Negative Temperature Coefficient thermistor into the battery pack; for those battery packs that do not have a thermistor, we recommend including an external NTC alongside the battery pack.

The Japanese Electronics and Information Technology Industries Association (JEITA) guidelines for improving battery charging safety outline a series of battery temperature thresholds which can affect the charging parameters when crossed. These thresholds are typically defined as: cold temperatures below 0°C, cool temperatures below 10°C but above 0°C, warm temperatures above 45°C but below 60°C, and hot temperatures above 60°C. The prescribed behavior for the temperatures below the cold threshold and above the hot threshold is to cease charging until battery temperature has normalized. For battery temperatures in the cool and warm regions charge current and maximum charge voltage can be reduced. Different guidelines apply to different applications, we recommend checking the specific guidelines that apply to a given battery pack.




Figure 1-1. JEITA Charging Parameters

#### 1.2 Current Driven TS Function

The operation and configurability of the TS function varies from charger to charger. The BQ25180's TS function is implemented as a current driven TS sensing. This means that a fixed current source biases an external resistor network placed at the TS pin with  $I_{TS\_BIAS}$ . The NTC's temperature dependent resistance correlates the resistance, and therefore voltage, at the TS pin with the battery pack temperature. This voltage is then compared with a series of reference voltages to determine the temperature range within which the battery pack is operating. Although these reference voltages are tuned to work with NTC thermistors with a specific Beta ( $\beta$ ) and calibrated impedance, additional resistors can be placed to allow the use of NTCs with different  $\beta$  values and calibrated impedance with minimal error. The TS application is described in Figure 1-2.

www.ti.com Temperature Sensing




Figure 1-2. Typical Current Driven TS Application

## 1.3 Calculating R<sub>S</sub> and R<sub>P</sub>

The series resistor ( $R_S$ ) and parallel resistor ( $R_p$ ) can be calculated using a few formulas. The resistance of an NTC thermistor is governed by Equation 1:

$$\beta = \frac{\ln\left(\frac{R_{T1}}{R_{CAL}}\right)}{\left(\frac{1}{T_1} - \frac{1}{T_{CAL}}\right)} \tag{1}$$

 $R_{CAL}$  is the resistance of the thermistor calibrated at  $T_{CAL}$ , typically 25°C.  $\beta$  is given in terms of Kelvin so  $T_1$  and  $T_{CAL}$  are expressed in Kelvin. This equation allows us to calculate the thermistor resistance at different temperatures, notably at the HOT JEITA threshold of 60°C ( $R_H$ ) and at the COLD JEITA threshold 0°C ( $R_C$ ). The resistor network and bias current of the TS current source produce a voltage calculated by Equation 2:

$$V_{TS} = I_{TS BIAS}(R_P | | (R_S + R_{NTC}))$$
(2)

The charger data sheet provides voltage thresholds for the various JEITA temperature thresholds. These voltages, in place of  $V_{TS}$ , in Equation 2 allows the use of a system of equations to solve for the two variables needed to create our TS circuit:  $R_P$  and  $R_S$ . Because there are only have two variables to compensate the system with, only two JEITA thresholds can be met with total accuracy. Typically, HOT JEITA threshold ( $V_C$ ) are prioritized.

Using known values  $V_H$ ,  $V_C$ ,  $R_H$ , and  $R_C$ , as well as Equation 2, we create and provide a system of equations to derive Equation 3 and Equation 4 to calculate  $R_S$  and  $R_P$ .

$$R_{S} = \frac{-(R_{H} + R_{C}) \pm \sqrt{\left\{ (R_{H} + R_{C})^{2} - 4\left(R_{H} \times R_{C} + \frac{V_{H} \times V_{C}}{(V_{H} - V_{C}) \times I_{TS\_BIAS} \times (R_{C} - R_{H})\right)\right\}}}{2}}$$
(3)

$$R_P = \frac{V_H \times (R_H + R_S)}{I_{TS BIAS} \times (R_H + R_S) - V_H} \tag{4}$$



# 2 BQ25180 and NTC Monitoring Calculator

The BQ25180 implements a 38 uA current source for biasing the resistor network. The voltage thresholds are tuned to work with a thermistor with a  $\beta$  of 3435 that is calibrated to 10 k  $\Omega$  at 25°C. As mentioned before, external resistors can be used to allow the BQ25180 to work with other NTCs. Additionally, the BQ25180 allows for adjustable HOT and COLD voltage thresholds for applications which require different ranges. The COOL and WARM thresholds can selectively be disabled through I2C.

TI offers the *External NTC Monitoring (TS) Calculator* for the BQ25180 to facilitate configuration checking. This calculator can be accessed by selecting the calculator icon from the left menu bar on the BQ25180 TI Charger GUI page.




Figure 2-1. Menu Logo

The planned NTC's specifications can be entered as well as any calculated  $R_S$  values,  $R_P$  values, and register configurations. Once all configuration specifications have been entered, pressing the calculate button populates the outputs with the expected temperatures in Celsius at which the device is expected to enter and exit JEITA thresholds.






Figure 2-2. External NTC Monitoring (TS) Calculator Page View



# 3 Example of TS Circuit Design

If a BQ25180 used with a battery pack that includes an NTC with a calibrated resistance of 10 k  $\Omega$  and a beta value of 4250, the TS circuit will need to be compensated with additional resistors. Without additional resistors, using this NTC would cause the charger to enter the cold threshold at 5°C and enter the hot threshold at 52°C, thus significantly reducing the battery temperature range within which the charger can operate normally.




Figure 3-1. TS Thresholds Without Compensating Resistors

To calculate the necessary additional resistors, the following values are obtained from the BQ25180 data sheet or are calculated using Equation 1 and known thermistor values.

**Table 3-1. Equation Constants** 

V <sub>H</sub>	V <sub>C</sub>	I <sub>TS_BIAS</sub>	R <sub>H</sub> ( R <sub>NTC</sub> at 60°C)	R <sub>C</sub> ( R <sub>NTC</sub> at 0°C)
0.115 V	1.0075 V	38 μΑ	2.2 kΩ	36.8 kΩ

Using the values from the table to solve Equation 3 and Equation 4 we arrive at an  $R_s$  of 896  $\Omega$  and an  $R_P$  of 89 k $\Omega$ . With these resistors placed in the appropriate configuration, we achieve the following thresholds at the following temperature:

**Table 3-2. Expected JEITA Threshold Temperatures** 

V <sub>COLD</sub>	V <sub>COOL</sub>	V <sub>WARM</sub>	V <sub>HOT</sub>
0°C	10°C	44°C	60°C






Figure 3-2. TS Threshold with Compensating Resistors



# 4 References

- Texas Instruments, BQ25180 I2C Controlled, 1-Cell, 1-A Linear Battery Charger with Power Path and Ship Mode, data sheet.
- Texas Instruments, Li-ion Battery-Charger Solutions for JEITA Compliance, analog applications journal.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated