



ABSTRACT

This report presents the effect of neutron displacement damage (NDD) on the TL1431-SP device. The results show that all devices were fully functional and within production test limits after having been irradiated up to 1×10^{12} n/cm². A sample size of nine units were exposed per MIL-STD-883, Method 1017 for Neutron Irradiation, and three additional devices were used as control units. Electrical testing was performed before and after neutron irradiation using the production test program for the TL1431-SP.

Table of Contents

1 Overview.....	2
2 Test Procedures.....	3
3 Facility.....	4
4 Results.....	4
5 Data Sheet Electrical Parameters and Associated Tests.....	5
A Appendix: Test Results.....	6

List of Figures

Figure 2-1. TL1431-SP Device (Front).....	3
Figure 2-2. TL1431-SP Device (Back).....	3

List of Tables

Table 1-1. Overview Information.....	2
Table 2-1. Neutron Irradiation Conditions.....	3

Trademarks

All trademarks are the property of their respective owners.

1 Overview

The TL1431-SP is a precision programmable reference with specified thermal stability over automotive, commercial, and military temperature ranges. The output voltage can be set to any value between VI(ref) (approximately 2.5 V) and 36 V with two external resistors. This device has a typical output impedance of 0.2 Ω. Active output circuitry provides a very sharp turnon characteristic, making the device an excellent replacement for Zener diodes and other types of references in applications such as onboard regulation, adjustable power supplies, and switching power supplies.

Table 1-1. Overview Information

NDD Details	
TI Part Number	TL1431-SP
Device Name	5962R9962001VHA
Device Function	Programmable reference
Technology	JI SLM
Assembly Lot Number	2006815MTT
Unbiased Quantity Tested	9
Exposure Facility	VPT Rad
Neutron Fluence (1-MeV equivalent)	1.0×10^{12} , 5.0×10^{12} , 1.0×10^{13} n/cm ²
Irradiation Temperature	Room temperature
TI may provide technical, applications or design advice, quality characterization, and reliability data or service providing these items shall not expand or otherwise affect TI's warranties as set forth in the Texas Instruments Incorporated Standard Terms and Conditions of Sale for Semiconductor Products and no obligation or liability shall arise from Semiconductor Products and no obligation or liability shall arise from TI's provision of such items.	

2 Test Procedures

The TL1431-SP was electrically pre- and post-tested using the production automated test equipment program.

General test procedures adhered to MIL-STD-883, Method 1017 for Neutron Irradiation of TL1431-SP. Neutron irradiation conditions are listed in [Table 2-1](#).

Table 2-1. Neutron Irradiation Conditions

Group	Sample Qty	Neutron Fluence (n/cm^2)	Bias
A	3	1.0×10^{12}	Unbiased
B	3	5.0×10^{12}	Unbiased
C	3	1.0×10^{13}	Unbiased



Figure 2-1. TL1431-SP Device (Front)




Figure 2-2. TL1431-SP Device (Back)

3 Facility

VPT Rad performs all neutron displacement damage irradiation in a Low-Enriched, open-pool, water moderated, thermal neutron reactor. It utilizes flat-plate type fuel, and having a maximum thermal energy output of up to 1 MW. The Fast Neutron Irradiator (FNI) faces one side of the reactor core. The design produces a geometrical planar beam of fast neutrons that is approximately uniform over an area of 12 in \times 20 in. Lead and thermal neutron absorbing compounds are combined to filter out both fission gammas and thermal neutrons. The ratio of fast-to-thermal neutrons is approximately 400:1, with a gamma exposure of less than 150 rad (Si) for a 1E12 n/cm² (1 MeV Si equivalent) exposure. The FNI can accommodate a sample or samples with size up to 30 cm in diameter and 15-cm thick including packaging materials. The minimum neutron fluence rate is 1E6 n/cm²-s. The maximum neutron fluence rate is approximately 1.0 E11 n/cm²-s. (both values are 1 MeV Si equivalent).

The neutron fluence rate is determined using the previously-measured neutron radiation field for the FNI, performed in accordance with ASTM standards (ASTM F1190), and correlated to the measured reactor power level. The neutron dose is timed to meet the customer-specified fluence for the irradiation. Neutron dosimetry meets ASTM standards (ASTM E265). The facility retains source-suitability with the Defense Logistics Agency (DLA) Laboratory Suitability Program for ASTM Test Method 1017. The devices under test are typically irradiated in an unbiased condition as per TM1017.

4 Results

There were no functional failures up to 1×10^{12} n/cm². The devices exposed to 5×10^{12} n/cm² and 1×10^{13} n/cm² were no longer functional. [Section 5](#) lists the parameters. [Appendix A](#) shows the related data.

5 Data Sheet Electrical Parameters and Associated Tests

at specified free-air temperature, $I_{KA} = 10 \text{ mA}$ (unless otherwise noted)

Parameter		Test Conditions	T_A ⁽²⁾	Min	Typ	Max	Unit	Test Numbers
$V_{I(\text{ref})}$	Reference input voltage	$VKA = VI(\text{ref})$	25°C	2475	2500	2540	mV	
			Full range	2460		2550		7.0
$V_{I(\text{dev})}$	Deviation of reference input voltage over full temperature range ⁽³⁾	$VKA = VI(\text{ref})$	Full range		17	55 ⁽¹⁾	mV	
$\Delta V_{I(\text{ref})}/\Delta V_{KA}$	Ratio of change in reference input voltage to the change in cathode voltage	$\Delta VKA = 3 \text{ V to } 36 \text{ V}$	Full range		-1.1	-2	mV/V	16.0
$I_{I(\text{REF})}$	Reference input current	$R1 = 10 \text{ k}\Omega, R2 = \infty$	25°C		1.5	2.5	μA	
			Full range			5		15.2
$I_{I(\text{dev})}$	Deviation of reference input current over full temperature range ⁽³⁾	$R1 = 10 \text{ k}\Omega, R2 = \infty$	Full range		0.5	3 ⁽¹⁾	μA	
I_{\min}	Minimum cathode current for regulation	$VKA = VI(\text{ref})$	25°C		0.45	1	mA	11.0
I_{off}	Off-state cathode current	$VKA = 36 \text{ V}, VI(\text{ref}) = 0$	25°C		0.18	0.5	μA	
			Full range			2		2.0
$ Z_{KA} $	Output impedance ⁽⁴⁾	$VKA = VI(\text{ref}), f \leq 1 \text{ kHz}, I_{KA} = 1 \text{ mA to } 100 \text{ mA}$	Full range		0.2	0.4	Ω	14.1

1. On products compliant to MIL-PRF-38535, this parameter is not production tested.
2. Full range is -55°C to $+125^{\circ}\text{C}$.
3. The deviation parameters $VI(\text{dev})$ and $II(\text{dev})$ are defined as the differences between the maximum and minimum values obtained over the rated temperature range. For more details, see the device data sheet.
4. Please see device data sheet for details on output impedance.


A Appendix: Test Results

This appendix contains the detailed NDD test results.


NDD Report

TL1431-SP

7.0 __VREF @ VZ=VREF IZ=10MA				
Test Site	MTT	MTT		
Tester	LTX	LTX		
Test Number	XPM16108	XPM16108		
Unit	V	V		
Max Limit	2.55	2.55		
Min Limit	2.475	2.475		
N/cm ²	Serial #	Pre	Post	Delta
0	105	2.505	2.505	0.000
0	106	2.496	2.496	0.000
0	107	2.516	2.516	0.000
1E+12	415	2.502	2.507	0.005
1E+12	416	2.498	2.503	0.005
1E+12	417	2.507	2.513	0.007
Max		2.516	2.516	0.007
Average		2.504	2.507	0.003
Min		2.496	2.496	0.000
Std Dev		0.007	0.007	0.003




7.0 __VREF @ VZ=VREF IZ=10MA		
Test Site	MTT	
Tester	LTX	
Test Number	XPM16108	
Max Limit	2.55	V
Min Limit	2.475	V
N/cm ²	0	1E+12
LL	2.475	2.475
Min	2.496	2.503
Average	2.506	2.508
Max	2.516	2.513
UL	2.550	2.550




NDD Report

TL1431-SP

11.0 _IKA MIN WITH VREF AND				
Test Site	MTT	MTT		
Tester	LTX	LTX		
Test Number	XPM16108	XPM16108		
Unit	µA	µA		
Max Limit	1000	1000		
Min Limit	0.01	0.01		
N/cm ²	Serial #	Pre	Post	Delta
0	105	443.338	445.284	1.947
0	106	451.456	455.194	3.737
0	107	430.426	435.108	4.682
1E+12	415	442.310	443.191	0.881
1E+12	416	445.932	446.502	0.569
1E+12	417	439.419	443.450	4.030
Max		451.456	455.194	4.682
Average		442.147	444.788	2.641
Min		430.426	435.108	0.569
Std Dev		7.032	6.473	1.742




11.0 _IKA MIN WITH VREF AND		
Test Site	MTT	
Tester	LTX	
Test Number	XPM16108	
Max Limit	1000	µA
Min Limit	0.01	µA
N/cm ²	0	1E+12
LL	0.010	0.010
Min	435.108	443.191
Average	445.195	444.381
Max	455.194	446.502
UL	1000.000	1000.000




NDD Report

TL1431-SP

14.1 ZKA = DELTA V / DELTA				
Test Site	MTT	MTT		
Tester	LTX	LTX		
Test Number	XPM16108	XPM16108		
Unit				
Max Limit	0.4	0.4		
Min Limit	-0.4	-0.4		
N/cm ²	Serial #	Pre	Post	Delta
0	105	-0.006	0.049	0.055
0	106	-0.007	0.021	0.027
0	107	0.002	0.062	0.060
1E+12	415	0.024	0.290	0.266
1E+12	416	0.015	0.051	0.036
1E+12	417	-0.038	0.176	0.215
Max		0.024	0.290	0.266
Average		-0.001	0.108	0.110
Min		-0.038	0.021	0.027
Std Dev		0.022	0.104	0.103




14.1 ZKA = DELTA V / DELTA		
Test Site	MTT	
Tester	LTX	
Test Number	XPM16108	
Max Limit	0.4	
Min Limit	-0.4	
N/cm ²	0	1E+12
LL	-0.400	-0.400
Min	0.021	0.051
Average	0.044	0.173
Max	0.062	0.290
UL	0.400	0.400




NDD Report

TL1431-SP

15.2 __REFERENCE INPUT CURREN				
Test Site	MTT	MTT		
Tester	LTX	LTX		
Test Number	XPM16108	XPM16108		
Unit	µA	µA		
Max Limit	5	5		
Min Limit	0.01	0.01		
N/cm ²	Serial #	Pre	Post	Delta
0	105	0.892	0.914	0.022
0	106	0.969	0.942	-0.027
0	107	0.968	0.917	-0.051
1E+12	415	0.951	1.089	0.138
1E+12	416	1.001	1.125	0.124
1E+12	417	0.959	1.091	0.132
Max		1.001	1.125	0.138
Average		0.957	1.013	0.056
Min		0.892	0.914	-0.051
Std Dev		0.036	0.099	0.086




15.2 __REFERENCE INPUT CURREN				
Test Site	MTT			
Tester	LTX			
Test Number	XPM16108			
Max Limit	5	µA		
Min Limit	0.01	µA		
N/cm ²	0	1E+12		
LL	0.010	0.010		
Min	0.914	1.089		
Average	0.924	1.102		
Max	0.942	1.125		
UL	5.000	5.000		




NDD Report

TL1431-SP

16.0 __DELTA VKA				
Test Site	MTT	MTT		
Tester	LTX	LTX		
Test Number	XPM16108	XPM16108		
Unit	mV	mV		
Max Limit	-0.01	-0.01		
Min Limit	-2	-2		
N/cm ²	Serial #	Pre	Post	Delta
0	105	-0.707	-0.712	-0.006
0	106	-0.697	-0.708	-0.011
0	107	-0.709	-0.717	-0.008
1E+12	415	-0.721	-0.799	-0.078
1E+12	416	-0.725	-0.802	-0.076
1E+12	417	-0.695	-0.775	-0.080
Max		-0.695	-0.708	-0.006
Average		-0.709	-0.752	-0.043
Min		-0.725	-0.802	-0.080
Std Dev		0.012	0.045	0.038



16.0 __DELTA VKA		
Test Site	MTT	
Tester	LTX	
Test Number	XPM16108	
Max Limit	-0.01	mV
Min Limit	-2	mV
N/cm ²	0	1E+12
LL	-2.000	-2.000
Min	-0.717	-0.802
Average	-0.712	-0.792
Max	-0.708	-0.775
UL	-0.010	-0.010



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2023, Texas Instruments Incorporated