

Filename: PMP1941_REVB_bom.xls					
Date: 07/24/2006					
PMP1941_REVB BOM					
COUNT	RefDes	Description	Size	MFR	Part Number
1	C6	Capacitor, Ceramic, 0.01uF, 16V, X7R	603	TDK	Std
1	C13	Capacitor, Ceramic, 0.022uF, 25V, X7R	603	TDK	Std
1	C25	Capacitor, Ceramic, 0.047uF, 25V, X5R, 20%	603	TDK	Std
6	C17, C19, C20, C22, C33, C38	Capacitor, Ceramic, 0.1uF, 16V, X7R, 15%	603	TDK	Std
3	C3, C29, C32	Capacitor, Ceramic, 0.1uF, 50V, X7R, 15%	603	TDK	Std
1	C36	Capacitor, Ceramic, 1000pF, 50V, X7R	603	TDK	Std
2	C11, C26	Capacitor, Ceramic, 100-pF, 50-V, NPO, 15%	603	TDK	Std
4	C14, C15, C23, C28	Capacitor, Ceramic, 1uF, 16V, X7R	603	TDK	Std
1	C16	Capacitor, Ceramic, 220pF, 50V, NPO, 5%	603	TDK	Std
1	C37	Capacitor, Ceramic, 2700-pF, 25-V, NPO, 15%	603	TDK	Std
1	C30	Capacitor, Ceramic, 27pF, 50-V, NPO, 15%	603	TDK	Std
1	C24	Capacitor, Ceramic, 3300pF, 25V, X7R, 15%	603	TDK	Std
1	C39	Capacitor, Ceramic, 330-pF, 50-V, X7R, 15%	603	TDK	Std
1	C21	Capacitor, Ceramic, 390pF, 50V, NPO, 15%	603	TDK	Std
1	C31	Capacitor, Ceramic, 4700-pF, 25V, X7R, 15%	603	TDK	Std
1	C35	Capacitor, Ceramic, 47pF, 50-V, NPO, 15%	603	TDK	Std
2	C5, C8	Capacitor, Ceramic, 0.1uF, 100V, X7R, 20%	1206	TDK	C3216X7R2A104M
2	C4, C7	Capacitor, Ceramic, 0.47uF, 100V, X7R, 20%	1206	TDK	C3216X7R2A474M
1	C34	Capacitor, Ceramic, 22uF, 6.3V, X5R, 20%	1206	TDK	C3216X5R0J226M
1	C12	Capacitor, Alum, 10uF, 35V, 0.7 Ohms, 20%	0.201"x0.262"	Panasonic	EEEFK1V100R
1	C100	Capacitor, Alum, 220uF, 6.3V, 0.36 Ohms, ±20%	0.260"x0.276"	Panasonic	EEVFK0J221P
5	C1, C2, C9, C10, C27	Capacitor, Alum, 330uF, 35V, 0.85Arms, 20%	0.457"x0.406"	Panasonic	EEVFK1V331P
1	D3	Diode, Rectifier, 1A, 600V	SMA	Diodes Inc.	US1J
1	D1	Diode, Rectifier, 1A, 800V	SMA	Diodes Inc.	US1K
2	D5, D12	Diode, Rectifier, 50V, 1A	SMB	Diodes Inc.	B150B
1	D8	Diode, Schottky, 3-A, 60-V	SMC	Diodes Inc.	B360
4	D4, D7, D13, D100	Diode, Switching, 100-V, 200-mA, 225-mW,	SOD-123	On Semi	MMSD914T1
1	D2	Diode, Zener, 12V, 20mA	SOD123	On Semi	MMSZ5242BT1
1	D9	Diode, Zener, 15V, 350-mW	SOT-23	Diodes, Inc.	BZX84C15LT1
1	D11	Diode, Zener, 20V, 350-mW	SOT-23	Diodes, Inc.	BZX84C20LT1
1	D10	Diode, Zener, 30V, 350-mW	SOT-23	Diodes, Inc.	BZX84C30LT1
1	D6	Diode, Zener, 8.2V, 20mA	SOD123	On Semi	MMSZ5237BT1
1	L1	Inductor, SMT, 5.28A, 10.2 milliohm	0.300 sq"	Coiltronics	DR73-1R0
1	L2	Inductor, SMT, 330uH, 1.06A, 482 milliohm	0.492 sq"	Coiltronics	DR125-331
5	Q1, Q2, Q8, Q10, Q12	Bipolar, NPN, 40V, 200mA, 0.3W	SOT23	Diodes Inc.	MMBT3904
3	Q3, Q5, Q7	Bipolar, PNP, 40V, 200mA, 0.3W	SOT23	Diodes Inc.	MMBT3906
1	Q4	MOSFET, N-ch, 60V, 8.5A, 22 milliohm	SO8	Vishay	Si4850EY
1	Q6	MOSFET, P-ch, -60V, 19A, 60 milliohms	DPAK	Vishay	SUD19P06-60L
1	Q9	MOSFET, P-ch, -60-V, 3.5-A, 120-milliOhms	SO8	Vishay	Si9407AEY
1	R40	Resistor, Chip, 0-Ohms, 1/16-W, 1%	603	Std	Std
4	R4, R5, R6, R7	Resistor, Chip, 10 Ohms, 1/16W, 1%	603	Std	Std
4	R19, R32, R41, R49	Resistor, Chip, 100K-Ohms, 1/16-W, 1%	603	Std	Std
8	R8, R9, R10, R11, R26, R31, R54, R56	Resistor, Chip, 10K Ohms, 1/16W, 1%	603	Std	Std
1	R51	Resistor, Chip, 16.2K-Ohms, 1/16-W, 1%	603	Std	Std
5	R15, R25, R34, R39, R44	Resistor, Chip, 1K Ohms, 1/16W, 1%	603	Std	Std
1	R17	Resistor, Chip, 2.32K Ohms, 1/16W, 1%	603	Std	Std
1	R37	Resistor, Chip, 200K-Ohms, 1/16-W, 1%	603	Std	Std

3	R14, R47, R58	Resistor, Chip, 20K Ohms, 1/16W, 1%	603	Std	Std
1	R38	Resistor, Chip, 274K Ohms, 1/16W, 1%	603	Std	Std
1	R30	Resistor, Chip, 3.01K Ohms, 1/16W, 1%	603	Std	Std
1	R16	Resistor, Chip, 3.3 Ohms, 1/16W, 1%	603	Std	Std
1	R12	Resistor, Chip, 31.6K Ohms, 1/16W, 1%	603	Std	Std
1	R43	Resistor, Chip, 4.75K Ohms, 1/16W, 1%	603	Std	Std
4	R13, R24, R35, R100	Resistor, Chip, 4.99K Ohms, 1/16W, 1%	603	Std	Std
1	R46	Resistor, Chip, 432K Ohms, 1/16W, 1%	603	Std	Std
2	R28, R50	Resistor, Chip, 49.9 Ohms, 1/16W, 1%	603	Std	Std
2	R21, R29	Resistor, Chip, 5.11K Ohms, 1/16W, 1%	603	Std	Std
2	R22, R42	Resistor, Chip, 51.1K-Ohms, 1/16-W, 1%	603	Std	Std
1	R48	Resistor, Chip, 732K Ohms, 1/16W, 1%	603	Std	Std
1	R18	Resistor, Chip, 75.0K Ohms, 1/16W, 1%	603	Std	Std
1	R36	Resistor, Chip, 0.05 Ohm, 1/10W, 5%	805	Std	Std
1	R2	Resistor, Chip, 2.49KOhms, 1/10-W	805	Std	Std
1	R1	Resistor, Chip, 4.99KOhms, 1/10-W	805	Std	Std
1	R3	Resistor, Chip, 2.49K, 1/8W, 5%	1206	Std	Std
1	R33	Resistor, Chip, 10K, 1/2W, 5%	2010	Std	Std
1	R53	Resistor, Chip, 2.49K, 1W, 5%	2512	STD	STD
1	R27	Resistor, Chip, 0.2 Ohm, 1W, 5%	2512	STD	STD
1	T1	Transformer, Flyback	0.856"x0.677"	TDK	DCT15EFD-UXXS0A5
1	U1	IC, BiCmos, Current Mode, PWM Controller	SO8	Texas Instruments	UCC28C41D
1	U2	IC, Dual Op Amp, 2-36 Vin	TSSOP-8	Texas Instruments	LM2904AVQPWRQ1
1	U3	IC, High Input Voltage, 50 mA LDO, Adj	SOP-5 (DCK)	Texas Instruments	TPS71501DCKR
1	U4	IC, Low Cost Sync Buck Controller	SO-8	Texas Instruments	TPS40200D
1	U5	IC, Voltage Supervisor, Adj	SOP-5 (DCK)	Texas Instruments	TPS3803-01DCK
MISC					
1	J1	Terminal Block, 3-pin, 6-A, 3.5mm	0.41"x 0.25"	OST	ED1515
4	J2, J6, J7, J100	Header, 2-pin, 2mm spacing (36-pin strip)	0.079 x 2	NorComp	2136-36-01-P2
1	J3	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25	OST	ED1514
2	J4, J5	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25	OST	ED1514
1	C18	Capacitor, Ceramic, open	603	TDK	Std
4	R20, R23, R45, R52	Resistor, Chip, open	603	Std	Std
12	TP1, TP2, TP4, TP6, TP8, TP9, TP10, TP11, TP12, TP15, TP16, TP17	Test Point, Red, Thru Hole Color Keyed	0.100"x0.100"	Keystone	5000
6	TP3, TP5, TP7, TP13, TP14, TP18	Test Point, Black, Thru Hole Color Keyed	0.100"x0.100"	Keystone	5001

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video
Wireless	www.ti.com/wireless-apps

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated