

# ***TMS320VC5503 Hardware Designer's Resource Guide***

*DSP Hardware Application Team*

## **ABSTRACT**

The DSP Hardware Designer's Resource Guide is organized by development flow and functional areas to make your design effort as seamless as possible. Topics covered include getting started, board design, system testing, and checklists to aid in your initial design and debug efforts. Each section includes pointers to valuable information including technical documentation, models, symbols, and reference designs for use in each phase of design. Particular attention is given to peripheral interfacing and system level design concerns.

## **Contents**

<b>1</b>	<b>Getting Started</b> .....	<b>2</b>
1.1	Registering on my.TI .....	2
1.2	Training and Support .....	2
1.3	Technical Documentation .....	2
1.3.1	Where to Start .....	2
1.3.2	Using TI Literature Numbers .....	2
1.3.3	Technical Publication Descriptions .....	3
1.3.4	Peripheral Reference Guides .....	3
1.3.5	Application Reports .....	4
<b>2</b>	<b>Board Design and Layout</b> .....	<b>4</b>
2.1	Reference Design .....	4
2.2	Schematics .....	4
2.3	Signal Integrity and Timing Considerations .....	5
2.4	Board Layout .....	5
2.5	Power Supply and Sequencing Considerations .....	5
2.6	Power/Thermal Management Considerations .....	5
2.7	Boot Mode Configurations .....	5
2.8	Joint Test Action Group (JTAG) Emulation Interface .....	6
2.9	Board Manufacturing .....	6
<b>3</b>	<b>System Test</b> .....	<b>6</b>
3.1	Boundary Scan Description Language (BSDL) Model(s) .....	6
<b>4</b>	<b>Checklists</b> .....	<b>7</b>
4.1	Design Checklist .....	7
4.2	Debug Checklist .....	9
4.2.1	Peripherals Debug Tips .....	9
<b>5</b>	<b>Summary</b> .....	<b>13</b>

Trademarks are the property of their respective owners.

# 1 Getting Started

## 1.1 Registering on my.TI

my.TI is a customizable area within the Texas Instruments web site. By registering on my.TI, you can receive the following benefits:

- Quick Reference to information you select as part of your profile.
- Email alerts that inform you of updates to products, technical documentation, and errata.
- The my.TI newsletter providing information on the latest innovations and product releases.

To register on my.TI for updates related to the this device:

1. Go to the device product folder.
2. Select the link called “ADD To my.TI” in the upper right hand corner, and follow the on-screen instructions.
3. Select Customize my.TI to specify what you would like to receive notification about.

Use the following link to access the product folder.

[TMS320VC5503 DSP product folder](#)

## 1.2 Training and Support

Texas Instruments offers a variety of training options tailored for your specific needs and requirements. Options include on-line training, webcasts, seminars, single and multi-day workshops, and conferences. For more information about training, visit Texas Instruments [Training Home](#). For assistance with technical questions regarding TI Semiconductor products and services, you can access the [Semiconductor Technical Support KnowledgeBase](#).

## 1.3 Technical Documentation

### 1.3.1 *Where to Start*

The key area for obtaining documentation for this device is the product folder. When getting started, it is of great importance to have the latest data sheet and silicon errata. Often, a “Getting Started with” or “How to Begin Development with” application report is available as well. Listed below are links to this key information:

- [TMS320VC5503 DSP product folder](#)
- [TMS320VC5503 Fixed-Point Digital Signal Processor \(SPRS245\)](#)
- [C55x CPU Programmer’s Reference Supplement \(SPRU652\)](#)
- [TMS320VC5503 Digital Signal Processor Silicon Errata \(SPRZ218\)](#)

### 1.3.2 *Using TI Literature Numbers*

All TI documentation is assigned a literature number. This number can be used to search for the document on the Web. Technical documentation revisions are indicated by the alpha character at the end of the literature number on the title page, and in the file name.

Use the literature number (without the trailing alpha character) to search the TI website for the document. For example, if a data manual has a literature number of SPRS205B, the "B" indicates the revision of the document. If the document has no trailing alpha character, it is the original version of the document. When searching for this document on the TI web site, you can simply enter "SPRS205" as the search keyword.

### **1.3.3 Technical Publication Descriptions**

This section describes the content contained in technical publications which support this device. All of the technical publications described below can be found in the device product folder. Check your device product folder frequently for the most recent technical documentation.

#### **Data Sheets and Data Manuals**

The Data Sheet or Data Manual is the functional specification for the device. Topics covered in this document include but are not limited to the following:

- High-level functional overview
- Pinouts and packaging information
- Signal descriptions
- Device-specific information about peripherals and registers
- Electrical specifications

#### **Silicon Errata**

The Silicon Errata documents exceptions to the functional specification as defined in the Data Sheet or Data Manual.

#### **Reference Guides**

Reference Guides provide additional information describing the architecture and operation of hardware components of the DSP platform, generation, or device, beyond the scope of the Data Sheet or Data Manual.

#### **Application Reports**

Application Reports are written to describe implementation details specific to a device, peripheral, use of technology, or explanation of usage.

### **1.3.4 Peripheral Reference Guides**

Each peripheral has a reference guide that provides beneficial information for completing a design. Each peripheral and its respective reference guide is listed here. There are two categories. The first category contains peripherals which connect directly to external devices. The second category lists the internal peripherals.

**Peripherals that connect directly to external devices:**

- [TMS320VC5501/5502/5503/5507/5509/5510 DSP \(McBSP\) Reference Guide \(SPRU592\)](#)
- [TMS320VC5501/5502/5503/5507/5509 DSP Inter-Integrated Circuit \(I2C\) Module Reference Guide \(SPRU146\)](#)
- [TMS320VC5503/5507/5509 DSP External Memory Interface \(EMIF\) Reference Guide \(SPRU670\)](#)
- [TMS320VC5503/5507/5509 DSP Host Port Interface \(HPI\) Reference Guide \(SPRU619\)](#)
- [TMS320VC5503/5507/5509/5510 DSP Timers Reference Guide \(SPRU595\)](#)

**Internal peripherals:**

- [TMS320C55x DSP Peripherals Overview Reference Guide \(SPRU317\)](#)
- [TMS320VC5503/5507/5509 DSP Real-Time Clock \(RTC\) Reference Guide \(SPRU594\)](#)
- [TMS320VC5503/5507/5509/5510 Direct Memory Access\(DMA\) Controller Reference Guide \(SPRU587\)](#)

### 1.3.5 *Application Reports*

Organized by category and listed below are application reports that provide useful information for designing on this device.

**Inter-Integrated Circuit (I2C) Interface:**

- [Programming the TMS320VC5509 I2C Peripheral \(SPRA785\)](#)

## 2 Board Design and Layout

### 2.1 Reference Design

A reference design is not currently available for this device.

### 2.2 Schematics

This section includes ORCAD symbols to assist you in schematic generation. The method chosen to provide the ORCAD symbols is a multi-section or “heterogeneous” package. The logical parts in the package have different graphics, numbers of pins, or properties. This allows the schematic designer to easily connect the various parts on separate schematic pages and yet retain the same reference designator for the part across all schematic pages.

Some peripherals may use multiplexed pins. When pins are shared, one peripheral will be enabled and the other will be disabled. Please refer to the data manual for more information concerning multiplexed pins.

The ORCAD symbols are currently not available for this device.

## 2.3 Signal Integrity and Timing Considerations

High-speed interfaces require strict timings and accurate system design. To achieve the necessary timings for a given system, input/output buffer information specification (IBIS) models must be used. These models accurately represent the device drivers under various process conditions. Board characteristics, such as impedance, loading, length, number of nodes, etc., affect signal performance. IBIS models are not currently available for this device.

The following application report discusses how to use IBIS models for timing analysis:

[Using IBIS Models for Timing Analysis \(SPRA839\)](#)

## 2.4 Board Layout

The significance of electromagnetic compatibility (EMC) of electronic circuits and systems has recently been increasing. This increase has led to more stringent requirements for the electromagnetic properties of equipment. Two property aspects are of interest: the ability of a circuit to generate the lowest (or zero) interference, and the immunity of a circuit to the effects of the electromagnetic energy it is subjected to. The effects on electronic circuits and systems is well documented, but little attention has been paid to circuit behavior and the interference it generates. The following link discusses the important criteria that determine the EMC of a circuit.

[Printed-Circuit Board Layout for Improved Electromagnetic Compatibility \(SDYA011\)](#).

## 2.5 Power Supply and Sequencing Considerations

Texas Instruments offers several [Power Management Products](#) for this device. For a complete list of product offerings, visit the [power.ti.com](http://power.ti.com) website.

## 2.6 Power/Thermal Management Considerations

Circuit designers must always consider the effects of heat transfer from a device die to the surrounding package. The flow of heat from the device to ambient must be sufficient to maintain the device temperature as specified in the device data manual. The thermal resistance characteristics for this device are documented in the data manual.

## 2.7 Boot Mode Configurations

The TMS320VC5503 provides an on-chip bootloader and supports the following boot modes:

- EHPI boot (in multiplexed or non-multiplexed mode)
- EMIF boot (from 8-bit or 16-bit asynchronous memory)
- Direct execution from external 16-bit asynchronous memory
- Standard serial port boot from McBSP0 (with 8-bit or 16-bit word size)
- Serial SPI EEPROM boot from McBSP0 (with 16-bit or 24-bit addresses)
- I2C boot

The desired boot mode is selected by the state of the BOOTM pins at reset. These pins have a shared function with GPIO pins. For information on the operation of the bootloader, see the document:

[Using the TMS320VC5503/VC5507/VC5509/VC5509A Bootloader \(SPRA375\)](#)

## 2.8 Joint Test Action Group (JTAG) Emulation Interface

DSP devices have a JTAG interface that allows for emulation hardware and software to communicate with the DSP. The JTAG port also supports boundary scan testability. Listed below are links to this key information.

- [Emulation Fundamentals for TI DSP Solutions \(SPRA439\)](#)
- [60-pin Emulation Header Technical Reference \(SPRU655\)](#)

## 2.9 Board Manufacturing

When designing with a high-density BGA package, it is important to be aware of different techniques that aid in the quality of manufacturing. The following documentation discusses board manufacturing considerations:

- [High-Density Design With MicroStar™ BGAs \(SPRA471\)](#)
- [Electrostatic Discharge \(SSYA008\)](#)

# 3 System Test

## 3.1 Boundary Scan Description Language (BSDL) Model(s)

BSDL models can be used to perform board interconnect tests as well as other board level diagnostics and functions. Boundary scan tests require that each scan device on the board be described in the Boundary Scan Description Language (BSDL) model. Depending on the available silicon, more than one BSDL model may be available. The BSDL models are not yet available for this device.

## 4 Checklists

### 4.1 Design Checklist

The Design Checklist was put together by Texas Instruments application and field support staff as a guide to considerations made during the design phase of development. Use this check list to keep track of considerations you make during the design phase of development.

	Issue	Description
<input type="checkbox"/>	Clean power supplies	Noisy power supplies can create several problems in your system. Power supplies should conform to the specification in the DSP data manual and voltage ripple and switching noise should be minimized. Voltage ripple of less than 20 mV is recommended.
<input type="checkbox"/>	Decoupling capacitors	Decoupling capacitors provide power stability during current load transients and also help shunt system switching noise to ground instead of entering the logic inside the DSP. Decoupling capacitors should be placed as near the DSP package as possible.
<input type="checkbox"/>	RESET	It is important to be able to reset the DSP if it gets into an unstable state. It may be useful to provide a reset switch on the board to facilitate this during debug. Power supervisors also can trigger a reset if the system power supplies fall below a predefined level. For more information on power supervisors, see <a href="http://power.ti.com">power.ti.com</a> . Note that while RESET is low, the emulator will not initialize.
<input type="checkbox"/>	Bootmode Selection Pins (BOOTM)	Check to make sure the BOOTM pins are configured correctly for the desired boot mode. For debug purposes, it may be useful to provide the ability to change the BOOTM pins, such as using jumpers instead of hardwired connections.
	IO4 Visibility	IO4 is used by the bootloader for different purposes depending on the boot mode chosen. It is very useful during bootloader debug to have the ability to monitor IO4. Consider bringing IO4 to a via or test point where it can be observed using an oscilloscope or logic analyzer.
<input type="checkbox"/>	EMU0 and EMU1 pins high when unused	EMU0 and EMU1 are pins used by the emulator to communicate with the DSP. After debug, when the emulator is no longer in use and disconnected, it is essential that these pins are driven high. On the TMS320VC5503, internal pull-ups are provided on these two pins. You should ensure that nothing else in your design pulls down these pins when the emulator is not connected.
<input type="checkbox"/>	Do not pull-up TRST	TRST is the reset signal for the JTAG Test Access Port internal logic. This pin has an internal pull-down circuit inside the DSP. TRST should not be pulled up externally since the opposing circuits will pull the pin to an intermediate voltage and cause unpredictable behavior of the device.
<input type="checkbox"/>	CLKOUT	Even if CLKOUT is not being used in the design, it may be useful to bring CLKOUT to a test point for debug purposes. It is useful to verify PLL settings and behavior.

<input type="checkbox"/>	Unused EMIF ARDY signal should remain high	If the ARDY pin is not controlled by an external device, the board should be designed such that the ARDY is always driven high. If ARDY is uncontrolled, this can cause unpredictable behavior of the EMIF or cause the emulator to fail to initialize.
<input type="checkbox"/>	EMIF CE space(s) configuration	<p>The external memory space is divided into 4 spaces, each selected by a DSP signal CE0 –CE3. Each space is configured for a particular memory type in software. Some memory types also have timing controls that are configurable through software. Verify that the software configuration for each space is correct.</p> <p>Use of some SDRAM configurations requires that multiple CE spaces be used. The following CE spaces may be linked together in SDRAM mode depending on the configuration:</p> <p>CE0 and CE1, or CE2 and CE3, or CE0, CE1, CE2 and CE3</p> <p>If these configurations are used, all of the associated CE spaces must be configured as SDRAM. For more information, see the <i>TMS320VC5503/5507/5509 DSP External Memory Interface (EMIF) Reference Guide (SPRU670)</i>.</p>
<input type="checkbox"/>	EHPI timings	Verify that all EHPI timings are met as specified in the data manual. Incorrect timings can cause data errors and unpredictable operation of the EHPI.
<input type="checkbox"/>	Route peripheral signals to test points / vias	It may be useful to route the signals for the peripherals used to test points or vias on the board so they can be observed during debug. This assists in comparing the signals entering/leaving the peripheral with the desired send/receive data.
<input type="checkbox"/>	General Signal Visibility	If space allows, the more signals that are accessible, the easier the system will be to debug. At a minimum, signals can be routed to vias that are accessible from the top or bottom of the board. For other parallel and serial interfaces, it can be useful to have the buses routed to connectors that can be used with a logic analyzer. Once the design debug is completed, the connectors can be omitted from the final build of the board.
<input type="checkbox"/>	GPIO availability	<p>General-purpose I/O pins are very useful during debug. They can be used as indicators within the code to verify the progression of the algorithm. Even if some GPIO pins are not being used in the final design, consider bringing some of them out to vias or connectors on the board for debug purposes. GPIOs connected to LEDs provide very convenient observation tools during debug.</p> <p>XF is a dedicated general-purpose output controlled by the CPU. The other GPIOs are controlled as peripherals and have longer latency. XF responds within approximately one cycle of the execution of the instruction that modified it.</p> <p>GPIOs respond within approximately six cycles of the execution of the instruction that modified them.</p>

<input type="checkbox"/>	Controlling unused interrupts	Unused interrupt pins should be driven high. If left floating, noise coupled onto these pins can cause spurious interrupts to occur. Although most interrupts are maskable so these false interrupts could be masked in software, NMI is not maskable and cannot be prevented. It is good design practice to pull up any unused interrupt pin.
<input type="checkbox"/>	Timer Output Pin	Although the TMS320VC5503 supports two on-chip timers, only TIMER0 has an external pin on the device package. If the use of the timer requires, the function of the TIN/TOUT0 pin, this function should be assigned to Timer0. Internal timer operations can be performed on either Timer0 or Timer 1.

## 4.2 Debug Checklist

### 4.2.1 Peripherals Debug Tips

**Table 1. Power**

Issue		Description
<input type="checkbox"/>	Higher than expected idle power	The connection of the emulator to the JTAG header can increase a device power measurement. This can be due to current flow through the PD pin and due to the current generated on the DSP by the presence of TCK running. Power measurements on a final application should be made with the emulation cable disconnected.
<input type="checkbox"/>	Higher than expected idle power	If the McBSP remains enabled and operating, it can prevent the CLKGEN domain from idling because it still requires a clock. For minimum idle power, the McBSP should be placed in reset.
<input type="checkbox"/>	Higher than expected idle power	If an external oscillator is used as a clock source instead of a crystal (and the internal oscillator), the input clock provided to the DSP will not stop when all of the DSP domains are idled (standby). The clock input buffer on the DSP continues to toggle and consume some power even though the clocks to the rest of the DSP are disabled.
<input type="checkbox"/>	Higher than expected idle power	If the standby power (all domains disabled) is higher than expected and it is observed that the internal oscillator is still running, the oscillator has not been configured to idle correctly. See <a href="#">Disabling the Internal Oscillator With External Crystal on the TMS320VC5509 DSP (SPRA078)</a> for the correct procedure.
<input type="checkbox"/>	Idle mode changes	After the Idle Configuration Register (ICR) is modified (written), approximately six CPU clock cycles are required for the internal write to be completed. So an Idle instruction intended to use the new configuration should follow the ICR write by no less than six cycles. The instructions in between can be NOPs or other useful instructions that do not modify ICR.

**Table 2. Crystal Oscillator**

Issue		Description
<input type="checkbox"/>	Crystal startup problems	Startup problems can occur if the crystal is physically placed far away from the DSP on the board (due to additional resistance and parasitic effects). Place the crystal as close as possible to the DSP in the design layout. Use the recommended values for the load capacitors on the crystal. Changing load capacitors can alter the loop gain of the oscillator and cause slow or failed startup.
<input type="checkbox"/>	Higher than expected idle power	If an external oscillator is used as a clock source instead of a crystal (and the internal oscillator), the input clock provided to the DSP will not stop when all of the DSP domains are idled (standby). The clock input buffer on the DSP continues to toggle and consume some power even though the clocks to the rest of the DSP are disabled.
<input type="checkbox"/>	Higher than expected idle power	If the standby power (all domains disabled) is higher than expected and it is observed that the internal oscillator is still running, the oscillator has not been configured to idle correctly. See <a href="#">Disabling the Internal Oscillator With External Crystal on the TMS320VC5509 DSP (SPRA078)</a> for the correct procedure.
<input type="checkbox"/>	Unexpected wake-up from IDLE mode	There are several events that can wake the DSP from IDLE mode. Make sure that the events that are not used are prevented from occurring. See the data manual for a list of the events capable of waking the DSP from IDLE mode.

**Table 3. Phase Loop Lock (PLL)**

Issue		Description
<input type="checkbox"/>	CPU crashes after enabling the PLL	The TMS320VC5503 has different clock speeds associated with different voltage specifications. If the PLL is configured to generate a clock speed that cannot be supported by the current voltage level, unpredictable operation can occur. See the data manual for the appropriate voltage and speed combinations.
<input type="checkbox"/>	Excessive Jitter on the DPLL	The digital PLL (DPLL) used to provide clock to the DSP is sensitive to the quality of the power supply. Excessive power supply ripple can contribute to excessive clock edge jitter on the DPLL. CVdd power supply ripple of less than 20 mV is recommended for optimal DPLL jitter performance.
<input type="checkbox"/>	DPLL lock bit is active before the updated clock is passed to the rest of the DSP.	The LOCK bit in the DPLL indicates that the PLL has locked on the desired frequency. After this occurs, the clock logic on the DSP allows the new clock speed to propagate to the rest of the DSP. Because of this, the LOCK bit becomes active before the DSP is running at the new clock speed. The delay between the LOCK bit status and DSP operating at the new clock speed may be as long as 500 us.

**Table 4. Multi-channel Buffer Serial Port (McBSP)**

Issue		Description
<input type="checkbox"/>	Higher than expected idle power	If the McBSP remains enabled and operating, it can prevent the CLKGEN domain from idling because it still requires a clock. For minimum idle power, the McBSP should be placed in reset.

**Table 5. External Memory Interface (EMIF)**

Issue		Description
<input type="checkbox"/>	Random SDRAM Issues	<p>SDRAM is a synchronous memory type and relies on timing relative to a memory clock. Various problems can occur if the signal integrity of the interface is poor. Some issues that can contribute to SDRAM signal problems are:</p> <ul style="list-style-type: none"> <li>• SDRAMs are too far from the DSP on the board layout.</li> <li>• Interface is overloaded causing poor signal edge transitions. In this case, buffers should be used on the interface.</li> <li>• Interface signals are suffering reflections due to poor impedance matching. In this case, termination should be used</li> </ul>
<input type="checkbox"/>	Asynchronous memory interface hangs or behaves unpredictably	Make sure ARDY is controlled high if it is not used. If left floating, it can pick up environmental electrical noise and cause unpredictable behavior of the EMIF.
<input type="checkbox"/>	Unexpected timing between the CPU and the EMIF	When the CPU writes data to the EMIF, the EMIF latches the data and prepares to initiate the external write to the memory. When the data is latched, the EMIF acknowledges the receipt of the data to the CPU, so the CPU gets acknowledgement of the write before the write is actually completed externally.
<input type="checkbox"/>	Unexpected read / write order on the EMIF	The CPU pipeline schedules memory accesses in the most efficient way possible, which may not correspond to the order they occurred in the code. The pipeline will ensure that reads and writes to the same address occur in code order, but accesses to different addresses will be scheduled as efficiently as possible. For more information, see <a href="#">TMS320VC5503/5507/5509 DSP External Memory Interface (EMIF) Reference Guide (SPRU670)</a> .

<input type="checkbox"/>	EMIF timings	If EMIF problems occur, be sure to verify that the EMIF timings are consistent with the timing requirements of the external memory being used. Both the fixed timings in the data manual and the configurable timings affect the overall timing of the interface.
<input type="checkbox"/>	EMIF CE space(s) configuration	<p>The external memory space is divided into four spaces, each selected by a DSP signal CE0 –CE3. Each space is configured for a particular memory type in software. Some memory types also have timing controls that are configurable through software. Verify that the software configuration for each space is correct.</p> <p>Use of some SDRAM configurations requires that multiple CE spaces be used. The following CE spaces may be linked together in SDRAM mode depending on the configuration:</p> <p>CE0 and CE1, or CE2 and CE3, or CE0, CE1, CE2 and CE3</p> <p>If these configurations are used, all of the associated CE spaces must be configured as SDRAM. For more information, see <a href="#">TMS320VC5503/5507/5509 DSP External Memory Interface (EMIF) Reference Guide (SPRU670)</a>.</p>

**Table 6. Host Port Interface (HPI)**

Issue		Description
<input type="checkbox"/>	HPI errors or HRDY stuck low	The minimum low pulse width and high pulse width for the data strobe (HDS1 and/or HDS2) is not being met. Refer to the data manual for timing requirements for the HPI.
<input type="checkbox"/>	HPI errors	HPI transactions cannot be initiated until the previous transaction has been completed as indicated by HRDY. It is recommended to use HRDY since HPI latencies can depend on other CPU and DMA activity.

**Table 7. Real-Time Clock (RTC)**

Issue		Description
<input type="checkbox"/>	Powering the RTC peripheral if it is not used	The RTC power supply must be powered even if the RTC peripheral is not being used.
<input type="checkbox"/>	Dealing with the input clock pin to the RTC if it is not being used	If the RTC is not being used, the RTCINX1 pin should be held low. RTCINX2 can be left floating.
<input type="checkbox"/>	Missing interrupts	INT4 and the real-time clock peripheral share the same flag in the interrupt flag register (IFR1). The occurrence of this flag can indicate that either of these interrupt sources has occurred. If both sources are being used, the RTC status should be polled to determine if the interrupt source was INT4, the RTC or both. See the data manual IFR1 register description for more details.

**Table 8. Watchdog Timer**

Issue		Description
<input type="checkbox"/>	Missing interrupts	INT3 and the Watchdog time share the same flag in the interrupt flag register (IFR0). The occurrence of this flag can indicate that either of these interrupt sources has occurred. If both sources are being used, the Watchdog Timer status should be polled to determine if the interrupt source was INT3, the Watchdog Timer or Both. See the data manual IFR0 register description for more details.

**Table 9. Direct Memory Access (DMA)**

Issue		Description
<input type="checkbox"/>	Delay after enabling DMA channel	After a DMA channel is enabled, the DMA controller copies the channel context registers over to the working set. The working set of registers is used during the actual data movement on the DMA channel. This action causes some latency between the time the DMA channel is enabled and when the first transfer occurs.
<input type="checkbox"/>	DMA channel source and destination appear to be out of sync	The DMA channel FIFO can pre-fetch data from the source to be delivered later when the destination is ready. This can cause the source and destination address counters to appear to be out of sync.

## 5 Summary

Using the information provided in this document, along with documentation that is pointed out for each step of the design process, a DSP designer will be able to make more knowledgeable decisions concerning their design.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

<b>Products</b>		<b>Applications</b>	
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>	Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>	Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>	Broadband	<a href="http://www.ti.com/broadband">www.ti.com/broadband</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>	Digital Control	<a href="http://www.ti.com/digitalcontrol">www.ti.com/digitalcontrol</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>	Military	<a href="http://www.ti.com/military">www.ti.com/military</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>	Optical Networking	<a href="http://www.ti.com/opticalnetwork">www.ti.com/opticalnetwork</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>	Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
		Telephony	<a href="http://www.ti.com/telephony">www.ti.com/telephony</a>
		Video & Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
		Wireless	<a href="http://www.ti.com/wireless">www.ti.com/wireless</a>

Mailing Address: Texas Instruments  
Post Office Box 655303 Dallas, Texas 75265