

Sitara™ processors + WiLink™ 8 connectivity solutions



TI provides Sitara™ processors and WiLink™ 8 Wi-Fi® + Bluetooth® combo connectivity modules that work together to create high-performance solutions for developers in streaming audio, industrial, medical and a wide variety of other applications.

Sitara processors **key features**

- Single and multicore Arm Cortex-A8, Cortex-A9, Cortex-A15, and Cortex-A53 offerings
- Performance options from 600 to up to 10,500 DMIPS
- Linux®, Android™, Windows® CE and RTOS
- Peripherals can include: PCIe, SATA, Gigabit Ethernet, USB 3.0, USB 2.0, DCAN, QSPI, UART, McASP, I²C and more

Texas Instruments (TI) continues to optimize and expand its portfolio of Sitara processor solutions for the embedded market. The Sitara AM57x processors include single- and multi-core Arm Cortex-A15 cores and extend performance by 280 percent compared to standard dual-core Arm Cortex-A9 processors found in the broad embedded market. These high-performance successors to the popular Sitara AM335x and AM437x platforms integrate additional features to support a variety of markets from human

machine interface (HMI) to Internet of Things (IoT) gateways to industrial automation.

The TI WiLink 8 combo connectivity module family enables manufacturers to easily add fully integrated 2.4- and 5-GHz versions of Wi-Fi and dual-mode Bluetooth 4.2 solutions to embedded applications. WiLink 8 modules are well suited for power-optimized designs for home and building automation, smart energy, gateways, wireless audio, wearables and many more industrial and IoT applications. The WiLink 8 modules and software are both compatible and pre-integrated with a wide range of processors including TI's Sitara family of processors.

Benefits

The Sitara family of processors, together with WiLink 8 combo connectivity modules, is a game changer in the wireless industrial field as well as other applications. With the two devices combined, you get a high-performance platform enabling seamless cloud connectivity, high

wireless throughput, integrated dual-mode Bluetooth and Wi-Fi connectivity and a unified programming experience to control the system.

WiLink 8 combo connectivity **device features**

- High-performance Wi-Fi
 - 802.11 a/b/g/n 2.4- and 5-GHz
 - Up to 100Mbps (UDP) of throughput
 - Station and access point
 - Wi-Fi direct, multi-channel multi-role
- Dual-mode Bluetooth on-chip (Bluetooth and Bluetooth low energy)
- Wi-Fi/Bluetooth single antenna co-existence
- Built-in power management
- Advanced low-power modes
- Host interfaces: SDIO for Wi-Fi and UART for Bluetooth
- Temperature ranges:
 - -20°C to +70°C
 - -40°C to +85°C
- Small form factor:
13.4 × 13.3 × 2mm

Development tools

Product Number	Description	Benefits	Availability
 <p>BeagleBone Black</p>	BeagleBone Black is a low-cost, community-supported development platform based on Sitara AM335x processors for developers and hobbyists.	Boot Linux in under 10 seconds and get started on development in less than five minutes with just a single USB cable and extend the capabilities with a large portfolio of “Cape” plug-in boards.	Authorized distributors
 <p>WL1835MODCOM8</p>	The 2.4-GHz WL1835-based evaluation board is compatible with Sitara EVMs for AM335x, AM4x, AM5x, and AM6x as well as several other TI EVMs and reference designs.	The TI WiLink COM8 module for Wi-Fi and Bluetooth / Bluetooth low energy connectivity, provides a fast connectivity ramp with software, collateral and reference applications available from TI. The COM8 board can easily plug into the Sitara processor EVM boards.	TI store and authorized distributors
 <p>WL1837MOD Cape</p>	The WiLink 8 WL1837MOD audio cape used with BeagleBone Black is a best-in-class audio solution, featuring ultra-precise audio synchronization, multi-room capabilities, support for online music services, UPnP and more. The design is also Apple AirPlay® certifiable and supports Google Cast™ audio.	WiLink 8 cape paired with BeagleBone Black enables rapid software development through pluggable hardware and open source community.	Authorized distributors
 <p>WL1837MODCOM8</p>	The 5-GHz WL1837-based evaluation board is compatible with Sitara EVMs for AM335x, AM4x, AM5x, and AM6x as well as several other TI EVMs and reference designs.	The TI WiLink COM8 module for Wi-Fi and Bluetooth / Bluetooth low energy connectivity, provides a fast connectivity ramp with software, collateral and reference applications available from TI. The COM8 board can easily plug into the Sitara processor EVM boards.	TI store and authorized distributors

Learn how to get started with WiLink 8 on any Sitara processor [here](#).

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

The platform bar, Sitara and WiLink are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2019, Texas Instruments Incorporated