



## ABSTRACT

This user's guide describes the characteristics, operation, and the use of the TPS552882EVM-400kHz evaluation module (EVM). The EVM contains the TPS552882 device, which is a high-performance, high-efficiency synchronous buck-boost converter which integrates two 16-A MOSFETs at the boost leg. The user's guide includes EVM specifications, recommended test setup, test result, schematic diagram, bill of materials, and the board layout.

---

## Table of Contents

|   |   |
|---|---|
| <b>Trademarks</b> .....                                       | 1 |
| <b>1 Introduction</b> .....                                   | 2 |
| 1.1 Performance Specification.....                            | 2 |
| 1.2 Modification.....   | 2 |
| <b>2 Connector, Test Point and Jumper Descriptions</b> .....  | 2 |
| 2.1 Connector and Test Point Descriptions.....                | 2 |
| 2.2 Jumper Configuration.....                                 | 2 |
| <b>3 Test Procedure</b> .....                                 | 3 |
| <b>4 Schematic, Bill of Materials, and Board Layout</b> ..... | 4 |
| 4.1 Schematic.....  | 4 |
| 4.2 Bill of Materials.....                                    | 5 |
| 4.3 Board Layout.....   | 7 |
| <b>5 Revision History</b> .....                               | 9 |

## List of Figures

|   |   |
|---|---|
| Figure 4-1. TPS552882EVM-400kHz Schematic.....          | 4 |
| Figure 4-2. TPS552882EVM-400kHz Top-Side Layout.....    | 7 |
| Figure 4-3. TPS552882EVM-400kHz Inner Layer1.....       | 7 |
| Figure 4-4. TPS552882EVM-400kHz Inner Layer2.....       | 8 |
| Figure 4-5. TPS552882EVM-400kHz Bottom-Side Layout..... | 8 |

## List of Tables

|   |   |
|---|---|
| Table 1-1. Performance Specification Summary..... | 2 |
| Table 2-1. Connectors and Test Points.....        | 2 |
| Table 4-1. Bill of Materials.....                 | 5 |

## Trademarks

All trademarks are the property of their respective owners.

## 1 Introduction

### 1.1 Performance Specification

Table 1-1 provides a summary of the TPS552882 EVM performance specifications. All specifications are given for an ambient temperature of 25°C.

**Table 1-1. Performance Specification Summary**

| Parameter                   | Test Condition                                   | Value    | Unit |
|-----------------------------|--|----------|------|
| Input Voltage               | N/A  | 2.7 - 36 | V    |
| Output Voltage              | N/A  | 0.8 - 20 | V    |
| Maximum Output Current      | $V_{IN} \geq 2.7\text{ V}, V_{OUT} = 5\text{ V}$ | 5        | A    |
|                             | $V_{IN} \geq 5\text{ V}, V_{OUT} = 9\text{ V}$   |          |      |
|                             | $V_{IN} \geq 9\text{ V}, V_{OUT} = 15\text{ V}$  |          |      |
|                             | $V_{IN} \geq 12\text{ V}, V_{OUT} = 20\text{ V}$ |          |      |
| Default Switching Frequency | N/A  | 400      | KHz  |

### 1.2 Modification

The printed-circuit board (PCB) for this EVM is designed to accommodate some modifications by the user. The external component can be changed according to the real application.

## 2 Connector, Test Point and Jumper Descriptions

This section describes how to properly connect, set up, and use the TPS552882EVM-400kHz.

### 2.1 Connector and Test Point Descriptions

This EVM includes I/O connectors and test points as shown in Table 2-1. The power supply must be connected to input connectors, J1 and J2. The load must be connected to output connectors, J3 and J4.

**Table 2-1. Connectors and Test Points**

| Reference Designator | Description                       |
|----------------------|-----------------------------------|
| J1                   | Input voltage positive connection |
| J2                   | Input voltage return connection   |
| J3                   | Output voltage connection         |
| J4                   | Output voltage return connection  |

### 2.2 Jumper Configuration

#### 2.2.1 JP1 (ENABLE)

The JP1 jumper enables the device. By default, this jumper is set to the ON position. Put this jumper in the OFF position to disable the output.

#### 2.2.2 JP2(SYNC)

The JP2 jumper is for the frequency dithering selection. Placing a jumper across JP2 disables the frequency dithering function. Left JP2 opens when using frequency dithering function.

### 3 Test Procedure

Use the following steps for the test procedure:

1. Set the power supply current limit to 15 A. Set the power supply to something around 12 V. Turn off the power supply. Connect the positive output of the power supply to J1 and the negative output to J2.
2. Connect the load to J3 for the positive connection and J4 for the negative connection.
3. Turn on the power supply.
4. Slowly increase the load while monitoring the output voltage between J3 and J4. It must remain in regulation when the load current is lower than 5 A.
5. Slowly sweep the input voltage from 5 V to 20 V. The output voltage must remain in regulation when the load current is lower than the maximum load current specified in [Table 2-1](#).
6. Turn off the load, turn off the power supply. Then turn on the load to discharge the output capacitors.

## 4 Schematic, Bill of Materials, and Board Layout

This section provides the TPS552882EVM-400kHz schematic, bill of materials (BOM), and board layout.

### 4.1 Schematic

Figure 4-1 shows the EVM schematic.




Figure 4-1. TPS552882EVM-400kHz Schematic

## 4.2 Bill of Materials

Table 4-1 lists the EVM bill of materials.

**Table 4-1. Bill of Materials**


| Designator          | QTY | Value  | Description   | Package                       | Part Number              | Manufacturer                        |
|---------------------|-----|--------|---|-------------------------------|--------------------------|-------------------------------------|
| C1                  | 1   | 68uF   | CAP, Polymer Hybrid, 68 uF, 50 V, ±20%, 30 ohm, 8x10 SMD  | 8x10                          | EEHZA1H680P              | Panasonic                           |
| C2, C3              | 2   | 10uF   | CAP, CERM, 10 µF, 75 V,±20%, X7R, AEC-Q200 Grade 1, 1210  | 1210                          | CGA6P1X7R1N106M250A<br>C | TDK                                 |
| C4, C5, C11,<br>C17 | 4   | 1uF    | CAP, CERM, 1 µF, 50 V,±20%, X5R, AEC-Q200 Grade 3, 0603   | 0603                          | GRT188R61H105ME13D       | MuRata                              |
| C6, C7, C8, C9      | 4   | 10uF   | CAP, CERM, 10 µF, 50 V,±10%, X7R, AEC-Q200 Grade 1, 1206  | 1206                          | CGA5L1X7R1H106K160AC     | TDK                                 |
| C10                 | 1   | 220uF  | CAP, Polymer Hybrid, 220 uF, 25 V, ±20%, 27 ohm, 8x10 SMD   | 8x10                          | EEHZA1E221P              | Panasonic                           |
| C12, C13, C18       | 3   | 0.1uF  | CAP, CERM, 0.1 uF, 50 V, ±10%, X7R, AEC-Q200 Grade 1, 0402  | 0402                          | CGA2B3X7R1H104K050BB     | TDK                                 |
| C14                 | 1   | 4.7uF  | CAP, CERM, 4.7 µF, 16 V,±10%, X5R, AEC-Q200 Grade 3, 0603   | 0603                          | GRT188R61C475KE13D       | MuRata                              |
| C15, C23            | 2   | 0.01uF | CAP, CERM, 0.01 uF, 50 V, ±10%, X7R, AEC-Q200 Grade 1, 0402   | 0402                          | CGA2B3X7R1H103K050BB     | TDK                                 |
| C16                 | 1   | 100pF  | CAP, CERM, 100 pF, 50 V, ±5%, C0G/NP0, AEC-Q200 Grade 1, 0402   | 0402                          | CGA2B2C0G1H101J050BA     | TDK                                 |
| C19, C20            | 2   |        | 0.1µF ±10% 50V Ceramic Capacitor X8L 0603 (1608 Metric)   | 0603                          | GCM188L81H104KA57D       | Murata Electronics<br>North America |
| J1, J2, J3, J4      | 4   |        | Terminal, Turret, TH, Double  | Keystone1502-<br>2            | 1502-2                   | Keystone                            |
| J5, J6, J7, JP2     | 4   |        | Header, 100mil, 2x1, Tin, TH  | Header, 2 PIN,<br>100mil, Tin | PEC02SAAN                | Sullins Connector<br>Solutions      |
| JP1                 | 1   |        | Header, 100mil, 3x1, Tin, TH  | Header, 3 PIN,<br>100mil, Tin | PEC03SAAN                | Sullins Connector<br>Solutions      |
| L1                  | 1   | 4.7uH  | Inductor, Shielded, Composite, 4.7 uH, 24 A, 0.01 ohm, SMD  | Inductor,<br>11.3x10x10mm     | XAL1010-472MEB           | Coilcraft                           |
| Q1, Q2              | 2   | 40V    | MOSFET, N-CH, 40 V, 40 A, AEC-Q101, SON-8   | SON-8                         | IPZ40N04S5L4R8ATMA1      | Infineon<br>Technologies            |
| R1, R15, R16        | 3   | 102k   | RES, 102 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402   | 0402                          | CRCW0402102KFKED         | Vishay-Dale                         |
| R2                  | 1   | 11.3k  | RES, 11.3 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402  | 0402                          | CRCW040211K3FKED         | Vishay-Dale                         |
| R3                  | 1   | 49.9   | RES, 49.9, 1%, 0.063 W, AEC-Q200 Grade 0, 0402  | 0402                          | CRCW040249R9FKED         | Vishay-Dale                         |
| R4                  | 1   |        | 10 mOhms ±1% 1W Chip Resistor 1206 (3216 Metric) Automotive AEC-Q200, Current Sense, Moisture Resistant Metal Element | 1206                          | CRF1206-FZ-R010ELF       | Bourns                              |
| R5, R6              | 2   | 1.00   | RES, 1.00, 1%, 0.1 W, AEC-Q200 Grade 0, 0603  | 0603                          | CRCW06031R00FKEA         | Vishay-Dale                         |
| R7                  | 1   | 49.9k  | RES, 49.9 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402  | 0402                          | CRCW040249K9FKED         | Vishay-Dale                         |
| R8                  | 1   | 0      | RES, 0, 5%, 0.063 W, AEC-Q200 Grade 0, 0402   | 0402                          | CRCW04020000Z0ED         | Vishay-Dale                         |
| R9                  | 1   | 20.0k  | RES, 20.0 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402  | 0402                          | CRCW040220K0FKED         | Vishay-Dale                         |
| R10                 | 1   | 15.0k  | RES, 15.0 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402  | 0402                          | CRCW040215K0FKED         | Vishay-Dale                         |
| R11                 | 1   | 150k   | RES, 150 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402   | 0402                          | CRCW0402150KFKED         | Vishay-Dale                         |

**Table 4-1. Bill of Materials (continued)**


| Designator                                   | QTY | Value  | Description                                     | Package                          | Part Number        | Manufacturer      |
|--|-----|--------|---|----------------------------------|--------------------|-------------------|
| R12  | 1   | 0      | RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0603       | 0603                             | CRCW06030000Z0EA   | Vishay-Dale       |
| R13  | 1   | 147k   | RES, 147 k, 1%, 0.1 W, 0603                     | 0603                             | RC0603FR-07147KL   | Yageo             |
| R14  | 1   | 115k   | RES, 115 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402 | 0402                             | CRCW0402115KFKED   | Vishay-Dale       |
| TP1, TP2, TP3,<br>TP4, TP5, TP6,<br>TP7, TP8 | 8   |        | Test Point, Miniature, Orange, TH               | Orange<br>Miniature<br>Testpoint | 5003               | Keystone          |
| U1   | 1   |        | 36-V, 16-A Buck-boost Converter                 | VQFN-HR26                        | TPS552882RPM       | Texas Instruments |
| C21, C22                                     | 0   | 2200pF | CAP, CERM, 2200 pF, 250 V, ±10%, X7R, 0805      | 0805                             | GRM21AR72E222KW01D | MuRata            |
| R17, R18                                     | 0   | 1.0    | RES, 1.0, 5%, 0.5 W, 1206                       | 1206                             | CRM1206-JW-1R0ELF  | Bourns            |

### 4.3 Board Layout


Figure 4-2 through Figure 4-5 illustrate the EVM board layouts.




**Figure 4-2. TPS552882EVM-400kHz Top-Side Layout**



**Figure 4-3. TPS552882EVM-400kHz Inner Layer1**



**Figure 4-4. TPS552882EVM-400kHz Inner Layer2**



**Figure 4-5. TPS552882EVM-400kHz Bottom-Side Layout**

## 5 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| <b>Changes from Revision * (June 2020) to Revision A (November 2020)</b> | <b>Page</b> |
|--|-------------|
|--|-------------|

---

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2022, Texas Instruments Incorporated