

LMX2820 with Internal Doubler versus LMX2594



Russell Hoppenstein

Introduction

The LMX2594 RF synthesizer operates with a fundamental frequency range from 7.5GHz to 15GHz. The LMX2820 RF synthesizer operates with a fundamental range of 5.65GHz to 11.3GHz. The LMX2820 includes an internal doubler to extend the frequency range up to 22.6GHz.

Generally speaking, the LMX2820 is a newer device and provides improved phase noise compared to the predecessor. However, there is an ambiguous overlap of 3.7GHz (from 11.3GHz to 15GHz) where one device operates within the fundamental range and the other uses a doubler. Within that high frequency overlap, which option provides the best phase noise performance?

Phase Noise Comparison

Both devices were tested at 13.2GHz. This represents a common frequency that is externally doubled to reach K-band (for example, 26.4GHz). The reference frequency is 100MHz supplied from a Rohde and Schwarz SMA100B signal generator. The 100MHz reference signal is internally multiplied by two to set the PFD (Phase Frequency Detector) to 200MHz. Both devices are set up with the same frequencies and configuration.

Figure 1 shows the phase noise performance comparison of LMX2594 and the LMX2820 operating with an internal doubler at 13.2GHz.




Figure 1-1. Phase Noise Comparison of LMX2594 vs LMX2820 with Internal Doubler at 13.2GHz

Sub-Harmonics

One of the key concerns with using a doubler is that the fundamental frequency of the VCO bleeds through to the output and manifest as a sub-harmonic spur. [Table 1](#) lists the sub-harmonic spur data of the LMX2820. The sub-harmonic spur performance of the LMX2820 is good as a result of the integrated sub-harmonic filtering. Since the LMX2594 operates within the fundamental range, the device does not generate a sub-harmonic spur.

Table 1. Sub-Harmonic Spur Performance

Device	Frequency (GHz)	Spur (dBc)
LMX2820 with internal doubler	6.6	58

Conclusion

In general, the newer LMX2820-with-internal-doubler performs better than the LMX2594 operating within the fundamental range. Specifically, the phase noise performance at close-in frequencies from under 1kHz to 10kHz is better. Phase noise between 10kHz and 10MHz offset is roughly equivalent. The LMX2594 wields a slight advantage at high frequency offsets above 10MHz with a better noise floor. This is expected as the doubler in the LMX2820 introduces an additional thermal noise component. Sub-harmonic performance of the LMX2820 with internal doubler is reasonable and can be filtered if additional rejection is required.

References

1. Texas Instruments, [External Doubler Extends LMX2820 Operation to 44 GHz](#), application brief.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated