

Broadcast and Professional Video Interface Solutions

Extend reach, distribute video over SDI and IP networks



**Upgrade your system to support
4K/8K video over coax, optical fiber**




Industry leading interface and timing solutions

Texas Instruments is a total solutions provider to the professional and broadcast video industry. Our comprehensive portfolio of energy efficient and easy to use analog, mixed signal, and DSP solutions accelerate design and reduce development cost.

Offering best in class performance in signal integrity and power efficiency, TI's interface products extend reach and distribute high speed video signals for serial digital video interface (SDI), Ethernet (video over IP), HDMI, display port, PCIe, SAS/SATA, LVDS, and other common signaling technologies.

TI's clocking and timing portfolio of buffers, clock generators, and oscillators deliver the industry's best phase noise and jitter performance (90 fs RMS, typical). With programmable features to support multiple standards ,TI's easy-to-use clocking solutions generate multiple frequencies in different I/O formats.



Extend reach, distribute video over SDI, IP networks

Texas Instruments (TI) offers the industry's most comprehensive multi-rate portfolio of serial digital interface (SDI) and Ethernet solutions to transport 4K/8K video resolution over coaxial cables, printed circuit board material, and optical fiber interconnects.


Offering best in class performance in signal integrity, power and cable reach, TI's interface products simplify system design for broadcast, professional, and commercial video applications.

Flexible products with easy upgrade path

Bidirectional I/O	Easy upgrade	Dual media, dual protocol
Configurable as receive equalizer or transmit driver to enable design reuse, dynamic port provisioning.	Pin compatible portfolio simplifies transition from 3G SDI to 12G SDI.	Single chip solution supports SDI and Ethernet IP based video transport over coax or fiber.


Industry's first: LMH1297

12G SDI Bidirectional I/O with integrated reclocker and return loss network enables design reuse, and dynamic port provisioning.



- Configurable as SDI equalizer or cable driver: Provides transport flexibility
- Integrated reclocker and return loss network: Saves board space and simplifies design
- Cable equalizer: Extends reach up to 75m+ at 12G, 120m+ at 6G, 200m+ at 3G, 300m at HD
- EQ Mode: Additional line-side reclocked 75- Ω loop-through output
- CD Mode: Additional host-side reclocked 100- Ω loopback output
- Small package: QFN32, 5mm x 5mm. Pin compatible 3G-SDI option available (LMH0397)
- Pin compatible cable driver options available (LMH1228, LMH1208)

Industry leading interface and timing solutions




Industry's first: LMH1219 / LMH0324


Pin compatible cable equalizer portfolio simplifies upgrade from 3G-SDI to 12G-SDI.

	LMH0324	LMH1219
Function	Cable Equalizer	Cable Equalizer with Integrated Reclocker
Data Rates	3G, 1.5G, 270M	12G, 10G, 6G, 3G, 1.5G, 270M
Protocols Supported	SDI	SDI & 10GbE (SMPTE 2022-5/6)
Media Supported	Coax	Coax, Optical (SFP+)
Cable Reach	200m+ at 3G	75m+ at 12G, 120m+ at 6G, 200m+ at 3G
Power (Typ.)	75mW	250mW
Package	Pin compatible for easy upgrade 4 mm x 4 mm , QFN 24	

200m at 3G-SDI (EQ)



75m at 12G-SDI (EQ + Reclocker)



Easy to analyze, evaluate and design

Featured reference designs and EVMs



FPGA FMC development module for 4K video supporting 12G SDI and video over IP

- Supports Devices: LMH1218, LMH1219




LMH0324-18EVM: 3G distribution amplifier TI reference design

- Supports Devices: LMH0324, LMH0318



LMH1297EVM: 12G Bidirectional I/O with Reclocker and Integrated Return Loss Network Evaluation Module

- Supports Devices: LMH1297, LMH0397




TIDA-00428: 12G distribution amplifier TI reference design

- Supports Devices: LMH1218, LMH1219

Industry's first: LMH1218

12G cable driver with integrated reclocker to support SDI and IP-based 4K video.



- SDI and 10 GbE (SMPTE 2022-5/6): Single device provides transport flexibility
- Dual media (coax and optical): Enables both short and long haul applications
- Integrated reference-less reclocker: 40% board area savings with faster lock time
- Low power consumption (300 mW typ): 30% lower than a discrete solution
- Integrated eye monitor: Accelerates system debug and diagnostics
- Small package: QFN24, 4mm x 4mm. **Pin compatible 3G-SDI option available (LMH0318)**

Design resources and references




E2E high speed interface forum

ti.com/e2ehsi

Get more information on TI's professional and broadcast video portfolio at:

ti.com/sdi.

WEBENCH® Interface Designer



Get results faster with easy-to-use design tools that deliver custom results.

- Easily create new high-speed serial interface systems
- Analyze and enhance signal integrity for existing designs
- Select the right interface devices for your requirements

Get more information

ti.com/webench

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty, or endorsement thereof.

The platform bar and E2E are trademarks and WEBENCH is a registered trademark of Texas Instruments. All other trademarks are the property of their respective owners.

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated