

# NVME and PCI Express: What's the Difference?

---



Alexander Hanchett

When you ask a bunch of hardware engineers, “What is NVME?,” you might get the following responses:

“NVME is an acronym for ‘nonvolatile memory express’.”

- “NVME is the best thing to ever happen to solid-state storage!”
- “I think NVME is, uh, related to PCI Express?”

While these answers are all essentially correct, they won’t help you build a storage system that leverages the advantages of this game-changing new technology. Texas Instruments has many years of experience in the hardware behind [PCI Express](#) (PCIe) and enterprise storage, and we can share insight into this important technology and how it impacts future hardware designs. Here’s how I would answer the question:

“NVME is a protocol developed explicitly for solid-state memory. While Serial Advanced Technology Attachment (SATA) remains the heavyweight champion of storage protocols, it wasn’t built to deal with solid-state storage and can’t offer the advantages of NVME.”

In order to explain SATA and NVME, let’s compare them to a physically similar counterpart: a record player. In order to play music, a turntable needle reads information from a record and outputs that data to speakers. SATA hard drives allow their “records” to spin up to 15,000rpm while reading data over a read/write head; like a record player, the architecture relies on a single needle. In comparison, NVME running on a solid-state drive (SSD) is more like an MP3 file. All of the data is laid out in a readable format, and can be read by as many as 64,000 parallel “needles” at the same time.

When it comes to transporting your data, SATA is also a physical bus, like the wire between your music player and speakers. Traditionally, it hasn’t been the bottleneck for storage drives, but a faster bus like PCIe could “boost” the maximum achievable speed.


## Why Should I Care about NVME?

In terms of input/output (I/O) operations per second (IOPS), typical hard-disk drives range in the low hundreds, while NVME SSDs post numbers in the hundreds of thousands to millions of IOPS. In terms of read and write speeds, SATA hard disks support several hundred megabytes per second, while NVME supports several gigabytes per second – one order of magnitude greater. All of this translates to unparalleled performance gains.

## How Do I Build NVME?

OK, so you get it – NVME is fast. But this is a guide for hardware engineers, right? So far, we’ve been describing the car without talking about the road it’s driving on. Fortunately for everyone, the answer is very simple: the PCIe bus.

NVME is a storage protocol, but the physical layer that NVME runs on is plain old PCIe. This means that hardware engineers can leverage existing resources to check [compliance](#), use existing [reference designs](#), and simulate with existing [modeling tools](#). It also means that products qualified by the PCI Special Interest Group (SIG) to support PCIe Gen 3, like [DS80PCI810](#), can support NVME applications.



**Figure 1. DS80PCI810 PCIe Gen 3 Redriver Typical Application Block Diagram**

As I mentioned earlier, TI has turned decades of industry experience into reference designs and resources to get your system off the ground today. TI can also deliver all of the components to develop next-generation PCIe NVME drives, from power to signal chain.

Now that you know the basics of NVME and PCIe, leave us a note below and let us know what other topics related to PCIe you would be interested in hearing about.

#### Additional Resources

- Learn about [enterprise SSD systems](#).
- Get started with the [High-Speed Front-End for PCIe Gen-3 Cards Reference Design](#).
- Read a [PCIe compliance](#) application note.
- Find out more about the [DS80PCI810 PCIe Gen 3 redriver](#).

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2023, Texas Instruments Incorporated