


# Stellaris<sup>®</sup> DK-LM3S-DRV8312

## 3-Phase Brushless DC & AC Motor Control Kit

The Texas Instruments Medium Voltage Digital Motor Control Kit for Stellaris Microcontrollers (DK-LM3S-DRV8312) is a development platform for spinning 3-phase brushless DC (BLDC) and brushless AC (BLAC, aka PMSM) motors. The low-cost Stellaris LM3S818 microcontroller (MCU) on the MDL-LM3S818CNCD controlCARD module comes pre-programmed with the necessary firmware in Flash memory to run the Texas Instruments (TI) InstaSPIN<sup>™</sup> BLDC motor control solution out-of-the-box once plugged into the DRV8312 baseboard. The system will automatically detect and spin a customer's 3-phase brushless DC motor.

The operation of this system is controllable and viewable across a USB interface using an included Crosshairs-enabled environment that consists of a PC application interface and Crosshairs' embedded kernel running on the LM3S818 MCU. The LM3S818 MCU provides all of the necessary computational requirements to run TI's InstaSPIN BLDC technology and other customer-developed applications as well.

Follow the steps in the kit's README First document to quickly get up and running. Using TI's InstaSPIN BLDC technology, you can quickly identify a 3-phase brushless motor's key characteristics in order to spin the motor successfully.



### Features

The DK-LM3S-DRV8312 motor control kit contains a cost-effective, Stellaris LM3S818 MCU-based controlCARD module compatible with other TI motor control platforms.

In addition to instantly spinning your motor, the kit also demonstrates the InstaSPIN BLDC motor control solution's operational advantages with simplified tuning, immediate acceleration adaptation, reliable low-speed operation, and more.

The included Crosshairs solution enables users to control and monitor the total solution through an easy-to-use PC application that can be extended for end-customer applications.



Crosshairs control GUI Windows application

- Hardware compatible with the following TI DRV baseboards
  - DRV8312 Rev C and Rev D
  - DRV8301HC (High Current 60A) Rev A and DRV8301 (6A) Kit

### Contents

The DK-LM3S-DRV8312 is a bundle of the following components:

- MDL-LM3S818CNCD controlCARD module
  - Stellaris 50-MHz ARM<sup>®</sup> Cortex<sup>™</sup>-M3 LM3S818 MCU with on-board Stellaris In-Circuit Debug Interface (ICDI)
  - Pluggable 100-pin DIMM form factor
  - Auto-isolation enabling upon debug connection
- DRV8312 baseboard (TI-integrated 3P motor driver board supporting up to 52.5V and 6.5A)
- NEMA17 BLDC/PMSM 55W motor
- 24V 2.5A DC power adapter, 110-240V AC input, USA power cable
- USB-miniB to USB-A plug cable (for debug and serial communication)
- Kit CD
  - Documentation
  - LM Flash programmer utility for firmware updates
  - Crosshairs GUI
  - Applicable source code
  - Schematics
- TI's Code Composer Studio<sup>™</sup> Integrated Development Environment (IDE)

### Ordering information

Product Number	Description
DK-LM3S-DRV8312	3-Phase BLDC Motor Kit with DRV8312 and Stellaris LM3S818 controlCARD Module
MDL-LM3S818CNCD	Stellaris LM3S818 controlCARD Module for 3-Phase BLDC motors in single-unit packaging

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated