



An Introduction to the Tiva™ C Series Platform of Microcontrollers

Leading analog integration, low power consumption and floating-point performance in the next generation of ARM® Cortex™-M4 processors from Texas Instruments

Introduction

TI's Tiva™ C Series platform of microcontrollers (MCUs) traces its roots to the first MCUs on the market based on the ARM® Cortex™-M processor architecture, an architecture that has quickly become the de facto industry standard. Since that time, TI's Cortex-M products have remained true to their original purpose – providing the broadest portfolio of highly connected, low-cost and easy-to-use 32-bit MCUs. The new Tiva C Series refines TI's offering of connected MCUs, greatly improving performance and raising features to a new level of quality.

Tiva C Series MCUs provide a high level of connectivity and sensor aggregation, which make them perfect for connected applications, such as home, building and industrial automation. These MCUs take advantage of two significant technologies: the latest ARM Cortex-M4 core processor and the design techniques and process technologies perfected at Texas Instruments. The result is a 32-bit MCU platform with processing performance that is more effective per clock cycle, integrated mixed-signal circuits that are on par with traditional standalone components, Flash

memory with erase-write endurance that is best-in-class and power consumption that is highly competitive with other 32-bit MCUs in both active and standby modes. Such qualities will further increase the breadth of applications powered by Tiva C Series MCUs and enable connected applications that were not previously feasible. The major features of Tiva C Series ARM Cortex-M4 Microcontrollers (MCUs) are depicted in the block diagram of Figure 1. A more thorough list can be found in the product data sheets.




Figure 1. Block diagram of TI's Tiva C Series TM4C123x microcontrollers.

ARM Cortex-M4: Higher performance, still compatible

The Tiva C Series platform makes use of the most advanced ARM architecture core for MCUs, the Cortex-M4. As a 32-bit processor architecture, Cortex-M MCUs enjoy a rich instruction set

with far greater flexibility than 8- or even 16-bit architectures and can operate on data that is up to 32 bits wide with ease. The long and successful history of the ARM architecture in embedded applications assures the greatest selection of third-party hardware and software support, pre-packaged off-the-shelf software like stacks and real-time operating systems (RTOSs) and experienced engineering and programming personnel for any project. Previous generations of TI's ARM-based MCUs under the brand "Stellaris®" used the original Cortex™-M3 architecture. The Thumb-2® instruction set of this earlier version of the Cortex-M core is a high-density, power-efficient instruction set suitable for a wide variety of general-purpose data processing and control operations. The Cortex-M3 Thumb-2 instructions include arithmetic, logical, bit, branch and data movement operations found on many MCUs. It also adds more advanced operations and multiplication, bit-field manipulation, conditional prefixes and operates on 8-, 16- and 32-bits of data. The ARM Cortex-M3 has become a standard for modern 32-bit MCUs.

The new Cortex-M4 core expands the instruction offering of the Cortex-M3 by adding digital signal processing (DSP) extensions and single instruction, multiple data (SIMD) instructions. Tiva C Series devices also include the floating-point option across the entire portfolio of Tiva C Series products. The DSP operations of Tiva C Series devices include single-cycle 32-bit or dual 16-bit multiply-accumulate (MAC) instructions and saturating arithmetic instructions. Optimized SIMD instructions can perform four 8-bit or two 16-bit arithmetic operations in a single cycle and are therefore, very effective at performing arithmetic operations on large arrays of data. The hardware divide logic produces a result in between 2 and 12 clock cycles. Together, these instructions add DSP-like capabilities to a responsive controller core. The single precision floating-point instructions are compliant with the IEEE 754 standard and include functions such as square root and a fused MAC that enable higher precision. Numerous data type conversions are available, speeding transitions between domains.

Besides providing a significant performance increase for math-intensive operations, floating-point support greatly simplifies the implementation and programming of floating-point routines. It is not uncommon for a customer to spend one week developing a digital filter in MATLAB® then spend another month converting the filter to a fixed-point implementation to ensure it is both precise and stable. This development time is not required when programmers can program their filters in the native floating-point format.

Embracing TI's integrated technologies

Now firmly embedded into TI's MCU catalog, the new Tiva C Series MCUs have taken full advantage of the advances and technologies that TI has honed to excellence with its proprietary MSP and C2000™ MCUs. In some cases, like the mixed-signal circuits and the memory structures, specific circuits were targeted. On the other hand, an aggressive process technology has led to a reduction in power consumption across the board. In the end, Tiva C Series MCUs are an accumulation of many feature enhancements and technology improvements.

Precision integrated analog

In building Tiva C Series MCUs, special effort went into designing high-quality, high-resolution analog-to-digital converters (ADCs). The result is seen in the integrated high-resolution 12-bit ADC that samples as fast as 1 MSPS, a sample rate that supports both the full resolution and accuracy of the ADCs, unlike other MCUs that degrade the quality of the readings to achieve higher sample rates. Two of these converters are on-chip and can be fed from 24 independent inputs.

To enhance precision, a differential external reference voltage can be applied to dedicated inputs. The ADCs can generate processor interrupts based on a conversion completion, as well as on a match to one of eight digital comparators. Readings from the ADCs can be queued, compared and averaged within the ADC. The on-chip micro direct memory access controller (μ DMA) can feed ADC readings from the ADC FIFOs to RAM or another peripheral without waking up or distracting the ARM core. There are also three on-chip analog comparators that can be used with a programmable internal voltage reference detect when an input analog signal has crossed a specific threshold. These three analog comparators, along with the digital comparators, remove the requirement of continuously polling incoming ADC values and free up the CPU to focus on real-time application tasks.

Motion control is just one application that can take advantage of fast, accurate ADCs, floating-point performance to run more sophisticated algorithms and on-chip comparators. The more quickly and precisely the motor driver can track the dynamics of a motor during actual operation, the less pushback resistance the generated PWMs will encounter and the more efficient the control signals will be. Less energy will be expended, and the shaft will spin smoother and maintain speed or accelerate in spite of varying loads. The on-chip comparators can be used to check for fault conditions in the system, requiring immediate response.

Reliable memory can be distinctive

It can be hard to get excited about memory. It is often simply taken for granted. But changing to a TI 65-nanometer (nm) process for Tiva C Series MCUs raises the products to a new level of reliability and integration.

Borrowing the Flash technology that TI developed for use in automotive products, Tiva C Series MCUs have extended memory durability by an order of magnitude beyond the competition. The minimum number of times the Flash memory on these MCUs can be erased and reprogrammed is as high as 100,000 cycles. For most applications, this breakthrough eliminates any concern of wearing out the memory from re-flashing for data collection, configuration parameters or program modifications.

More of the high-reliability Flash is also available for customer-written code because TivaWare™ software drivers are embedded in a small mask ROM on-chip. All Tiva C Series MCUs have the TivaWare software binaries committed in on-chip ROM, including the peripheral drivers, the in-system programming routines, utilities such as cyclic redundancy check (CRC) algorithms and advanced encryption standard (AES) tables. These application programming interfaces (APIs) let the programmer take full advantage of these well-proven services, routines and tables, while leaving all of the Flash for customer and application-specific code.

There are many other memory features on the MCUs, but one new memory type deserves special attention. The new Tiva C Series MCUs have 2K Bytes of secure, on-chip EEPROM. EEPROM is normally used to store long-term variables that may even need to survive power outages and dead batteries. Since the implementation is interrupt enabled, the integrated memory allows for the execution of code while writing values to nonvolatile memory (execute-while-write). The EEPROM use is architected using a built-in wear-leveling technique that ensures each location can be modified 500,000 times. If the data was re-written 100 times a day, the EEPROM would last nearly 15 years!

Power savings extend battery life

The power requirements for embedded systems continue to be a key design parameter for consideration. Many end equipments run off a battery; therefore a long battery life can set a customer's product apart from competing systems. Even mains-powered equipment often has limitations on the power budget. As an example, many new products now draw their power solely from a USB cable, which is limited by the USB 2.0 specification to a maximum of 500 mA.

The first way TI reduced the power consumption was by using a proprietary 65-nm process. This special 65-nm process lowers power consumption for the MCU without sacrificing the high performance available from the ARM Cortex-M4 core.

Tiva C Series MCUs also have a number of clock and power domains that can be gated as needed to manage power. When the DSP or floating-point units are not needed, for example, or if any of the peripherals will be idle, power and/or clocking to those modules can be shut down in order to optimize power consumption. Tiva C Series devices provide sleep, deep-sleep and hibernate (HIB) modes to save power when minimal functionality is required. In the hibernate mode, power to the entire chip is cut off except to the HIB block, leaving the MCU in a state where it can be brought back to life when the need arises. The HIB block includes a 32-kHz oscillator circuit, a supporting real-time clock (RTC) module, a battery monitor circuit and sixteen 32-bit words of backup battery SRAM. This minimalist implementation allows the power consumption to be reduced, in hibernate (HIB) mode, to as little as 1.6 μ A. Tiva C Series devices can be awakened from hibernation by an RTC match, from an external signal, or from a low-voltage-detection circuit. It might be minutes, hours, or even days between events that cause the device to come out of hibernation. The longer the duration and the lower the power of the hibernation state, the longer between recharges or replacement of batteries.

Additionally, the state of all GPIO lines can be saved during hibernation until the chip wakes up. Upon awakening, the chip goes through a power-on reset and starts executing instructions in a maximum of 500 μ S. In full 80-MHz execution mode from Flash, Tiva C Series devices consume a typical 30 mA. A full description of the power modes is shown in Figure 2 on the following page:

Mode → Parameter ↓	Run Mode	Sleep Mode	Deep Sleep Mode	Hibernate (VDD3ON)	Hibernate (RTC)	Hibernate (no RTC)
I _{DD}	30 mA [#]	4.5 mA	600 µA*	5 µA	1.7 µA	1.6 µA
V _{DD}	3.3 V	3.3 V	3.3 V	3.3 V (for GPIO state ret)	0 V	0 V
V _{BAT}	N/A	N/A	N/A	3 V	3 V	3 V
System Clock	80 MHz with PLL	16 MHz no PLL	30 kHz	Off	Off	Off
Core	Powered On	Powered On	Powered On	Off	Off	Off
	Clocked	Not Clocked	Not Clocked	Not Clocked	Not Clocked	Not Clocked
Peripherals	All Off	All Off	All Off	All Off	All Off	All Off

[#] Specs provided are nominal, running from Flash

* Preliminary, subject to change

Figure 2. A full description of the power modes available on Tiva C Series MCUs

Tiva C Series microcontrollers: The right devices for your application

With more than 50 Tiva C Series ARM® MCUs in production today, the TM4C123x series represents the beginning of a much broader platform of Cortex™-M4 implementations from TI.

A few key points from the Tiva C Series have been highlighted: floating-point performance, the integrated analog, the integrated memory, and the low power consumption. Many of these advantages come as a result of either integrating the new ARM Cortex-M4 core, leveraging the TI analog design expertise, or as a result from using TI's differentiated 65-nm process technology.

For the future, customers can expect a roadmap that leads to higher integration, more performance and connectivity, and even lower power. To evaluate the current Tiva C Series devices, TI offers the Tiva C Series EK-TM4C123GXL Launchpad Evaluation Kit, priced at \$12.99 USD, which includes all the hardware and software to get started in 10 minutes or less.

Find out more about TI's Tiva ARM MCUs, tools and software

Tiva C Series MCUs: www.ti.com/tiva-c-series

TivaWare software libraries: www.ti.com/tivaware

Tiva C Series EK-TM4C123GXL Launchpad evaluation kit: www.ti.com/ek-tm4c123gxl

Tiva C Series TM4C123x data sheet: www.ti.com/tm4c123x-ds

Make the Switch to Texas Instruments MCUs: www.ti.com/make-the-switch

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

C2000, Tiva and TivaWare are trademarks and Stellaris is a registered trademark of Texas Instruments Incorporated. All other trademarks are the property of their respective owners.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products	Applications		
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com	TI E2E Community	
OMAP Applications Processors	www.ti.com/omap	e2e.ti.com	
Wireless Connectivity	www.ti.com/wirelessconnectivity		