

# Driver Examples on the DM642 EVM

Video and Imaging Systems

## **ABSTRACT**

The video driver example suite has twelve examples that illustrate the use of the video driver on the DM642 Evaluation Module (EVM). The examples cover all supported video capture- and display formats, and are grouped in seven project categories:

- NTSC capture and display
- PAL capture and display
- 16-bit RGB565 VGA display and NTSC/PAL capture
- 8-bit grayscale VGA display and NTSC/PAL capture
- 480p/720p/1080i High-definition display and NTSC/PAL capture
- Capture scaling using the scaling capability of the Phillips SAA7115 video decoder
- Run-time switching of video input sources

This application report explains how to build and run the examples and how to modify an existing project to support a different format.

	Contents	
1	Overview	2
2	Building and Running the Examples	3
	List of Figures	
1	Hardware Setup	4
2	Configuration Drop-Down List	5
	List of Tables	
1	Projects, Configurations, and Supported Video Formats	2
2	Configurations and Supported Scaling Project Formats	3



## 1 Overview

The video driver examples are located under ti\boards\evmdm642\examples\video\driver. There are five projects in the driver directory:

- ntsc.pjt for NTSC capture and display.
- pal.pjt for PAL capture and display.
- vga.pjt for 16-bit RGB565 VGA display and NTSC/PAL capture.
- hd.pjt for high-definition display and NTSC/PAL capture.
- scaling.pjt for capture scaling using the scaling capability of the Phillips SAA7115 video decoder.
- grayscale.pjt for 8-bit grayscale VGA display.
- switchcamera.pjt for run-time switching of video inputs of the SAA7115s.

Each of the first four projects has three configurations:

- DISPLAY\_ONLY: Running color bars display
- LOOPBACK: Single-channel capture and display loop-back
- LOOPBACK\_PIP: Dual-channel capture and picture-in-picture display loop-back

Table 1 summarizes the projects, configurations, and supported video formats. The formats in bold are default settings of the examples

Table 1. Projects, Configurations, and Supported Video Formats

		DISPLAY_ONLY	LOOPBACK	LOOPBACK_PIP	
NTSC	Display		NTSC with BT.656 embedded sync. NTSC with external timing control.		
	Capture	NTSC with BT656 embed external timing control.	NTSC with BT656 embedded sync. NTSC with external timing control.		
PAL	Display		PAL with BT.656 embedded sync. PAL with external timing control.		
	Capture		PAL with BT656 embedded sync. PAL with external timing control.		
VGA	Display	RGB566 640x480 @60Hz RGB565 800x600 @60Hz RGB565 1024x768 @60H	z		
	Capture		NTSC with BT656 embedded sync. NTSC with external timing control.		
HD	Display	480p@60fps 720p@60fps <b>1080i@30fps</b>			
	Capture		NTSC with BT656 embedded sync. NTSC with external timing control.		



Table 2 summarizes the configurations and supported formats for the scaling project. The formats in bold are default settings of the examples.

Table 2. Configurations and Supported Scaling Project Formats

Video source format	Configurations			
(camera, DVD player, etc.)	scaling_NTS C	scaling_PAL	scaling_USE R	
NTSC	CIF, QCIF, SQCIF, SIF, NTSC640 (square pixel)		352x240 or any resolution that is a scale-down. The scaled frame can be either inter- laced or pro- gressive.	
PAL		CIF, QCIF, SQCIF, SIF, PAL768 (square pixel)	Any resolution that is a scale-down.	

The scaling example uses the hardware scaler in SAA7115. It can be easily modified to support different image sizes such as VGA, SIF, CIF, QCIF, and any user defined image sizes. For more information, please refer to the comments in the video\_scaling.c file located at \TI\_DIR\boards\evmdm642\examples\video\driver\test.

The grayscale display example illustrates how to display 8-bit grayscale image using the color look-up table of the SAA7105. By default, the input format is NTSC composite and the output format is 640x480 VGA.

The switchcamera project shows how to switch among video inputs of the SAA7115s while still keeping video source in synchronization with the DSP's video port and EDMA. This is one of the new features supported by the updated video capture driver. The default video format is NTSC, but it can be easily modified to support PAL.

## 2 Building and Running the Examples

### 2.1 Hardware Setup

To run the examples, the hardware must be set up properly.

- 1. The DM642 EVM must be connected to the appropriate power source
- 2. The XDX510/560 emulator must be connected to the JTAG pins to download the demonstration code to the board and control it from Code Composer Studio™ Integrated Development Environment (IDE).

#### For video input:

- The RCA connector designated as Composite Video In must be connected to an NTSC (PAL) video source.
- 2. (Optional, for the LOOPBACK\_PIP configurations) The RCA connector designated as Composite Video In II must be connected to NTSC (PAL) video source.

#### For video output:

- 1. For NTST and PAL examples (ntsc.pjt and pal.pjt), the RCA connector designated as Composite Video Out (Blue) must be connected to an NTSC and/or a PAL-compatible TV monitor.
- 2. For VGA examples (vga.pjt), the D-Sub 15 connector designated as RGB Video Out must be connected to a regular computer monitor that supports XGA, SVGA, and VGA resolutions at 60 Hz.



3. For high definition examples (hd.pjt), all three RCA connector designated as Component Out Y/G, Component Out Pr/R and Component Out Pb/B, respectively, must be connected to a high definition TV monitor that can support the 480p, 720p, and 1080i resolutions.

Figure 1 shows the setup to run NTSC/PAL examples in DISPLAY\_ONLY and LOOPBACK configurations.




Figure 1. Hardware Setup

# 2.2 Building the Examples

The simplest way to build all examples is to run the build.bat file in the driver directory from the Windows command interpreter. Use the "-a" option for rebuild all.

The simplest way to build all examples is to run the build.bat file in the driver directory from Windows command interpreter. Use the "-a" option for rebuild all.

To rebuild an individual example:

- Start Code Composer Studio™ IDE on your PC.
- 2. Select Project-> Open to open the project to be rebuilt from the examples\video\driver folder.
- 3. Select the configuration that needs to be rebuilt from the configuration drop-down list. The default configuration is XXXX\_DISPLAY\_ONLY.






Figure 2. Configuration Drop-Down List

4. Select Project -> Build or Project -> Rebuild All to re-build the project for the selected configuration

# 2.3 Modifying a Project to Support a Different Video Format

As an example, the following steps explain how to change the video display format in the VGA project (vga.pjt) from the default XGA(1024x768) format to SVGA(800x600) format.

- 1. Follow steps 1, 2, and 3 in Section 2.2 above to open the vga.pjt project under the examples/video/driver directory and select the configuration to be modified.
- 2. In line 64, change EVMDM642\_DIS\_PARAMS\_CHAN\_RGB565\_DEFAULT(XGA) to EVMDM642\_DIS\_PARAMS\_CHAN\_RGB565\_DEFAULT(SVGA).
- 3. In line 67, change EVMDM642\_DIS\_PARAMS\_SAA7105\_RGB565\_DEFAULT(XGA) to EVMDM642\_DIS\_PARAMS\_SAA7105\_RGB565\_DEFAULT(SVGA)
- 4. Select Project -> Build or Project -> Build to build the new executable.

For the scaling project, the following steps change the captured image size from the default CIF resolution to QCIF resolution.

- 1. Follow steps 1, 2, and 3 in Section 2.2 above to open the scaling.pjt project under the examples/video/driver directory and select the configuration scaling NTSC or scaling PAL.
- 2. Select Project->Build Options, in the pop-up window, and select Preprocessor, under Category.
- 3. Change \_CIF in the text box labeled as defined symbols to \_QCIF. Click OK.
- 4. Rebuild the project.

For the scaling project, to change the image resolution to a non-standard size, such as 480 x480:

- 1. Follow steps 1, 2, and 3 in Section 2.2 to open the scaling.pjt project under the examples/video/driver directory and select the configuration scaling\_USER.
- 2. Open the evmdm642\_capParamsSDTVDefault.h file under examples\video\driver\settings\ drivers\include\evmdm642\_capParamsSDTVDefault.h.
- 3. Search for USER\_LINE\_SZ, USER\_NUM\_LINES\_PER\_FLD and USER\_INTERLACED, modify the values of those as necessary. For example, change USER\_LINE\_SZ from 352 to 560, change NUM\_LINES\_PER\_FLD from (240>>1) to (360>>1), and change USER\_INTERLACED from FALSE to TRUE.
- 4. Save the file. Rebuild the project.

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2004, Texas Instruments Incorporated