



## 1 Test Prerequisites

### 1.1 Voltage and Current Requirements


**Table 1. Voltage and Current Requirements**

PARAMETER	SPECIFICATIONS
$V_{IN}$	9.0 V - 16.0 V (5.0 V - 24.0 V operational)
$V_{OUT}$	45.0V @ 1.0 A
Nominal switching frequency	350 kHz (up to 390 kHz with dithering)

## 2 Testing and Results

### 2.1 Efficiency Graphs

Figure 1. Efficiency at 9.0 V, 12.0 V and 16.0 V in



### 2.2 Efficiency Data

Table 2. Efficiency data for the 9.0 V input

Voltage [V]	Current [A]	Power [W]	Voltage [V]	Current [A]	Power [W]	Losses [W]	Efficiency [%]
8.998	1.0997	9.8951	44.93	0.2018	9.0669	0.828	91.6
8.998	2.126	19.1297	44.82	0.4014	17.9907	1.139	94.0
8.997	3.167	28.4935	44.71	0.601	26.8707	1.623	94.3
8.997	4.225	38.0123	44.63	0.8006	35.7308	2.282	94.0
8.997	5.317	47.8370	44.57	1.0029	44.6993	3.138	93.4

Table 3. Efficiency data for the 12.0 V input


Voltage [V]	Current [A]	Power [W]	Voltage [V]	Current [A]	Power [W]	Losses [W]	Efficiency [%]
12	0.8349	10.0188	45.01	0.2018	9.0830	0.936	90.7
12	1.599	19.1880	44.94	0.4014	18.0389	1.149	94.0
12	2.367	28.4040	44.86	0.6009	26.9564	1.448	94.9
12	3.144	37.7280	44.78	0.8006	35.8509	1.877	95.0
12	3.937	47.2440	44.72	1.0028	44.8452	2.399	94.9

**Table 4. Efficiency data for the 16.0 V input**

Voltage [V]	Current [A]	Power [W]	Voltage [V]	Current [A]	Power [W]	Losses [W]	Efficiency [%]
15.99	0.6205	9.9218	45.04	0.2018	9.0891	0.833	91.6
15.99	1.206	19.2839	45.01	0.4013	18.0625	1.221	93.7
15.99	1.779	28.4462	44.95	0.601	27.0150	1.431	95.0
15.99	2.355	37.6565	44.9	0.8005	35.9425	1.714	95.4
15.99	2.94	47.0106	44.84	1.0028	44.9656	2.045	95.6

### 2.3 Thermal Images

**Figure 2. Thermal image of the PCB's top side at 12.0 V in, 45.0 V out and 1.0 A load current.**




### 2.4 Dimensions

Circuit: smaller than 30 mm x 30 mm

### 3 Waveforms

#### 3.1 Switching


Figure 3. Switching Node at 12.0 Vin, 45.0 V out and 1.0 A load current.



- Ch2: Switching node signal [scale: 10.0V/div, 1.0us/div]

### 3.2 Output Voltage Ripple


Figure 4. AC-coupled output voltage signal at 9.0V, 12.0V and 16.0V in.



- M1: 5.38 V peak-peak ripple [scale: 2.0 V/div, 2.0us/div]
- M2: 4.29 V peak-peak ripple [scale: 2.0 V/div, 2.0us/div]
- M3: 3.74 V peak-peak ripple [scale: 2.0 V/div, 2.0us/div]

### 3.3 Input Voltage Ripple


Figure 5. AC-coupled input voltage signal at 9.0V, 12.0V and 16.0V in.



- M1: 627 mV peak-peak ripple [scale: 200 mV/div, 2.0us/div]
- M2: 483 mV peak-peak ripple [scale: 200 mV/div, 2.0us/div]
- M3: 384 mV peak-peak ripple [scale: 200 mV/div, 2.0us/div]

### 3.4 Bode Plot


Figure 6. Bode plot at 9.0 V, 12.0 V and 16.0 V in.



- 9.0V in, 1.0A load current: f<sub>co</sub> 726Hz, 82deg phase margin, -29dB gain margin
- 12.0V in, 1.0A load current: f<sub>co</sub> 974Hz, 84deg phase margin, -29dB gain margin
- 16.0V in, 1.0A load current: f<sub>co</sub> 1.31kHz, 86deg phase margin, -29dB gain margin

### 3.5 Load Transients


Figure 7. Load transient from 0.5 A to 1.0 A at 12.0 V in results in 1.51 V undershoot (3.3%) and 1.50 V overshoot (3.3%).



- Ch1: output current) [scale: 0.5A/div, 1.0ms/div]
- Ch3: AC-coupled output voltage, bw limited (20MHz) [scale: 1.0V/div, 1.0ms/div]

### 3.6 Start-up Sequence


Figure 8. Start-up sequence at 12.0 V in with no load attached.



- Ch1: input voltage [scale: 10.0V/div, 10.0ms/div]
- Ch2: output voltage [scale: 10.0V/div, 10.0ms/div]

### 3.7 Undervoltage Protection

Figure 9. Undervoltage protection with a 1.0 A load attached.



- Ch1: input voltage [scale: 10.0V/div, 10.0ms/div]
- Ch2: output voltage [scale: 10.0V/div, 10.0ms/div]

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2021, Texas Instruments Incorporated