

# How to Protect Industrial Human-machine Interfaces from Electrical Overstress

---



Jeffrey Craig

A human-machine interface (HMI) gives people the ability to assess and control industrial automation equipment. HMI devices are often connected to programmable logic controllers (PLCs) and are an essential part of the control structure for the manufacturing of many products we use every day.

HMI solutions need to be very robust to properly function in often hazardous manufacturing environments. They are at particular risk for electrical overstress (EOS) because of the many electrical transients that exist in industrial or manufacturing environments. In this post, I will discuss the standards used to govern devices that protect against aggressive electrical transients and a particular device type often chosen to protect HMI solutions.

## The IEC 61000-4-X Electrical Transient Immunity Standard

When you look at data sheets for semiconductor devices used in HMI applications (such as Ethernet PHYs and microprocessors), you'll see human-body model (HBM) and charged-device model (CDM) Electrostatic Discharge (ESD) ratings. The HBM rating provides an indication of the chip's resilience to ESD damage from human handling, while the CDM rating is related to the chip's ability to resist ESD damage during automated manufacturing.

Neither HBM nor CDM device ratings address the need for overall system transient immunity. So the International Electrotechnical Commission (IEC) released system-level transient immunity standards to ensure that complete systems, like HMIs, would be protected against EOS. They are:

- IEC 61000-4-2: electrostatic discharge immunity test.
- IEC 61000-4-4: electrical fast transient (EFT) immunity test.
- IEC 61000-4-5: surge immunity test.

Compared to CDM and HBM, the IEC 61000-4-2 standard tests to higher levels of ESD energy; see [Figure 1](#). The IEC 61000-4-4 and IEC 61000-4-5 standards provide an extra layer of transient protection to ensure a robust final product.





Figure 1. ESD Test Comparison

### Transient Voltage Suppressors

Transient voltage suppressor (TVS) diodes deliver IEC 61000-4-x system-level protection for industrial applications, including HMI. TVS diodes should be placed as close as possible to USB, Ethernet, High-Definition Multimedia Interface (HDMI), RS-232/485, Video Graphics Array (VGA), Liquid Crystal Display (LCD), or touch-screen interfaces because each serve as a gateway that allows damaging electrical transients (ESD, EFT, surge) to enter HMI systems. When a TVS diode detects an electrical transient like ESD, it will begin conducting the current of that high-energy transient to ground instead of allowing it to be transmitted into the system. [Figure 2](#) shows how the [TPD4E05U06](#) responds to a +8kV ESD event. Furthermore, engineers can take advantage of the low capacitance and easy straight-through routing package offered by the TPD4E05U06 for interfaces found in HMI applications (HDMI, Ethernet, LCD and USB).



**Figure 2. TPD4E05U06 IEC 61000-4-2 Clamping Voltage, +8kV Contact**

To learn more about Texas Instruments protection devices, visit the [ESD protection overview page](#). The overview page includes additional information about TI protection product families, the [ESD by Interface table](#) which recommends champion parts and links to parametric search by clicking “View Products”.

#### Additional Resources

- Learn more about TI circuit protection devices on the [TI ESD protection diodes landing page](#).
- To learn more about TVS diodes, test setups and layout, check out these application reports:
  - [“ESD Protection Layout Guide.”](#)
  - [“IEC61000-4-x Tests for TI’s Protection Devices.”](#)
  - [“Reading and Understanding an ESD Protection Datasheet.”](#)

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2023, Texas Instruments Incorporated