


Efficiency

The efficiency of the converter is shown below:


								Conv Only	Conv Only
		J1	J1	J1	J3	J3	J3	D1-K	D1-K
Iout	Vout	Iin	Vin	Eff	Iin	Vin	Eff	Vin	Eff
0.00	5.077	0.011	48.00	0.0%	0.011	48.00	0.0%	47.66	0.0%
0.10	5.077	0.022	48.00	48.1%	0.022	48.00	48.1%	47.63	48.5%
0.20	5.077	0.033	48.00	64.1%	0.033	48.00	64.1%	47.61	64.6%
0.30	5.077	0.043	48.00	73.8%	0.043	48.00	73.8%	47.60	74.4%
0.40	5.077	0.054	48.00	78.3%	0.054	48.00	78.3%	47.59	79.0%
0.50	5.077	0.065	48.00	81.4%	0.065	48.00	81.4%	47.58	82.1%
0.75	5.076	0.092	48.00	86.2%	0.092	48.00	86.2%	47.56	87.0%
1.00	5.076	0.120	48.00	88.1%	0.120	48.00	88.1%	47.54	89.0%
1.25	5.076	0.148	48.00	89.3%	0.148	48.00	89.3%	47.52	90.2%
1.50	5.076	0.177	48.00	89.6%	0.176	48.00	90.1%	47.51	91.1%
1.75	5.075	0.205	48.00	90.3%	0.204	48.00	90.7%	47.49	91.7%
2.00	5.075	0.235	48.00	90.0%	0.233	48.00	90.8%	47.47	91.8%
2.30	5.075	0.270	48.00	90.1%	0.268	48.00	90.7%	47.46	91.8%




Ripple and Noise

Ripple measurements taken with 48VIN at J1, 2.3A load, and 20MHz BWL.

Output Ripple (C24), 20mV/div, 2us/div:
Measured 46.3mV pk-pk




Input Ripple (C17), 50mV/div, 2us/div:
Measured 125mV pk-pk



Dynamic Loading

Load Step, 48VIN at J1 100mV/div, 500usec/div
1A to 2A Load Step, 20mA/usec
Measured 381mV peak to peak:




Turn On Response

48VIN, 2.3A Load, 500usec/div:



48VIN, 0A Load, 500usec.div:



Stability (Loop Gain)

The figure below is the loop gain of the converter with a 48V input and 2.3A load. The Bandwidth is 7.4 KHz, the Phase Margin is 59 degrees, and the Gain Margin is 15 dB.






Photo:

TOP:



BOTTOM:



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated