

# PMP40274 Test Results

#### 1 General

#### 1.1 PURPOSE

The PMP40274 is a power module reference design solution for power train applications. The module enables a high efficiency with flyback-CCM synchronous rectifier. The efficiency is >88% at full load. This design features <0.2W standby power. Integrated input UVLO, OVP and output OVP, OCP keeps the whole power system reliability. The design is achieved in a compact form factor (50.8mm X 40.6mm X 15mm).

#### **TEST EQUIPMENTS**

Multi-meter: Fluke Multimeter 287C, Agilent 34401A, Fluke 8845A

DC Source: TDK-Lambda, DC Load: Chroma 63103A

Ambient Temperature at 25DegC

#### 1.2 TEST Setup Photos



Top View of the Board



**Bottom View of the Board** 

# 2 INPUT & Output CHARACTERISTICS

## 2.1: Efficiency data vs Output




Vin(V)	lin(A)	Vout(V)	Iout(A)	Efficiency	Pin(W)
18.149	0.01	5.091	0		0.18
18.265	0.176	5.048	0.4972	0.7808	3.21
18.218	0.329	5.047	0.9981	0.8404	5.99
18.125	0.624	5.046	1.9984	0.8916	11.31
18.025	0.933	5.044	3.0008	0.9000	16.82
17.921	1.247	5.041	4.0025	0.9029	22.35
17.820	1.579	5.034	5.0038	0.8952	28.14
17.721	1.932	5.025	6.0024	0.8809	34.24


Vin(V)	lin(A)	Vout(V)	Iout(A)	Efficiency	Pin(W)
24.367	0.006	5.061	0		0.15
23.991	0.145	5.044	0.4972	0.7209	3.48
23.957	0.255	5.042	0.9981	0.8238	6.11
23.887	0.481	5.038	1.9984	0.8763	11.49
23.810	0.722	5.029	3.0008	0.8779	17.19
23.737	0.949	5.027	4.0025	0.8932	22.53
23.661	1.185	5.026	5.0038	0.8970	28.04
23.579	1.430	5.024	6.0024	0.8944	33.72

Vin(V)	lin(A)	Vout(V)	lout(A)	Efficiency	Pin(W)
36.258	0.004	5.063	0		0.15
36.316	0.103	5.038	0.4972	0.6697	3.74
36.293	0.177	5.030	0.9981	0.7815	6.42
36.248	0.329	5.023	1.9984	0.8417	11.93
36.194	0.493	5.021	3.0008	0.8444	17.84
36.151	0.653	5.017	4.0025	0.8506	23.61
36.107	0.798	5.016	5.0038	0.8711	28.81
36.061	0.947	5.016	6.0024	0.8816	34.15






# 2.2: <u>Startup</u>




CH1=Vin;CH4=Vout; 24Vin Startup with no load






CH1=Vin; CH4=Vout; Startup with Full load

### 2.3: Primary MOSFET Voltage Stress




24Vin, CH1=Vin; CH2=Vprids





CH1=Vin; CH2=Vprids; CH4=Vout; 36Vin

### 2.4: Secondary Synchronous Rectifier MOSFET




CH2=Vsrdrv; 36Vin

### 2.5: Output Voltage Ripple

Note: C8 is replaced by 4pcs 0805 X7R/25V ceramic capacitor for the following output voltage ripple

Test condition: 24Vin 5V/6A full load





Oscilloscope Full Bandwidth

4.00µs


**4** 50.0mV ∿

2.50G次/秒 100k 点 **4** \ 400mV 57月 2 16:49:26


## 2.6: **Dynamic Response**

Test condition: 24Vin, Load step from 1.5A to 3A(25%-50%), 500Hz cycle, 1A/us






#### **Overshoot**



**Undershoot** 


## 2.7: Input Under Voltage Protection





CH1=Vin; CH4=Vout; UVLO 16V

### 2.8: Input Over Voltage Protection




CH1=Vin; CH4=Vout; UVLO 40V


#### 2.9: Frequency Response

Test condition: 24Vin 5V/6A full load





## 2.10: Thermal image



24V Input, output is 6A load (30 minutes) without fan cooling

#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated