

BQ77216xx 具有内部延迟计时器、适用于 3 节至 16 节串联锂离子电池的电压和温度保护器

1 特性

- 3 节至 16 节串联电池保护
- 高精度过压保护
 - $\pm 10\text{mV}$ (25°C 时)
 - $\pm 20\text{mV}$ (0°C 至 60°C 时)
- 3.55V 至 5.1V 的过压保护选项
- 1.0V 至 3.5V 的欠压保护选项
- 开路连接检测
- 过热保护
- 欠温保护
- 支持电池随机连接
- 功能安全型
- 固定内部延迟计时器
- 固定检测阈值
- 固定输出驱动类型，适用于每个 COUT 和 DOUT
 - 高电平有效或低电平有效
 - 高电平有效驱动达 6V
 - 漏极开路，可从外部上拉至 VDD
- 低功耗 $I_{CC} \approx 1\mu\text{A}$ ($V_{\text{CELL(ALL)}} < V_{\text{OV}}$)
- 每个电池输入具有小于 100nA 的低漏电流，且禁用开路检测
- 封装尺寸选项：
 - 24 引脚带引线 TSSOP，引线间距为 0.65mm

2 应用

- 锂离子电池组保护，可应用于：
 - 手持园艺工具
 - 手持电动工具
 - 无线真空吸尘器
 - UPS 备用电池
 - 轻型电动车辆 (电动自行车、电动踏板车、踏板辅助自行车)

3 说明

BQ77216xx 产品系列提供了多种电压和温度监测功能，包括适用于锂离子电池组系统的过压 (OVP)、欠压 (UVP)、开路 (OW)、欠温 (UT) 和过热 (OT) 保护。可独立监控每节电池是否具有过压、欠压和开路情况。通过增加外部 NTC 热敏电阻，该器件可以检测到欠温和过热情况。

当检测到存在过压、欠压、开路、欠温或过热情况时，BQ77216xx 器件将立即启动内部延迟计时器。延迟计时器过期时，将触发相应的输出进入其工作状态 (根据配置的不同，为高电平或低电平状态)。

如果检测到过压故障，将触发 COUT 引脚；如果检测到欠压故障，将触发 DOUT 引脚。如果检测到过热或开路故障，则同时触发 DOUT 和 COUT 引脚。为了实现更快速的产品线测试，BQ77216xx 器件可提供延迟时间大幅缩短的客户测试模式 (CTM)。

封装信息

器件型号	封装	本体尺寸 (标称值)
BQ77216xx ⁽¹⁾	TSSOP (24)	4.40mm × 7.80mm (6.40mm × 7.80mm，含引线)

(1) 如需了解可用封装和预编程器件版本，请参阅数据表末尾的可订购产品附录和 “[Device Comparison Table](#)”。




图 3-1. 简化版原理图



Table of Contents

1 特性	1	8 Application and Implementation	14
2 应用	1	8.1 Application Information.....	14
3 说明	1	8.2 Systems Example.....	17
4 Device Comparison Table	3	9 Power Supply Recommendations	18
5 Pin Configuration and Functions	5	10 Layout	19
6 Specifications	6	10.1 Layout Guidelines.....	19
6.1 Absolute Maximum Ratings	6	10.2 Layout Example.....	19
6.2 ESD Ratings	6	11 Device and Documentation Support	20
6.3 Recommended Operating Conditions	6	11.1 第三方产品免责声明.....	20
6.4 Thermal Information	7	11.2 接收文档更新通知.....	20
6.5 DC Characteristics	7	11.3 支持资源.....	20
6.6 Timing Requirements.....	9	11.4 Trademarks.....	20
7 Detailed Description	10	11.5 静电放电警告.....	20
7.1 Overview.....	10	11.6 术语表.....	21
7.2 Functional Block Diagram.....	10	12 Revision History	21
7.3 Feature Description.....	10	13 Mechanical, Packaging, and Orderable	
7.4 Device Functional Modes.....	12	Information	21

4 Device Comparison Table

表 4-1. BQ77216xx Device Comparison

PART NUMBER	T _A	PACKAGE	PACKAGE DESIGNATOR	OVP (V)	OV HYSTERESIS (V)	OVP DELAY	UVP (V)	UVP DELAY
BQ7721600	- 40°C to 110°C	24-Pin TSSOP	PW	4.325	0.100	1s	2.25	1s
BQ7721602	- 40°C to 110°C	24-Pin TSSOP	PW	4.325	0.100	1s	2.25	1s
BQ7721603	- 40°C to 110°C	24-Pin TSSOP	PW	4.3	0.100	2s	2	2s
BQ7721605	- 40°C to 110°C	24-Pin TSSOP	PW	4.225	0.100	1s	2.6	1s
BQ7721606	- 40°C to 110°C	24-Pin TSSOP	PW	4.275	0.100	1s	2.5	1s
BQ7721607	- 40°C to 110°C	24-Pin TSSOP	PW	4.25	0.100	4s	2.5	2s
BQ7721609	- 40°C to 110°C	24-Pin TSSOP	PW	4.35	0.200	4s	Disabled	
BQ7721610	- 40°C to 110°C	24-Pin TSSOP	PW	4.25	0.100	4s	2.5	2s
BQ7721611	- 40°C to 110°C	24-Pin TSSOP	PW	3.8	0.200	4s	1.5	1s
BQ7721612	- 40°C to 110°C	24-Pin TSSOP	PW	3.6	0.200	2s	2.0	2s
BQ7721613	- 40°C to 110°C	24-Pin TSSOP	PW	4.25	0.100	4s	2.0	2s
BQ7721614	- 40°C to 110°C	24-Pin TSSOP	PW	3.9	0.100	4s	1.85	2s
BQ7721615	- 40°C to 110°C	24-Pin TSSOP	PW	4.23	0.100	4s	2.0	2s
BQ7721616	- 40°C to 110°C	24-Pin TSSOP	PW	4.18	0.100	4s	2.0	2s
BQ7721617	- 40°C to 110°C	24-Pin TSSOP	PW	3.8	0.100	2s	1.5	2s
BQ7721618	- 40°C to 110°C	24-Pin TSSOP	PW	4.22	0.200	4s	2.2	2s
BQ77216xx ⁽¹⁾	- 40°C to 110°C	24-Pin TSSOP	PW	3.55 – 5.10	0.100, 0.200	0.25s, 0.5s, 1s, 2s, 4s	1.0 – 3.5	0.25s, 0.5s, 1s, 2s

表 4-2. BQ77216xx Device Comparison (continued)

PART NUMBER	UV HYSTERESIS (V)	OTC (°C)	UTC (°C)	OW	LATCH	OUTPUT DRIVE	TAPE AND REEL
BQ7721600	0.100	70	NA	Enabled	Disabled	Active Low	BQ7721600PWR
BQ7721602	0.100	70	NA	Enabled	Disabled	Active High, 6V Drive	BQ7721602PWR
BQ7721603	0.100	75	NA	Enabled	Disabled	Active High, 6V Drive	BQ7721603PWR
BQ7721605	0.200	75	NA	Disabled	Disabled	Active High, 6V Drive	BQ7721605PWR
BQ7721606	0.200	75	NA	Disabled	Disabled	Active High, 6V Drive	BQ7721606PWR
BQ7721607	0.100	83	- 30	Enabled	Disabled	Active High, 6V Drive	BQ7721607PWR
BQ7721609	Disabled	83	NA	Enabled	Disabled	Active High, 6V Drive	BQ7721609PWR
BQ7721610	0.100	83	NA	Enabled	Disabled	Active High, 6V Drive (COUT) Active Low (DOUT)	BQ7721610PWR
BQ7721611	0.200	70	NA	Disabled	Disabled	Active High, 6V Drive	BQ7721611PWR
BQ7721612	0.200	75	NA	Disabled	Disabled	Active Low	BQ7721612PWR
BQ7721613	0.200	83	- 30	Enabled	Disabled	Active High, 6V Drive	BQ7721613PWR
BQ7721614	0.100	75	NA	Enabled	Disabled	Active High, 6V Drive	BQ7721614PWR

表 4-2. BQ77216xx Device Comparison (continued) (续)

PART NUMBER	UV HYSTERESIS (V)	OTC (°C)	UTC (°C)	OW	LATCH	OUTPUT DRIVE	TAPE AND REEL
BQ7721615	0.200	83	-20	Disabled	Disabled	Active High, 6V Drive	BQ7721615PWR
BQ7721616	0.200	80	-20	Disabled	Disabled	Active High, 6V Drive	BQ7721616PWR
BQ7721617	0.200	NA	NA	Disabled	Disabled	Active High, 6V Drive	BQ7721617PWR
BQ7721618	0.200	83	-20	Disabled	Disabled	Active High, 6V Drive	BQ7721618PWR
BQ77216xx ⁽¹⁾	0.100, 0.200	62, 65, 70, 75, 80, 83, Disabled	-30, -20, -10, 0, Disabled	Enabled, Disabled	Enabled, Disabled	Open Drain Active Low, Active High 6V, Active High VDD	TBD

(1) Contact TI for more information.

5 Pin Configuration and Functions




表 5-1. 24-Lead Pin Functions

NO.	NAME	TYPE	DESCRIPTION ⁽¹⁾
1	NC	—	Not electrically connected and can be left floating
2	VDD	P	Power supply
3	V16	I	Sense input for positive voltage of the sixteenth cell from the bottom of the stack
4	V15	I	Sense input for positive voltage of the fifteenth cell from the bottom of the stack
5	V14	I	Sense input for positive voltage of the fourteenth cell from the bottom of the stack
6	V13	I	Sense input for positive voltage of the thirteenth cell from the bottom of the stack
7	V12	I	Sense input for positive voltage of the twelfth cell from the bottom of the stack
8	V11	I	Sense input for positive voltage of the eleventh cell from the bottom of the stack
9	V10	I	Sense input for positive voltage of the tenth cell from the bottom of the stack
10	V9	I	Sense input for positive voltage of the ninth cell from the bottom of the stack
11	V8	I	Sense input for positive voltage of the eighth cell from the bottom of the stack
12	V7	I	Sense input for positive voltage of the seventh cell from the bottom of the stack
13	V6	I	Sense input for positive voltage of the sixth cell from the bottom of the stack
14	V5	I	Sense input for positive voltage of the fifth cell from the bottom of the stack
15	NC	—	Not electrically connected and can be left floating
16	NC	—	Not electrically connected and can be left floating
17	V4	I	Sense input for positive voltage of the fourth cell from the bottom of the stack
18	V3	I	Sense input for positive voltage of the third cell from the bottom of the stack
19	V2	I	Sense input for positive voltage of the second cell from the bottom of the stack
20	V1	I	Sense input for positive voltage of the lowest cell in the stack
21	VSS	P	Electrically connected to IC ground and negative terminal of the lowest cell in the stack
22	COUT	O	Output drive for overvoltage, open wire, undertemperature, and overtemperature. It can be left floating if not used.
23	DOUT	O	Output drive for undervoltage, open wire, undertemperature, and overtemperature. It can be left floating if not used.
24	TS	I	Temperature sensor input. If not used, connect it with a 10k Ω resistor to VSS.

(1) I = Input, O = Output, P = Power Connection

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		MIN	MAX	UNIT
Supply voltage range	VDD – VSS	– 0.3	85	V
Input voltage range	Vn – VSS where n = 1 to 16	– 0.3	85	V
	TS	– 0.3	1.5	V
Output voltage range	COUT – VSS, DOUT – VSS	– 0.3	85	V
Functional temperature, T _{FUNC}		– 40	110	°C
Storage temperature, T _{STG}		– 65	150	°C

- (1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

6.2 ESD Ratings

			VALUE	UNIT
V _(ESD)	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	±2000	V
		Charged device model (CDM), per ANSI/ESDA/JEDEC JS-002, all pins	±500	

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V _{DD}	Supply voltage ⁽¹⁾	5		75	V
V _{IN}	Input voltage range of Vn – Vn-1 where n = 2 to 16 and V1 – VSS	0		5	V
	TS	0		1.5	V
V _{CTM}	Customer Test Mode Entry V _{DD} > V16 + V _{CTM}	12		13	V
C _{TS}	Total capacitance on the TS Pin			200	pF
T _A	Ambient temperature	– 40		85	°C
T _J	Junction temperature	– 65		150	°C

- (1) V_{DD} is equal to top of stack voltage

6.4 Thermal Information

THERMAL METRIC ⁽¹⁾		DEVICE	UNIT
		PW (TSSOP)	
		24 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	97.8	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	40.5	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	53.1	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	4.3	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	52.7	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	NA	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

6.5 DC Characteristics

Typical values stated where $T_A = 25^\circ\text{C}$ and $V_{DD} = 58\text{V}$, MIN/MAX values stated where $T_A = -40^\circ\text{C}$ to 85°C and $V_{DD} = 5\text{V}$ to 75V (unless otherwise noted).

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
OVER VOLTAGE PROTECTION (OV)						
V_{OV}	OV Detection Range		3.55		5.1	V
V_{OV_STEP}	OV Detection Steps			25		mV
V_{OV_HYS}	OV Detection Hysteresis	Selected OV Hysteresis depends on the part number. See the device selection table for details.		$V_{OV} - 100$		mV
		Selected OV Hysteresis depends on the part number. See the device selection table for details.		$V_{OV} - 200$		mV
V_{OV_ACC}	OV Detection Accuracy	$T_A = 25^\circ\text{C}$	- 10		10	mV
	OV Detection Accuracy	$0^\circ\text{C} \leq T_A \leq 60^\circ\text{C}$	- 20		20	mV
	OV Detection Accuracy	$-40^\circ\text{C} \leq T_A \leq 110^\circ\text{C}$	- 50		50	mV
UNDER VOLTAGE PROTECTION (UV)						
V_{UV}	UV Detection Range		1.0		3.5	V
V_{UV_STEP}	UV Detection Steps			50		mV
V_{UV_HYS}	UV Detection Hysteresis	Selected UV Hysteresis depends on the part number. See the device selection table for details.		$V_{UV} + 100$		mV
		Selected UV Hysteresis depends on the part number. See the device selection table for details.		$V_{UV} + 200$		mV
V_{UV_ACC}	UV Detection Accuracy	$T_A = 25^\circ\text{C}$	- 30		30	mV
	UV Detection Accuracy	$-40 \leq T_A \leq 110^\circ\text{C}$	- 50		50	mV
V_{UV_MIN}	UV Detection Disabled Threshold	$V_n - V_{n-1}$ where $n = 2$ to 16 and $V_1 - V_{SS}$	450	500	550	mV
OVER TEMPERATURE PROTECTION (OT)						
T_{OT}	OT Detection Range	Available options: 62°C , 65°C , 70°C , 75°C , 80°C , 83°C	62.0		83.0	°C

6.5 DC Characteristics (续)

Typical values stated where $T_A = 25^\circ\text{C}$ and $V_{DD} = 58\text{V}$, MIN/MAX values stated where $T_A = -40^\circ\text{C}$ to 85°C and $V_{DD} = 5\text{V}$ to 75V (unless otherwise noted).

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
R _{OT_EXT}	OT Detection External Resistance	62°C		2850		Ω
		65°C		2570		
		70°C		2195		
		75°C		1915		
		80°C		1651		
		83°C		1525		
T _{TOT_ACC} (1)	OT Detection Accuracy		- 5		5	°C
T _{TOT_HYS} (2)	OT Detection Hysteresis			- 10		°C
				4186		Ω
				3530		Ω
R _{NTC}	Internal Pullup Resistor	After TI Factory Trim	19.5	20	20.6	k Ω
OPEN WIRE PROTECTION (OW)						
V _{OW}	OW Detection Threshold	V _n < V _{n-1} where n = 2 to 16		- 200		mV
		V1 - VSS		500		mV
V _{OW_HYS}	OW Detection Hysteresis	V _n < V _{n-1} where n = 1 to 16		V _{OW} +100		mV
V _{OW_ACC}	OW Detection Accuracy	- 40 °C ≤ T _A ≤ 110°C	- 25		25	mV
SUPPLY AND LEAKAGE CURRENT						
I _{CC}	Supply Current	No fault detected		2	3.5	μA
I _{IN} (2)	Input Current at V _x Pins	V _n - V _{n-1} and V1 - VSS = 4V, where n = 2 to 16, Open Wire Enabled	- 0.3		0.3	μA
		V _n - V _{n-1} and V1 - VSS = 4V, where n = 2 to 16, Open Wire Disabled	- 0.1		0.1	μA
OUTPUT DRIVE, COUT and DOUT, CMOS ACTIVE HIGH VERSIONS ONLY						
V _{OUT_AH}	Output Drive Voltage for COUT and DOUT, Active High 6V	V _n - V _{n-1} or V1 - VSS > V _{OV} , where n = 2 to 16, VDD = 58V, I _{OH} = 100μA measured out of COUT, DOUT pin	6			V
	Output Drive Voltage for COUT and DOUT, Active High VDD	VDD - V _{COUT} or V _{DOUT} , V _n - V _{n-1} or V1 - VSS > V _{OV} , where n = 2 to 16, I _{OH} = 10μA measured out of COUT, DOUT pin	0	1	1.5	V
	Output Drive Voltage for COUT and DOUT, Active High 6V	VDD - V _{COUT} or V _{DOUT} , if 15 of 16 cells are short-circuited and only one cell remains powered and > V _{OV} , VDD = V _x (cell voltage), I _{OH} = 100μA,	0	1	1.5	V
	Output Drive Voltage for COUT and DOUT, Active High 6V and VDD	V _n - V _{n-1} and V1 - VSS < V _{OV} , where n = 2 to 16, VDD = 58V, I _{OH} = 100μA measured into pin		250	400	mV
R _{OUT_AH}	Internal Pullup Resistor		80	100	120	k Ω
I _{OUT_AH_H}	OUT Source Current (during OV)	V _n - V _{n-1} or V1 - VSS > V _{OV} , where n = 2 to 16, VDD = 58V, OUT = 0V. Measured out of COUT, DOUT pin			4.5	mA
I _{OUT_AH_L}	OUT Sink Current (no OV)	V _n - V _{n-1} and V1 - VSS < V _{OV} , where n = 2 to 16, VDD = 58V, OUT = VDD. Measured into COUT, DOUT pin	0.3		3	mA
OUTPUT DRIVE, COUT and DOUT, NCH OPEN DRAIN ACTIVE LOW VERSIONS ONLY						

6.5 DC Characteristics (续)

Typical values stated where $T_A = 25^\circ\text{C}$ and $V_{DD} = 58\text{V}$, MIN/MAX values stated where $T_A = -40^\circ\text{C}$ to 85°C and $V_{DD} = 5\text{V}$ to 75V (unless otherwise noted).

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
$V_{\text{OUT_AL}}$	Output Drive Voltage for COUT and DOUT, Active Low	$V_n - V_{n-1}$ or $V_1 - V_{SS} > V_{\text{OV}}$, where $n = 2$ to 16 , $V_{DD} = 58\text{V}$, $I_{\text{OH}} = 100\mu\text{A}$ measured into COUT, DOUT pin		250	400	mV
$I_{\text{OUT_AL_L}}$	OUT Source Current (during OV)	$V_n - V_{n-1}$ or $V_1 - V_{SS} > V_{\text{OV}}$, where $n = 2$ to 16 , $V_{DD} = 58\text{V}$, $\text{OUT} = V_{DD}$. Measured into COUT, DOUT pin	0.3		3	mA
$I_{\text{OUT_AL_H}}$	OUT Sink Current (no OV)	$V_n - V_{n-1}$ and $V_1 - V_{SS} < V_{\text{OV}}$, where $n = 2$ to 16 , $V_{DD} = 58\text{V}$, $\text{OUT} = V_{DD}$. Measured out of COUT, DOUT pin			100	nA

- (1) Assured by Design. This accuracy assumes the external resistance is within $\pm 2\%$ of the $R_{\text{OT_EXT}}$ values for the corresponding temperature threshold.
- (2) Assured by Design

6.6 Timing Requirements

Typical values stated where $T_A = 25^\circ\text{C}$ and $V_{DD} = 58\text{V}$, MIN/MAX values stated where $T_A = -40^\circ\text{C}$ to 85°C and $V_{DD} = 5\text{V}$ to 85V (unless otherwise noted).

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
$t_{\text{OV_DELAY}}$	OV Delay Time			0.25		s
				0.5		s
				1		s
				2		s
				4		s
$t_{\text{UV_DELAY}}$	UV Delay Time			0.25		s
				0.5		s
				1		s
				2		s
$t_{\text{OT_DELAY}}$	OT Delay Time			4		s
$t_{\text{OW_DELAY}}$	OW Delay Time			4		s
$t_{\text{DELAY_ACC}}$	Delay Time Accuracy	For 0.25s, 0.5s delays	- 128		128	ms
$t_{\text{DELAY_ACC}}$	Delay Time Accuracy	For 1s delays	- 150		150	ms
$t_{\text{DELAY_DR}}$	Delay time drift across operating temp	For all delays other than 0.25s, 0.5s, 1s delays	- 10%		10%	
$t_{\text{CTM_DELAY}}$	Fault Detection Delay Time during Customer Test Mode	See Customer Test Mode.		50		ms


7 Detailed Description

7.1 Overview

The BQ77216xx family of devices provides a range of voltage and temperature monitoring including overvoltage (OVP), undervoltage (UVP), open wire (OW), and overtemperature (OT) protection for Li-ion battery pack systems. Each cell is monitored independently for overvoltage, undervoltage, and open-wire conditions. With the addition of an external NTC thermistor, the device can detect overtemperature conditions. An internal delay timer is initiated upon detection of an overvoltage, undervoltage, open-wire, or overtemperature condition. Upon expiration of the delay timer, the respective output is triggered into its active state (either high or low, depending on the configuration). The overvoltage triggers the COUT pin if a fault is detected, and undervoltage triggers the DOUT pin if a fault is detected. If an undertemperature, overtemperature, or open-wire fault is detected, then both the DOUT and COUT are triggered.

For quicker production-line testing, the BQ77216xx device provides a Customer Test Mode (CTM) with greatly reduced delay time.

7.2 Functional Block Diagram



7.3 Feature Description

7.3.1 Voltage Fault Detection

In the BQ77216xx device, each cell is monitored independently. Overvoltage is detected by comparing the actual cell voltage to a protection voltage reference, V_{OV} . If any cell voltage exceeds the programmed OV value, a timer circuit is activated. When the timer expires, the COUT pin goes from inactive to active state. The timer is reset if the cell voltage falls below the recovery threshold ($V_{OV} - V_{OV_HYS}$). Undervoltage is detected by comparing the actual cell voltage to a protection voltage reference, V_{UV} . If any cell voltage falls below the programmed UV value, a timer circuit is activated. When the timer expires, the DOUT pin goes from inactive to active state. The timer is reset if the cell voltage rises below the recovery threshold ($V_{UV} + V_{UV_HYS}$).




图 7-1. Timing for Overvoltage Sensing




图 7-2. Timing for Undervoltage Sensing

7.3.2 Open-Wire Fault Detection

In the BQ77216xx device, each cell input is monitored independently to determine if the input is connected to a cell or not by applying a $50\ \mu\text{A}$ pull down current to ground that is activated for $128\ \mu\text{s}$ every 128ms . If the device detects that $V_n < V_n - 1 - V_{OW}\text{ V}$, then a timer is activated. When the timer expires, the COUT and DOUT pins go from an inactive to active state. The timer is reset if the cell input rises above or below the recovery threshold ($V_{OW} + V_{OW_HYS}$).

7.3.3 Temperature Fault Detection

In the BQ77216xx device, the TS pin is ratiometrically monitored with an internal pullup resistance R_{NTC} . Overtemperature is detected by evaluating the TS input voltage to determine the external resistance falls below a protection resistance, R_{OT_EXT} . If the resistance falls below the programmed OT value, a timer circuit is activated. When the timer expires, the COUT and DOUT pins go from inactive to active state. The timer is reset if the resistance rises above the recovery threshold ($R_{OT} + R_{OT_HYS}$). Under temperature is detected by evaluating the TS input voltage to determine the external resistance falls below a protection resistance, R_{UT_EXT} . If the resistance rises above the programmed UT value, a timer circuit is activated. When the timer expires, the

COUT and DOUT pins go from inactive to active state. The timer is reset if the resistance falls below above the recovery threshold ($R_{OT} - R_{OT_HYS}$). If external capacitance is added to the TS pin, it needs to be within the spec limit shown in recommended operating conditions.

备注

Texas Instruments does not recommend adding an external capacitor to the TS pin. The capacitance on this pin will affect the TS measurement accuracy if greater than C_{TS} .

7.3.4 Oscillator Health Check

The device can detect if the internal oscillator slows down below the f_{OSC_FAULT} threshold. When this occurs then the COUT and DOUT go from inactive to active state. If the oscillator returns to normal then the fault recovers.

7.3.5 Sense Positive Input for V_x

This is an input to sense each single battery cell voltage. A series resistor and a capacitor across the cell for each input are required for noise filtering and stable voltage monitoring.

7.3.6 Output Drive, COUT and DOUT

These pins serve as the fault signal outputs and may be ordered in either active HIGH with drive to 6 V or active LOW options configured through internal OTP.

The COUT and DOUT respond per the following table when a fault is detected if the specific fault is enabled.

表 7-1. Fault Detection vs COUT and DOUT Action

FAULT Detected	COUT	DOUT
Overvoltage	Active	Inactive
Undervoltage	Inactive	Active
Open Wire	Active	Active
Overtemperature	Active	Active
Oscillator Health	Active	Active

7.3.7 The LATCH Function

The device can be enabled to latch the fault signal, which effectively disables the recovery functions of all fault detections. The only way to recover from a fault state when the latch is enabled is a POR of the device.

7.3.8 Supply Input, VDD

This pin is the unregulated input power source for the IC. A series resistor is connected to limit the current, and a capacitor is connected to ground for noise filtering.

7.4 Device Functional Modes

7.4.1 NORMAL Mode

When COUT and DOUT are inactive (no fault detected), the device operates in NORMAL mode and monitors for voltage, open-wire, and temperature faults.

The COUT and DOUT pins are inactive and if configured:

- Active high is low.
- Active low is being externally pulled up and is an open drain.

7.4.2 FAULT Mode

FAULT mode is entered if the COUT or DOUT pins are activated. The OUT pin is either pulled high internally if configured as active high or is pulled low internally if configured as active low. When COUT and DOUT are deactivated, the device returns to NORMAL mode.

7.4.3 Customer Test Mode

Customer Test Mode (CTM) helps to reduce test time for checking the delay timer parameter once the circuit is implemented in the battery pack. To enter CTM, VDD should be set to at least V_{CTM} higher than V16 (see 图 7-3). The delay timer is greater than 10ms, but considerably shorter than the timer delay in normal operation. To exit Customer Test Mode, remove the VDD to a V16 voltage differential of 10V so that the decrease in this value automatically causes an exit.

小心

Avoid exceeding any Absolute Maximum Voltages on any pins when placing the part into Customer Test Mode. Also avoid exceeding Absolute Maximum Voltages for the individual cell voltages ($V_{Cn} - V_{Cn-1}$) and ($V1 - VSS$). Stressing the pins beyond the rated limits may cause permanent damage to the device.

图 7-3 shows the timing for the Customer Test Mode.




图 7-3. Timing for Customer Test Mode

8 Application and Implementation

备注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

8.1 Application Information

Changes to the ranges stated in 表 8-1 will impact the accuracy of the cell measurements.




图 8-1. Application Configuration

8.1.1 Design Requirements

Changes to the ranges stated in 表 8-1 will impact the accuracy of the cell measurements. 图 8-1 shows each external component.

表 8-1. Parameters

PARAMETER	EXTERNAL COMPONENT	MIN	NOM	MAX	UNIT
Voltage monitor filter resistance	R_{IN}	900	1000	1100	Ω
Voltage monitor filter capacitance	C_{IN}	0.01		0.1	μF
Supply voltage filter resistance	R_{VD}	100	300	1K	Ω
Supply voltage filter capacitance	C_{VD}	0.05	0.1	1	μF

备注

The device is calibrated using an R_{IN} value = $1k\Omega$. Using a value other than this recommended value changes the accuracy of the cell voltage measurements and V_{OV} trigger level.

8.1.2 Detailed Design Procedure

图 8-2 shows the measurement for current consumption for the product for both VDD and Vx.




图 8-2. Configuration for IC Current Consumption Test

8.1.2.1 Cell Connection Sequence

The BQ77216xx device can be connected to the array of cells in any order without damaging the device.

During cell attachment, the device could detect a fault if the cells are not connected within a fault detection delay period. If this occurs, then COUT and/or DOUT could transition from inactive to active. Both COUT and DOUT can be tied to VSS or VDD to prevent any change in output state during cell attach.

8.2 Systems Example

In this application example, the choice of a FUSE or FETs is required on the COUT and DOUT pins—configured as an active-high drive to 6V outputs.




图 8-3. 14-Series Cell Configuration with Active High 6V Option

When pairing with the BQ769x2 or BQ76940 devices, the top cell must be used. For the BQ77216xx device to drive the CHG and DSG FETs, the active high 6V option is preferred. Its COUT and DOUT are controlling two N-CH FETs to jointly control the CHG and DSG FETs with the monitoring device. For such joint architecture, the open-wire feature of the BQ77216xx device may be affected if the primary protector or monitor device is actively measuring the cells. Care is needed to ensure the V_{OW} spec of the BQ77216xx device is met or to choose a version of the BQ77216xx device with open wire disabled. When working with a BQ769x2 device, set the LOOP_SLOW to 0x11 to ensure the BQ77216xx V_{OW} spec is met.




图 8-4. BQ77216 with BQ76952

9 Power Supply Recommendations

The maximum power supply of this device is 85V on VDD.

10 Layout

10.1 Layout Guidelines

- Ensure the RC filters for the Vn and VDD pins are placed as close as possible to the target terminal.
- The VSS pin should be routed to the CELL - terminal.

10.2 Layout Example




图 10-1. Example Layout

11 Device and Documentation Support

11.1 第三方产品免责声明

TI 发布的与第三方产品或服务有关的信息，不能构成与此类产品或服务或保修的适用性有关的认可，不能构成此类产品或服务单独或与任何 TI 产品或服务一起的表示或认可。

11.2 接收文档更新通知

要接收文档更新通知，请导航至 [ti.com](https://www.ti.com) 上的器件产品文件夹。点击 [通知](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

11.3 支持资源

[TI E2E™ 中文支持论坛](#) 是工程师的重要参考资料，可直接从专家处获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题，获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的 [使用条款](#)。

11.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

11.5 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

11.6 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

12 Revision History

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision J (November 2023) to Revision K (April 2025)	Page
• 更新了“ 特性 ”	1
• 更新了“ 说明 ”	1
• Updated the Device Comparison Table	3

Changes from Revision I (July 2023) to Revision J (November 2023)	Page
• Updated the Device Comparison Table	3
• Updated the TS pin description.....	5
• Added the undertemperature protection description.....	11

Changes from Revision H (March 2023) to Revision I (July 2023)	Page
• Updated the Device Comparison Table	3

Changes from Revision G (July 2022) to Revision H (March 2023)	Page
• Updated the Device Comparison Table	3

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
BQ7721600PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	BQ7721600
BQ7721600PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721600
BQ7721602PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	BQ7721602
BQ7721602PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721602
BQ7721603PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	BQ7721603
BQ7721603PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721603
BQ7721605PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721605
BQ7721605PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721605
BQ7721606PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721606
BQ7721606PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721606
BQ7721607PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721607
BQ7721607PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721607
BQ7721609PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721609
BQ7721609PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721609
BQ7721610PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721610
BQ7721610PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721610
BQ7721611PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721611
BQ7721611PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721611
BQ7721612PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721612
BQ7721612PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721612
BQ7721613PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721613
BQ7721613PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721613
BQ7721614PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721614
BQ7721614PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721614
BQ7721615PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721615
BQ7721615PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721615
BQ7721616PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721616
BQ7721616PWR.A	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721616
BQ7721617PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721617

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
BQ7721618PWR	Active	Production	TSSOP (PW) 24	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 110	BQ7721618

- ⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).
- ⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.
- ⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.
- ⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- ⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.
- ⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION



*All dimensions are nominal



Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
BQ7721600PWR	TSSOP	PW	24	2000	330.0	16.4	6.95	8.3	1.6	8.0	16.0	Q1
BQ7721617PWR	TSSOP	PW	24	2000	330.0	16.4	6.95	8.3	1.6	8.0	16.0	Q1
BQ7721618PWR	TSSOP	PW	24	2000	330.0	16.4	6.95	8.3	1.6	8.0	16.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
BQ7721600PWR	TSSOP	PW	24	2000	356.0	356.0	35.0
BQ7721617PWR	TSSOP	PW	24	2000	353.0	353.0	32.0
BQ7721618PWR	TSSOP	PW	24	2000	353.0	353.0	32.0



4220208/A 02/2017

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

EXAMPLE BOARD LAYOUT


PW0024A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



4220208/A 02/2017

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

PW0024A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4220208/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 [TI 的销售条款](#) 或 [ti.com](#) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
版权所有 © 2025，德州仪器 (TI) 公司