

Sample &

🖥 Buy







ZHCS757A - FEBRUARY 2012 - REVISED APRIL 2016

Support &

Community

2.2

# CDCM9102 低噪声双通道 100MHz 时钟发生器

Technical

Documents

# 1 特性

- 包括锁相环路 (PLL)、压控振荡器 (VCO)、和回路 过滤器的集成型低噪声时钟生成器
- 2 个低噪声 100MHz 时钟(低电压正射极耦合逻辑 (LVPECL),低压差分信号 (LVDS),或者低压 CMOS (LVCOMS)对)
  - 支持高速电流控制逻辑 (HCSL) 信号传输电平
     (交流耦合)
  - 典型周期抖动:峰值到峰值 (pk-pk) 21ps
  - 典型随机抖动: 510ps RMS
  - 由引脚设定的输出类型
- 附加单端 25MHz 输出
- 集成晶振输入接受 25MHz 晶振
- 输出使能引脚,可关断器件和输出
- 32 引脚 5mm × 5mm 超薄型四方扁平无引线 (VQFN) 封装
- 静电放电 (ESD) 保护超过 2000V 人体模型 (HBM) 和 500V 带电器件模型 (CDM)
- 工业温度范围(-40°C 至 85°C)
- 3.3V 电源

- 2 应用范围
- PCI Express
   1 代、2 代和 3 代的基准时钟生成

Tools &

Software

• 通用计时

# 3 说明

CDCM9102 是一款为诸如 PCI Express™的通信标准 提供基准时钟而设计的低抖动时钟生成器. 该器件最高 支持 PCIE 3 代,易于配置和使用。CDCM9102 提供 2 个 100MHz 差分时钟端口。这些端口支持的输出类 型包括 LVPECL,LVDS,或者一对 LVCMOS 缓冲 器。HCSL 信号传输由交流耦合网络提供支持。用户配 置捆绑器件引脚所需的输出缓冲器类型。此外,提供一 个单端 25 MHz 时钟输出端口。这一端口的使用包括 通用计时、计时以太网物理层 (PHY)、或者为附加的 时钟生成器提供一个基准时钟。所有生成的时钟来自一 个单一外部 25MHz 晶体。

哭	任	信	貟	(1)
前了	T.	IH.	忑	• •

器件型号	封装	封装尺寸 (标称值)
CDCM9102	VQFN (32)	5.00mm x 5.00mm

(1) 要了解所有可用封装,请见数据表末尾的可订购产品附录。





Page

# 目录

1	特性	
2	应用	范围1
3	说明	1
4	修订	历史记录 2
5	Dev	ice Comparison Table 3
6	Pin	Configuration and Functions 3
7	Spe	cifications5
	7.1	Absolute Maximum Ratings 5
	7.2	ESD Ratings 5
	7.3	Recommended Operating Conditions 5
	7.4	Thermal Information 5
	7.5	Electrical Characteristics
	7.6	Timing Requirements 7
	7.7	Typical Characteristics 7
8	Para	ameter Measurement Information
	8.1	Test Configurations 8
9	Deta	ailed Description 10
	9.1	Overview

# 4 修订历史记录

注: 之前版本的页码可能与当前版本有所不同。

## Changes from Original (February 2012) to Revision A

•	已添加 ESD 额定值表,特性 描述部分,器件功能模式,应用和实施部分,电源相关建议部分,布局部分,器件和文	
	档文持部分以及机械、封装种可订购信息部分	1
•	已添加 文本至 <i>说明</i> "该器件最高支持 PCIE 3 代,"	1
•	Changed part number to 1134 25M0000000	. 11
•	Changed part number to FP2500002	. 11
•	Added text and Figure 16 to PCI Express Applications	. 15

	9.2	Functional Block Diagrams	10
	9.3	Feature Description	10
	9.4	Device Functional Modes	10
	9.5	Programming	12
10	Арр	lication and Implementation	. 13
	10.1	Application Information	13
	10.2	Typical Application	16
11	Pow	er Supply Recommendations	. 19
	11.1	Thermal Management	19
	11.2	Power Supply Filtering	19
12	Layo	out	. 20
	12.1	Layout Guidelines	20
	12.2	Layout Example	20
13	器件	和文档支持	. 21
	13.1	社区资源	21
	13.2	商标	21
	13.3	静电放电警告	21
	13.4	Glossary	21

14 机械、封装和可订购信息...... 21



# 5 Device Comparison Table

PACKAGED DEVICES	FEATURES	T <sub>A</sub>
CDCM9102RHBT	32-pin VQFN (RHB) package, small tape and reel	–40°C to 85°C
CDCM9102RHBR	32-pin VQFN (RHB) package, tape and reel	

# 6 Pin Configuration and Functions



### **Pin Functions**

PIN			DESCRIPTION	
NAME	NAME NO.			
POWER SUPP	PLIES			
GND	Thermal pad, 14, 22	G	Power supply ground and thermal relief	
REGCAP1	19	Р	Capacitor for internal regulator, connect 10-µF Y5V capacitor to GND	
REGCAP2	17	Р	Capacitor for internal regulator, connect 10-µF Y5V capacitor to GND	
VDD1	4	Р	Power Supply, OUT0 clock port	
VDD2	1	Р	Power Supply, OUT1 clock port	
VDD3	9	Р	Power supply, low-noise clock generator	
VDD4	16	Р	Power supply, low-noise clock generator	
VDD5	18	Р	Power supply, low-noise clock generator	
VDD6	20	Р	Power supply, crystal oscillator input	

(1) G = Ground, I = Input, O = Output, P = Power

CDCM9102 ZHCS757A – FEBRUARY 2012 – REVISED APRIL 2016

www.ti.com.cn

NSTRUMENTS

EXAS

## Pin Functions (continued)

PIN			DECODIDITION		
NAME	NO.	ITPE''	DESCRIPTION		
DEVICE CONF	FIGURATION AND CO	NTROL			
NC	8, 13, 15, 24–32	—	No connection permitted		
OE	7	0	Output enable/shutdown control input (see Table 2)		
OS1	10	0	Output format select control inputs (see Table 3)		
OS0	11	0	Output format select control inputs (see Table 3)		
RESET	12	I	Device reset input (active-low) (see Table 4) <sup>(2)</sup>		
CRYSTAL OS	CILLATOR				
XIN	21	I	Parallel resonant crystal input (25 MHz)		
DEVICE OUTF	PUTS				
OSCOUT	23	0	Oscillator output port (25 MHz)		
OUTON	5	0	Output 0 – negative terminal (100 MHz)		
OUT0P	6	0	Output 0 – positive terminal (100 MHz)		
OUT1N	2	0	Output 1 – negative terminal (100 MHz)		
OUT1P	3	0	Output 1 – positive terminal (100 MHz)		

(2) For proper device startup, it is recommended that a capacitor be installed from pin 12 to GND. See *Start-Up Time Estimation* for more details.



## 7 Specifications

## 7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
I <sub>IN</sub>	Input current		20	mA
I <sub>OUT</sub>	Output current		50	mA
V <sub>DDx</sub>	Supply voltage <sup>(2)</sup>	-0.5	4.6	V
V <sub>IN</sub>	Input voltage <sup>(3)</sup>	-0.5	V <sub>DDx</sub> + 0.5	V
V <sub>OUT</sub>	Output voltage <sup>(3)</sup>	-0.5	V <sub>DDx</sub> + 0.5	V
T <sub>A</sub>	Operating temperature		85	°C
T <sub>stg</sub>	Storage temperature	-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) Supply voltages must be applied simultaneously.

(3) The input and output negative voltage ratings may be exceeded if the input and output clamp-current ratings are observed

## 7.2 ESD Ratings

			VALUE	UNIT
V <sub>(ESD)</sub> Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	±2000	V	
	Electrostatic discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	±500	v

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## 7.3 Recommended Operating Conditions

		MIN	NOM	MAX	UNIT
V <sub>DDX</sub>	DC power-supply voltage	3	3.3	3.6	V
T <sub>A</sub>	Ambient temperature	-40		85	°C

## 7.4 Thermal Information

		CDCM9102	
	THERMAL METRIC <sup>(1)(2)</sup>	RHB (VQFN)	UNIT
		32 PINS	
$R_{\thetaJA}$	Junction-to-ambient thermal resistance	33.1	°C/W
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	25.7	°C/W
$R_{ extsf{ heta}JB}$	Junction-to-board thermal resistance	0.3	°C/W
Ψ <sub>JT</sub>	Junction-to-top characterization parameter	7.1	°C/W
$\Psi_{JB}$	Junction-to-board characterization parameter	2	°C/W
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistance	6.12	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

(2)  $4 \times 4$  Vias on Pad.

ZHCS757A-FEBRUARY 2012-REVISED APRIL 2016

## 7.5 Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP MAX	UNIT			
LVCMOS INPUTS <sup>(1)</sup>								
VIH	Input high voltage		$0.6 \times V_{DD}$		V			
V <sub>IL</sub>	Input low voltage			$0.4 \times V_{DD}$	V			
I <sub>IH</sub>	Input high current	$V_{DD} = 3.6 \text{ V}, \text{ V}_{IL} = 0 \text{ V}$		200	μA			
I <sub>IL</sub>	Input low current	V <sub>DD</sub> = 3 V, V <sub>IH</sub> = 3.6 V		-200	μA			
C <sub>IN</sub>	Input capacitance			8 10	pF			
R <sub>PU</sub>	Input pullup resistor			150	kΩ			
CRYSTAL	CHARACTERISTICS (XIN) <sup>(2)</sup>							
f <sub>XTAL</sub>	Crystal input frequency	Fundamental mode		25	MHz			
ESR	Effective series resistance of crystal			50	Ω			
C <sub>IN</sub>	On-chip load capacitance			8 10	pF			
XTAL <sub>DL</sub>	Maximum drive level - XTAL		0.1	1	mW			
C <sub>SHUNT</sub>	Maximum shunt capacitance			7	pF			
CLOCK OU	JTPUT BUFFER (OUTPUT MODE	= LVPECL) <sup>(3)</sup>						
V <sub>OH</sub>	Output high voltage		V <sub>DD</sub> - 1.18	$V_{DD} - 0.73$	V			
V <sub>OL</sub>	Output low voltage		$V_{DD} - 2$	V <sub>DD</sub> – 1.55	V			
V <sub>OD</sub>	Differential output voltage		0.6	1.23	V			
$t_{\rm R}$ and $t_{\rm F}$	Output rise and fall time	20% to 80%		175	ps			
ODC	Output duty cycle		45%	55%				
t <sub>SKEW</sub>	Skew between outputs			20	ps			
CLOCK OU	JTPUT BUFFER (OUTPUT MODE	= LVDS) <sup>(4)</sup>						
V <sub>OD</sub>	Differential output voltage		0.247	0.454	V			
$\Delta V_{OD}$	V <sub>OD</sub> magnitude change			50	mV			
V <sub>OS</sub>	Common-mode voltage		1.125	1.375	V			
$\Delta V_{OS}$	V <sub>OS</sub> magnitude change			50	mV			
$t_{R}$ and $t_{F}$	Output rise and fall time	20% to 80%		255	ps			
ODC	Output duty cycle		45%	55%				
t <sub>SKEW</sub>	Skew between outputs			30	ps			
CLOCK OUTPUT BUFFER (OUTPUT MODE = LVCMOS) <sup>(5)</sup>								
V <sub>OH</sub>	Output high voltage	$V_{CC}$ = 3 V to 3.6 V, $I_{OH}$ = -100 µA	V <sub>DD</sub> – 0.5		V			
V <sub>OL</sub>	Output low voltage	$V_{CC}$ = 3 V to 3.6 V, $I_{OH}$ = 100 $\mu$ A		0.3	V			
t <sub>SLEW</sub>	Output rise/fall slew rate	20% to 80%	2.4		V/ns			
ODC	Output duty cycle		45%	55%				
t <sub>SKEW</sub>	Skew between outputs			50	ps			

(1) LVCMOS inputs at  $T_A = -40^{\circ}$ C to 85°C (2) Crystal characteristics for external 25 MHz crystal with  $V_{DD} = 3.3 \text{ V}$ ,  $T_A = -40^{\circ}$ C to 85°C (3) Clock output buffer with output mode = LVPECL at VDD1, VDD2 = 3.3 V;  $T_A = -40^{\circ}$ C to 85°C (4) Clock output buffer with output mode = LVDS at VDD1, VDD2 = 3.3 V;  $T_A = -40^{\circ}$ C to 85°C (5) Clock output buffer with output mode = LVCMOS at VDD1, VDD2 = 3.3 V;  $T_A = -40^{\circ}$ C to 85°C



## 7.6 Timing Requirements

 $f_{OUT}$  = 100 MHz,  $V_{DD}$  = 3.3 V,  $T_A$  = 25°C, and jitter integration bandwidth between 10 kHz and 20 MHz (unless otherwise noted)

	MIN	TYP	MAX	UNIT
LVCMOS OUTPUT MODE				
Random jitter			507	fs RMS
Period jitter			24.5	ps pk-pk
LVPECL OUTPUT MODE				
Random jitter			510	fs RMS
Period jitter			20.7	ps pk-pk
LVDS OUTPUT MODE				
Random jitter			533	fs RMS
Period jitter			26.5	ps pk-pk

## 7.7 Typical Characteristics



Figure 1. CDCM9102 Typical Phase Noise Performance (LVPECL Mode)



## 8 Parameter Measurement Information

## 8.1 Test Configurations



Figure 2. LVCMOS Output Test Load



Figure 3. LVCMOS AC Configuration for Device Test



Figure 4. LVPECL DC Configuration for Device Test







# **Test Configurations (continued)**



Figure 6. LVDS DC Configuration for Device Test



Figure 7. LVDS AC Configuration for Device Test

CDCM9102 ZHCS757A – FEBRUARY 2012 – REVISED APRIL 2016



## 9 Detailed Description

## 9.1 Overview

The CDCM9102 is a high-performance PLL that generates 2 copies of commonly-used reference clocks with less than 1-ps RMS jitter from a low-cost crystal.

## 9.2 Functional Block Diagrams



## 9.3 Feature Description

The CDCM9102 includes an on-chip PLL with an on-chip VCO. The PLL blocks consist of a crystal input interface, a phase frequency detector (PFD), a charge pump, an on-chip loop filter, and prescaler and feedback dividers. Completing the CDCM9102 device are the output divider and universal output buffer. The PLL and output divider are pre-programmed to generate 2 copies of 100 MHz in LVCMOS, LVPECL or LVDS format.

The PLL is powered by on-chip, low-dropout (LDO) linear voltage regulators. The regulated supply network is partitioned such that the sensitive analog supplies are powered from separate LDOs rather than the digital supplies which use a separate LDO regulator. These LDOs provide isolation for the PLL from any noise in the external power-supply rail. The REG\_CAP1 and REG\_CAP2 pins should each be connected to ground by  $10-\mu$ F capacitors to ensure stability.

## 9.4 Device Functional Modes

## 9.4.1 Crystal Input (XIN) Interface

The CDCM9102 implements a *Colpitts oscillator*, therefore, one side of the crystal connects to the XIN pin and the other crystal terminal connects to ground. The device requires the use of a fundamental-mode crystal, and the oscillator operates in parallel resonance mode. The correct load capacitance is necessary to ensure that the circuit oscillates properly. The load capacitance comprises all capacitances in the oscillator feedback loop (the capacitances seen between the terminals of the crystal in the circuit). It is important to account for all sources of capacitance when calculating the correct value for the external discrete load capacitance shown in Figure 8.







## **Device Functional Modes (continued)**

The CDCM9102 has been characterized with 10-pF parallel-resonant crystals. The input stage of the crystal oscillator in the CDCM9102 is designed to oscillate at the correct frequency for all parallel-resonant crystals with low-pull capability and rated with a load capacitance that is equal to the sum of the on-chip load capacitance at the XIN pin ( $C_{IN} = 10$  pF maximum), crystal stray capacitance, and board parasitic capacitance between the crystal and XIN pin. To minimize stray and parasitic capacitances, minimize the trace distance routed from the crystal to the XIN pin and avoid other active traces and active circuitry in the area of the crystal oscillator circuit. Table 1 lists crystal types that have been evaluated with the CDCM9102.

MANUFACTURER	PART NUMBER
Vectron	VXC1-1134 25M0000000
Fox	218-3
Saronix	FP2500002

A mismatch of the load capacitance results in a frequency error according to Equation 1.

$$\frac{\Delta f}{f} = \frac{C_{\rm S}}{2(C_{\rm Lr} + C_{\rm O})} - \frac{C_{\rm S}}{2(C_{\rm La} + C_{\rm O})}$$

where

- $\Delta f$  is the frequency error required by the application.
- f is the fundamental frequency of the crystal.
- C<sub>s</sub> is the motional capacitance of the crystal. This is a parameter in the data sheet of the crystal.
- C<sub>0</sub> is the shunt capacitance of the crystal. This is a parameter in the data sheet of the crystal.
- C<sub>Lr</sub> is the rated load capacitance of the crystal. This is a parameter in the data sheet of the crystal.
- $C_{La}$  is the actual load capacitance implemented on the PCB ( $C_{IN}$  + stray capacitance + parasitic capacitance +  $C_L$ ). (1)

The difference between the rated load capacitance (from the crystal datasheet) and the actual load capacitance ( $C_{La} = C_{IN} + C_{L} + C_{STRAY} + C_{PARASITIC}$ ) should be minimized. A crystal with a low pullability rating (low  $C_{S}$ ) is ideal.

Design Example:

Desired frequency tolerance  $\Delta f \le \pm 80$  ppm

Crystal Vendor Parameters:

Intrinsic Frequency Tolerance = ±30 ppm

- $C_0 = 7 \text{ pF}$  (shunt capacitance)
- $C_{S} = 10 \text{ fF}$  (motional capacitance)
- $C_{Lr} = 12 \text{ pF}$  (load capacitance)

Substituting these parameters into Equation 1 yields a maximum value of  $C_{La} = 17 \text{ pF}$  to achieve the desired  $\Delta f$  (±50 ppm). Recall that  $C_{La} = C_{IN} + C_L + C_{STRAY} + C_{PARASITIC} = 8 \text{ pF} + (C_L + C_{STRAY} + C_{PARASITIC})$ . Ideally, the load presented to this crystal should be 12 pF; therefore, the sum of ( $C_L + C_{STRAY} + C_{PARASITIC}$ ) must be less than 9 pF. Stray and parasitic capacitance must be controlled. This is because the Colpitts oscillator is particularly sensitive to capacitance in parallel with the crystal; therefore, good layout practice is essential. TI recommends that the designer extract the stray and parasitic capacitance from the printed-circuit board design tool and adjust  $C_L$  accordingly to achieve  $C_{Lr} = C_{La}$ . In common scenarios, the external load capacitor is often unnecessary; however, TI recommends that pads be implemented to accommodate an external load capacitor so that the ppm error can be minimized.

## 9.4.2 Interfacing between LVPECL and HCSL (PCI Express)

Certain PCI Express applications require HCSL signaling. Because the common-mode voltage for LVPECL and HCSL are different, applications requiring HCSL signaling must use AC-coupling as shown in Figure 9. The 150- $\Omega$  resistors ensure proper biasing of the CDCM9102 LVPECL output stage. The 471- $\Omega$  and 56- $\Omega$  resistor network biases the HCSL receiver input stage.





 $C_{IN}$  = 8 pF (typical), 10 pF (maximum); see *Electrical Characteristics*.

## Figure 9. Interfacing Between LVPECL and HCSL

## 9.5 Programming

Table 2 and Table 3 list the pin controls and pin configurations of the CDCM9102 output. Table 4 lists the device reset.

### 9.5.1 Device Configuration

### Table 2. CDCM9102 Pin Control of Output Enable

OE (Pin 7) MODE		DEVICE CORE	OUTPUT	
0	Power down	Power down	Hi-Z	
1	Normal	Active	Active	

## Table 3. CDCM9102 Pin Configuration of Output Type

CONTROL	- PINS		
OS1 (Pin 10) OS0 (Pin 11)		COTFOT MODE	
0	0	LVCMOS, OSCOUT = OFF	
0 1		LVDS, OSCOUT = OFF	
1	0	LVPECL, OSCOUT = OFF	
1	1	LVPECL, OSCOUT = ON	

## Table 4. CDCM9102 Device Reset

RESET (Pin 12)	OPERATING MODE	DEVICE OUTPUTS		
0	Device reset	Hi-Z		
$0 \rightarrow 1$	Clock generator calibration	Hi-Z		
1	Normal	Active		



## **10** Application and Implementation

## NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

## **10.1** Application Information

## 10.1.1 Start-Up Time Estimation

The CDCM9102 contains a low-noise clock generator that calibrates to an optimal operating point at device power up. To ensure proper device operation, the oscillator must be stable before the low-noise clock generator calibration procedure. Quartz-based oscillators can take up to 2 ms to stabilize; therefore, TI recommends that the application ensure that the RESET pin is de-asserted at least 5 ms after the power supply has finished ramping. This can be accomplished by controlling the RESET pin directly, or by applying a 47-nF capacitor to ground on the RESET pin (this provides a delay because the RESET pin includes a 150-k $\Omega$  pullup resistor.

The CDCM9102 start-up time can be estimated based on parameters defined in Table 5 and graphically shown in Figure 10.

PARAMETER	DEFINITION	DESCRIPTION	FORMULA OR METHOD OF DETERMINATION
t <sub>REF</sub>	Reference clock period	The reciprocal of the applied reference frequency in seconds	$t_{\text{REF}} = \frac{1}{f_{\text{REF}}} = 0.04 \mu\text{s}$
t <sub>pul</sub>	Power-up time (low limit)	Power-supply rise time to low limit of power- on-reset trip point	Time required for power supply to ramp to 2.27 V
t <sub>puh</sub>	Power-up time (high limit)	Power supply rise time to high limit of power- on-reset trip point	Time required for power supply to ramp to 2.64 V
t <sub>rsu</sub>	Reference start-up time	After POR releases, the Colpitts oscillator is enabled. This start-up time is required for the oscillator to generate the requisite signal levels for the delay block to be clocked by the reference input.	500 µs best case and 800 µs worst case (for a crystal input)
t <sub>delay</sub>	Delay time	Internal delay time generated from the reference clock. This delay provides time for the reference oscillator to stabilize.	t <sub>delay</sub> = 16,384 × t <sub>REF</sub> = 655 μs
t <sub>vco_cal</sub>	VCO calibration time	VCO calibration time generated from the reference clock. This process selects the operating point for the VCO based on the PLL settings.	$t_{VCO_CAL} = 550 \times t_{REF} = 22 \ \mu s$
t <sub>PLL_LOCK</sub>	PLL lock time	Time requried for PLL to lock within ±10 ppm of ${\rm f}_{\rm REF}$	The PLL settles in 12.5 µs

## Table 5. CDCM9102 Start-Up Time Dependencies

NSTRUMENTS

EXAS





The CDCM9102 start-up time limi	s, t <sub>MAX</sub> and t <sub>MIN</sub> ,	can now be calculated with	Equation 2 and Equation 3.
---------------------------------	--	----------------------------	----------------------------

$t_{MAX} = t_{puh} + t_{rsu} + t_{delay} + t_{VCO\_CAL} + t_{PLL\_LOCK}$	(2)
$t_{MIN} = t_{pul} + t_{rsu} + t_{delay} + t_{VCO\_CAL} + t_{PLL\_LOCK}$	(3)

## 10.1.2 Output Termination

The CDCM9102 is a 3.3-V clock driver which has the following options for the output type: LVPECL, LVDS, and LVCMOS.

## 10.1.3 LVPECL Termination

The CDCM9102 is an open emitter for LVPECL outputs. Therefore, proper biasing and termination is required to ensure correct operation of the device and to optimize signal integrity. The proper termination for LVPECL is 50  $\Omega$  to (Vcc-2) V but this DC voltage is not readily available on a board. Thus a Thevenin's equivalent circuit is worked out for the LVPECL termination in both direct-coupled (DC) and AC-coupled cases, as shown in Figure 11 and Figure 12. TI recommends placing all resistive components close to either the driver end or the receiver end. If the supply voltages of the driver and receiver are different, AC coupling is required.



Figure 11. LVPECL Output Termination (DC-Coupled)



CDCM9102 ZHCS757A – FEBRUARY 2012 – REVISED APRIL 2016



Figure 12. LVPECL Output Termination (AC-Coupled)

## 10.1.4 LVDS Termination

The proper LVDS termination for signal integrity over two  $50-\Omega$  lines is  $100 \ \Omega$  between the outputs on the receiver end. Either a direct-coupled (dc) termination or ac-coupled termination can be used for LVDS outputs, as shown in Figure 13 and Figure 14. TI recommends placing all resistive components close to either the driver end or the receiver end. If the supply voltages of the driver and receiver are different, AC coupling is required.



Figure 13. LVDS Output Termination (DC Coupled)



Figure 14. LVDS Output Termination (AC Coupling)

## 10.1.5 LVCMOS Termination

Series termination is a common method to maintain the signal integrity for LVCMOS drivers, if connected to a receiver with a high-impedance input. For series termination, a series resistor, Rs, is placed close to the driver, as shown in Figure 15. The sum of the driver impedance and Rs should be close to the transmission-line impedance, which is usually 50  $\Omega$ . Because the LVCMOS driver in the CDCM9102 has an impedance of 30  $\Omega$ , TI recommends Rs be 22  $\Omega$  to maintain proper signal integrity.



Figure 15. LVCMOS Output Termination

## 10.1.6 PCI Express Applications

Texas Instruments offers a complete clock solution for PCI Express applications. The CDCUN1208LP can be used to fan out reference clock generated by the CDCM9102 as shown in Figure 16.





Figure 16. Clock Solution for PCIE Express Applications

## **10.2 Typical Application**



Figure 17. CDCM9102 Typical Application Example

## 10.2.1 Design Requirements

Consider a typical wired communications application, like a top-of-rack switch, which needs to clock PCI Express Gen 2 or 3 PHYs. For such asynchronous systems, the reference input can be a crystal. In such systems, the clocks are expected to be available upon power up without the need for any device-level programming. An example of clock input and output requirements is shown below:

- Clock Input:
  - 25-MHz crystal
- Clock Outputs:
  - 2x 100 MHz clock for PCI Express Gen 3 (8 GT/s), LVPECL

See *Detailed Design Procedure* for how to generate the required output frequencies for this application using the CDCM9102.



## **Typical Application (continued)**

### 10.2.2 Detailed Design Procedure

Design of all aspects of the CDCM61004 is quite involved and software support is available to assist in part selection and phase noise simulation. This design procedure will give a quick outline of the process.

- 1. Device Selection
  - The first step is to calculate the VCO frequency given the required output frequency. The device must be able to produce the VCO frequency that can be divided down to the required output frequency.
  - The WEBENCH Clock Architect Tool from TI will aid in the selection of the right device that meets the customer's output frequencies and format requirements.
- 2. Device Configuration
  - The WEBENCH Clock Architect Tool attempts to maximize the phase detector frequency, use smallest dividers, and maximizes PLL bandwidth.

### 10.2.2.1 Device Selection

Use the WEBENCH Clock Architect Tool. Enter the required frequencies and formats into the tool. To use this device, find a solution using the CDCM9102.

### 10.2.2.1.1 Calculation Using LCM

In this example, the valid VCO frequency for CDCM9102 is 1.8 GHz.

### 10.2.2.2 Device Configuration

For this example, when using the WEBENCH Clock Architect Tool, the reference would have been manually entered as 25 MHz according to input frequency requirements. Enter the desired output frequencies and click on Generate Solutions. Select CDCM9102 from the solution list.

From the simulation page of the WEBENCH Clock Architect Tool, it can be seen that to maximize phase detector frequencies, the N divider is set to 24 and prescaler divider is set to 3. This results in a VCO frequency of 1.8 GHz. The output divider is set to 6. At this point the design meets all input and output frequency requirements and simulate performance on the clock outputs. Figure 18 shows the typical phase noise plot of the 100 MHz LVPECL output.



# **Typical Application (continued)**

## 10.2.3 Application Curve



Figure 18. Typical Phase Noise Plot of 100 MHz LVPECL Output



## **11 Power Supply Recommendations**

 $T_A = -40^{\circ}C$  to 85°C, VDDx = 3.3 V, OE = 1, values represent cumulative current/power on all VDDx pins.

BLOCK CONDITION		CURRENT (mA)	DEVICE POWER (mW)	EXTERNAL RESISTOR POWER (mW)
Entire device, core current		85	280	
	LVPECL	28	42.4	50
Output Buffers	LVDS	20	66	
	LVCMOS	$V \times f_{out} \times (C_{L} + 20 \times 10^{-12}) \times 10^{3}$	$V^2 \times f_{out} \times (C_L + 20 \times 10^{-12}) \times 10^3$	

### Table 6. Device Current Consumption

## **11.1 Thermal Management**

To ensure optimal performance and reliability, good thermal design practices are important when using the CDCM9102. Die temperature should be limited to a maximum of 125°C. That is, as an estimate,  $T_A$  (ambient temperature) plus device power consumption times  $R_{\theta JA}$  should not exceed 125°C.

The device package has an exposed pad that provides the primary heat removal path as well as an electrical grounding to the printed circuit board (PCB). To maximize the removal of heat from the package, a thermal landing pattern including multiple vias to a ground plane must be incorporated on the PCB within the footprint of the package. The exposed pad must be soldered down to ensure adequate heat conduction out of the package. A recommended land and via pattern is shown in Figure 19.



Figure 19. Recommended PCB Layout for CDCM9102

## 11.2 Power Supply Filtering

PLL-based frequency synthesizers are very sensitive to noise on the power supply, which can dramatically increase the jitter of the PLL. This is especially true for analog-based PLLs. Thus, it is essential to reduce noise from the system power supply, especially when jitter/phase noise is very critical to applications. A PLL has attenuated jitter due to power supply noise at frequencies beyond the PLL bandwidth due to attenuation by the loop response.

Filter capacitors are used to eliminate the low-frequency noise from the power supply, where the bypass capacitors provide the very low-impedance path for high-frequency noise and guard the power supply system against induced fluctuations. The bypass capacitors also provide a source of instantaneous current as required by the device output stages. Therefore, bypass capacitors must have low ESR. To properly use the bypass capacitors, they must be placed very close to the power supply pins and must be laid out with short loops to minimize inductance.

Figure 20 shows a general recommendation for decoupling the power supply. The CDCXM9102 power supplies fall into one of two categories: analog supplies (VDD3, VDD4, and VDD5), and input/output supplies (VDD1, VDD2, and VDD6). Short the analog supplies together to form the analog supply node; likewise, short the input/output supplies together to form the I/O supply node. Isolate the analog node from the PCB power supply and I/O node by inserting a ferrite bead. This helps isolate the high-frequency switching noises generated by the clock drivers and I/O from the sensitive analog supply node. Choosing an appropriate ferrite bead with low dc resistance is important, as it is imperative to maintain a voltage at the power-supply pin of the CDCM9102 that is over the minimum voltage needed for its proper operation.



## **Power Supply Filtering (continued)**



Figure 20. CDCM9102 Power Supply Decoupling – Power Pin Bypass Concept

# 12 Layout

## 12.1 Layout Guidelines

The CDCM9102 is a high-performance device; therefore, pay careful attention to device configuration and printed-circuit board layout with respect to power consumption. Observing good thermal layout practices enables the thermal pad on the backside of the 32-pin VQFN package to provide a good thermal path between the die contained within the package and the ambient air. This thermal pad also serves as the ground connection the device; therefore, a low inductance connection to the ground plane is essential.

## 12.2 Layout Example

Figure 21 shows a general recommendation of PCB layout with the CDCM9102 that ensures good system-level thermal reliability.



Figure 21. Recommended PCB Layout



# 13 器件和文档支持

## 13.1 社区资源

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E<sup>™</sup> Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support TI's Design Support** Quickly find helpful E2E forums along with design support tools and contact information for technical support.

## 13.2 商标

E2E is a trademark of Texas Instruments. PCI Express is a trademark of PCI-SIG. All other trademarks are the property of their respective owners.

## 13.3 静电放电警告



这些装置包含有限的内置 ESD 保护。存储或装卸时,应将导线一起截短或将装置放置于导电泡棉中,以防止 MOS 门极遭受静电损 、伤。

## 13.4 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 14 机械、封装和可订购信息

以下页中包括机械、封装和可订购信息。这些信息是针对指定器件可提供的最新数据。这些数据会在无通知且不对 本文档进行修订的情况下发生改变。要获得这份数据表的浏览器版本,请查阅左侧的导航栏。



## **PACKAGING INFORMATION**

Orderable part number	Status	Material type	Package   Pins	Package qty   Carrier	RoHS	Lead finish/	MSL rating/	Op temp (°C)	Part marking
	(1)	(2)			(3)	Ball material	Peak reflow		(6)
						(4)	(5)		
CDCM9102RHBR	Active	Production	VQFN (RHB)   32	3000   LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 85	CDCM
			· · ·						9102
CDCM9102RHBR.B	Active	Production	VQFN (RHB)   32	3000   LARGE T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 85	CDCM
									9102
CDCM9102RHBT	Active	Production	VQFN (RHB)   32	250   SMALL T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 85	CDCM
									9102
CDCM9102RHBT.B	Active	Production	VQFN (RHB)   32	250   SMALL T&R	Yes	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 85	CDCM
			. , , ,						9102

<sup>(1)</sup> **Status:** For more details on status, see our product life cycle.

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

<sup>(4)</sup> Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

# PACKAGE OPTION ADDENDUM

23-May-2025



Texas

STRUMENTS

## TAPE AND REEL INFORMATION





## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal													
	Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CD	CM9102RHBR	VQFN	RHB	32	3000	330.0	12.4	5.3	5.3	1.5	8.0	12.0	Q2
CD	CM9102RHBT	VQFN	RHB	32	250	180.0	12.4	5.3	5.3	1.5	8.0	12.0	Q2



www.ti.com

# PACKAGE MATERIALS INFORMATION

24-Jul-2025



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CDCM9102RHBR	VQFN	RHB	32	3000	353.0	353.0	32.0
CDCM9102RHBT	VQFN	RHB	32	250	213.0	191.0	35.0

# **RHB 32**

5 x 5, 0.5 mm pitch

# **GENERIC PACKAGE VIEW**

# VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



# **RHB0032E**



# **PACKAGE OUTLINE**

# VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



# **RHB0032E**

# **EXAMPLE BOARD LAYOUT**

# VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

 Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



# **RHB0032E**

# **EXAMPLE STENCIL DESIGN**

# VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



## 重要通知和免责声明

TI"按原样"提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源, 不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担 保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验 证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。 严禁以其他方式对这些资源进行 复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索 赔、损害、成本、损失和债务,TI 对此概不负责。

TI 提供的产品受 TI 的销售条款或 ti.com 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址:Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 版权所有 © 2025,德州仪器 (TI) 公司