

Wide-Temperature, Precision INSTRUMENTATION AMPLIFIER

FEATURES

PRECISION

LOW OFFSET: 100µV (max) LOW OFFSET DRIFT: 0.4µV/°C (max) EXCELLENT LONG-TERM STABILITY VERY-LOW 1/f NOISE

- SMALL SIZE microPACKAGE: MSOP-8, MSOP-10
- LOW COST

APPLICATIONS

- LOW-LEVEL TRANSDUCER AMPLIFIER FOR BRIDGES, LOAD CELLS, THERMOCOUPLES
- WIDE DYNAMIC RANGE SENSOR MEASUREMENTS
- HIGH-RESOLUTION TEST SYSTEMS
- WEIGH SCALES
- MULTI-CHANNEL DATA ACQUISITION SYSTEMS
- MEDICAL INSTRUMENTATION
- AUTOMOTIVE APPLICATIONS
- GENERAL-PURPOSE

DESCRIPTION


The INA337 and INA338 (with shutdown) are high temperature, high-performance, low-cost, precision instrumentation amplifiers. They are true single-supply instrumentation amplifiers with very-low DC errors and input common-mode ranges that extends beyond the positive and approaches the negative rail. These features make them suitable for applications ranging from general-purpose to high-accuracy.

Excellent long-term stability and very low 1/f noise assure low offset voltage and drift throughout the life of the product.

The INA337 (without shutdown) comes in the MSOP-8 package. The INA338 (with shutdown) is offered in MSOP-10. Both are specified over the temperature range, -40° C to $+125^{\circ}$ C.

INA337 AND INA338 RELATED PRODUCTS

PRODUCT	FEATURES
INA326	Precision, Rail-to-Rail I/O, 2.4mA I _Q
INA114	50μV V _{OS} , 0.5nA I _B , 115dB CMR, 3mA I _Q , 0.25μV/°C drift
INA118	50μV V _{OS} , 1nA I _B , 120dB CMR, 385μA I _Q , 0.5μV/°C drift
INA122	250μV V _{OS} , –10nA I _B , 85μA I _Q , Rail-to-Rail Output, 3μV/°C drift
INA128	50μV V _{OS} , 2nA I _B , 125dB CMR, 750μA I _Q , 0.5μV/°C drift
INA321	500 μ V V _{OS} , 0.5pA I _B , 94dB CMRR, 60 μ A I _Q , Rail-to-Rail Output





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



PACKAGE/ORDERING INFORMATION

PRODUCT	PACKAGE-LEAD	PACKAGE DESIGNATOR ⁽¹⁾	SPECIFIED TEMPERATURE RANGE	PACKAGE MARKING	ORDERING NUMBER	TRANSPORT MEDIA, QUANTITY
INA337	MSOP-8	DGK	–40°C to +125°C	BIM	INA337AIDGKT	Tape and Reel, 250
"	"	"	"	"	INA337AIDGKR	Tape and Reel, 2500
INA338	MSOP-10	DGS	–40°C to +125°C	BIL	INA338AIDGST	Tape and Reel, 250
"	"	"	"	"	INA338AIDGSR	Tape and Reel, 2500

NOTE: (1) For the most current specifications and package information, refer to our web site at www.ti.com.

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

Supply Voltage	+5.5V
Signal Input Terminals: Voltage ⁽²⁾	
Current ⁽²⁾	±10mA
Output Short-Circuit	Continuous
Operating Temperature Range	–40°C to +150°C
Storage Temperature Range	–65°C to +150°C
Junction Temperature	+150°C
Lead Temperature (soldering, 10s)	+300°C


NOTES: (1) Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those specified is not implied. (2) Input terminals are diode clamped to the power-supply rails. Input signals that can swing more than 0.5V beyond the supply rails should be current limited to 10mA or less.

ELECTROSTATIC DISCHARGE SENSITIVITY

This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

PIN CONFIGURATION



ELECTRICAL CHARACTERISTICS: $V_s = +2.7V$ to +5.5V

BOLDFACE limits apply over the specified temperature range, $T_A = -40^{\circ}C$ to $+125^{\circ}C$

At $T_A = +25^{\circ}$ C, $R_L = 10k\Omega$, G = 100 ($R_1 = 2k\Omega$, $R_2 = 100k\Omega$), external gain set resistors, and $IA_{COMMON} = V_S/2$, with external equivalent filter corner of 1kHz filters, unless otherwise noted.

		INA3				
PARAMETER	CONDITION	MIN TYP		MAX	UNITS	
INPUT						
Offset Voltage, RTI V _C	$V_{S} = +5V, V_{CM} = V_{S}/2$		±20	±100	μV	
Over Temperature				±140	μV	
vs Temperature dV _{os} /d	r		±0.1	±0.4	μV/°C	
vs Power Supply PS		±20	±3	-	μV/V	
Long-Term Stability	$v_{\rm g} = v_{\rm Z}, v_{\rm H} = v_{\rm g} / 2$		See Note (1)		μ.,,,	
Input Impedance, Differential			10 ¹⁰ 2		Ω∥pF	
Common-Mode			10 ¹⁰ 14			
		() () (0.05	1010 14	01.3 . 0.4	Ω pF	
Input Voltage Range		(V–) + 0.25		(V+) + 0.1	V	
Safe Input Voltage		(V–) –0.5		(V+) + 0.5	V	
	$R V_{S} = +5V, V_{CM} = (V-) + 0.25V \text{ to } (V+) + 0.1V$	106	120		dB	
Over Temperature		100			dB	
INPUT BIAS CURRENT	$V_{CM} = V_S/2$					
Bias Current	в V _S = +5V		±0.2	±2	nA	
vs Temperature		See	Typical Character	istics		
Offset Current I _C	_S V _S = +5V		±0.2	±2	nA	
NOISE						
Voltage Noise, RTI	$R_{S} = 0\Omega, G = 100, R_{1} = 2k\Omega, R_{2} = 100k\Omega$					
f = 10Hz			33		nV/√Hz	
f = 100Hz			33		nV/√Hz	
			33		nV/√Hz	
f = 1 kHz						
f = 0.01Hz to 10Hz			0.8		μVр-р	
Voltage Noise, RTI	$R_{S} = 0\Omega, \ G = 10, \ R_1 = 20 \mathrm{k}\Omega, \ R_2 = 100 \mathrm{k}\Omega$				_	
f = 10Hz			120		nV/√Hz	
f = 100Hz			97		nV/√Hz	
f = 1kHz			97		nV/√Hz	
f = 0.01Hz to $10Hz$			4		μVp-p	
Current Noise, RTI						
f = 1 kHz			0.15		pA/√Hz	
f = 0.01Hz to 10Hz			4.2		pAp-p	
Output Ripple, V_{O} Filtered ⁽²⁾		See	Applications Inform	hation	Pr P P	
GAIN						
Gain Equation			$G = 2(R_2/R_1)$			
Range of Gain		< 0.1	$0 = 2(12/12_1)$	> 10000	V/V	
		< 0.1	0.00			
Gain Error ⁽³⁾	$G = 10, 100, V_S = +5V, V_O = 0.25V \text{ to } 4.925V$		0.08	±0.2	%	
vs Temperature	G = 10, 100, V_{S} = +5V, V_{O} = 0.25V to 4.925V		±6	±25	ppm/°C	
Nonlinearity	G = 10, 100, V_S = +5V, V_O = 0.25V to 4.925V		±0.003	±0.01	% of FS	
OUTPUT						
Voltage Output Swing from Positive Ra	iI $R_L = 10k\Omega, V_S = 5V$	(V+) – 0.075	(V+) - 0.01		V	
Over Temperature	2 0	(V+) - 0.075			v	
Voltage Output Swing from Negative R	ai $R_1 = 10k\Omega, V_S = 5V$	(V–) + 0.25	(V+) + 0.01		V	
Over Temperature	······································	(V-) + 0.25			v	
Capacitive Load Drive		(1) F 0.20	500		pF	
Short-Circuit Current			±25		mA	
5			<u> </u>		IIIA	
INTERNAL OSCILLATOR						
Frequency of Auto-Correction			90		kHz	
Accuracy			±20		%	
FREQUENCY RESPONSE						
Bandwidth ⁽⁴⁾ , –3dB BV	G = 1 to 1k		1		kHz	
Slew Rate ⁽⁴⁾			Filter Limited			
	$_{\rm S}$ 1kHz Filter, G = 1 to 1k, V _O = 2V step, C _L = 100pF		0.95		ms	
.	5 100 + 100 000 = 100 100 000 = 100 000					
0.01%			1.3		ms	
0.1%	10kHz Filter, G = 1 to 1k, V_O = 2V step, C_L = 100pF		130		μs	
0.01%			160		μs	
Overload Recovery ⁽⁴⁾	1kHz Filter, 50% Output Overload, G = 1 to 1k		30		μs	
	10kHz Filter, 50% Output Overload, G = 1 to 1k		5		μs	



ELECTRICAL CHARACTERISTICS: $V_s = +2.7V$ to +5.5V (Cont.)

BOLDFACE limits apply over the specified temperature range, $T_A = -40^{\circ}C$ to $+125^{\circ}C$

At $T_A = +25^{\circ}$ C, $R_L = 10k\Omega$, G = 100 ($R_1 = 2k\Omega$, $R_2 = 100k\Omega$), external gain set resistors, and $IA_{COMMON} = V_S/2$, with external equivalent filter corner of 1kHz filters, unless otherwise noted.


		INA3			
PARAMETER	CONDITION	MIN	ТҮР	MAX	UNITS
POWER SUPPLY Specified Voltage Range Quiescent Current I _Q Over Temperature	I_{O} = 0, Diff V_{IN} = 0V, V_{S} = +5V	+2.7	2.4	+5.5 3.4 3.7	V mA mA
SHUTDOWN Disable (Logic-Low Threshold) Enable (Logic-High Threshold) Enable Time ⁽⁵⁾ Disable Time Shutdown Current and Enable Pin Current	V _S = +5V, Disabled	1.6	75 100 2	0.25	V V μs μs μA
TEMPERATURE RANGE Specified Range Operating Range Storage Range Thermal Resistance θ _{JA}	MSOP-8 Surface-Mount	40 40 65	150	+125 +150 +150	°C °C °C W.S°


NOTES: (1) 1000-hour life test at 150°C demonstrated randomly distributed variation in the range of measurement limits—approximately 10 μ V. (2) See Applications Information section, Figures 1 and 2. (3) Does not include error and TCR of external gain-setting resistors. (4) Dynamic response is limited by filtering. Higher bandwidths can be achieved by adjusting the filter. (5) See Typical Characteristics, "Input Offset Voltage vs Warm-Up Time".





TYPICAL CHARACTERISTICS


At $T_A = 25^{\circ}$ C, $V_S = +5V$, Gain = 100, $R_L = 10k\Omega$ with external equivalent filter corner of 1kHz filters, unless otherwise noted.













INPUT-REFERRED VOLTAGE NOISE AND INPUT BIAS CURRENT NOISE vs FREQUENCY 10kHz Filter





TYPICAL CHARACTERISTICS (Cont.)


At $T_A = 25^{\circ}$ C, $V_S = +5$ V, Gain = 100, $R_L = 10 k\Omega$ with external equivalent filter corner of 1kHz filters, unless otherwise noted.






TYPICAL CHARACTERISTICS (Cont.)


At $T_A = 25^{\circ}$ C, $V_S = +5$ V, Gain = 100, $R_L = 10$ k Ω with external equivalent filter corner of 1kHz filters, unless otherwise noted.




OFFSET VOLTAGE DRIFT PRODUCTION DISTRIBUTION G = 1




OFFSET VOLTAGE DRIFT PRODUCTION DISTRIBUTION G = 10





Offset Voltage (µV)

OFFSET VOLTAGE DRIFT PRODUCTION DISTRIBUTION G = 100 and 1000 $\,$





INA337, INA338 SBOS222A





TYPICAL CHARACTERISTICS (Cont.)


At $T_A = 25^{\circ}$ C, $V_S = +5$ V, Gain = 100, $R_L = 10$ k Ω with external equivalent filter corner of 1kHz filters, unless otherwise noted.















APPLICATIONS INFORMATION

Figure 1 shows the basic connections required for operation of the INA337. A 0.1µF capacitor, placed close to and across the power-supply pins is strongly recommended for highest accuracy. RoCo is an output filter that minimizes auto-correction circuitry noise. This output filter may also serve as an antialiasing filter ahead of an Analog-to-Digital (A/D) converter. It is also optional based on desired precision.

The output reference terminal is taken at the low side of R₂ (IA_{COMMON}).

The INA337 uses a unique internal topology to achieve excellent common-mode rejection (CMR). Unlike conventional instrumentation amplifiers, CMR is not affected by resistance in the reference connections. See "Inside the INA337" for further detail. To achieve best high-frequency CMR, minimize capacitance on pins 1 and 8.

DESIRED

GAIN

0.1

0.2

05

1

2

5

10

20

50

100

200

500

1000

2000

5000

10000

SETTING THE GAIN

The INA337 is a 2-stage amplifier with each stage gain set by R₁ and R₂, respectively (see Figure 4, "Inside the INA337", for details.) Overall gain is described by the equation:


$$G = \frac{2R_2}{R_1}$$
(1)

The stability and temperature drift of the external gain-setting resistors will affect gain by an amount that can be directly inferred from the gain equation (1).

Resistor values for commonly used gains are shown in Figure 1. Gain-set resistor values for best performance are different for +5V single-supply and for ±2.5V dual-supply operation. Optimum value for R₁ can be calculated by:

$$R_1 = V_{IN, MAX} / 12.5 \mu A$$
 (2)


where R_1 must be no less than $2k\Omega$.



Each individual pole is at 1.5kHz. (2) Output voltage is referenced to IA_{COMMON} (see text).

DESIRED GAIN	R ₁ (Ω)	R₂ ∥ C₂ (Ω ∥ nF)
0.1	400k	20k 5
0.2	400k	40k 2.5
0.5	400k	100k 1
1	400k	200k 0.5
2	200k	200k 0.5
5	80k	200k 0.5
10	40k	200k 0.5
20	20k	200k 0.5
50	8k	200k 0.5
100	4k	200k 0.5
200	2k	200k 0.5
500	2k	500k 0.2
1000	2k	1M 0.1
2000	2k	2M 0.05
5000	2k	5M 0.02
10000	2k	10M 0.01

Single-Supply Operation



NOTES: (1) C_2 and C_0 combine to form a 2-pole response that is –3dB at 1kHz. Each individual pole is at 1.5kHz. (2) Output voltage is referenced to IA_{COMMON} (see text). (3) Output pedestal required for measurement near zero (see Figure 6).

FIGURE 1. Basic Connections. NOTE: Connections for INA338 differ-see Pin Configuration for detail.

INA337, INA338 SBOS222A



Following this design procedure for R_1 produces the maximum possible input stage gain for best accuracy and lowest noise.

Circuit layout and supply bypassing can affect performance. Minimize the stray capacitance on pins 1 and 8. Use recommended supply bypassing, including a capacitor directly from pin 7 to pin 4 (V+ to V–), even with dual (split) power supplies (see Figure 1).

DYNAMIC PERFORMANCE

The typical characteristic "Gain vs Frequency" shows that the INA337 has nearly constant bandwidth regardless of gain. This results from the bandwidth limiting from the recommended filters.

NOISE PERFORMANCE

Internal auto-correction circuitry eliminates virtually all 1/f noise (noise that increases at low frequency) in gains of 100 or greater. Noise performance is affected by gain-setting resistor values. Follow recommendations in the "Setting Gain" section for best performance.

Total noise is a combination of input stage noise and output stage noise. When referred to the input, the total mid-band noise is:

$$V_{N} = 33nV / \sqrt{Hz} + \frac{800nV / \sqrt{Hz}}{G}$$
(3)

The output noise has some 1/f components that affect performance in gains less than 10. See typical characteristic "Input-Referred Voltage Noise vs Frequency."

High-frequency noise is created by internal auto-correction circuitry and is highly dependent on the filter characteristics chosen. This may be the dominant source of noise visible when viewing the output on an oscilloscope. Low cutoff frequency filters will provide lowest noise. Figure 2 shows the typical noise performance as a function of cutoff frequency.




FIGURE 2. Total Output Noise vs Filter Cutoff Frequency.

Applications sensitive to the spectral characteristics of highfrequency noise may require consideration of the spurious frequencies generated by internal clocking circuitry. "Spurs" occur at approximately 90kHz and its harmonics (see typical characteristic "Input Referred Ripple") which may be reduced by additional filtering below 1kHz.

Insufficient filtering at pin 5 can cause nonlinearity with large output voltage swings (very near the supply rails). Noise must be sufficiently filtered at pin 5 so that noise peaks do not "hit the rail" and change the average value of the signal. Figure 2 shows guidelines for filter cutoff frequency.

HIGH-FREQUENCY NOISE

 C_2 and C_0 form filters to reduce internally generated autocorrection circuitry noise. Filter frequencies can be chosen to optimize the tradeoff between noise and frequency response of the application, as shown in Figure 2. The cutoff frequencies of the filters are generally set to the same frequency. Figure 2 shows the typical output noise for four gains as a function of the –3dB cutoff frequency of each filter response. Small signals may exhibit the addition of internally generated auto-correction circuitry noise at the output. This noise, combined with broadband noise, becomes most evident in higher gains with filters of wider bandwidth.

INPUT BIAS CURRENT RETURN PATH

The input impedance of the INA337 is extremely high approximately $10^{10}\Omega$. However, a path must be provided for the input bias current of both inputs. This input bias current is approximately ±0.2nA. High input impedance means that this input bias current changes very little with varying input voltage.

Input circuitry must provide a path for this input bias current for proper operation. Figure 3 shows provisions for an input bias current path in a thermocouple application. Without a bias current path, the inputs will float to an undefined potential and the output voltage may not be valid.




FIGURE 3. Providing Input Bias Current Return Path.



INPUT AND OUTPUT VOLTAGE

The INA337 and INA338 feature nearly rail-to-rail input behavior, with the linear input voltage range extending from 0.25V above the negative rail to 0.1V above the positive rail. The output is able to swing to within 0.25V of the negative rail and 0.075V of the positive rail. See Typical Characteristics Curve "Output Swing to the Negative Rail" for additional detail.

INPUT PROTECTION

The inputs of the INA337 are protected with internal diodes connected to the power-supply rails. These diodes will clamp the applied signal to prevent it from damaging the input circuitry. If the input signal voltage can exceed the power supplies by more than 0.5V, the input signal current should be limited to less than 10mA to protect the internal clamp diodes. This can generally be done with a series input resistor. Some signal sources are inherently current-limited and do not require limiting resistors.

INSIDE THE INA337

The INA337 uses a new, unique internal circuit topology that provides near rail-to-rail input. Unlike other instrumentation amplifiers, it can linearly process inputs from 0.25V above the negative rail to 0.1V beyond the positive rail. Conventional instrumentation amplifier circuits cannot deliver such performance, even if rail-to-rail op amps are used.

The ability to reject common-mode signals is derived in most instrumentation amplifiers through a combination of amplifier CMR and accurately matched resistor ratios. The INA337 converts the input voltage to a current. Currentmode signal processing provides rejection of commonmode input voltage and power-supply variation without accurately matched resistors.

The topology of the INA337 avoids aliasing issues that appear in instrumentation amplifiers that use sampled data techniques.

A simplified diagram shows the basic circuit function. The differential input voltage, $(V_{IN}+) - (V_{IN}-)$ is applied across R_1 . The signal-generated current through R_1 comes from A1 and A2's output stages. A2 combines the current in R_1 with a mirrored replica of the current from A1. The resulting current in A2's output and associated current mirror is two times the current in R_1 . This current flows in (or out) of pin 5 into R_2 . The resulting gain equation is:

$$G = \frac{2R_2}{R_1}$$

Amplifiers A1, A2 and their associated mirrors are powered from internal charge-pumps that provide voltage supplies that are beyond the positive negative supply. As a result, the voltage developed on R_2 can actually swing 100mV *above* the positive power-supply rail. A3 provides a buffered output of the voltage on R_2 . A3's input stage is also operated from the charge-pumped power supplies for true rail-to-rail operation.




FIGURE 4. Simplified Circuit Diagram.

FILTERING

Filtering can be adjusted through selection of R_2C_2 and R_0C_0 for the desired tradeoff of noise and bandwidth. Adjustment of these components will result in more or less ripple due to auto-correction circuitry noise and will also affect broadband noise. Filtering limits slew rate, settling time, and output overload recovery time.

It is generally desirable to keep the resistance of R_o relatively low to avoid DC gain error created by the subsequent stage loading. This may result in relatively high values for C_o to produce the desired filter response. The impedance of R_oC_o can be scaled higher to produce smaller capacitor values if the load impedance is very high.

Certain capacitor types greater than 0.1μ F may have dielectric absorption effects that can significantly increase settling time in high-accuracy applications (settling to 0.01%). Polypropylene, polystyrene, and polycarbonate types are generally good. Certain "high-K" ceramic types may produce slow settling "tails." Settling time to 0.1% is not generally affected by high-K ceramic capacitors. Electrolytic types are not recommended for C₂ and C₀.

INA338 ENABLE FUNCTION

The INA338 can be enabled by applying a logic "High" voltage level to the Enable pin. Conversely, a logic "Low" voltage level will disable the amplifier, reducing its supply current from 2.4mA to typically 2μ A. For battery-operated applications, this feature may be used to greatly reduce the average current and extend battery life. This pin should be connected to a valid high or low voltage or driven, not left open circuit. The Enable pin can be modeled as a CMOS input gate as in Figure 5.




FIGURE 5. Enable Pin Model.

The enable time following shutdown is 75μ s plus the settling time due to filters (see Typical Characteristics, "Input Offset Voltage vs Warm-up Time"). Disable time is 100 μ s. This allows the INA338 to be operated as a "gated" amplifier, or to have its output multiplexed onto a common output bus. When disabled, the output assumes a high-impedance state.

INA338 PIN 5

Pin 5 of the INA338 should be connected to V+ to ensure proper operation.




FIGURE 6. Output Range Pedestal.




FIGURE 7. High-Side Shunt Measurement of Current Load.





FIGURE 8. Output Referenced to $V_{REF}/2$.





DGK (R-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE




NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion.
- D. Falls within JEDEC MO-187

DGS (S-PDSO-G10)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion.
- A. Falls within JEDEC MO-187





PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS	Lead finish/	MSL rating/	Op temp (°C)	Part marking
	(1)	(2)			(3)	Ball material	Peak reflow		(6)
						(4)	(5)		
INA337AIDGKR	Active	Production	VSSOP (DGK) 8	2500 LARGE T&R	Yes	Call TI Nipdauag	Level-2-260C-1 YEAR	-40 to 125	BIM
INA337AIDGKR.B	Active	Production	VSSOP (DGK) 8	2500 LARGE T&R	Yes	Call TI	Level-2-260C-1 YEAR	-40 to 125	BIM
INA337AIDGKT	Active	Production	VSSOP (DGK) 8	250 SMALL T&R	Yes	Call TI Nipdauag	Level-2-260C-1 YEAR	-40 to 125	BIM
INA337AIDGKT.B	Active	Production	VSSOP (DGK) 8	250 SMALL T&R	Yes	Call TI	Level-2-260C-1 YEAR	-40 to 125	BIM
INA338AIDGST	Active	Production	VSSOP (DGS) 10	250 SMALL T&R	Yes	Call TI Nipdauag	Level-2-260C-1 YEAR	-40 to 125	BIL
INA338AIDGST.B	Active	Production	VSSOP (DGS) 10	250 SMALL T&R	Yes	Call TI	Level-2-260C-1 YEAR	-40 to 125	BIL

⁽¹⁾ **Status:** For more details on status, see our product life cycle.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

⁽⁴⁾ Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

PACKAGE OPTION ADDENDUM

23-May-2025

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025, Texas Instruments Incorporated