

## LM158QML Low Power Dual Operational Amplifiers

Check for Samples: [LM158QML](#)

### FEATURES

- Available with Radiation Specification
  - High Dose Rate 100 krad(Si)
  - ELDRS Free 100 krad(Si)
- Internally Frequency Compensated for Unity Gain
- Large DC Voltage Gain: 100 dB
- Wide Bandwidth (Unity Gain): 1 MHz  
z(Temperature Compensated)
- Wide Power Supply Range:
  - Single Supply: 3V to 32V
  - Or Dual Supplies:  $\pm 1.5V$  to  $\pm 16V$
- Very Low Supply Current Drain (500  $\mu A$ ) –  
Essentially Independent of Supply Voltage
- Low Input Offset Voltage: 2 mV
- Input Common-mode Voltage Range Includes Ground
- Differential Input Voltage Range Equal to the Power Supply Voltage
- Large Output Voltage Swing: 0V to  $V^+ - 1.5V$

### UNIQUE CHARACTERISTICS

- In the Linear Mode the Input Common-Mode Voltage Range Includes Ground and the Output Voltage can also Swing to Ground, even though Operated from only a Single Power Supply Voltage.
- The Unity Gain Cross Frequency is Temperature Compensated.
- The Input Bias Current is also Temperature Compensated.

### ADVANTAGES

- Two Internally Compensated Op Amps
- Eliminates Need for Dual Supplies
- Allows Direct Sensing Near Gnd and  $V_O$  also Goes to Gnd
- Compatible with all Forms of Logic
- Power Drain Suitable for Battery Operation

### DESCRIPTION

The LM158 series consists of two independent, high gain, internally frequency compensated operational amplifiers which were designed specifically to operate from a single power supply over a wide range of voltages. Operation from split power supplies is also possible and the low power supply current drain is independent of the magnitude of the power supply voltage.

Application areas include transducer amplifiers, dc gain blocks and all the conventional op amp circuits which now can be more easily implemented in single power supply systems. For example, the LM158 series can be directly operated off of the standard +5V power supply voltage which is used in digital systems and will easily provide the required interface electronics without requiring the additional  $\pm 15V$  power supplies.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.


PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 2005–2013, Texas Instruments Incorporated


## Connection Diagrams



**Figure 1. TO-99 Package**  
See Package Number LMC0008C




**Figure 2. CDIP Package**  
See Package Number NAB0008A



**Figure 3. 10 Lead CLGA Package**  
See Package Number NAC0010A

## Schematic Diagram

(Each Amplifier)



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

**Absolute Maximum Ratings<sup>(1)</sup>**

|                                                                                                                               |                 |                            |                                           |
|-------------------------------------------------------------------------------------------------------------------------------|-----------------|----------------------------|-------------------------------------------|
| Supply Voltage, V <sup>+</sup>                                                                                                |                 |                            | 32V <sub>DC</sub>                         |
| Differential Input Voltage                                                                                                    |                 |                            | 32V <sub>DC</sub>                         |
| Input Voltage                                                                                                                 |                 |                            | -0.3V <sub>DC</sub> to +32V <sub>DC</sub> |
| Power Dissipation <sup>(2)</sup>                                                                                              |                 |                            | 830 mW                                    |
| Output Short-Circuit to GND <sup>(3)</sup><br>(One Amplifier)<br>V <sup>+</sup> ≤ 15V <sub>DC</sub> and T <sub>A</sub> = 25°C |                 |                            | Continuous                                |
| Maximum Junction Temperature (T <sub>Jmax</sub> )                                                                             |                 |                            | 150°C                                     |
| Input Current (V <sub>I</sub> < -0.3V) <sup>(4)</sup>                                                                         |                 |                            | 50 mA                                     |
| Operating Temperature Range                                                                                                   |                 |                            | -55°C ≤ T <sub>A</sub> ≤ +125°C           |
| Storage Temperature Range                                                                                                     |                 |                            | -65°C ≤ T <sub>A</sub> ≤ +150°C           |
| Lead Temperature (Soldering, 10 seconds)                                                                                      |                 | TO-99                      | 300°C                                     |
|                                                                                                                               |                 | CDIP                       | 260°C                                     |
|                                                                                                                               |                 | CLGA                       | 260°C                                     |
| Thermal Resistance                                                                                                            | θ <sub>JA</sub> | TO-99 (Still Air)          | 155°C/W                                   |
|                                                                                                                               |                 | TO-99 (500LF/Min Air Flow) | 80°C/W                                    |
|                                                                                                                               |                 | CDIP (Still Air)           | 132°C/W                                   |
|                                                                                                                               |                 | CDIP (500LF/Min Air Flow)  | 81°C/W                                    |
|                                                                                                                               |                 | CLGA (Still Air)           | 195°C/W                                   |
|                                                                                                                               |                 | CLGA (500LF/Min Air Flow)  | 131°C/W                                   |
|                                                                                                                               | θ <sub>JC</sub> | TO-99                      | 42°C/W                                    |
|                                                                                                                               |                 | CDIP                       | 23°C/W                                    |
|                                                                                                                               |                 | CLGA                       | 33°C/W                                    |
| Package Weight                                                                                                                | TO-99           |                            | 1,000mg                                   |
|                                                                                                                               | CDIP            |                            | 1,100mg                                   |
|                                                                                                                               | CLGA            |                            | 220mg                                     |
| ESD Tolerance <sup>(5)</sup>                                                                                                  |                 |                            | 250V                                      |

- (1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not ensure specific performance limits. For ensured specifications and test conditions, see the Electrical Characteristics. The ensured specifications apply only for the test conditions listed. Some performance characteristics may degrade when the device is not operated under the listed test conditions.
- (2) The maximum power dissipation must be derated at elevated temperatures and is dictated by  $T_{Jmax}$  (maximum junction temperature),  $\theta_{JA}$  (package junction to ambient thermal resistance), and  $T_A$  (ambient temperature). The maximum allowable power dissipation at any temperature is  $P_{Dmax} = (T_{Jmax} - T_A)/\theta_{JA}$  or the number given in the Absolute Maximum Ratings, whichever is lower.
- (3) Short circuits from the output to  $V^+$  can cause excessive heating and eventual destruction. When considering short circuits to ground, the maximum output current is approximately 40 mA independent of the magnitude of  $V^+$ . At values of supply voltage in excess of +15V, continuous short-circuits can exceed the power dissipation ratings and cause eventual destruction. Destructive dissipation can result from simultaneous shorts on all amplifiers.
- (4) This input current will only exist when the voltage at any of the input leads is driven negative. It is due to the collector-base junction of the input PNP transistors becoming forward biased and thereby acting as input diode clamps. In addition to this diode action, there is also lateral NPN parasitic transistor action on the IC chip. This transistor action can cause the output voltages of the op amps to go to the  $V^+$  voltage level (or to ground for a large overdrive) for the time duration that an input is driven negative. This is not destructive and normal output states will re-establish when the input voltage, which was negative, again returns to a value greater than -0.3V (at 25°C).
- (5) Human body model, 1.5 k $\Omega$  in series with 100 pF.

**Quality Conformance Inspection**

Mil-Std-883, Method 5005 - Group A

| Subgroup | Description         | Temp °C |
|----------|---------------------|---------|
| 1        | Static tests at     | +25     |
| 2        | Static tests at     | +125    |
| 3        | Static tests at     | -55     |
| 4        | Dynamic tests at    | +25     |
| 5        | Dynamic tests at    | +125    |
| 6        | Dynamic tests at    | -55     |
| 7        | Functional tests at | +25     |
| 8A       | Functional tests at | +125    |
| 8B       | Functional tests at | -55     |
| 9        | Switching tests at  | +25     |
| 10       | Switching tests at  | +125    |
| 11       | Switching tests at  | -55     |
| 12       | Settling time at    | +25     |
| 13       | Settling time at    | +125    |
| 14       | Settling time at    | -55     |

## LM158 Electrical Characteristics SMD 5962–8771001 DC Parameters

The following conditions apply, unless otherwise specified. All voltages referenced to device ground.

| Parameter           |                              | Test Conditions                                                                               | Notes                   | Min  | Max  | Units | Sub-groups |
|---------------------|------------------------------|-----------------------------------------------------------------------------------------------|-------------------------|------|------|-------|------------|
| I <sub>CC</sub>     | Power Supply Current         | +V <sub>CC</sub> = 5V, R <sub>L</sub> = 100K, V <sub>O</sub> = 1.4V                           |                         |      | 1.2  | mA    | 1, 2, 3    |
|                     |                              | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 100K, V <sub>O</sub> = 1.4V                          |                         |      | 3.0  | mA    | 1          |
|                     |                              |                                                                                               |                         |      | 4.0  | mA    | 2, 3       |
| V <sub>OH</sub>     | Output Voltage High          | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 2KΩ                                                  |                         | 26   |      | V     | 1, 2, 3    |
|                     |                              | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 10KΩ                                                 |                         | 27   |      | V     | 1, 2, 3    |
| V <sub>OL</sub>     | Output Voltage Low           | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 10KΩ                                                 |                         |      | 20   | mV    | 1, 2, 3    |
|                     |                              | +V <sub>CC</sub> = 30V, I <sub>Sink</sub> = 1μA                                               |                         |      | 20   | mV    | 1, 2, 3    |
|                     |                              | +V <sub>CC</sub> = 5V, R <sub>L</sub> = 10KΩ                                                  |                         |      | 20   | mV    | 1, 2, 3    |
| I <sub>Sink</sub>   | Output Sink Current          | +V <sub>CC</sub> = 15V, V <sub>O</sub> = 200mV, +V <sub>I</sub> = 0V, -V <sub>I</sub> = +65mV |                         | 12   |      | μA    | 1          |
|                     |                              | +V <sub>CC</sub> = 15V, V <sub>O</sub> = 2V, +V <sub>I</sub> = 0V, -V <sub>I</sub> = +65mV    |                         | 10   |      | mA    | 1          |
|                     |                              |                                                                                               |                         | 5.0  |      | mA    | 2, 3       |
| I <sub>Source</sub> | Output Source Current        | +V <sub>CC</sub> = 15V, V <sub>O</sub> = 2V, +V <sub>I</sub> = 0V, -V <sub>I</sub> = -65mV    |                         |      | -20  | mA    | 1          |
|                     |                              |                                                                                               |                         |      | -10  | mA    | 2, 3       |
| I <sub>OS</sub>     | Short Circuit Current        | +V <sub>CC</sub> = 5V, V <sub>O</sub> = 0V                                                    |                         | -60  |      | mA    | 1          |
| V <sub>IO</sub>     | Input Offset Voltage         | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 0V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V     |                         | -5.0 | 5.0  | mV    | 1          |
|                     |                              |                                                                                               |                         | -7.0 | 7.0  | mV    | 2, 3       |
|                     |                              | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 28.5V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V  |                         | -5.0 | 5.0  | mV    | 1          |
|                     |                              | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 28V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V    |                         | -7.0 | 7.0  | mV    | 2, 3       |
|                     |                              | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V      |                         | -5.0 | 5.0  | mV    | 1          |
|                     |                              |                                                                                               |                         | -7.0 | 7.0  | mV    | 2, 3       |
| CMRR                | Common Mode Rejection Ratio  | +V <sub>CC</sub> = 30V, R <sub>S</sub> = 50Ω, V <sub>I</sub> = 0V to 28.5V,                   |                         | 70   |      | dB    | 1          |
| ±I <sub>IB</sub>    | Input Bias Current           | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V                                                   | See <sup>(1)</sup>      | -150 | -1.0 | nA    | 1          |
|                     |                              |                                                                                               | See <sup>(1)</sup>      | -300 | -1.0 | nA    | 2, 3       |
| I <sub>IO</sub>     | Input Offset Current         | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V                                                   |                         | -30  | 30   | nA    | 1          |
|                     |                              |                                                                                               |                         | -100 | 100  | nA    | 2, 3       |
| PSRR                | Power Supply Rejection Ratio | +V <sub>CC</sub> = 5V to 30V, V <sub>CM</sub> = 0V                                            |                         | 65   |      | dB    | 1          |
| V <sub>CM</sub>     | Common Mode Voltage Range    | +V <sub>CC</sub> = 30V                                                                        | See <sup>(2), (3)</sup> |      | 28.5 | V     | 1          |
|                     |                              |                                                                                               | See <sup>(2), (3)</sup> |      | 28.0 | V     | 2, 3       |
| V <sub>Diff</sub>   | Differential Input Voltage   |                                                                                               | See <sup>(4)</sup>      |      | 32   | V     | 1, 2, 3    |
| A <sub>VS</sub>     | Large Signal Gain            | +V <sub>CC</sub> = 15V, R <sub>L</sub> = 2KΩ, V <sub>O</sub> = 1V to 11V                      |                         | 50   |      | V/mV  | 4          |
|                     |                              |                                                                                               |                         | 25   |      | V/mV  | 5, 6       |

- (1) The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so no loading change exists on the input lines.
- (2) The input common-mode voltage of either input signal voltage should not be allowed to go negative by more than 0.3V (at 25°C). The upper end of the common-mode voltage range is V<sup>+</sup> -1.5V (at 25°C), but either or both inputs can go to +32V without damage, independent of the magnitude of V<sup>+</sup>.
- (3) Specified by input offset voltage.
- (4) Specified parameter not tested.

## LM158A Electrical Characteristics SMD 5962–8771002, High Dose Rate DC Parameters

The following conditions apply, unless otherwise specified. All voltages referenced to device ground.

| Parameter           |                              | Test Conditions                                                                               | Notes                  | Min  | Max  | Units | Sub-groups |
|---------------------|------------------------------|-----------------------------------------------------------------------------------------------|------------------------|------|------|-------|------------|
| I <sub>CC</sub>     | Power Supply Current         | +V <sub>CC</sub> = 5V, R <sub>L</sub> = 100K, V <sub>O</sub> = 1.4V                           |                        |      | 1.2  | mA    | 1, 2, 3    |
|                     |                              | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 100K, V <sub>O</sub> = 1.4V                          |                        |      | 3.0  | mA    | 1          |
|                     |                              |                                                                                               |                        |      | 4.0  | mA    | 2, 3       |
| V <sub>OH</sub>     | Output Voltage High          | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 2KΩ                                                  |                        | 26   |      | V     | 1, 2, 3    |
|                     |                              | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 10KΩ                                                 |                        | 27   |      | V     | 1, 2, 3    |
| V <sub>OL</sub>     | Output Voltage Low           | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 10KΩ                                                 |                        |      | 40   | mV    | 1          |
|                     |                              |                                                                                               |                        |      | 100  | mV    | 2, 3       |
|                     |                              | +V <sub>CC</sub> = 30V, I <sub>Sink</sub> = 1μA                                               |                        |      | 40   | mV    | 1          |
|                     |                              |                                                                                               |                        |      | 100  | mV    | 2, 3       |
|                     |                              | +V <sub>CC</sub> = 5V, R <sub>L</sub> = 10KΩ                                                  |                        |      | 40   | mV    | 1          |
|                     |                              |                                                                                               |                        |      | 100  | mV    | 2, 3       |
| I <sub>Sink</sub>   | Output Sink Current          | +V <sub>CC</sub> = 15V, V <sub>O</sub> = 200mV, +V <sub>I</sub> = 0V, -V <sub>I</sub> = +65mV |                        | 12   |      | μA    | 1          |
|                     |                              | +V <sub>CC</sub> = 15V, V <sub>O</sub> = 2V, +V <sub>I</sub> = 0V, -V <sub>I</sub> = +65mV    |                        | 10   |      | mA    | 1          |
|                     |                              |                                                                                               |                        | 5.0  |      | mA    | 2, 3       |
| I <sub>Source</sub> | Output Source Current        | +V <sub>CC</sub> = 15V, V <sub>O</sub> = 2V, +V <sub>I</sub> = 0V, -V <sub>I</sub> = -65mV    |                        |      | -20  | mA    | 1          |
|                     |                              |                                                                                               |                        |      | -10  | mA    | 2, 3       |
| I <sub>OS</sub>     | Short Circuit Current        | +V <sub>CC</sub> = 5V, V <sub>O</sub> = 0V                                                    |                        | -60  |      | mA    | 1          |
| V <sub>IO</sub>     | Input Offset Voltage         | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 0V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V     |                        | -2.0 | 2.0  | mV    | 1          |
|                     |                              |                                                                                               |                        | -4.0 | 4.0  | mV    | 2, 3       |
|                     |                              | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 28.5V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V  |                        | -2.0 | 2.0  | mV    | 1          |
|                     |                              | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 28V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V    |                        | -4.0 | 4.0  | mV    | 2, 3       |
|                     |                              | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V      |                        | -2.0 | 2.0  | mV    | 1          |
|                     |                              |                                                                                               |                        | -4.0 | 4.0  | mV    | 2, 3       |
| CMRR                | Common Mode Rejection Ratio  | +V <sub>CC</sub> = 30V, R <sub>S</sub> = 50Ω, V <sub>I</sub> = 0V to 28.5V,                   |                        | 70   |      | dB    | 1          |
| ±I <sub>IB</sub>    | Input Bias Current           | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V                                                   | See <sup>(1)</sup>     | -50  | -1.0 | nA    | 1          |
|                     |                              |                                                                                               | See <sup>(1)</sup>     | -100 | -1.0 | nA    | 2, 3       |
| I <sub>IO</sub>     | Input Offset Current         | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V                                                   |                        | -10  | 10   | nA    | 1          |
|                     |                              |                                                                                               |                        | -30  | 30   | nA    | 2, 3       |
| PSRR                | Power Supply Rejection Ratio | +V <sub>CC</sub> = 5V to 30V, V <sub>CM</sub> = 0V                                            |                        | 65   |      | dB    | 1          |
| V <sub>CM</sub>     | Common Mode Voltage Range    | +V <sub>CC</sub> = 30V                                                                        | See <sup>(2) (3)</sup> |      | 28.5 | V     | 1          |
|                     |                              |                                                                                               | See <sup>(2) (3)</sup> |      | 28.0 | V     | 2, 3       |
| V <sub>Diff</sub>   | Differential Input Voltage   |                                                                                               | See <sup>(4)</sup>     |      | 32   | V     | 1, 2, 3    |
| A <sub>VS</sub>     | Large Signal Gain            | +V <sub>CC</sub> = 15V, R <sub>L</sub> = 2KΩ, V <sub>O</sub> = 1V to 11V                      |                        | 50   |      | V/mV  | 4          |
|                     |                              |                                                                                               |                        | 25   |      | V/mV  | 5, 6       |

- (1) The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so no loading change exists on the input lines.
- (2) The input common-mode voltage of either input signal voltage should not be allowed to go negative by more than 0.3V (at 25°C). The upper end of the common-mode voltage range is V<sup>+</sup> -1.5V (at 25°C), but either or both inputs can go to +32V without damage, independent of the magnitude of V<sup>+</sup>.
- (3) Specified by input offset voltage.
- (4) Specified parameter not tested.

## SMD 5962–8771002, High Dose Rate DC Drift Parameters

The following conditions apply, unless otherwise specified. All voltages referenced to device ground. Delta calculations are performed on QMLV devices at Group B, Subgroup 5 only.

| Parameter       |                      | Test Conditions                                                                              | Notes              | Min  | Max | Units | Sub-groups |
|-----------------|----------------------|----------------------------------------------------------------------------------------------|--------------------|------|-----|-------|------------|
| V <sub>IO</sub> | Input Offset Voltage | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 0V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V    |                    | -0.5 | 0.5 | mV    | 1          |
|                 |                      | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 28.5V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V |                    | -0.5 | 0.5 | mV    | 1          |
|                 |                      | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V     |                    | -0.5 | 0.5 | mV    | 1          |
| ±I <sub>B</sub> | Input Bias Current   | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V                                                  | See <sup>(1)</sup> | -10  | 10  | nA    | 1          |

- (1) The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so no loading change exists on the input lines.

## SMD 5962–8771002, High Dose Rate SMD 5962–8771002, High Dose Rate 100K Post Radiation Limits @ +25°C<sup>(1)</sup> DC Parameters

The following conditions apply, unless otherwise specified. All voltages referenced to device ground.

| Parameter       |                      | Test Conditions                                                                              | Notes                 | Min  | Max  | Units | Sub - groups |
|-----------------|----------------------|----------------------------------------------------------------------------------------------|-----------------------|------|------|-------|--------------|
| V <sub>IO</sub> | Input Offset Voltage | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 0V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V    | See <sup>(1)</sup>    | -4.0 | 4.0  | mV    | 1            |
|                 |                      | +V <sub>CC</sub> = 30V, V <sub>CM</sub> = 28.5V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V | See <sup>(1)</sup>    | -4.0 | 4.0  | mV    | 1            |
|                 |                      | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V, R <sub>S</sub> = 50Ω, V <sub>O</sub> = 1.4V     | See <sup>(1)</sup>    | -4.0 | 4.0  | mV    | 1            |
| ±I <sub>B</sub> | Input Bias Current   | +V <sub>CC</sub> = 5V, V <sub>CM</sub> = 0V                                                  | See <sup>(1)(2)</sup> | -60  | -1.0 | nA    | 1            |
| I <sub>CC</sub> | Power Supply Current | +V <sub>CC</sub> = 5V, R <sub>L</sub> = 100K, V <sub>O</sub> = 1.4V                          | See <sup>(1)</sup>    |      | 1.5  | mA    | 1            |

- (1) Pre and post irradiation limits are identical to those listed under AC and DC electrical characteristics except as listed in the Post Radiation Limits Table. These parts may be dose rate sensitive in a space environment and demonstrate enhanced low dose rate sensitivity. Radiation end point limits for the noted parameters are specified only for the conditions as specified in MIL-STD-883, per Test Method 1019, Condition A.
- (2) The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so no loading change exists on the input lines.

## LM158A Electrical Characteristics SMD 5962–8771003 ELDRS Free Only DC Parameters

The following conditions apply, unless otherwise specified. All voltages referenced to device ground.

| Parameter       |                      | Test Conditions                                                      | Notes | Min | Max | Units | Sub-groups |
|-----------------|----------------------|----------------------------------------------------------------------|-------|-----|-----|-------|------------|
| I <sub>CC</sub> | Power Supply Current | +V <sub>CC</sub> = 5V, R <sub>L</sub> = 100K, V <sub>O</sub> = 1.4V  |       |     | 1.2 | mA    | 1, 2, 3    |
|                 |                      | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 100K, V <sub>O</sub> = 1.4V |       |     | 3.0 | mA    | 1,         |
|                 |                      |                                                                      |       |     | 4.0 |       | 2, 3       |
| V <sub>OH</sub> | Output Voltage High  | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 2KΩ                         |       | 26  |     | V     | 1, 2, 3    |
|                 |                      | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 10KΩ                        |       | 27  |     | V     | 1, 2, 3    |
| V <sub>OL</sub> | Output Voltage Low   | +V <sub>CC</sub> = 30V, R <sub>L</sub> = 10KΩ                        |       |     | 40  | mV    | 1          |
|                 |                      |                                                                      |       |     | 100 | mV    | 2, 3       |
|                 |                      | +V <sub>CC</sub> = 30V, I <sub>Sink</sub> = 1μA                      |       |     | 40  | mV    | 1          |
|                 |                      |                                                                      |       |     | 100 | mV    | 2, 3       |
|                 |                      | +V <sub>CC</sub> = 5V, R <sub>L</sub> = 10KΩ                         |       |     | 40  | mV    | 1          |
|                 |                      |                                                                      |       |     | 100 | mV    | 2, 3       |

## LM158A Electrical Characteristics SMD 5962–8771003 ELDRS Free Only

### DC Parameters (continued)

The following conditions apply, unless otherwise specified. All voltages referenced to device ground.

| Parameter    |                              | Test Conditions                                              | Notes                   | Min  | Max  | Units   | Sub-groups |
|--------------|------------------------------|--------------------------------------------------------------|-------------------------|------|------|---------|------------|
| $I_{Sink}$   | Output Sink Current          | $+V_{CC} = 15V, V_O = 200mV, +V_I = 0V, -V_I = +65mV$        |                         | 12   |      | $\mu A$ | 1          |
|              |                              | $+V_{CC} = 15V, V_O = 2V, +V_I = 0V, -V_I = +65mV$           |                         | 10   |      | mA      | 1          |
|              |                              |                                                              |                         | 5.0  |      | mA      | 2, 3       |
| $I_{Source}$ | Output Source Current        | $+V_{CC} = 15V, V_O = 2V, +V_I = 0V, -V_I = -65mV$           |                         |      | -20  | mA      | 1          |
|              |                              |                                                              |                         |      | -10  | mA      | 2, 3       |
| $I_{OS}$     | Short Circuit Current        | $+V_{CC} = 5V, V_O = 0V$                                     |                         | -60  |      | mA      | 1          |
| $V_{IO}$     | Input Offset Voltage         | $+V_{CC} = 30V, V_{CM} = 0V, R_S = 50\Omega, V_O = 1.4V$     |                         | -2.0 | 2.0  | mV      | 1          |
|              |                              |                                                              |                         | -4.0 | 4.0  | mV      | 2, 3       |
|              |                              | $+V_{CC} = 30V, V_{CM} = 28.5V, R_S = 50\Omega, V_O = 1.4V$  |                         | -2.0 | 2.0  | mV      | 1          |
|              |                              | $+V_{CC} = 30V, V_{CM} = 28V, R_S = 50\Omega, V_O = 1.4V$    |                         | -4.0 | 4.0  | mV      | 2, 3       |
|              |                              | $+V_{CC} = 5V, V_{CM} = 0V, R_S = 50\Omega, V_O = 1.4V$      |                         | -2.0 | 2.0  | mV      | 1          |
|              |                              |                                                              |                         | -4.0 | 4.0  | mV      | 2, 3       |
| CMRR         | Common Mode Rejection Ratio  | $+V_{CC} = 30V, R_S = 50\Omega, V_I = 0V \text{ to } 28.5V,$ |                         | 70   |      | dB      | 1          |
| $\pm I_{IB}$ | Input Bias Current           | $+V_{CC} = 5V, V_{CM} = 0V$                                  | See <sup>(1)</sup>      | -50  | -1.0 | nA      | 1          |
|              |                              |                                                              | See <sup>(1)</sup>      | -100 | -1.0 | nA      | 2, 3       |
| $I_{IO}$     | Input Offset Current         | $+V_{CC} = 5V, V_{CM} = 0V$                                  |                         | -10  | 10   | nA      | 1          |
|              |                              |                                                              |                         | -30  | 30   | nA      | 2, 3       |
| PSRR         | Power Supply Rejection Ratio | $+V_{CC} = 5V \text{ to } 30V, V_{CM} = 0V$                  |                         | 65   |      | dB      | 1          |
| $V_{CM}$     | Common Mode Voltage Range    | $+V_{CC} = 30V$                                              | See <sup>(2), (3)</sup> |      | 28.5 | V       | 1          |
|              |                              |                                                              | See <sup>(2), (3)</sup> |      | 28.0 | V       | 2, 3       |
| $V_{Diff}$   | Differential Input Voltage   |                                                              | See <sup>(4)</sup>      |      | 32   | V       | 1, 2, 3    |
| $A_{VS}$     | Large Signal Gain            | $+V_{CC} = 15V, R_L = 2K\Omega, V_O = 1V \text{ to } 11V$    |                         | 50   |      | V/mV    | 4          |
|              |                              |                                                              |                         | 25   |      | V/mV    | 5, 6       |

- (1) The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so no loading change exists on the input lines.
- (2) The input common-mode voltage of either input signal voltage should not be allowed to go negative by more than 0.3V (at 25°C). The upper end of the common-mode voltage range is  $V^+ - 1.5V$  (at 25°C), but either or both inputs can go to +32V without damage, independent of the magnitude of  $V^+$ .
- (3) Specified by input offset voltage.
- (4) Specified parameter not tested.

## SMD 5962–8771003 ELDRS Free Only

### DC Drift Parameters

The following conditions apply, unless otherwise specified. All voltages referenced to device ground. Delta calculations are performed on QMLV devices at Group B, Subgroup 5 only.

| Parameter |                      | Test Conditions                                             | Notes | Min  | Max | Units | Sub-groups |
|-----------|----------------------|-------------------------------------------------------------|-------|------|-----|-------|------------|
| $V_{IO}$  | Input Offset Voltage | $+V_{CC} = 30V, V_{CM} = 0V, R_S = 50\Omega, V_O = 1.4V$    |       | -0.5 | 0.5 | mV    | 1          |
|           |                      | $+V_{CC} = 30V, V_{CM} = 28.5V, R_S = 50\Omega, V_O = 1.4V$ |       | -0.5 | 0.5 | mV    | 1          |
|           |                      | $+V_{CC} = 5V, V_{CM} = 0V, R_S = 50\Omega, V_O = 1.4V$     |       | -0.5 | 0.5 | mV    | 1          |

**SMD 5962–8771003 ELDRS Free Only  
DC Drift Parameters (continued)**

The following conditions apply, unless otherwise specified. All voltages referenced to device ground.  
Delta calculations are performed on QMLV devices at Group B, Subgroup 5 only.

| Parameter    |                    | Test Conditions             | Notes              | Min | Max | Units | Sub-groups |
|--------------|--------------------|-----------------------------|--------------------|-----|-----|-------|------------|
| $\pm I_{IB}$ | Input Bias Current | $+V_{CC} = 5V, V_{CM} = 0V$ | See <sup>(1)</sup> | -10 | 10  | nA    | 1          |

- (1) The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so no loading change exists on the input lines.

**SMD 5962–8771003 ELDRS Free Only  
100K Post Radiation Limits @ +25°C<sup>(1)</sup>  
DC Parameters**

The following conditions apply, unless otherwise specified. All voltages referenced to device ground.

| Parameter    |                      | Test Conditions                                             | Notes                 | Min  | Max  | Units | Sub - groups |
|--------------|----------------------|-------------------------------------------------------------|-----------------------|------|------|-------|--------------|
| $V_{IO}$     | Input Offset Voltage | $+V_{CC} = 30V, V_{CM} = 0V, R_S = 50\Omega, V_O = 1.4V$    | See <sup>(1)</sup>    | -4.0 | 4.0  | mV    | 1            |
|              |                      | $+V_{CC} = 30V, V_{CM} = 28.5V, R_S = 50\Omega, V_O = 1.4V$ | See <sup>(1)</sup>    | -4.0 | 4.0  | mV    | 1            |
|              |                      | $+V_{CC} = 5V, V_{CM} = 0V, R_S = 50\Omega, V_O = 1.4V$     | See <sup>(1)</sup>    | -4.0 | 4.0  | mV    | 1            |
| $\pm I_{IB}$ | Input Bias Current   | $+V_{CC} = 5V, V_{CM} = 0V$                                 | See <sup>(1)(2)</sup> | -60  | -1.0 | nA    | 1            |

- (1) Pre and post irradiation limits are identical to those listed under AC and DC electrical characteristics except as listed in the Post Radiation Limits Table. These parts may be sensitive in a high dose environment. Low dose rate testing has been performed on a wafer-by-wafer basis, per Test Method 1019, Condition D of MIL-STD-883, with no enhanced low dose rate sensitivity (ELDRS).  
(2) The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so no loading change exists on the input lines.

## Typical Performance Characteristics




Figure 4.




Figure 5.




Figure 6.




Figure 7.




Figure 8.




Figure 9.

## Typical Performance Characteristics (continued)




Figure 10.




Figure 11.




Figure 12.




Figure 13.




Figure 14.




Figure 15.

## APPLICATION HINTS

The LM158 series are op amps which operate with only a single power supply voltage, have true-differential inputs, and remain in the linear mode with an input common-mode voltage of  $0 V_{DC}$ . These amplifiers operate over a wide range of power supply voltage with little change in performance characteristics. At 25°C amplifier operation is possible down to a minimum supply voltage of  $2.3 V_{DC}$ .

Precautions should be taken to insure that the power supply for the integrated circuit never becomes reversed in polarity or that the unit is not inadvertently installed backwards in a test socket as an unlimited current surge through the resulting forward diode within the IC could cause fusing of the internal conductors and result in a destroyed unit.

Large differential input voltages can be easily accommodated and, as input differential voltage protection diodes are not needed, no large input currents result from large differential input voltages. The differential input voltage may be larger than  $V^+$  without damaging the device. Protection should be provided to prevent the input voltages from going negative more than  $-0.3 V_{DC}$  (at 25°C). An input clamp diode with a resistor to the IC input terminal can be used.

To reduce the power supply current drain, the amplifiers have a class A output stage for small signal levels which converts to class B in a large signal mode. This allows the amplifiers to both source and sink large output currents. Therefore both NPN and PNP external current boost transistors can be used to extend the power capability of the basic amplifiers. The output voltage needs to raise approximately 1 diode drop above ground to bias the on-chip vertical PNP transistor for output current sinking applications.

For ac applications, where the load is capacitively coupled to the output of the amplifier, a resistor should be used, from the output of the amplifier to ground to increase the class A bias current and prevent crossover distortion. Where the load is directly coupled, as in dc applications, there is no crossover distortion.

Capacitive loads which are applied directly to the output of the amplifier reduce the loop stability margin. Values of 50 pF can be accommodated using the worst-case non-inverting unity gain connection. Large closed loop gains or resistive isolation should be used if larger load capacitance must be driven by the amplifier.



The bias network of the LM158 establishes a drain current which is independent of the magnitude of the power supply voltage over the range of  $3 V_{DC}$  to  $30 V_{DC}$ .

Output short circuits either to ground or to the positive power supply should be of short time duration. Units can be destroyed, not as a result of the short circuit current causing metal fusing, but rather due to the large increase in IC chip dissipation which will cause eventual failure due to excessive junction temperatures. Putting direct short-circuits on more than one amplifier at a time will increase the total IC power dissipation to destructive levels, if not properly protected with external dissipation limiting resistors in series with the output leads of the amplifiers. The larger value of output source current which is available at 25°C provides a larger output current capability at elevated temperatures (see [Typical Performance Characteristics](#)) than a standard IC op amp.

The circuits presented in the section on typical applications emphasize operation on only a single power supply voltage. If complementary power supplies are available, all of the standard op amp circuits can be used. In general, introducing a pseudo-ground (a bias voltage reference of  $V^+/2$ ) will allow operation above and below this value in single power supply systems. Many application circuits are shown which take advantage of the wide input common-mode voltage range which includes ground. In most cases, input biasing is not required and input voltages which range to ground can easily be accommodated.


## Typical Single-Supply Applications

( $V^+ = 5.0 V_{DC}$ )




\*R not needed due to temperature independent  $I_{IN}$

Figure 16. Non-Inverting DC Gain (0V Output)




Where:  $V_O = V_1 + V_2 - V_3 - V_4$   
 $(V_1 + V_2) \geq (V_3 + V_4)$  to keep  $V_O > 0 V_{DC}$

Figure 17. DC Summing Amplifier  
 $(V_{IN'S} \geq 0 V_{DC}$  and  $V_O \geq 0 V_{DC}$ )



$V_O = 0 V_{DC}$  for  $V_{IN} = 0 V_{DC}$   
 $A_V = 10$

Figure 18. Power Amplifier



$$f_o = 1 \text{ kHz}$$

$$Q = 50$$

$$A_v = 100 \text{ (40 dB)}$$

Figure 19. "BI-QUAD" RC Active Bandpass Filter




Figure 20. Fixed Current Sources




Figure 21. Lamp Driver





Figure 22. LED Driver



$$V_O = \frac{1V(I_L)}{1A}$$

\*(Increase R1 for  $I_L$  small)

$$V_L \leq V^+ - 2V$$

Figure 23. Current Monitor





Figure 24. Driving TTL



$$V_O = V_{IN}$$

Figure 25. Voltage Follower




Figure 26. Pulse Generator




Figure 27. Squarewave Oscillator






Figure 28. Pulse Generator



HIGH  $Z_{IN}$   
LOW  $Z_{OUT}$

Figure 29. Low Drift Peak Detector



$I_O = 1 \text{ amp/volt } V_{IN}$   
(Increase  $R_E$  for  $I_O$  small)

Figure 30. High Compliance Current Sink






Figure 31. Comparator with Hysteresis



\*WIDE CONTROL VOLTAGE RANGE:  $0 V_{DC} \leq V_C \leq 2 (V^+ - 1.5V_{DC})$

Figure 32. Voltage Controlled Oscillator (VCO)



$$A_V = \frac{R_f}{R_1} \quad (\text{As shown, } A_V = 10)$$

Figure 33. AC Coupled Inverting Amplifier






Figure 34. Ground Referencing a Differential Input Signal



$$A_V = 1 + \frac{R_2}{R_1}$$


$A_V = 11$  (As Shown)

Figure 35. AC Coupled Non-Inverting Amplifier




$f_o = 1 \text{ kHz}$   
 $Q = 1$   
 $A_V = 2$

Figure 36. DC Coupled Low-Pass RC Active Filter



$f_o = 1 \text{ kHz}$   
 $Q = 25$

Figure 37. Bandpass Active Filter





For  $\frac{R1}{R2} = \frac{R4}{R3}$  (CMRR depends on this resistor ratio match)

$$V_O = 1 + \frac{R4}{R3} (V_2 - V_1)$$

As Shown:  $V_O = 2 (V_2 - V_1)$

Figure 38. High Input Z, DC Differential Amplifier




For  $\delta \ll 1$  and  $R_f \gg R$

$$V_O \approx V_{REF} \left( \frac{\delta}{2} \right) \frac{R_f}{R}$$

Figure 39. Photo Voltaic-Cell Amplifier

Figure 40. Bridge Current Amplifier



If  $R1 = R5$  &  $R3 = R4 = R6 = R7$  (CMRR depends on match)

$$V_O = 1 + \frac{2R1}{R2} (V_2 - V_1)$$

As shown  $V_O = 101 (V_2 - V_1)$

Figure 41. High Input Z Adjustable-Gain DC Instrumentation Amplifier




Figure 42. Using Symmetrical Amplifiers to Reduce Input Current (General Concept)

## REVISION HISTORY

### Changes from Revision E (March 2013) to Revision F

### Page

- Changed layout of National Data Sheet to TI format ..... [20](#)

## PACKAGING INFORMATION

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                                                                       |
|---------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|-------------------------------------------------------------------------------------------|
| <a href="#">5962-8771002GA</a>  | Active        | Production           | TO-99 (LMC)   8 | 20   JEDEC TRAY (5+1) | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   | LM158AH-SMD<br>5962-8771002GA Q A<br>CO<br>5962-8771002GA Q ><br>T                        |
| <a href="#">5962-8771002QXA</a> | Active        | Production           | CFP (NAC)   10  | 54   JEDEC TRAY (5+1) | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AWG<br>/883 Q<br>5962-87710<br>(02QXA ACO, 02QYA<br>ACO)<br>(02QXA >T, 02QYA ><br>T) |
| 5962R8771002V9A                 | Active        | Production           | DIESALE (Y)   0 | 38   NOT REQUIRED     | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   |                                                                                           |
| <a href="#">5962R8771002VGA</a> | Active        | Production           | TO-99 (LMC)   8 | 20   JEDEC TRAY (5+1) | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   | LM158AHRQMLV<br>5962R8771002VGA Q<br>ACO<br>5962R8771002VGA Q<br>>T                       |
| <a href="#">5962R8771002VPA</a> | Active        | Production           | CDIP (NAB)   8  | 40   TUBE             | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AJRQMLV<br>5962R87710<br>02VPA Q ACO<br>02VPA Q >T                                   |
| <a href="#">5962R8771002VXA</a> | Active        | Production           | CFP (NAC)   10  | 54   JEDEC TRAY (5+1) | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AWG<br>(RLQMLV Q, RQMLV Q<br>)<br>5962R87710<br>02VXA ACO<br>02VXA >T                |
| 5962R8771003V9A                 | Active        | Production           | DIESALE (Y)   0 | 456   NOT REQUIRED    | Yes         | Call TI                              | Level-1-NA-UNLIM                  | 25 to 25     |                                                                                           |
| <a href="#">5962R8771003VGA</a> | Active        | Production           | TO-99 (LMC)   8 | 20   JEDEC TRAY (5+1) | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   | LM158AHLQMLV<br>5962R8771003VGA Q<br>ACO<br>5962R8771003VGA Q<br>>T                       |

| Orderable part number | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier     | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                                                 |
|-----------------------|---------------|----------------------|-----------------|---------------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------------------------------------------------------|
| 5962R8771003VPA       | Active        | Production           | CDIP (NAB)   8  | 40   TUBE                 | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AJRLQV<br>5962R87710<br>03VPA Q ACO<br>03VPA Q >T              |
| 5962R8771003VXA       | Active        | Production           | CFP (NAC)   10  | 54   JEDEC<br>TRAY (5+1)  | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AWG<br>RLQMLV Q<br>5962R87710<br>03VXA ACO<br>03VXA >T         |
| LM158 MD8             | Active        | Production           | DIESALE (Y)   0 | 400   JEDEC<br>TRAY (5+1) | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   |                                                                     |
| LM158A MDE            | Active        | Production           | DIESALE (Y)   0 | 456   NOT REQUIRED        | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   |                                                                     |
| LM158A MDR            | Active        | Production           | DIESALE (Y)   0 | 38   NOT REQUIRED         | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   |                                                                     |
| LM158AH-SMD           | Active        | Production           | TO-99 (LMC)   8 | 20   JEDEC<br>TRAY (5+1)  | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   | LM158AH-SMD<br>5962-8771002GA Q A<br>CO<br>5962-8771002GA Q ><br>T  |
| LM158AH/883           | Active        | Production           | TO-99 (LMC)   8 | 20   JEDEC<br>TRAY (5+1)  | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   | LM158AH/883 Q ACO<br>LM158AH/883 Q >T                               |
| LM158AHLQMLV          | Active        | Production           | TO-99 (LMC)   8 | 20   JEDEC<br>TRAY (5+1)  | No          | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   | LM158AHLQMLV<br>5962R8771003VGA Q<br>ACO<br>5962R8771003VGA Q<br>>T |
| LM158AHRQMLV          | Active        | Production           | TO-99 (LMC)   8 | 20   JEDEC<br>TRAY (5+1)  | No          | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   | LM158AHRQMLV<br>5962R8771002VGA Q<br>ACO<br>5962R8771002VGA Q<br>>T |
| LM158AJ/883           | Active        | Production           | CDIP (NAB)   8  | 40   TUBE                 | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AJ/883<br>5962-87710<br>02PA Q ACO<br>02PA Q >T                |
| LM158AJRLQMLV         | Active        | Production           | CDIP (NAB)   8  | 40   TUBE                 | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AJRLQV<br>5962R87710<br>03VPA Q ACO<br>03VPA Q >T              |

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier    | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                                                                       |
|--------------------------------|---------------|----------------------|-----------------|--------------------------|-------------|--------------------------------------|-----------------------------------|--------------|-------------------------------------------------------------------------------------------|
| <a href="#">LM158AJRQMLV</a>   | Active        | Production           | CDIP (NAB)   8  | 40   TUBE                | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AJRQMLV<br>5962R87710<br>02VPA Q ACO<br>02VPA Q >T                                   |
| <a href="#">LM158AWG/883</a>   | Active        | Production           | CFP (NAC)   10  | 54   JEDEC<br>TRAY (5+1) | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AWG<br>/883 Q<br>5962-87710<br>(02QXA ACO, 02QYA<br>ACO)<br>(02QXA >T, 02QYA ><br>T) |
| <a href="#">LM158AWGRLQMLV</a> | Active        | Production           | CFP (NAC)   10  | 54   JEDEC<br>TRAY (5+1) | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AWG<br>RLQMLV Q<br>5962R87710<br>03VXA ACO<br>03VXA >T                               |
| <a href="#">LM158AWGRQMLV</a>  | Active        | Production           | CFP (NAC)   10  | 54   JEDEC<br>TRAY (5+1) | No          | SNPB                                 | Level-1-NA-UNLIM                  | -55 to 125   | LM158AWG<br>(RLQMLV Q, RQMLV Q<br>)<br>5962R87710<br>02VXA ACO<br>02VXA >T                |
| <a href="#">LM158H/883</a>     | Active        | Production           | TO-99 (LMC)   8 | 20   JEDEC<br>TRAY (5+1) | Yes         | Call TI                              | Level-1-NA-UNLIM                  | -55 to 125   | LM158H/883 Q ACO<br>LM158H/883 Q >T                                                       |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF LM158QML, LM158QML-SP :**

- Military : [LM158QML](#)
- Space : [LM158QML-SP](#)

NOTE: Qualified Version Definitions:


- Military - QML certified for Military and Defense Applications
- Space - Radiation tolerant, ceramic packaging and qualified for use in Space-based application

## TUBE



\*All dimensions are nominal

| Device          | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962R8771002VPA | NAB          | CDIP         | 8    | 40  | 506.98 | 15.24  | 13440  | NA     |
| 5962R8771003VPA | NAB          | CDIP         | 8    | 40  | 506.98 | 15.24  | 13440  | NA     |
| LM158AJ/883     | NAB          | CDIP         | 8    | 40  | 506.98 | 15.24  | 13440  | NA     |
| LM158AJRLQMLV   | NAB          | CDIP         | 8    | 40  | 506.98 | 15.24  | 13440  | NA     |
| LM158AJRQMLV    | NAB          | CDIP         | 8    | 40  | 506.98 | 15.24  | 13440  | NA     |


**TRAY**


Chamfer on Tray corner indicates Pin 1 orientation of packed units.



\*All dimensions are nominal

| Device          | Package Name | Package Type | Pins | SPQ | Unit array matrix | Max temperature (°C) | L (mm) | W (mm) | K0 (μm) | P1 (mm) | CL (mm) | CW (mm) |
|-----------------|--------------|--------------|------|-----|-------------------|----------------------|--------|--------|---------|---------|---------|---------|
| 5962-8771002GA  | LMC          | TO-CAN       | 8    | 20  | 2 X 10            | 150                  | 126.49 | 61.98  | 8890    | 11.18   | 12.95   | 18.54   |
| 5962-8771002QXA | NAC          | CFP          | 10   | 54  | 6 X 9             | 100                  | 101.6  | 101.6  | 8001    | 2.78    | 16.08   | 16.08   |
| 5962R8771002VGA | LMC          | TO-CAN       | 8    | 20  | 2 X 10            | 150                  | 126.49 | 61.98  | 8890    | 11.18   | 12.95   | 18.54   |
| 5962R8771002VXA | NAC          | CFP          | 10   | 54  | 6 X 9             | 100                  | 101.6  | 101.6  | 8001    | 2.78    | 16.08   | 16.08   |
| 5962R8771003VGA | LMC          | TO-CAN       | 8    | 20  | 2 X 10            | 150                  | 126.49 | 61.98  | 8890    | 11.18   | 12.95   | 18.54   |
| 5962R8771003VXA | NAC          | CFP          | 10   | 54  | 6 X 9             | 100                  | 101.6  | 101.6  | 8001    | 2.78    | 16.08   | 16.08   |
| LM158AH-SMD     | LMC          | TO-CAN       | 8    | 20  | 2 X 10            | 150                  | 126.49 | 61.98  | 8890    | 11.18   | 12.95   | 18.54   |
| LM158AH/883     | LMC          | TO-CAN       | 8    | 20  | 2 X 10            | 150                  | 126.49 | 61.98  | 8890    | 11.18   | 12.95   | 18.54   |
| LM158AHRQLMLV   | LMC          | TO-CAN       | 8    | 20  | 2 X 10            | 150                  | 126.49 | 61.98  | 8890    | 11.18   | 12.95   | 18.54   |
| LM158AHRQMLV    | LMC          | TO-CAN       | 8    | 20  | 2 X 10            | 150                  | 126.49 | 61.98  | 8890    | 11.18   | 12.95   | 18.54   |
| LM158AWG/883    | NAC          | CFP          | 10   | 54  | 6 X 9             | 100                  | 101.6  | 101.6  | 8001    | 2.78    | 16.08   | 16.08   |
| LM158AWGRLQMLV  | NAC          | CFP          | 10   | 54  | 6 X 9             | 100                  | 101.6  | 101.6  | 8001    | 2.78    | 16.08   | 16.08   |
| LM158AWGRQMLV   | NAC          | CFP          | 10   | 54  | 6 X 9             | 100                  | 101.6  | 101.6  | 8001    | 2.78    | 16.08   | 16.08   |
| LM158H/883      | LMC          | TO-CAN       | 8    | 20  | 2 X 10            | 150                  | 126.49 | 61.98  | 8890    | 11.18   | 12.95   | 18.54   |

NAB0008A



CONTROLLING DIMENSION IS INCH  
VALUES IN [ ] ARE MILLIMETERS



J08A (Rev M)

# LMC0008A

**TO-CAN - 5.72 mm max height**

## TRANSISTOR OUTLINE




1. All linear dimensions are in inches [millimeters]. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Pin numbers shown for reference only. Numbers may not be marked on package.
4. Reference JEDEC registration MO-002/TO-99.

# EXAMPLE BOARD LAYOUT

LMC0008A

TO-CAN - 5.72 mm max height

TRANSISTOR OUTLINE



LAND PATTERN EXAMPLE  
NON-SOLDER MASK DEFINED  
SCALE: 12X

4220610/B 09/2024



**CFP - 2.33mm max height**


Technical drawing of a rectangular component with dimensions and notes. The drawing shows a rectangular part with a central cavity. Dimensions are given in inches and millimeters (in brackets). Notes specify lead 1 ID and supplier options.

Dimensions:

- Top edge:  $.010 \pm .002$  [0.25 ± 0.05]
- Right edge:  $.005 \text{ MIN}$  [0.12] TYP
- Left edge:  $.2410 \pm .0030$  [6.121 ± 0.076]
- Right edge:  $.241 \pm .020$  [6.12 ± 0.50]
- Bottom edge:  $.410 \pm .010$  [10.41 ± 0.25]
- Right edge:  $8 \times .050 \pm .002$  [1.27 ± 0.05]
- Right edge:  $10 \times .017 \pm .002$  [0.43 ± 0.05]

Notes:

- LEAD 1 ID NOTE 3
- SUPPLIER OPTION NOTE 3




1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. For solder thickness and composition, see the "Lead Finish Composition/Thickness" link in the packaging section of the Texas Instruments website
3. Lead 1 identification shall be:
  - a) A notch or other mark within this area
  - b) A tab on lead 1, either side
4. No JEDEC registration as of December 2021

# EXAMPLE BOARD LAYOUT



NAC0010A

CFP - 2.33mm max height

CERAMIC FLATPACK



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 7X



4215196/D 08/2022

REVISIONS

| REV | DESCRIPTION                                      | E.C.N.  | DATE       | BY/APP'D                |
|-----|--------------------------------------------------|---------|------------|-------------------------|
| A   | RELEASE TO DOCUMENT CONTROL                      | 2197877 | 12/30/2021 | DAVID CHIN / ANIS FAUZI |
| B   | NO CHANGE TO DRAWING; REVISION FOR YODA RELEASE; | 2198820 | 02/14/2022 | K. SINCERBOX            |
| C   | CHANGE PIN 1 ID LOCATION ON PIN                  | 2198845 | 02/18/2022 | D. CHIN / K. SINCERBOX  |
| D   | .2410± .0030 WAS .2700 +.0012/-.0002;            | 2200915 | 08/08/2022 | D. CHIN / K. SINCERBOX  |

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated