







LM62440-Q1 ZHCSL46E - MARCH 2020 - REVISED APRIL 2022


LM62440-Q1 汽车类 3V 至 36V、4A 低 EMI 同步降压转换器

1 特性

- 符合面向汽车应用的 AEC-Q100 标准
 - 温度等级 1: -40°C 至 +150°C, T」
- 提供功能安全
 - 有助于进行功能安全系统设计的文档
- 针对超低 EMI 要求进行了优化
 - HotRod™ 封装和并行输入路径可最大限度地减 少开关节点振铃
 - 扩频可降低峰值发射
 - 出厂时可选择 2.1 MHz 和 400 kHz 频率
 - 可调节 SW 节点上升时间
 - 轻负载下可通过引脚可选 FPWM 模式提供恒定 频率
- 专为汽车应用而设计
 - 支持 42V 的汽车负载突降
 - ±1% 的总输出稳压精度
 - V_{OUT} 可在 1V 至 95% 的 V_{IN} 之间调节,出厂时 可选择 5V 和 3.3V 固定输出电压
- 可在所有负载下进行高效电源转换
 - 在 13.5V_{IN}、3.3V_{OUT} 下具有 7µA 的无负载电流
 - 在 1mA、13.5V_{IN}、5V_{OUT} 下 PFM 效率为 83%
 - 具有用于提升效率的外部偏置选项
- 适用于可扩展电源
 - 与以下器件引脚兼容:
 - LM61440-Q1 (36V、4A、可调节 f_{SW})
 - LM61460-Q1 (36V、6A、可调节 f_{SW})
 - LMQ62440-Q1 (36V、4A、内部电容器)

2 应用

- 汽车信息娱乐系统与仪表组:音响主机、媒体集线 器、USB 充电器、显示屏
- 汽车 ADAS 和车身电子装置



传导 EMI: V_{OUT}=5V, f_{SW}=2100kHz

3 说明

LM62440-Q1 是一款汽车专用的高性能直流/直流同步 降压转换器。该器件具有集成式高侧和低侧 MOSFET,能够在 3.0V 至 36V 的宽输入电压范围内 提供高达 4A 的输出电流;可耐受 42V 电压,支持持 续时间为 400 ms 的负载突降。LM62440-Q1 可对压降 进行软恢复,因此无需对输出进行过冲。


LM62440-Q1 专门设计用于降低 EMI。该器件具有假 随机展频、可调节 SW 节点上升时间和低 EMI,并采 用具有低开关节点振铃和易用、优化型引脚排列的 VQFN-HR 封装。开关频率可在 200 kHz 至 2.2 MHz 范围内同步,从而避开噪声敏感频段。另外,出厂时可 选择 2.1 MHz 或 400 kHz 频率,从而在低工作频率下 提高效率,或在高工作频率下缩小解决方案尺寸。

自动模式可在轻负载运行时进行频率折返,实现仅 7µA(典型值)的空载电流消耗和高轻负载效率。 PWM 和 PFM 模式之间的无缝转换,以及超低的 MOSFET 导通电阻和外部偏置输入,可在整个负载范 围内实现卓越的效率。

器件信息

器件型号	封装 ⁽¹⁾	封装尺寸(标称值)			
LM62440-Q1	VQFN-HR (14)	4.00mm × 3.50mm			

如需了解所有可用封装,请参阅数据表末尾的可订购产品附



效率:V_{OUT} = 5V,F_{SW} = 2200kHz



Table of Contents

1 特性	1	9.3 Feature Description	
2 应用	1	9.4 Device Functional Modes	
3 说明		10 Application and Implementation	
4 Revision History	<mark>2</mark>	10.1 Application Information	
5 说明(续)		10.2 Typical Application	33
6 Device Comparison Table		11 Power Supply Recommendations	
7 Pin Configuration and Functions		12 Layout	
8 Specifications		12.1 Layout Guidelines	
8.1 Absolute Maximum Ratings	5	12.2 Layout Example	
8.2 ESD Ratings		13 Device and Documentation Support	
8.3 Recommended Operating Conditions		13.1 Documentation Support	49
8.4 Thermal Information		13.2 接收文档更新通知	49
8.5 Electrical Characteristics		13.3 支持资源	49
8.6 Timing Characteristics		13.4 Trademarks	49
8.7 Systems Characteristics		13.5 Electrostatic Discharge Caution	49
8.8 Typical Characteristics		13.6 术语表	49
9 Detailed Description		14 Mechanical, Packaging, and Orderable	
9.1 Overview		Information	49
9.2 Functional Block Diagram			
4 Revision History 注:以前版本的页码可能与当前版本的页码不	「同		
Changes from Revision D (June 2021) to I	Revision E	(April 2022)	Page
• 添加了 400 kHz 选项			1
Changes from Revision C (April 2021) to I	Revision D	(June 2021)	Page

5 说明(续)

LM62440-Q1 符合汽车 AEC-Q100 1 级标准,并采用具有可润湿侧翼的 14 引脚 VQFN-HR 封装。电气特性额定结温范围为 -40° C 至 $+150^{\circ}$ C。如需其他资源,请参阅*相关文档*。

6 Device Comparison Table

Device	Orderable Part Number	Reference Part Number	Light Load Mode	Spread Spectrum	Output Voltage	Switching Frequency
	LM62440APPQRJRRQ1	LM62440APP-Q1	Pin Selectable	Pin Selectable	Adjustable	2.1 MHz
	LM62440BPPQRJRRQ1	LM62440BPP-Q1	Pin Selectable	Pin Selectable	3.3 V	2.1 MHz
LM62440-Q1	LM62440CPPQRJRRQ1	LM62440CPP-Q1	Pin Selectable	Pin Selectable	5 V	2.1 MHz
LIVI02440-Q1	LM62440ALPQRJRRQ1	LM62440ALP-Q1	Pin Selectable	Pin Selectable	Adjustable	400 kHz
	LM62440BLPQRJRRQ1	LM62440BLP-Q1	Pin Selectable	Pin Selectable	3.3 V	400 kHz
	LM62440CLPQRJRRQ1	LM62440CLP-Q1	Pin Selectable	Pin Selectable	5 V	400 kHz



7 Pin Configuration and Functions




图 7-1. 14-Pin VQFN-HR RJR Package (Top View)

表 7-1 Pin Functions

PIN I/O			DESCRIPTION
NAME	I/O		DESCRIPTION
BIAS	1	Р	Input to internal LDO. Connect to the output voltage point to improve efficiency. Connect an optional high quality 0.1-μF to 1-μF capacitor from this pin to ground for improved noise immunity. If output voltage is above 12 V, connect this pin to ground.
		Internal LDO output. Used as a supply to internal control circuits. Do not connect to any external loads. Connect a high-quality 1-µF capacitor from this pin to AGND.	
AGND	3	G	Analog ground for internal circuitry. Feedback and VCC are measured with respect to this pin. Must connect AGND to both PGND1 and PGND2 on PCB.
FB	4	I	Output voltage feedback input to the internal control loop. Connect to the output voltage sense point for fixed 3.3-V or 5-V output voltage factory options. Connect to the feedback divider tap point for adjustable output voltage. Do not float or connect to ground.
PGOOD	5	0	Open-drain power-good status output. Pull this pin up to a suitable voltage supply through a current limiting resistor. High = power OK, low = fault. PGOOD output goes low when EN = low, $V_{IN} > 1$ V.
MODE/SYNC 6 I		I	This pin controls the mode of operation of the LM62440-Q1. Modes include auto mode (automatic PFM and PWM operation), FPWM, and synchronization to an external clock. When synchronized, the clock triggers on the rising edge of an external clock. Also, spread spectrum operation is controlled by this pin. See † 9.3.2. Do not float this pin.
EN	7	1	Precision enable input. High = on, Low = off. Can be connected to VIN. Precision enable allows the pin to be used as an adjustable UVLO. See 节 10.
VIN1	8	Р	Input supply to the converter. Connect a high-quality bypass capacitor or capacitors from this pin to PGND1. Low impedance connection must be provided to VIN2.
PGND1	9	G	Power ground to the internal low-side MOSFET. Connect to system ground. Low impedance connection must be provided to PGND2. Connect a high-quality bypass capacitor or capacitors from this pin to VIN1.
SW	10	0	Switch node of the converter. Connect to the output inductor.
PGND2	11	G	Power ground to the internal low-side MOSFET. Connect to system ground. Low impedance connection must be provided to PGND1. Connect a high-quality bypass capacitor or capacitors from this pin to VIN2.
VIN2	12	Р	Input supply to the converter. Connect a high-quality bypass capacitor or capacitors from this pin to PGND2. Low impedance connection must be provided to VIN1.
RBOOT 13 I/O Connect to CBOOT through a resistor. This resistance must be between 0 Ω and open. resistance determines SW node rise time.		Connect to CBOOT through a resistor. This resistance must be between 0 $^\Omega$ and open. This resistance determines SW node rise time.	
CBOOT 14 I/O High-side driver upper supply rail. Connect a 100-nF capacitor between SW and diode connects to VCC and allows CBOOT to charge while SW node is low.		High-side driver upper supply rail. Connect a 100-nF capacitor between SW and CBOOT. An internal diode connects to VCC and allows CBOOT to charge while SW node is low.	

Product Folder Links: LM62440-Q1

Submit Document Feedback

8 Specifications

8.1 Absolute Maximum Ratings

Over the recommended operating junction temperature range of -40°C to $+150^{\circ}\text{C}$ (unless otherwise noted)⁽¹⁾

	PARAMETER	MIN	MAX	UNIT
	VIN1, VIN2 to AGND, PGND	- 0.3	42	V
	RBOOT to SW	- 0.3	5.5	V
	CBOOT to SW	- 0.3	5.5	V
	BIAS to AGND, PGND	- 0.3	16	V
Input Voltage	EN to AGND, PGND	- 0.3	42	V
	SYNC/MODE to AGND, PGND	- 0.3	lower of 42 & V _{IN} +5	V
	FB to AGND, PGND	- 0.3	16	V
	PGOOD to AGND, PGND	0	20	V
	PGND to AGND ⁽³⁾	- 1	2	V
Output Valtage	SW to AGND, PGND ⁽²⁾	- 0.3	V _{IN} +0.3	V
Output Voltage	VCC to AGND, PGND	- 0.3	5.5	V
Current	PGOOD sink current ⁽⁴⁾		10	mA
T _J	Junction temperature	- 40	150	°C
T _{stg}	Storage temperature	- 40	150	°C

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- (2) A voltage of 2 V below GND and 2 V above V_{IN} can appear on this pin for ≤ 200 ns with a duty cycle of ≤ 0.01%.
- (3) This specification applies to voltage durations of 100 ns or less. The maximum D.C. voltage should not exceed ± 0.3 V.
- (4) Do not exceed the voltage rating of the pin.

8.2 ESD Ratings

				VALUE	UNIT
V	Human body model (HBM), per AEC Q100-002 ⁽¹⁾ Device HBM Classification Level 2	±2000			
ľ	V _(ESD)		Charged device model (CDM), per AEC Q100-011 Device CDM Classification Level C5 ±750		V

⁽¹⁾ AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

8.3 Recommended Operating Conditions

Over the recommended operating junction temperature range of -40°C to 150°C (unless otherwise noted) (1)

0 101 110 10001111110	riada oporating janotion tomporatare range of	10 0 10 100 0 (411	.000 041101 11110	o notou,	
		MIN	NOM	MAX	UNIT
Input voltage	Input voltage range after start-up	3		36	V
Output voltage	Output voltage range for adjustable version (2)	1		0.95 × V _{IN}	V
Frequency	Free running frequency 2.1-MHz option		2.1		MHz
Frequency	Free running frequency 400-kHz option		400		kHz
Sync frequency	Synchronization frequency range	200		2200	kHz
Load current	Output DC current range (3)	0		4	Α
Temperature	Operating junction temperature T _J range	- 40		150	°C

⁽¹⁾ Recommended operating conditions indicate conditions for which the device is intended to be functional, but do not ensure specific performance limits. For compliant specifications, see the *Electrical Characteristics* table.

⁽²⁾ Under no conditions should the output voltage be allowed to fall below 0 V.



(3) Maximum continuous DC current may be derated when operating with high switching frequency, high ambient temperature, or both. See 节 10 for details.

8.4 Thermal Information

The value of R $_{\theta}$ JA given in this table is only valid for comparison with other packages and cannot be used for design purposes. These values were calculated in accordance with JESD 51-7, and simulated on a 4-layer JEDEC board. They do not represent the performance obtained in an actual application. For example, with a 4-layer PCB, a R $_{\theta}$ JA = 25 $^{\circ}$ C/W can be achieved. For design information see Maximum Ambient Temperature versus Output Current.

		LM62440-Q1	
	THERMAL METRIC (1)	RJR (QFN)	UNIT
		14 PINS	
R ₀ JA	Junction-to-ambient thermal resistance (LM61460-Q1 EVM)	25	°C/W
R ₀ JA	Junction-to-ambient thermal resistance (JESD 51-7)	58.7	°C/W
R _{θ JC(top)}	Junction-to-case (top) thermal resistance	26.1	°C/W
R _{θ JB}	Junction-to-board thermal resistance	19.2	°C/W
$\Psi_{\sf JT}$	Junction-to-top characterization parameter	1.4	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	19	°C/W
R _{θ JC(bot)}	Junction-to-case (bottom) thermal resistance	_	°C/W

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

8.5 Electrical Characteristics

Limits apply over the recommended operating junction temperature range of -40°C to +150°C, unless otherwise stated. Minimum and Maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at $T_J = 25$ °C, and are provided for reference purposes only. Unless otherwise stated the following conditions apply: $V_{IN} = 13.5$ V. VIN1 shorted to VIN2 = V_{IN} . V_{OUT} is converter output voltage.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY VOLTAGE	E AND CURRENT				'	
	Input energing valtage(2)	Needed to start up	3.95			V
V _{IN_OPERATE}	Input operating voltage ⁽²⁾ Once operating 3.0			V		
V _{IN_OPERATE_H}	Hysteresis ⁽²⁾			1		V
I _{Q_VIN}	Operating quiescent current (not switching)	V _{FB} = +5%, V _{BIAS} = 5 V		9	18	μΑ
SD	Shutdown quiescent current; measured at the VIN pin	EN = 0 V, T _J = 25℃		0.6	6	μΑ
ENABLE			1			
V _{EN}	Enable input threshold voltage - rising			1.263		V
V _{EN-ACC}	Enable input threshold voltage - rising deviation from typical		- 5%		5%	
V _{EN-HYST}	Enable threshold hysteresis as percentage of V _{EN} (typical)		24%	28%	32%	
V _{EN-WAKE}	Enable wake-up threshold		0.4			V
EN	Enable pin input current	V _{IN} = EN = 13.5 V		2.3		nA
LDO - VCC						
V _{cc}	Internal V _{CC} voltage	V _{BIAS} > 3.4 V, CCM operation ⁽²⁾		3.3		V
		V _{BIAS} = 3.1 V, non-switching		3.1		
V _{CC_UVLO}	Internal V _{CC} input undervoltage lockout	V _{CC} rising undervoltage threshold		3.6		V
V _{CC_UVLO_HYST}	Internal V _{CC} input undervoltage lockout	Hysteresis below V _{CC_UVLO}		1.1		V
FEEDBACK			•			

Limits apply over the recommended operating junction temperature range of -40°C to +150°C, unless otherwise stated. Minimum and Maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at T_J = 25°C, and are provided for reference purposes only. Unless otherwise stated the following conditions apply: V_{IN} = 13.5 V. VIN1 shorted to VIN2 = V_{IN} . V_{OUT} is converter output voltage.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
V _{FB_acc}	Initial reference voltage accuracy	V _{IN} = 3.3 V to 36 V, FPWM mode	- 1%		1%	
V _{OUT_acc}	Reference voltage accuracy for fixed 3.3-V V _{OUT} trim option	V _{IN} = 13.5 V, FPWM mode	3.2587	3.3	3.3413	V
V _{OUT_acc}	Reference voltage accuracy for fixed 5-V V _{OUT} trim option	V _{IN} = 13.5 V, FPWM mode	4.9375	5	5.0625	V
R _{FB}	Resistance from FB to AGND	5-V option 3.3-V option		1.85		MΩ
FB	Input current from FB to AGND	Adjustable versions only, FB = 1 V		10		nA
OSCILLATOR						
 	Minimum adjustable frequency by SYNC		0.18	0.2	0.22	MHz
ADJ	Adjustable frequency by SYNC		0.36	0.4	0.44	MHz
	Maximum adjustable frequency by SYNC		1.98	2.2	2.42	MHz
fsw	Switching frequency	V _{IN} = 13.5 V, center frequency with or without spread spectrum, PWM operation, 2.1-MHz option	1.9	2.1	2.3	MHz
SW4	Switching frequency	V _{IN} = 13.5 V, center frequency with or without spread spectrum, PWM operation, 400-kHz option	360	400	440	kHz
s S SS	Frequency span of spread spectrum operation - largest deviation from center frequency	Spread spectrum active		2%		
PSS	Spread spectrum pattern frequency ⁽²⁾	Spread spectrum active, f _{SW} = 2.1 MHz			1.5	Hz
MODE/SYNC PIN					'	
	MODE/SYNC pin leakage	V _{IN} = 13.5 V, V _{SYNC/MODE} = 3.3 V		1		nA
MODE/SYNC	current after start-up	V _{IN} = 13.5 V, V _{SYNC/MODE} = 5.5 V		1		ША
/ _{MODE_L}	MODE/SYNC input voltage low				0.4	V
/ _{MODE_H}	MODE/SYNC input voltage high		1.6			V
/ _{SYNCD_HYST}	MODE/SYNC input voltage hysteresis		0.155		1	V
/ _{MODE_H2}	Spread spectrum on if MODE/ SYNC voltage is below this voltage and above V _{MODE_H}	Level-dependent operation	2.5			V
V _{MODE_H3}	Spread spectrum off if MODE/ SYNC is above this voltage	Level-dependent operation			4.9	V
R _{MODE_} H	MODE/SYNC attached resistance indicating spread spectrum off	Level-dependent operation	30			kΩ

www.ti.com.cn

Limits apply over the recommended operating junction temperature range of -40°C to +150°C, unless otherwise stated. Minimum and Maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at $T_J = 25^{\circ}$ C, and are provided for reference purposes only. Unless otherwise stated the following conditions apply: $V_{total} = 13.5 \text{ V}$ VIN1 shorted to VIN2 = V_{total} is converted output voltage.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
R _{MODE_L}	MODE/SYNC attached resistance indicating spread spectrum on	Level-dependent operation			6	kΩ
MOSFETS	'				'	
R _{DS(ON)_HS}	Power switch on-resistance	High-side MOSFET R _{DS(ON)}		41	82	mΩ
R _{DS(ON)_LS}	Power switch on-resistance	Low-side MOSFET R _{DS(ON)}		21	45	$m\Omega$
V _{BOOT_UVLO}	Voltage on CBOOT pin compared to SW which will turn off high-side switch			2.1		V
CURRENT LIMIT	S				·	
I _{L-HS}	High-side switch current limit ⁽¹⁾	Duty cycle approaches 0%	6	7	8.1	Α
I _{L-LS}	Low-side switch current limit		4	4.8	5.4	Α
I _{L-ZC}	Zero-cross current limit. Positive current direction is out of the SW pin	Auto mode, static measurement		0.25		Α
I _{L-NEG}	Negative current limit FPWM and SYNC Modes. Positive current direction is out of the SW pin.	FPWM operation		- 2		А
I _{PK_MIN_0}	Minimum peak command in auto mode and device current rating	Pulse duration < 100 ns		25%		
I _{PK_MIN_100}	Minimum peak command in auto mode and device current rating	Pulse duration > 1 μs		12.5%		
V _{HICCUP}	Ratio of FB voltage to in- regulation FB voltage	Not during soft start		40%		
POWER GOOD			,		'	
PGD _{OV}	PGOOD upper threshold - rising	% of V _{OUT} setting	105%	107%	110%	
PGD _{U V}	PGOOD lower threshold - falling	% of V _{OUT} setting	92%	94%	96.5%	
PGD _{HYST}	PGOOD upper threshold (rising and falling)	% of V _{OUT} setting		1.3%		
V _{IN(PGD_VALID)}	Input voltage for proper PGOOD function		1.0			V
		46-μA pullup to the PGOOD pin, V _{IN} = 1.0 V, EN = 0 V			0.4	
$V_{PGD(LOW)}$	Low level PGOOD function output voltage	1-mA pullup to the PGOOD pin, V _{IN} = 13.5 V, EN = 0 V			0.4	V
		2-mA pullup to the PGOOD pin, V _{IN} = 13.5 V, EN = 3.3 V			0.4	
Raca	Recovered PGOOD output	1-mA pullup to PGOOD pin, EN = 0 V		17	40	Ω
R_{PGD}	R _{DS(ON)} of PGOOD output	1-mA pullup to PGOOD pin, EN = 3.3 V		40	90	Ω
I _{OV}	Pulldown current at the SW node under overvoltage condition			0.5		mA

Limits apply over the recommended operating junction temperature range of -40°C to +150°C, unless otherwise stated. Minimum and Maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at T_J = 25°C, and are provided for reference purposes only. Unless otherwise stated the following conditions apply: V_{IN} = 13.5 V. VIN1 shorted to VIN2 = V_{IN} . V_{OUT} is converter output voltage.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
T _{SD_R}	Thermal shutdown rising threshold ⁽²⁾		158	168	180	°C
T _{SD_HYST}	Thermal shutdown hysteresis ⁽²⁾			10		$^{\circ}$ C

- (1) High-side current limit is function of duty factor. High-side current limit is highest at small duty factor and less at higher duty factors.
- (2) Parameter specified by design, statistical analysis and production testing of correlated parameters.

8.6 Timing Characteristics

Limits apply over the recommended operating junction temperature range of -40° C to +150°C, unless otherwise stated. Minimum and Maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at $T_J = 25^{\circ}$ C, and are provided for reference purposes only. Unless otherwise stated the following conditions apply: $V_{IN} = 13.5 \text{ V}$.

	Parameter	Test Condition	MIN	TYP	MAX	UNIT
SWITCH NOD	E					
t _{ON_MIN}	Minimum HS switch on time	V _{IN} = 20 V, I _{OUT} = 2 A, RBOOT short to CBOOT		55	70	ns
t _{ON_MAX}	Maximum HS switch on time			9		μs
t _{OFF_MIN}	Minimum LS switch on time	V _{IN} = 4.0 V, I _{OUT} = 1 A, RBOOT short to CBOOT		65	85	ns
t _{SS}	Time from first SW pulse to Vref at 90%, of set point. $V_{IN} \geqslant 4.2 \ V$ 2 3		3	4	ms	
t _{SS2}	Time from first SW pulse to release of FPWM lockout if output not in regulation	$V_{IN}\geqslant 4.2\ V$	4.5 6.5		8.5	ms
t _W	Short circuit wait time ("Hiccup" time)			40		ms
ENABLE					·	
t _{EN}	Turn-on delay ⁽¹⁾	C_{VCC} = 1 μ F, time from EN high to first SW pulse if output starts at 0 V	0.7			ms
t _B	Blanking of EN after rising or falling edges	Low level is 0.6 V.	4		9	μs
SYNC						
t _{PULSE_H}	High duration needed to be recognized as a pulse		100			ns
t _{PULSE_L}	Low duration needed to be recognized as a pulse		100			ns
t _{MODE}	Time at one level needed to indicate FPWM or auto mode		16.5			μs
t _{SYNC}	High or low signal duration in a valid synchronization signal				8	μs
C _{LOCK}	Time needed for clock to lock to a valid synchronization signal in sync cycles ⁽¹⁾			2048		cycle
t _{MEAS}	SYNC/MODE pin duration of resistance test upon entering Auto Mode level dependent SYNC/MODE pin operation 25			μs		
POWER GOO	D					
t _{PGDFLT(rise)}	Delay time to PGOOD high signal		1.5	2	2.5	ms

Product Folder Links: LM62440-Q1

www.ti.com.cn

Limits apply over the recommended operating junction temperature range of - 40°C to +150°C, unless otherwise stated. Minimum and Maximum limits are specified through test, design or statistical correlation. Typical values represent the most likely parametric norm at T_J = 25°C, and are provided for reference purposes only. Unless otherwise stated the following conditions apply: $V_{IN} = 13.5 \text{ V}$.

	Parameter	Test Condition	MIN	TYP	MAX	UNIT
TDODELT(f-II)	Glitch filter time constant for PGOOD function			24		μs

⁽¹⁾ Parameter specified using design, statistical analysis and production testing of correlated parameters; not tested in production.

8.7 Systems Characteristics

The following values are specified by design provided that the component values in the typical application circuit are used. Limits apply over the junction temperature range of -40°C to +150°C, unless otherwise noted. Minimum and Maximum limits are derived using test, design or statistical correlation. Typical values represent the most likely parametric norm at T_J = 25°C, and are provided for reference purposes only. Unless otherwise stated the following conditions apply: V_{IN} = 13.5 V. VIN1 shorted to VIN2 = V_{IN}. V_{OUT} is output setting. These parameters are not tested in production.

	PARAMETER	TEST CONDITIONS	MIN	MIN TYP		UNIT	
EFFICIENCY							
		$V_{OUT} = 5 \text{ V}, I_{OUT} = 4 \text{ A}, R_{BOOT} = 0 \Omega$		93%			
η _{5V_2p1MHz}	Typical 2.1-MHz efficiency	V_{OUT} = 5 V, I_{OUT} = 100 μA, R_{BOOT} = 0 Ω, R_{FBT} = 1 MΩ		73%			
n	Typical 2.1-MHz efficiency	V_{OUT} = 3.3 V, I_{OUT} = 4 A, R_{BOOT} = 0 Ω		91%			
ຐ 3p3V_2p1MHz	Typical 2. 1-WHZ efficiency	V_{OUT} = 3.3 V, I_{OUT} = 100 μ A, R_{BOOT} = 0 Ω , R_{FBT} = 1 $M\Omega$		71%			
		$V_{OUT} = 5 \text{ V}, I_{OUT} = 4 \text{ A}, R_{BOOT} = 0 \Omega$		95%			
η _{5V_400kHz}	Typical 400-kHz efficiency	V_{OUT} = 5 V, I_{OUT} = 100 μA, R_{BOOT} = 0 Ω, R_{FBT} = 1 MΩ		76%			
RANGE OF O	PERATION						
V _{VIN_MIN1}	V _{IN} for full functionality at reduced load, after start-up.	V _{OUT} set to 3.3 V	3.0			V	
V _{VIN_MIN2}	V _{IN} for full functionality at 100% of maximum rated load, after start-up.	V _{OUT} set to 3.3 V	3.95			V	
	Operating quiescent current ⁽¹⁾	V_{OUT} = 3.3 V, I_{OUT} = 0 A, auto mode, R_{FBT} = 1 M Ω		7		μΑ	
I _{Q-VIN}		V_{OUT} = 5 V, I_{OUT} = 0 A, auto mode, R_{FBT} = 1 M Ω		10		μΛ	
	Output voltage for 5-V factory	V _{IN} = 5.8 V to 36 V, I _{OUT} = 4 A	4.9	5	5.1		
V _{OUT5}	option	Auto mode, V _{IN} = 5.5 V to 36 V, I _{OUT} = 100 µA to 100 mA	4.9	5.05	5.125	V	
	Output voltage for 3.3-V factory	V _{IN} = 3.9 V to 36 V, I _{OUT} = 4 A	3.24	3.3	3.35		
V _{OUT3}	option	V_{IN} = 3.9 V to 36 V, I_{OUT} = 100 μA to 100 mA	3.24	3.33	3.38	V	
W	Input to output voltage differential to maintain regulation accuracy without inductor DCR drop output accuracy at 2 $V_{OUT} = 3.3 \text{ V, } I_{OUT} = 3.4 \text{ V}$	V_{OUT} = 3.3 V, I_{OUT} = 4 A, -3% output accuracy at 25 $^{\circ}$ C		0.4		V	
V _{DROP1}		V _{OUT} = 3.3 V, I _{OUT} = 4 A, −3% output accuracy at 125°C		0.55		V	
V _{DROP2}	Input to output voltage differential	V _{OUT} = 3.3 V, I _{OUT} = 4 A, −3% regulation accuracy at 25°C		0.8		V	
	to maintain $f_{SW} \ge 1.85$ MHz, without DCR drop	V _{OUT} = 3.3 V, I _{OUT} = 4 A, −3% regulation accuracy at 125 °C		1.2		V	
D _{MAX}	Maximum switch duty cycle	f _{SW} = 1.85 MHz		87%			
	I MAXIII MILL SWILLI LULLY CYCLE	While in frequency foldback	98%				



The following values are specified by design provided that the component values in the typical application circuit are used. Limits apply over the junction temperature range of -40°C to +150°C, unless otherwise noted. Minimum and Maximum limits are derived using test, design or statistical correlation. Typical values represent the most likely parametric norm at $T_J = 25$ °C, and are provided for reference purposes only. Unless otherwise stated the following conditions apply: $V_{IN} = 13.5$ V. VIN1 shorted to VIN2 = V_{IN} . V_{OUT} is output setting. These parameters are not tested in production.

		PARAMETER	TEST CONDITIONS	MIN TYP MAX		MAX	UNIT
	t _{RISE}		$R_{BOOT} = 0 \Omega$, $I_{OUT} = 2 A$ (10% to 80%)		2.15		ns
			R_{BOOT} = 100 Ω, I_{OUT} = 2 A (10% to 80%)		2.7		ns


(1) See detailed description for the meaning of this specification and how it can be calculated.

Submit Document Feedback




8.8 Typical Characteristics

Unless otherwise specified, V_{IN} = 13.5 V and f_{SW} = 2100 kHz.







9 Detailed Description

9.1 Overview

The LM62440-Q1 is a wide input, synchronous peak-current mode buck regulator designed for a wide variety of automotive applications. The regulator can operate over a wide range of switching frequencies including sub-AM band at 400 kHz and above the AM band at 2.1 MHz. This device operates over a wide range of conversion ratios. If minimum on time or minimum off time does not support the desired conversion ratio, the frequency is reduced automatically, allowing output voltage regulation to be maintained during input voltage transients with a high operating-frequency setting.

The LM62440-Q1 has been designed for low EMI and is optimized for both above and below AM band operation:

- · Meets CISPR25 class 5 standard
- HotRod package minimizes switch node ringing
- · Parallel input path minimizes parasitic inductance
- Spread spectrum reduces peak emissions
- · Adjustable SW node rise time


These features together can eliminate shielding and other expensive EMI mitigation measures.

This device is designed to minimize end-product cost and size while operating in demanding automotive environments. The LM62440-Q1 operates at a default frequency of either 2.1 MHz or 400 kHz but can be synchronized across the 200-kHz through 2.2-MHz range. Operation at 2.1 MHz allows for the use of small passive components. In addition, this device has low unloaded current consumption, which is desirable for off-battery, always-on applications. The low shutdown current and high maximum operating voltage also allow for the elimination of an external load switch and input transient protection. To further reduce system cost, an advanced PGOOD output is provided, which can often eliminate the use of an external reset or supervisory device.

The LM62440-Q1 devices are AEC-Q100-qualified and have electrical characteristics compliant up to a maximum junction temperature of 150°C.



9.2 Functional Block Diagram



9.3 Feature Description

9.3.1 EN Uses for Enable and VIN UVLO

Start-up and shutdown are controlled by the EN input and V_{IN} UVLO. For the device to remain in shutdown mode, apply a voltage below V_{EN_WAKE} (0.4 V) to the EN pin. In shutdown mode, the quiescent current drops to 0.6 μ A (typical). At a voltage above V_{EN_WAKE} and below V_{EN} , VCC is active and the SW node is inactive. Once the EN voltage is above V_{EN} , the chip begins to switch normally, provided the input voltage is above 3 V.

The EN pin cannot be left floating. The simplest way to enable the operation is to connect the EN pin to V_{IN} , allowing self-start-up of the LM62440-Q1 when V_{IN} drives the internal VCC above its UVLO level. However, many applications benefit from the employment of an enable divider network as shown in $\[]$ 9-1, which establishes a precision input undervoltage lockout (UVLO). This can be used for sequencing, preventing retriggering of the device when used with long input cables, or reducing the occurrence of deep discharge of a battery power source. Note that the precision enable threshold, V_{EN} , has a 5% tolerance. Hysteresis must be enough to prevent re-triggering. External logic output of another IC can also be used to drive the EN pin, allowing system power sequencing.




图 9-1. VIN UVLO Using the EN pin

Resistor values can be calculated using 方程式 1. See 节 10.2.2.11 for additional information.

$$R_{ENB} = R_{ENT} \cdot \frac{V_{EN}}{V_{ON} - V_{EN}}$$
(1)

where

V_{ON} is the desired typical start-up input voltage for the circuit being designed.

9.3.2 MODE/SYNC Pin Operation

The LM62440-Q1 features selectable operating modes through the MODE/SYNC input pin. The LM62440-Q1 can operate in one of three selectable modes:

- Auto mode: Pulse frequency modulation (PFM) operation is enabled during light load and diode emulation prevents reverse current through the inductor. See 节 9.4.3.2 for more details.
- FPWM mode: In FPWM mode, diode emulation is disabled, allowing current to flow backwards through the inductor. This allows operation at full frequency even without load current. See † 9.4.3.3 for more details.
- SYNC mode: The LM62440-Q1 clock locks to an external signal applied to the MODE/SYNC pin. As long as
 output voltage can be regulated at full frequency and is not limited by minimum off time or minimum on time,
 clock frequency is matched to the frequency of the signal applied to the MODE/SYNC pin. While the
 LM62440-Q1 is in SYNC mode, the device operates as though in FPWM mode: diode emulation is disabled
 allowing the frequency applied to the MODE/SYNC pin to be matched without a load.

In addition, the MODE/SYNC pin can be used to activate or deactivate the spread spectrum feature of the LM62435 40-Q1. The MODE/SYNC pin can be configured in two ways: level dependent MODE/SYNC control (see † 9.3.2.1) or pulse dependent MODE/SYNC pin control (see † 9.3.2.2).

9.3.2.1 Level-Dependent MODE/SYNC Pin Control

If only a single mode is used, the part can be configured using level-dependent control. Note that the LM62440-Q1 cannot be synchronized to an external clock signal in level-dependent mode. $\frac{1}{2}$ 9-1 shows a summary of level-dependent mode selection settings. The level-dependent mode selection setting registers after t_{MODE} . The level-dependent mode summary is also depicted in $\frac{1}{2}$ 9-2.

表 9-1. Level-Dependent Mode Selection Settings

MODE/SYNC Input	Mode
GND	Auto mode with spread spectrum
VCC OR > V _{MODE_H} AND < V _{MODE_H2}	FPWM mode with spread spectrum
VIN OR > V _{MODE_H3}	FPWM mode without spread spectrum




图 9-2. Level-Dependent Mode Selection Settings

Note that during dropout operation, the input voltage is close to VCC. Since this condition is typically seen while operating in dropout, frequency is typically folded back and spread spectrum is deactivated. When VIN increases and the device is no longer in frequency foldback, spread spectrum is reactivated. When the input voltage is between 3 V to 3.7 V and the LM62440-Q1 is not in dropout operation, the spread spectrum operation is not guaranteed.

One purpose of level-dependent MODE/SYNC pin control is to dynamically change between FPWM and auto mode. To make sure the resistance from MODE/SYNC to ground is $< R_{SYNC_L}$, it is recommended to use 6 k Ω to ground. The MODE/SYNC pin can then be toggled between FPWM and auto mode as shown in $\frac{1}{8}$ 9-1.

If auto mode without spread spectrum operation is desired, tie the MODE/SYNC pin to ground through a 100-k Ω resistor. Auto mode without spread spectrum is a fixed option, and the mode cannot be changed dynamically.

9.3.2.2 Pulse-Dependent MODE/SYNC Pin Control

Most systems that require more than a single mode of operation from the LM62440-Q1 are controlled by digital circuitry such as a microprocessor. These systems can generate dynamic signals easily but have difficulty generating multi-level signals. Pulse-Dependent MODE/SYNC pin control is useful with these systems.

To initiate Pulse-Dependent MODE/SYNC pin control, a valid sync signal must be applied. Upon completion of the fourth pulse in a valid synchronization pulse train, the SYNC mode pin operates in Pulse-Dependent MODE/SYNC control mode, shown in 图 9-3 and 图 9-4. The only way to return to Level-Dependent MODE/SYNC control is to restart the LM62440-Q1.

Submit Document Feedback




图 9-3. Transition from FPWM Mode to Pulse-Dependent Control




图 9-4. Transition from Auto Mode to Pulse-Dependent Control

Once Pulse-Dependent MODE/SYNC control has been initiated, 表 9-2 shows a summary of the pulse dependent mode selection settings.

表 9-2. Pulse-Dependent Mode Selection Settings

MODE/SYNC Input	Mode
> V _{MODE_H}	FPWM with spread spectrum
< V _{MODE_L}	Auto mode with spread spectrum
Synchronization Clock	SYNC mode without spread spectrum
> V _{MODE_H} AND Double Pulse (图 9-6)	FPWM without spread spectrum
< V _{MODE_L} AND Double Pulse (图 9-7)	Auto mode without spread spectrum

§ 9-5 shows the transition between auto mode and FPWM mode while in Pulse-Dependent MODE/SYNC control. The LM62440-Q1 transitions to a new mode of operation after the time, t_{MODE}.




图 9-5. Transition from Auto Mode and FPWM Mode

Two positive going pulses can be used to turn off spread spectrum in auto and FPWM modes. The two positive pulses must be consistent with the characteristics of a valid sync signal. 图 9-6 through 图 9-9 show the only waveforms that result in spread spectrum being turned off. Refer to the *Electrical Characteristics* for more information about the timing specifications.




图 9-6. Spread Spectrum Disabled in FPWM Mode




图 9-7. Spread Spectrum Disabled in Auto Mode




图 9-8. Spread Spectrum Disabled in Transition from FPWM Mode to Auto Mode




图 9-9. Spread Spectrum Disabled in Transition from Auto Mode to FPWM Mode

To enter the SYNC mode, the valid synchronization signal must be present for 2048 cycles.

If MODE/SYNC voltage becomes constant longer than t_{MODE} , the LM62440-Q1 enters either auto mode or FPWM mode. At this time, spread spectrum is turned on and MODE/SYNC operates in Pulse-Dependent mode.



图 9-10. Transition from SYNC Mode to Auto Mode





图 9-11. Transition from SYNC Mode to FPWM Mode

9.3.2.3 Clock Locking

Once a valid synchronization signal is detected, a clock locking procedure is initiated. The LM62440-Q1 receives this signal over the MODE/SYNC pin. After approximately 2048 pulses, the clock frequency completes a smooth transition to the frequency of the synchronization signal without output variation. Note that while the frequency is adjusted suddenly, phase is maintained so the clock cycle that lies between operation at the default frequency and at the synchronization frequency is of intermediate length. This eliminates very long or very short pulses. Once frequency is adjusted, phase is adjusted over a few tens of cycles so that rising synchronization edges correspond to rising SW node pulses. See $\boxed{\$}$ 9-12.



Pulses four and synchronization signal is detected. After the pulse, approximately 2048 ready to synchronize and frequency is adjusted using a glitch free technique. Later, phase is locked.

图 9-12. Synchronization Process

Also note that the LM62440-Q1 turns on spread spectrum after the first edge in the synchronization pulse. See the MODE/SYNC pin description in † 7. Upon adjustment of frequency on the approximate 2048th pulse, spread spectrum is turned off. Finally, if the device runs at reduced frequency due to low or high input voltage or during current limit, frequency lock does not occur until the condition causing low frequency operation has been removed.

9.3.3 PGOOD Output Operation

The PGOOD function is implemented to replace a discrete reset device, reducing BOM count and cost. The PGOOD pin voltage goes low when the feedback voltage is outside of the specified PGOOD thresholds (see \boxtimes 8-8). This can occur in current limit and thermal shutdown, as well as while disabled and during normal start-up. A glitch filter prevents false flag operation for short excursions of the output voltage, such as during line and load transients. Output voltage excursions that are shorter than t_{PGDFLT_FALL} do not trip the power-good flag. Power-good operation can be best understood by referring to \boxtimes 9-13.

The power-good output consists of an open-drain NMOS, requiring an external pullup resistor to a suitable logic supply or V_{OUT} . When EN is pulled low, the flag output is also forced low. With EN low, power good remains valid as long as the input voltage is \geq 1 V (typical).




图 9-13. PGOOD Timing Diagram (Excludes OV Events)

Fault Condition Initiated	Fault Condition Ends (After Which t _{PGDFLT(rise)} Must Pass Before PGOOD Output Is Released) ⁽¹⁾
$V_{OUT} < V_{OUT-target} \times PGD_{UV} AND t > t_{PGDFLT(fall)}$	Output voltage in regulation: $V_{OUT\text{-target}} \times (PGD_{UV} + PGD_{HYST}) < V_{OUT} < V_{OUT\text{-target}} \times (PGD_{OV} - PGD_{HYST})$ (See $\boxed{8}$ 8-8)
V _{OUT} > V _{OUT-target} × PGD _{OV} AND t > t _{PGDFLT(fall)}	Output voltage in regulation
$T_J > T_{SD_R}$	T _J < T _{SD_F} AND output voltage in regulation
EN < V _{EN} Falling	EN > V _{EN} Rising AND output voltage in regulation
Vcc < Vcc_uvlo - Vcc_uvlo_hyst	V _{CC} > V _{CC_UVLO} AND output voltage in regulation

⁽¹⁾ As an additional operational check, PGOOD remains low during soft start, defined as until the lesser of either full output voltage reached or t_{SS2} has passed since initiation.

9.3.4 Internal LDO, VCC UVLO, and BIAS Input

The VCC pin is the output of the internal LDO used to supply the control circuits of the LM62440-Q1. The nominal output is 3 V to 3.3 V. The BIAS pin is the input to the internal LDO. This input can be connected to

V_{OUT} to provide the lowest possible input supply current. If the BIAS voltage is less than 3.1 V, VIN1 and VIN2 directly powers the internal LDO.

To prevent unsafe operation, VCC has a UVLO that prevents switching if the internal voltage is too low. See V_{CC_UVLO} and $V_{CC_UVLO_HYST}$ in the *Electrical Characteristics*. Note that these UVLO values and the dropout of the LDO are used to derive minimum V_{IN} OPERATE and V_{IN} OPERATE H values.

9.3.5 Bootstrap Voltage and V_{CBOOT-UVLO} (CBOOT Pin)

The driver of the high-side (HS) switch requires bias higher than V_{IN} . The capacitor, CBOOT, connected between CBOOT and SW, works as a charge pump to boost voltage on the CBOOT pin to SW + VCC. A boot diode is integrated on the LM62440-Q1 die to minimize external component count. It is recommended that a 100-nF capacitor rated for 10 V or higher is used. The V_{BOOT_UVLO} threshold (2.1 V typical) is designed to maintain proper HS switch operation. If the CBOOT capacitor voltage drops below V_{BOOT_UVLO} , then the device initiates a charging sequence, turning on the low-side switch before attempting to turn on the HS switch.

9.3.6 Adjustable SW Node Slew Rate

To allow optimization of EMI with respect to efficiency, the LM62440-Q1 is designed to allow a resistor to select the strength of the driver of the high-side FET during turn on. See § 9-14. The current drawn through the RBOOT pin (the dotted loop) is magnified and drawn through from CBOOT (the dashed line). This current is used to turn on the high-side power MOSEFT.




图 9-14. Simplified Circuit Showing How RBOOT Functions

With RBOOT short circuited to CBOOT, rise time is very fast. As a result, SW node harmonics do not "roll off" until above 150 MHz. A boot resistor of 100 Ω corresponds to approximately 2.7-ns SW node rise, and this 100- Ω boot resistor virtually eliminates SW node overshoot. The slower rise time allows energy in SW node harmonics to roll off near 100 MHz under most conditions. Rolling off harmonics eliminates the need for shielding and common mode chokes in many applications. Note that rise time increases with increasing input voltage. Noise due to stored charge is also greatly reduced with higher RBOOT resistance. Switching with slower slew rate also decreases the efficiency.

9.3.7 Spread Spectrum

Spread spectrum is pin-controlled. The purpose of spread spectrum is to eliminate peak emissions at specific frequencies by spreading these emissions across a wider range of frequencies rather than apart with fixed frequency operation. In most systems containing the LM62440-Q1, low frequency-conducted emissions from the first few harmonics of the switching frequency can be easily filtered. A more difficult design criterion is reduction of emissions at higher harmonics that fall in the FM band. These harmonics often couple to the environment through electric fields around the switch node and inductor. The LM62440-Q1 uses a ±2% spread of frequencies

Product Folder Links: LM62440-Q1

which can spread energy smoothly across the FM and TV bands but is small enough to limit subharmonic emissions below the device switching frequency. Peak emissions at the switching frequency of the part are only reduced slightly, by less than 1 dB, while peaks in the FM band are typically reduced by more than 6 dB.

The LM62440-Q1 uses a cycle-to-cycle frequency hopping method based on a linear feedback shift register (LFSR). This intelligent pseudo-random generator limits cycle-to-cycle frequency changes to limit output ripple. The pseudo-random pattern repeats at less than 1.5 Hz, which is below the audio band.

The spread spectrum is only available while the clock of the LM62440-Q1 devices are free running at their natural frequency. Any of the following conditions overrides spread spectrum, turning it off:

- · The clock is slowed during dropout.
- The clock is slowed at light load in auto mode. In FPWM mode, spread spectrum is active even if there is no load.
- At a high input voltage/low output voltage ratio when the device operates at minimum on-time, the internal clock is slowed, disabling spread spectrum. See the *Timing Characteristics*.
- The clock is synchronized with an external clock.

9.3.8 Soft Start and Recovery From Dropout


The LM62440-Q1 uses a reference-based soft start that prevents output voltage overshoots and large inrush currents during start-up. Soft start is triggered by any of the following conditions:


- Power is applied to the VIN pin of the IC, releasing UVLO.
- · EN is used to turn on the device.
- · Recovery from a hiccup waiting period
- Recovery from shutdown due to overtemperature protection

Once soft start is triggered, the IC takes the following actions:

- The reference used by the IC to regulate output voltage is slowly ramped. The net result is that output voltage takes t_{SS} to reach 90% of its desired value.
- Operating mode is set to auto, activating diode emulation. This allows start-up without pulling output low if there is a voltage already present on output.

These actions together provide start-up with limited inrush currents and also allow the use of larger output capacitors and higher loading conditions that cause current to border on current limit during start-up without triggering hiccup. See § 9-15.





Soft start works with both output voltages starting from 0 V on the left curves, or if there is already voltage on the output, as shown on right. In either case, output voltage must reach within 10% of the desired value t_{SS} after soft start is initiated. During soft start, FPWM and hiccup are disabled. Both hiccup and FPWM are enabled once output reaches regulation or t_{SS2} , whichever happens first.


图 9-15. Soft-Start Operation

Any time the output voltage falls more than a few percent, the output voltage ramps up slowly. This condition is called recovery from dropout and differs from soft start in three important ways:

- The reference voltage is set to approximately 1% above what is needed to achieve the existing output voltage.
- Hiccup is allowed if output voltage is less than 0.4 times its set point. Note that during dropout regulation itself, hiccup is inhibited.
- FPWM mode is allowed during recovery from dropout. If the output voltage were to suddenly be pulled up by an external supply, the LM62440-Q1 can pull down on the output.

Despite being called recovery from dropout, this feature is active whenever output voltage drops to a few percent lower than the set point. This primarily occurs under the following conditions:

- Dropout: When there is insufficient input voltage for the desired output voltage to be generated
- Overcurrent: When there is an overcurrent event that is not severe enough to trigger hiccup



Whether output voltage falls due to high load or low input voltage, once the condition that causes output to fall below its set point is removed, the output climbs at the same speed as during start-up. Even though hiccup does not trigger due to dropout, it can, in principle, be triggered during recovery if output voltage is below 0.4 times the output set point for more than 128 clock cycles.

图 9-16. Recovery From Dropout

9.3.9 Output Voltage Setting

If the LM62440-Q1 has fixed 5-V or fixed 3.3-V output, simply connect FB to output. See 节 10 for layout information.

For versions of the LM62440-Q1 with adjustable output voltage, a feedback resistor divider network between the output voltage and the FB pin is used to set output voltage level. See

9-17.




图 9-17. Setting Output Voltage of Adjustable Versions

Adjustable versions of the LM62440-Q1 use a 1-V reference voltage for the feedback (FB) pin. The FB pin voltage is regulated by the internal controller to be the same as the reference voltage. The output voltage level is then set by the ratio of the resistor divider. <math> 2 can be used to determine R_{FBB} for a desired output voltage

Product Folder Links: LM62440-Q1



and a given R_{FBT} . Usually R_{FBT} is between 10 k Ω and 1 M Ω . 100 k Ω is recommended for R_{FBT} for improved noise immunity compared to 1 M Ω and reduced current consumption compared to lower resistance values.

$$R_{FBB} = \frac{R_{FBT}}{V_{OUT} - 1}$$

(2)

In addition, a feedforward capacitor, C_{FF} , connected in parallel with R_{FBT} can be required to optimize the transient response.

9.3.10 Overcurrent and Short Circuit Protection

The LM62440-Q1 is protected from overcurrent conditions with cycle-by-cycle current limiting on both the high-side and the low-side MOSFETs.

High-side MOSFET overcurrent protection is implemented by the nature of the peak-current mode control. The HS switch current is sensed when the HS is turned on after a short blanking time. Every switching cycle, the HS switch current is compared to either the minimum of a fixed current set point or the output of the voltage regulation loop minus slope compensation. Because the voltage loop has a maximum value and slope compensation increases with duty cycle, HS current limit decreases with increased duty cycle when duty cycle is above 35%.

When the LS switch is turned on, the switch current is also sensed and monitored. Like the high-side device, the low-side device turns off as commanded by the voltage control loop and low-side current limit. If the LS switch current is higher than I_{LS Limit} at the end of a switching cycle, the switching cycle is extended until the LS current reduces below the limit. The LS switch is turned off once the LS current falls below its limit, and the HS switch is turned on again as long as at least one clock period has passed since the last time the HS device has turned on.




图 9-18. Current Limit Waveforms

Since the current waveform assumes values between I_{L-HS} and I_{L-LS} , the maximum output current is very close to the average of these two values. Hysteretic control is used and current does not increase as output voltage approaches zero.


The LM62440-Q1 employs hiccup overcurrent protection if there is an extreme overload, and the following conditions are met for 128 consecutive switching cycles:

- Output voltage is below approximately 0.4 times the output voltage set point.
- Greater than t_{SS2} has passed since soft start has started; see 节 9.3.8.
- The part is not operating in dropout, which is defined as having minimum off time controlled duty cycle.

In hiccup mode, the device shuts itself down and attempts to soft start after t_W . Hiccup mode helps reduce the device power dissipation under severe overcurrent conditions and short circuits. See $\boxed{8}$ 9-19.

Once the overload is removed, the device recovers as though in soft start; see

9-20.



9.3.11 Thermal Shutdown

Thermal shutdown prevents the device from extreme junction temperatures by turning off the internal switches when the IC junction temperature exceeds 165°C (typical). Thermal shutdown does not trigger below 158°C. After thermal shutdown occurs, hysteresis prevents the device from switching until the junction temperature drops to approximately 155°C. When the junction temperature falls below 155°C (typical), the LM62440-Q1 attempts to soft start.

While the LM62440-Q1 is shut down due to high junction temperature, power continues to be provided to VCC. To prevent overheating due to a short circuit applied to VCC, the LDO that provides power for VCC has reduced current limit while the part is disabled due to high junction temperature. The VCC current limit is reduced to a few milliamperes during thermal shutdown.

9.3.12 Input Supply Current

The LM62440-Q1 is designed to have very low input supply current when regulating light loads. This is achieved by powering much of the internal circuitry from the output. The BIAS pin is the input to the LDO that powers the majority of the control circuits. By connecting the BIAS input pin to the output of the regulator, a small amount of current is drawn from the output. This current is reduced at the input by the ratio of V_{OUT}/V_{IN} .

$$I_{Q_{-}VIN\,(SW)} = I_{EN} + I_{Q_{-}VIN} \times \left(\frac{1}{\eta_{eff}}\right) + I_{div} \times \left(\frac{Output\ Voltage}{Input\ Voltage \times \eta_{eff}}\right) \tag{3}$$

where

- $I_{Q\ VIN}$ is the current consumed by the operating (switching) buck converter while unloaded.
- I_Q is the current drawn from the V_{IN} terminal. See I_Q in \ddagger 8.5.
- I_{EN} is current drawn by the EN terminal. Include this current if EN is connected to VIN. See I_{EN} in 节 8.5. Note that this current drops to a very low value if connected to a voltage less than 5 V.
- I_{div} is the current drawn by the feedback voltage divider used to set output voltage.
- η_{eff} is the light-load efficiency of the buck converter with I_{Q_VIN} removed from the input current of the buck converter. η_{eff} = 0.8 is a conservative value that can be used under normal operating conditions.

9.4 Device Functional Modes

9.4.1 Shutdown Mode

The EN pin provides electrical ON and OFF control of the device. When the EN pin voltage is below 0.4 V, both the converter and the internal LDO have no output voltage and the device is in shutdown mode. In shutdown mode, the quiescent current drops to typically 0.6 µA.

9.4.2 Standby Mode

The internal LDO has a lower EN threshold than the output of the converter. When the EN pin voltage is above 1.1 V (maximum) and below the precision enable threshold for the output voltage, the internal LDO regulates the VCC voltage at 3.3 V typical. The precision enable circuitry is ON once VCC is above its UVLO. The internal power MOSFETs of the SW node remain off unless the voltage on EN pin goes above its precision enable threshold. The LM62440-Q1 also employs UVLO protection. If the VCC voltage is below its UVLO level, the output of the converter is turned off.

9.4.3 Active Mode

The LM62440-Q1 is in active mode whenever the EN pin is above V_{EN} , V_{IN} is high enough to satisfy $V_{IN_OPERATE}$, and no other fault conditions are present. The simplest way to enable the operation is to connect the EN pin to V_{IN} , which allows self start-up when the applied input voltage exceeds the minimum V_{IN} OPERATE.

In active mode, depending on the load current, input voltage, and output voltage, the LM62440-Q1 is in one of five modes:

- Continuous conduction mode (CCM) with fixed switching frequency when load current is above half of the inductor current ripple.
- Auto mode Light-Load Operation: PFM when switching frequency is decreased at very light load.
- FPWM mode Light-Load Operation: Discontinuous conduction mode (DCM) when the load current is lower than half of the inductor current ripple.
- Minimum on time: At high input voltage and low output voltages, the switching frequency is reduced to maintain regulation.
- Dropout mode: When switching frequency is reduced to minimize voltage dropout.

9.4.3.1 CCM Mode

The following operating description of the LM62440-Q1 refers to $\ ^+$ 9.2 and to the waveforms in $\ ^-$ 9-21. In CCM, the LM62440-Q1 supplies a regulated output voltage by turning on the internal high-side (HS) and low-side (LS) NMOS switches with varying duty cycle (D). During the HS switch on-time, the SW pin voltage, V_{SW} , swings up to approximately V_{IN} , and the inductor current, i_L , increases with a linear slope. The HS switch is turned off by the control logic. During the HS switch off time, t_{OFF} , the LS switch is turned on. Inductor current discharges through the LS switch, which forces the V_{SW} to swing below ground by the voltage drop across the LS switch. The converter loop adjusts the duty cycle to maintain a constant output voltage. D is defined by the on-time of the HS switch over the switching period:

$$D = T_{ON} / T_{SW}$$
 (4)

In an ideal buck converter where losses are ignored, D is proportional to the output voltage and inversely proportional to the input voltage:

$$D = V_{OUT} / V_{IN}$$
 (5)






图 9-21. SW Voltage and Inductor Current Waveforms in Continuous Conduction Mode (CCM)

9.4.3.2 Auto Mode - Light-Load Operation

The LM62440-Q1 can have two behaviors while lightly loaded. One behavior, called auto mode operation, allows for seamless transition between normal current mode operation while heavily loaded and highly efficient light load operation. The other behavior, called FPWM mode, maintains full frequency even when unloaded. Which mode the LM62440-Q1 operates in depends on the configuration of the MODE/SYNC pin. See 表 9-1. When using the LM62440-Q1, light load behavior is selected using the MODE/SYNC pin. Note that all parts operate in FPWM mode when synchronizing frequency to an external signal.

In auto mode, light load operation is employed in the LM62440-Q1. Light load operation employs two techniques to improve efficiency:

- Diode emulation, which allows DCM operation
- Frequency reduction


Note that while these two features operate together to create excellent light load behavior, they operate independently of each other.

9.4.3.2.1 Diode Emulation

Diode emulation prevents reverse current through the inductor, which requires a lower frequency needed to regulate given a fixed peak inductor current. Diode emulation also limits ripple current as frequency is reduced. With a fixed peak current, as output current is reduced to zero, frequency must be reduced to near zero to maintain regulation.

Submit Document Feedback






In auto mode, the low-side device is turned off once SW node current is near zero. As a result, once output current is less than half of what inductor ripple would be in CCM, the part operates in DCM which is equivalent to the statement that diode emulation is active.

图 9-22. PFM Operation

The device has a minimum peak inductor current setting while in auto mode. Once current is reduced to a low value with fixed input voltage, on time is constant. Regulation is then achieved by adjusting frequency. This mode of operation is called PFM mode regulation.

9.4.3.2.2 Frequency Reduction

The LM62440-Q1 reduces frequency whenever output voltage is high. This function is enabled whenever Comp, an internal signal, is low and there is an offset between the regulation set point of FB and the voltage applied to FB. The net effect is that there is larger output impedance while lightly loaded in auto mode than in normal operation. Output voltage must be approximately 1% high when the part is completely unloaded.



In auto mode, once output current drops below approximately 1/10th the rated current of the part, output resistance increases so that output voltage is 1% high while the buck is completely unloaded.


图 9-23. Steady State Output Voltage Versus Output Current in Auto Mode

In PFM operation, a small DC positive offset is required on the output voltage to activate the PFM detector. The lower the frequency in PFM, the more DC offset is needed on V_{OUT} . If the DC offset on V_{OUT} is not acceptable, a dummy load at V_{OUT} or FPWM Mode can be used to reduce or eliminate this offset.

9.4.3.3 FPWM Mode - Light-Load Operation

Like auto mode operation, FPWM operation is selected using the MODE/SYNC pin, see # 9.

In FPWM mode, frequency is maintained while lightly loaded. To maintain frequency, a limited reverse current is allowed to flow through the inductor. Reverse current is limited by reverse current limit circuitry, see † 8.5 for reverse current limit values.



In FPWM mode, continuous conduction (CCM) is possible even if I_{OUT} is less than half of I_{ripple}.


图 9-24. FPWM Mode Operation

Transitions between auto mode and FPWM mode can be commanded during operation when using the LM62440-Q1. These transitions are gradual, taking tens of clock cycles, allowing minimal disruption of output voltage during transitions. If the load is heavy enough to operate in CCM, since operation is identical in FPWM and auto mode, no change in behavior is visible until the next time the circuit is lightly loaded.

For all devices, in FPWM mode, frequency reduction is still available if output voltage is high enough to command minimum on time even while lightly loaded, allowing good behavior during faults which involve output being pulled up.

9.4.3.4 Minimum On-Time (High Input Voltage) Operation

The LM62440-Q1 continues to regulate output voltage even if the input-to-output voltage ratio requires an on time less than the minimum on time of the chip with a given clock setting. This is accomplished using valley current control. At all times, the compensation circuit dictates both a maximum peak inductor current and a maximum valley inductor current. If for any reason, valley current is exceeded, the clock cycle is extended until valley current falls below that determined by the compensation circuit. If the converter is not operating in current limit, the maximum valley current is set above the peak inductor current, preventing valley control from being used unless there is a failure to regulate using peak current only. If the input-to-output voltage ratio is too high, even though current exceeds the peak value dictated by compensation, the high-side device cannot be turned off quickly enough to regulate output voltage. As a result, the compensation circuit reduces both peak and valley current. Once a low enough current is selected by the compensation circuit, valley current matches that being commanded by the compensation circuit. Under these conditions, the low-side device is kept on and the next clock cycle is prevented from starting until inductor current drops below the desired valley current. Since on-time is fixed at its minimum value, this type of operation resembles that of a device using a Constant On-Time (COT) control scheme; see § 9-25.




In valley control mode, minimum inductor current is regulated, not peak inductor current.

图 9-25. Valley Current Mode Operation

9.4.3.5 Dropout


Dropout operation is defined as any input-to-output voltage ratio that requires frequency to drop to achieve the required duty cycle. At a given clock frequency, duty cycle is limited by minimum off time. Once this limit is reached, if clock frequency were maintained, output voltage would fall. Instead of allowing the output voltage to drop, the LM62440-Q1 extends on time past the end of the clock cycle until the required peak inductor current is achieved. The clock is allowed to start a new cycle once peak inductor current is achieved or once a predetermined maximum on time, t_{ON_MAX} , of approximately 9 μ s passes. As a result, once the needed duty cycle cannot be achieved at the selected clock frequency due to the existence of a minimum off time, frequency drops to maintain regulation. If input voltage is low enough so that output voltage cannot be regulated even with an on time of t_{ON_MAX} , output voltage drops to slightly below the input voltage, V_{DROP1} . For additional information on recovery from dropout, reference \Re 9-16.



Output voltage and frequency versus input voltage: If there is little difference between input voltage and output voltage setting, the IC reduces frequency to maintain regulation. If input voltage is too low to provide the desired output voltage at approximately 110 kHz, input voltage tracks output voltage.

图 9-26. Frequency and Output Voltage in Dropout





Switching waveforms while in dropout. Inductor current takes longer than a normal clock to reach the desired peak value. As a result, frequency drops. This frequency drop is limited by $t_{\text{ON_MAX}}$.

图 9-27. Dropout Waveforms



10 Application and Implementation

备注

以下应用部分中的信息不属于 TI 器件规格的范围, TI 不担保其准确性和完整性。TI 的客户应负责确定器件是否适用于其应用。客户应验证并测试其设计,以确保系统功能。

10.1 Application Information

The LM62440-Q1 step-down DC-to-DC converter is typically used to convert a higher DC voltage to a lower DC voltage with a maximum output current of 4 A. The following design procedure can be used to select components for the LM62440-Q1.

10.2 Typical Application

图 10-1 shows a typical application circuit for the LM62440-Q1. This device is designed to function with a wide range of external components and system parameters. However, the internal compensation is optimized for a certain range of external inductance and output capacitance. As a quick start guide, 表 10-2 provides typical component values for some of the common configurations.




图 10-1. Example Application Circuit

10.2.1 Design Requirements

表 10-1 provides the parameters for the detailed design procedure example:

表 10-1. Detailed Design Parameters

Example

Design Parameter	Example Value
Input voltage	13.5 V (5 V to 36 V)
Input voltage for constant f _{SW}	8 V to 18 V
Output voltage	5 V
Maximum output current	0 A to 4 A
Switching frequency	2.1 MHz

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback



表 10-2. Typical External Component Va	ılues
---------------------------------------	-------

f _{SW} (kHz)	V _{OUT} (V)	L1 (µH)	C _{OUT} (RATED)	R _{FBT} (kΩ)	R _{FBB} (kΩ)	C _{BOOT} (μF)	R _{BOOT} (Ω)	C _{VCC} (µF)	C _{FF} (pF)	R _{FF} (kΩ)
2100	3.3	1.5	3 × 22 μF ceramic	100	43.2	0.1	0	1	10	1
400	3.3	8.2	4 × 22 μF ceramic	100	43.2	0.1	0	1	4.7	1
2100	5	1.5	2 × 22 μF ceramic	100	24.9	0.1	0	1	22	1
400	5	8.2	3 × 22 μF ceramic	100	24.9	0.1	0	1	22	1

10.2.2 Detailed Design Procedure

The following design procedure applies to 图 10-1 and 表 10-1.

10.2.2.1 Choosing the Switching Frequency

The choice of switching frequency is a compromise between conversion efficiency and overall solution size. Lower switching frequency implies reduced switching losses and usually results in higher system efficiency. However, higher switching frequency allows for the use of smaller inductors and output capacitors, hence, a more compact design.

When choosing operating frequency, the most important consideration is thermal limitations. This constraint typically dominates frequency selection. See № 10-2 for circuits running at 400 kHz and № 10-3 for circuits running at 2.1 MHz. These curves show how much output current can be supported at a given ambient temperature given these switching frequencies. Note that power dissipation is layout-dependent so while these curves are a good starting point, thermal resistance in any design will be different from the estimates used to generate № 10-2 and № 10-3. The maximum temperature ratings are based on a 100-mm × 80-mm, 4-layer EVM PCB design, LM61460EVM.




图 10-2. Maximum Ambient Temperature Versus Output Current




图 10-3. Maximum Ambient Temperature Versus
Output Current

Two other considerations are what maximum and minimum input voltage the part must maintain its frequency setting. Since the LM62440-Q1 adjusts its frequency under conditions in which regulation would normally be prevented by minimum on time or minimum off time, these constraints are only important for input voltages requiring constant frequency operation.

If foldback is undesirable at high input voltage, then use 方程式 6:

$$f_{SW} \le \frac{V_{OUT}}{V_{IN}(MAX2) \cdot t_{ON_MIN}(MAX)}$$
 (6)

If foldback at low input voltage is a concern, use 方程式 7:

$$f_{SW} \le \frac{V_{INeff}(MIN2) - V_{OUT}}{V_{INeff}(MIN2) \cdot t_{OFF_MIN}(MAX)}$$
(7)

where:

- $V_{INeff}(MIN2) = V_{IN}(MIN2) I_{OUT}(MAX) \cdot (R_{DS(ON) HS}(MAX) + DCR(MAX))$
- · DCR(MAX) is the maximum DCR of the inductor.
- See the Electrical Characteristics for t_{OFF MIN}(MAX).
- See the Electrical Characteristics for R_{DS(ON)} H_S(MAX).

The fourth constraint is the rated frequency range of the IC. See f_{ADJ} in *Electrical Characteristics*. All previously stated constraints (thermal, $V_{IN}(MAX2)$, $V_{IN}(MIN2)$, and device-specified frequency range) must be considered when selecting frequency.

Many applications require that the AM band can be avoided. These applications tend to operate at either 400 kHz below the AM band or 2.1 MHz above the AM band. In this example, 400 kHz is chosen.

10.2.2.2 Setting the Output Voltage

The adjustable output voltage device variant of LM62440-Q1 is externally adjustable using a resistor divider network. The range of recommended output voltage is found in 节 8.3. The divider network is comprised of R_{FBT} and R_{FBB}, and closes the loop between the output voltage and the converter. The converter regulates the output voltage by holding the voltage on the FB pin equal to the internal reference voltage, V_{REF}. The resistance of the divider is a compromise between excessive noise pickup and excessive loading of the output. Smaller values of resistance reduce noise sensitivity but also reduce the light load efficiency. The recommended value for R_{FBT} is 100 k Ω with a maximum value of 1 M Ω . If 1 M Ω is selected for R_{FBT}, then a feedforward capacitor must be used across this resistor to provide adequate loop phase margin (see 节 10.2.2.10). Once R_{FBT} is selected, 方程 2 is used to select R_{FBB}. V_{REF} is nominally 1 V. For this 5-V example, R_{FBT} = 100 k Ω and R_{FBB} = 24.9 k Ω are chosen.

For the fixed output voltage versions, FB is connected directly to the output voltage node, preferably, near the top of the output capacitor. If the feedback point is located further away from the output capacitors (that is, remote sensing), then a small 100-nF capacitor can be needed at the sensing point.

10.2.2.3 Inductor Selection

The parameters for selecting the inductor are the inductance and saturation current. The inductance is based on the desired peak-to-peak ripple current and is normally chosen to be in the range of 20% to 40% of the maximum output current. Experience shows that the best value for inductor ripple current is 30% of the maximum load current for systems with a fixed input voltage and 25% for systems with a variable input voltage such as the 12 volt battery in a car. Note that when selecting the ripple current for applications with much smaller maximum load than the maximum available from the device, the maximum device current must still be used. π 8 can be used to determine the value of inductance. The constant K is the percentage of inductor current ripple. For this example, K = 0.25 was chosen and an inductance of approximately 2 μ H was found. The next standard value of 1.5 μ H was selected.

$$L = \frac{V_{IN} - V_{OUT}}{f_{SW} \cdot K \cdot I_{OUT}(MAX)} \cdot \frac{V_{OUT}}{V_{IN}}$$
(8)

The saturation current rating of the inductor must be at least as large as the high-side switch current limit, I_{L-HS} (see \dagger 8.5). This ensures that the inductor does not saturate even during a short circuit on the output. When the inductor core material saturates, the inductance falls to a very low value, causing the inductor current to rise very rapidly. Although the valley current limit, I_{L-LS} , is designed to reduce the risk of current run-away, a saturated



inductor can cause the current to rise to high values very rapidly. This can lead to component damage; do not allow the inductor to saturate. Inductors with a ferrite core material have very hard saturation characteristics, but usually have lower core losses than powdered iron cores. Powdered iron cores exhibit a soft saturation, allowing some relaxation in the current rating of the inductor. However, they have more core losses at frequencies typically above 1 MHz. In any case, the inductor saturation current must not be less than the device high-side current limit, I_{L-HS} (see \dagger 8.5). To avoid subharmonic oscillation, the inductance value must not be less than that given in \hbar \pm 9. The maximum inductance is limited by the minimum current ripple required for the current mode control to perform correctly. As a rule-of-thumb, the minimum inductor ripple current must be no less than about 10% of the device maximum rated current under nominal conditions.

$$L \ge 0.5 \cdot \frac{V_{OUT}}{f_{SW}}$$
 (9)

方程式 9 assumes that this design must operate with input voltage near or in dropout. If minimum operating voltage for this design is high enough to limit duty factor to below 40%, 方程式 8 can be used in place of 方程式 9.

Note that choosing an inductor that is larger than the minimum inductance calculated using 方程式 8 and 方程式 9 results in less output capacitance being needed to limit output ripple but more output capacitance being needed to manage large load transients. See 节 10.2.2.4.

10.2.2.4 Output Capacitor Selection

The value of the output capacitor and its ESR determine the output voltage ripple and load transient performance. The output capacitor is usually determined by the load transient requirements rather than the output voltage ripple. $\gtrsim 10-3$ can be used to find the output capacitor and C_{FF} selection for a few common applications. Note that a 1-k Ω R_{FF} can be used in series with C_{FF} to further improve noise performance. In this example, improved transient performance is desired giving 2 × 47- μ F ceramic as the output capacitor and 22 pF as C_{FF} .

5-V Output 3.3-V Output Transient Frequency Performance **Ceramic Output Capacitance** C_{FF} **Ceramic Output Capacitance** C_{FF} 2.1 MHz Minimum 3 × 22 uF 10 pF 2 × 22 µF 22 pF 2.1 MHz Better Transient 2 × 47 uF 33 pF 3 × 22 µF 33 pF 400 kHz Minimum 4 × 22 μF 4.7 pF 3 × 22 µF 10 pF 400 kHz Better Transient 5 × 22 µF 33 pF 4 × 22 μF 33 pF

表 10-3. Recommended Output Ceramic Capacitors and CFF Values

To minimize ceramic capacitance, a low-ESR electrolytic capacitor can be used in parallel with minimal ceramic capacitance. As a starting point for designing with an output electrolytic capacitor, $\frac{10-4}{5}$ shows the recommended output ceramic capacitance C_{FF} values when using an electrolytic capacitor.

表 10-4. Recommended Electrolytic and Ceramic Capacitor and C_{FF} Values

Frequency Transient Performance		3.3-V Output	5-V Output		
		C _{OUT}	C _{FF}	C _{OUT}	C _{FF}
400 kHz	Minimum	2 × 22 μF ceramic + 1 × 470 μF, 100-m Ω electrolytic	10 pF	2 × 22 μF ceramic + 1 × 470 μF, 100-m Ω electrolytic	10 pF
400 kHz	Better Transient	4 × 22 μF ceramic + 2 × 280 μF,100-m Ω electrolytic	33 pF	3 × 22 μF ceramic + 1 × 560 μF, 100-m Ω electrolytic	22 pF

Most ceramic capacitors deliver far less capacitance than the rating of the capacitor indicates. Be sure to check any capacitor selected for initial accuracy, temperature derating, and voltage derating. $\frac{10-3}{2}$ and $\frac{10-4}{2}$ have been generated assuming typical derating for 16-V, X7R, automotive grade capacitors. If lower voltage, non-automotive grade, or lower temperature rated capacitors are used, more capacitors than listed are likely to be needed.

10.2.2.5 Input Capacitor Selection

The ceramic input capacitors provide a low impedance source to the converter in addition to supplying the ripple current and isolating switching noise from other circuits. A minimum of 10 $\,\mu$ F of ceramic capacitance is required on the input of the device. This must be rated for at least the maximum input voltage that the application requires; preferably twice the maximum input voltage. This capacitance can be increased to help reduce input voltage ripple and maintain the input voltage during load transients. In addition, a small case size 100-nF ceramic capacitor must be used at each input/ground pin pair, VIN1/PGND1 and VIN2/PGND2, immediately adjacent to the converter. This provides a high-frequency bypass for the control circuits internal to the device. These capacitors also suppress SW node ringing, which reduces the maximum voltage present on the SW node and EMI. The two 100 nF must also be rated at 50 V with an X7R or better dielectric. The VQFN-HR (RJR) package provides two input voltage pins and two power ground pins on opposite sides of the package. This allows the input capacitors to be split, and placed optimally with respect to the internal power MOSFETs, thus improving the effectiveness of the input bypassing. In this example, two 4.7- μ F and two 100-nF ceramic capacitors are used, one at each VIN/PGND location. A single 10- μ F capacitor can also be used on one side of the package.

Many times, it is desirable and necessary to use an electrolytic capacitor on the input in parallel with the ceramics. This is especially true if long leads or traces are used to connect the input supply to the converter. The moderate ESR of this capacitor can help damp any ringing on the input supply caused by the long power leads. The use of this additional capacitor also helps with momentary voltage dips caused by input supplies with unusually high impedance.

Most of the input switching current passes through the ceramic input capacitors. The approximate worst case RMS value of this current can be calculated from 方程式 10 and must be checked against the manufacturers' maximum ratings.

$$I_{RMS} \approx \frac{I_{OUT}}{2}$$
 (10)

10.2.2.6 BOOT Capacitor

The LM62440-Q1 requires a bootstrap capacitor connected between the CBOOT pin and the SW pin. This capacitor stores energy that is used to supply the gate drivers for the high-side power MOSFET. A high-quality (X7R) ceramic capacitor of 100 nF and at least 10 V is required.

10.2.2.7 BOOT Resistor

A BOOT resistor can be connected between the CBOOT and RBOOT pins. Unless EMI for the application being designed is critical, these two pins can be shorted. A $100^{-}\Omega$ resistor between these pins eliminates overshoot. Even with $0^{-}\Omega$, overshoot and ringing are minimal, less than 2 V if input capacitors are placed correctly. A boot resistor of $100^{-}\Omega$, which corresponds to approximately 2.7-ns SW node rise time and decreases efficiency by approximately 0.5% at 2 MHz. To maximize efficiency, $0^{-}\Omega$ is chosen for this example. Under most circumstances, selecting an RBOOT resistor value above $100^{-}\Omega$ is undesirable since the resulting small improvement in EMI is not enough to justify further decreased efficiency.

10.2.2.8 VCC

The VCC pin is the output of the internal LDO used to supply the control circuits of the converter. This output requires a 1- μ F, 16-V ceramic capacitor connected from VCC to AGND for proper operation. In general, avoid loading this output with any external circuitry. However, this output can be used to supply the pullup for the power-good function (see \ddagger 9.3.3). A pullup resistor with a value of 100 k Ω is a good choice in this case. Note, VCC remains high when V_{EN_WAKE} < EN < V_{EN} . The nominal output voltage on VCC is 3.3 V. Do not short this output to ground or any other external voltage.

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback

10.2.2.9 BIAS

Because V_{OUT} = 5 V in this design, the BIAS pin is tied to V_{OUT} to reduce LDO power loss. The output voltage is supplying the LDO current instead of the input voltage. The power saving is $I_{LDO} \times (V_{IN} - V_{OUT})$. The power saving is more significant when $V_{IN} >> V_{OUT}$ and with higher frequency operation. To prevent V_{OUT} noise and transients from coupling to BIAS, a series resistor, 1 Ω to 10 Ω , can be added between V_{OUT} and BIAS. A bypass capacitor with a value of 1 μ F or higher can be added close to the BIAS pin to filter noise. Note the maximum allowed voltage on the BIAS pin is 16 V.

10.2.2.10 C_{FF} and R_{FF} Selection

A feedforward capacitor, C_{FF} , is used to improve phase margin and transient response of circuits, which have output capacitors with low ESR. Since this capacitor can conduct noise from the output of the circuit directly to the FB node of the IC, a 1-k Ω resistor, R_{FF} , can be placed in series with C_{FF} . If the ESR zero of the output capacitor is below 200 kHz, no C_{FF} must be used.

If output voltage is less than 2.5 V, C_{FF} has little effect, so it can be omitted. If output voltage is greater than 14 V, C_{FF} must not be used since it introduces too much gain at higher frequencies.

10.2.2.11 External UVLO

In some cases, an input UVLO level different than that provided internal to the device is needed. This can be accomplished by using the circuit shown in 图 10-4. The input voltage at which the device turns on is designated V_{ON} while the turnoff voltage is V_{OFF} . First, a value for R_{ENB} is chosen in the range of 10 k Ω to 100 k Ω , then $\dot{\mathcal{D}}$ to 12 is used to calculate R_{ENT} and V_{OFF} . R_{ENB} is typically set based on how much current this voltage divider must consume. R_{ENB} can be calculated using $\dot{\mathcal{D}}$ #2 11.

$$R_{ENB} = \frac{V_{EN} \cdot V_{IN}}{I_{DIVIDER} \cdot V_{ON}}$$

$$\downarrow V_{IN}$$

$$\downarrow R_{ENT}$$

$$\uparrow R_{ENT}$$

$$\uparrow R_{ENT}$$

$$\uparrow R_{ENT}$$

$$\uparrow R_{ENT}$$

$$\uparrow R_{ENT}$$

$$\uparrow R_{ENT}$$




图 10-4. UVLO Using EN

$$R_{ENT} = \left(\frac{V_{ON}}{V_{EN}} - 1\right) \cdot R_{ENB}$$

$$V_{OFF} = V_{ON} \cdot (1 - V_{EN-HYST})$$
(12)


where

- V_{ON} is the V_{IN} turn-on voltage.
- V_{OFF} is the V_{IN} turn-off voltage.
- I_{DIVIDER} is the voltage divider current.




10.2.3 Application Curves


Unless otherwise specified, the following conditions apply: V_{IN} = 13.5 V, T_A = 25°C. The circuit is shown in \boxtimes 10-1, with the appropriate BOM from \gtrsim 10-5.

























图 10-35. Conducted EMI versus CISPR25 Limits (Yellow: Peak Signal, Blue: Average Signal), LM61460EVM



Note: All EMI measurements taken with 6-A Variant $F_{SW} = 2100 \text{ kHz}$

图 10-36. Recommended Input EMI Filter, LM61460EVM

表 10-5. BOM for Typical Application Curves

V _{OUT}	Frequency	R _{FBB}	R _T	C _{OUT}	C _{IN} + C _{HF}	L	C _{FF}	
3.3 V	2100 kHz	43.2 kΩ	6.04 kΩ	3 × 22 μF	2 × 4.7 µF + 2 × 100 nF	1.5 µH (MAPI 4020HT)	22 pF	
5 V	2100 kHz	24.9 kΩ	6.04 kΩ	2 × 22 µF	2 × 4.7 µF + 2 × 100 nF	1.5 µH (MAPI 4020HT)	22 pF	

Submit Document Feedback

11 Power Supply Recommendations

The characteristics of the input supply must be compatible with *Absolute Maximum Ratings* and *Recommended Operating Conditions* in this data sheet. In addition, the input supply must be capable of delivering the required input current to the loaded converter. The average input current can be estimated with 方程式 13.

$$I_{IN} = \frac{V_{OUT} \cdot I_{OUT}}{V_{IN} \cdot \eta}$$
(13)

where

η is the efficiency.

If the converter is connected to the input supply through long wires or PCB traces, special care is required to achieve good performance. The parasitic inductance and resistance of the input cables can have an adverse effect on the operation of the converter. The parasitic inductance, in combination with the low-ESR, ceramic input capacitors, can form an under-damped resonant circuit, resulting in overvoltage transients at the input to the converter or tripping UVLO. The parasitic resistance can cause the voltage at the VIN pin to dip whenever a load transient is applied to the output. If the application is operating close to the minimum input voltage, this dip can cause the converter to momentarily shutdown and reset. The best way to solve these kind of issues is to reduce the distance from the input supply to the converter and use an aluminum input capacitor in parallel with the ceramics. The moderate ESR of this type of capacitor helps damp the input resonant circuit and reduce any overshoot or undershoot at the input. A value in the range of 20 μ F to 100 μ F is usually sufficient to provide input damping and help hold the input voltage steady during large load transients.

In some cases, a transient voltage suppressor (TVS) is used on the input of converters. One class of this device has a snap-back characteristic (thyristor type). The use of a device with this type of characteristic is not recommended. When the TVS fires, the clamping voltage falls to a very low value. If this voltage is less than the output voltage of the converter, the output capacitors discharge through the device back to the input. This uncontrolled current flow can damage the TVS and cause large input transients.

The input voltage must not be allowed to fall below the output voltage. In this scenario, such as a shorted input test, the output capacitors discharge through the internal parasitic diode found between the VIN and SW pins of the device. During this condition, the current can become uncontrolled, possibly causing damage to the device. If this scenario is considered likely, then a Schottky diode between the input supply and the output must be used.

Copyright © 2022 Texas Instruments Incorporated

Submit Document Feedback



12 Layout

12.1 Layout Guidelines

The PCB layout of any DC-DC converter is critical to the optimal performance of the design. Bad PCB layout can disrupt the operation of an otherwise good schematic design. Even if the converter regulates correctly, bad PCB layout can mean the difference between a robust design and one that cannot be mass produced. Furthermore, the EMI performance of the converter is dependent on the PCB layout, to a great extent. In a buck converter, the most critical PCB feature is the loop formed by the input capacitor or capacitors and power ground, as shown in trace inductance. These unwanted transient voltages disrupt the proper operation of the converter. Because of this, the traces in this loop must be wide and short, and the loop area as small as possible to reduce the parasitic inductance. 🛚 12-2 shows a recommended layout for the critical components for the circuit of the device.

- Place the input capacitor or capacitors as close as possible input pin pairs: VIN1 to PGND1 and VIN2 to PGND2. Each pair of pins are adjacent, simplifying the input capacitor placement. With the VQFN-HR package, there are two VIN/PGND pairs on either side of the package. This provides for a symmetrical layout and helps minimize switching noise and EMI generation. Use a wide VIN plane on a lower layer to connect both of the VIN pairs together to the input supply.
- Place bypass capacitor for VCC close to the VCC pin and AGND pins: This capacitor must routed with short, wide traces to the VCC and AGND pins.
- Use wide traces for the CBOOT capacitor. Place the CBOOT capacitor as close to the device with short, wide traces to the CBOOT and SW pins. It is important to route the SW connection under the device through the gap between VIN2 and RBOOT pins, reducing exposed SW node area. If an RBOOT resistor is used, place as close as possible to CBOOT and RBOOT pins. If high efficiency is desired, RBOOT and CBOOT pins can be shorted. This short must be placed as close as possible to RBOOT and CBOOT pins as possible.
- Place the feedback divider as close as possible to the FB pin of the device: Place R_{FBB}, R_{FBT}, and C_{FF}, if used, physically close to the device. The connections to FB and AGND through R_{FBB} must be short and close to those pins on the device. The connection to V_{OUT} can be somewhat longer. However, this latter trace must not be routed near any noise source (such as the SW node) that can capacitively couple into the feedback path of the converter. For fixed output variants, the FB pin must be directly routed to the output of the device.
- Layer of the PCB beneath the top layer with the IC must be a ground plane: This plane acts as a noise shield and a heat dissipation path. Using the layer directly next to the IC reduces the inclosed area in the input circulating current in the input loop, reducing inductance.
- Provide wide paths for V_{IN} , V_{OUT} , and GND: These paths must be wide and direct as possible to reduce any voltage drops on the input or output paths of the converter and maximizes efficiency.
- Provide enough PCB area for proper heat sinking: Enough copper area must be used to ensure a low R θ JA, commensurate with the maximum load current and ambient temperature. Make the top and bottom PCB layers with two-ounce copper and no less than one ounce. If the PCB design uses multiple copper layers (recommended), thermal vias can also be connected to the inner layer heat-spreading ground planes. Note that the package of this device dissipates heat through all pins. Wide traces must be used for all pins except where noise considerations dictate minimization of area.
- Keep switch area small: Keep the copper area connecting the SW pin to the inductor as short and wide as possible. At the same time, the total area of this node must be minimized to help reduce radiated EMI.

Product Folder Links: LM62440-Q1






图 12-1. Input Current Loop

12.1.1 Ground and Thermal Considerations

As mentioned above, TI recommends using one of the middle layers as a solid ground plane. A ground plane provides shielding for sensitive circuits and traces. It also provides a quiet reference potential for the control circuitry. The AGND and PGND pins must be connected to the ground planes using vias next to the bypass capacitors. PGND pins are connected directly to the source of the low-side MOSFET switch, and also connected directly to the grounds of the input and output capacitors. The PGND net contains noise at the switching frequency and can bounce due to load variations. The PGND trace, as well as the VIN and SW traces, must be constrained to one side of the ground planes. The other side of the ground plane contains much less noise and must be used for sensitive routes.

TI recommends providing adequate device heat sinking by using vias near ground and V_{IN} to connect to the system ground plane or V_{IN} strap, both of which dissipate heat. Use as much copper as possible, for system ground plane, on the top and bottom layers for the best heat dissipation. Use a four-layer board with the copper thickness for the four layers, starting from the top as: 2 oz / 1 oz / 2 oz. A four-layer board with enough copper thickness and proper layout, provides low current conduction impedance, proper shielding, and lower thermal resistance.



12.2 Layout Example




图 12-2. Layout Example

13 Device and Documentation Support

13.1 Documentation Support

13.1.1 Related Documentation

For related documentation see the following:

- Texas Instruments, Designing High Performance, Low-EMI, Automotive Power Supplies Application Report
- Texas Instruments, LM61460-Q1 EVM User's Guide
- Texas Instruments, 30 W Power for Automotive Dual USB Type-C Charge Port Reference Design
- Texas Instruments, EMI Filter Components and Their Nonidealities for Automotive DC/DC Regulators Technical Brief
- Texas Instruments, AN-2020 Thermal Design by Insight, Not Hindsight Application Report
- Texas InstrumentsOptimizing the Layout for the TPS54424/TPS54824 HotRod QFN Package for Thermal Performance Application Report
- Texas Instruments, AN-2162 Simple Success With Conducted EMI From DC-DC Converters Application Report
- · Texas Instruments, Practical Thermal Design With DC/DC Power Modules Application Report

13.2 接收文档更新通知

要接收文档更新通知,请导航至 ti.com 上的器件产品文件夹。点击*订阅更新* 进行注册,即可每周接收产品信息更改摘要。有关更改的详细信息,请查看任何已修订文档中包含的修订历史记录。

13.3 支持资源

TI E2E™ 支持论坛是工程师的重要参考资料,可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者"按原样"提供。这些内容并不构成 TI 技术规范,并且不一定反映 TI 的观点;请参阅 TI 的《使用条款》。

13.4 Trademarks

HotRod™ and TI E2E™ are trademarks of Texas Instruments.

所有商标均为其各自所有者的财产。

13.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

13.6 术语表

TI术语表本术语表列出并解释了术语、首字母缩略词和定义。

14 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copyright © 2022 Texas Instruments Incorporated

www.ti.com

7-Nov-2025

PACKAGING INFORMATION

Orderable part number	Status	Material type	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material	MSL rating/ Peak reflow	Op temp (°C)	Part marking
						(4)	(5)		
LM62440ALPQRJRRQ1	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 ALP
LM62440ALPQRJRRQ1.A	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 ALP
LM62440APPQRJRRQ1	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 APP
LM62440APPQRJRRQ1.A	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 APP
LM62440BLPQRJRRQ1	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 BLP
LM62440BLPQRJRRQ1.A	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 BLP
LM62440BPPQRJRRQ1	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 BPP
LM62440BPPQRJRRQ1.A	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 BPP
LM62440CLPQRJRRQ1	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 CLP
LM62440CLPQRJRRQ1.A	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 CLP
LM62440CPPQRJRRQ1	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 CPP
LM62440CPPQRJRRQ1.A	Active	Production	VQFN-HR (RJR) 14	3000 LARGE T&R	Yes	SN	Level-2-260C-1 YEAR	-40 to 150	6244Q1 CPP

⁽¹⁾ Status: For more details on status, see our product life cycle.

⁽²⁾ Material type: When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ RoHS values: Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.



PACKAGE OPTION ADDENDUM

www.ti.com 7-Nov-2025

(4) Lead finish/Ball material: Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) MSL rating/Peak reflow: The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com 9-Nov-2025

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width						
В0	Dimension designed to accommodate the component length						
K0	Dimension designed to accommodate the component thickness						
W	Overall width of the carrier tape						
P1	Pitch between successive cavity centers						

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LM62440ALPQRJRRQ1	VQFN- HR	RJR	14	3000	330.0	12.4	3.8	4.3	1.5	8.0	12.0	Q2
LM62440APPQRJRRQ1	VQFN- HR	RJR	14	3000	330.0	12.4	3.8	4.3	1.15	8.0	12.0	Q2
LM62440APPQRJRRQ1	VQFN- HR	RJR	14	3000	330.0	12.4	3.8	4.3	1.5	8.0	12.0	Q2
LM62440BLPQRJRRQ1	VQFN- HR	RJR	14	3000	330.0	12.4	3.8	4.3	1.5	8.0	12.0	Q2
LM62440BPPQRJRRQ1	VQFN- HR	RJR	14	3000	330.0	12.4	3.8	4.3	1.15	8.0	12.0	Q2
LM62440BPPQRJRRQ1	VQFN- HR	RJR	14	3000	330.0	12.4	3.8	4.3	1.5	8.0	12.0	Q2
LM62440CLPQRJRRQ1	VQFN- HR	RJR	14	3000	330.0	12.4	3.8	4.3	1.5	8.0	12.0	Q2
LM62440CPPQRJRRQ1	VQFN- HR	RJR	14	3000	330.0	12.4	3.8	4.3	1.5	8.0	12.0	Q2



www.ti.com 9-Nov-2025




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LM62440ALPQRJRRQ1	VQFN-HR	RJR	14	3000	367.0	367.0	35.0
LM62440APPQRJRRQ1	VQFN-HR	RJR	14	3000	367.0	367.0	38.0
LM62440APPQRJRRQ1	VQFN-HR	RJR	14	3000	367.0	367.0	35.0
LM62440BLPQRJRRQ1	VQFN-HR	RJR	14	3000	367.0	367.0	35.0
LM62440BPPQRJRRQ1	VQFN-HR	RJR	14	3000	367.0	367.0	38.0
LM62440BPPQRJRRQ1	VQFN-HR	RJR	14	3000	367.0	367.0	35.0
LM62440CLPQRJRRQ1	VQFN-HR	RJR	14	3000	367.0	367.0	35.0
LM62440CPPQRJRRQ1	VQFN-HR	RJR	14	3000	367.0	367.0	35.0



PLASTIC QUAD FLATPACK - NO LEAD




NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.



PLASTIC QUAD FLATPACK - NO LEAD




NOTES: (continued)

3. This package is designed to be soldered to thermal pads on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).



PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



重要通知和免责声明

TI"按原样"提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务,您将全额赔偿,TI 对此概不负责。

TI 提供的产品受 TI 销售条款)、TI 通用质量指南 或 ti.com 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。 除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品,否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2025, 德州仪器 (TI) 公司

最后更新日期: 2025 年 10 月