

TLV243x and TLV243xA Rail-to-Rail Output, Wide-Input-Voltage Operational Amplifiers

1 Features

- Output swing includes both supply rails
- Extended common-mode input voltage range:
 - 0V to 4.5V (minimum) with 5V single supply
- No phase inversion
- Low Noise: $18\text{nV}/\sqrt{\text{Hz}}$ typical at $f = 1\text{kHz}$
- Low input offset voltage $950\mu\text{V}$ max at $T_A = 25^\circ\text{C}$ (TLV243xA)
- Low input bias current: 1pA typ
- Very low supply current: $125\mu\text{A}$ per channel maximum
- 600Ω output drive
- Automotive version available: [TLV243x-Q1](#)

2 Description

The TLV243x and TLV243xA are low-voltage operational amplifiers from Texas Instruments. The common-mode input voltage range for each device is extended over the typical CMOS amplifiers making them an excellent choice for a wide range of applications. In addition, these devices do not phase invert when the common-mode input is driven to

the supply rails. This feature satisfies most design requirements without paying a premium for rail-to-rail input performance. These devices also exhibit rail-to-rail output performance for increased dynamic range in single- or split-supply applications. These devices are fully characterized for 3V and 5V supplies, and are optimized for low-voltage operation. The TLV243x and TLV243xA only require $100\mu\text{A}$ (typical) of supply current per channel, making these devices an excellent choice for battery-powered applications. The TLV243x also have increased output drive over previous rail-to-rail operational amplifiers and are able to drive 600Ω loads for telecom applications.

Device Information

PART NUMBER ⁽¹⁾	CHANNEL COUNT	PACKAGE
TLV2432, TLV2432A	Dual	D (SOIC, 8)
		PW (TSSOP, 8)
TLV2434, TLV2434A	Quad	D (SOIC, 14)
		PW (TSSOP, 14)

(1) For more information, see [Section 8](#).




Table of Contents

1 Features	1	4.10 Electrical Characteristics, $V_{DD} = 5\text{ V}$, Q Suffix.....	10
2 Description	1	4.11 Operating Characteristics, $V_{DD} = 5\text{ V}$, Q Suffix.....	11
3 Pin Configuration and Functions	2	4.12 Typical Characteristics.....	12
4 Specifications	3	5 Detailed Description	21
4.1 Absolute Maximum Ratings.....	3	5.1 Overview.....	21
4.2 Dissipation Ratings.....	3	5.2 Functional Block Diagram.....	21
4.3 Recommended Operating Conditions.....	3	6 Device and Documentation Support	22
4.4 Electrical Characteristics, $V_{DD} = 3\text{ V}$, I and C Suffixes.....	4	6.1 Receiving Notification of Documentation Updates.....	22
4.5 Operating Characteristics, $V_{DD} = 3\text{ V}$, I and C Suffixes.....	5	6.2 Support Resources.....	22
4.6 Electrical Characteristics, $V_{DD} = 3\text{ V}$, Q Suffix.....	6	6.3 Trademarks.....	22
4.7 Operating Characteristics, $V_{DD} = 3\text{ V}$, Q Suffix.....	7	6.4 Electrostatic Discharge Caution.....	22
4.8 Electrical Characteristics, $V_{DD} = 5\text{ V}$, I and C Suffixes.....	8	6.5 Glossary.....	22
4.9 Operating Characteristics, $V_{DD} = 5\text{ V}$, C and I Suffixes.....	9	7 Revision History	22
		8 Mechanical, Packaging, and Orderable Information ..	23

3 Pin Configuration and Functions




Figure 3-1. TLV2432x: D Package, 8-Pin SOIC (Top View)




Figure 3-2. TLV2432x: PW Package, 8 Pin TSSOP (Top View)




Figure 3-3. TLV2434x: D Package, 14-Pin SOIC, and PW Package, 14-Pin TSSOP (Top View)

4 Specifications

4.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		VALUE	UNIT
V _{DD}	Supply voltage ⁽²⁾	12	V
V _{ID}	Differential input voltage ⁽³⁾	V _{DD±}	V
V _I	Input voltage range, (any input)	–0.3 to V _{DD}	V
I _I	Input current	± 5	mA
I _O	Output current	± 50	mA
	Total current into V _{DD+}	± 50	mA
	Total current out of V _{DD–}	± 50	mA
	Duration of short-circuit current at (or below) T _A = 25°C ⁽⁴⁾	Unlimited	
	Continuous total dissipation	See Section 4.2	
T _A	Operating free-air temperature	C suffix	0 to 70
		I suffix (dual)	–40 to +85
		I suffix (quad)	–40 to +125
		Q suffix	–40 to +125
T _{stg}	Storage temperature	–65 to +150	°C

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltage values, except differential voltages, are with respect to the midpoint between V_{CC+} and V_{CC–}.
- (3) Differential voltages are at IN+ with respect to IN–. Excessive current flows, if input, are brought to less than V_{CC–} –0.3 V.
- (4) The output is able to short to either supply. Limit temperature, supply voltages, or both to not exceed the maximum dissipation ratings.

4.2 Dissipation Ratings

PACKAGE	T _A ≤ 25°C POWER RATING	DERATING FACTOR ABOVE T _A = 25°C	T _A = 70°C POWER RATING	T _A = 85°C POWER RATING	T _A = 125°C POWER RATING
D (8)	725 mW	5.8 mW/°C	464 mW	377 mW	145 mW
D (14)	1022 mW	7.6 mW/°C	900 mW	777 mW	450 mW
FK	1375 mW	11.0 mW/°C	880 mW	715 mW	275 mW
JG	1050 mW	8.4 mW/°C	672 mW	546 mW	210 mW
PW (8)	525 mW	4.2 mW/°C	336 mW	273 mW	105 mW
PW (14)	720 mW	5.6 mW/°C	634 mW	547 mW	317 mW
U	675 mW	5.4 mW/°C	432 mW	350 mW	135 mW

4.3 Recommended Operating Conditions

		C SUFFIX		I SUFFIX (DUAL)		I SUFFIX (QUAD)		Q SUFFIX		UNIT
		MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
V _{DD}	Supply voltage	2.7	10	2.7	10	2.7	10	2.7	10	V
V _I	Input voltage	V _{DD–}	V _{DD+} – 0.8	V _{DD–}	V _{DD+} – 0.8	V _{DD–}	V _{DD+} – 0.8	V _{DD–}	V _{DD+} – 0.8	V
V _{IC}	Common-mode input voltage	V _{DD–}	V _{DD+} – 1.3	V _{DD–}	V _{DD+} – 1.3	V _{DD–}	V _{DD+} – 1.3	V _{DD–}	V _{DD+} – 1.3	V
T _A	Operating free-air temperature	0	70	–40	85	–40	125	–40	125	°C

4.4 Electrical Characteristics, $V_{DD} = 3\text{ V}$, I and C Suffixes

at specified free-air temperature, $V_{DD} = 3\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		$T_A^{(1)}$	TLV243xC, TLV243xI, TLV243xAC, TLV243xAI			UNIT
					MIN	TYP	MAX	
V_{IO}	Input offset voltage	$V_{IC} = 0\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$, $V_{DD\pm} = \pm 1.5\text{ V}$	TLV243xC, TLV243xI	25°C		300	2000	μV
				Full range			2500	
			TLV243xAC, TLV243xAI	25°C		300	950	
				Full range			1500	
α_{VIO}	Temperature coefficient of input offset voltage	$V_O = 0\text{ V}$, $V_{IC} = 0\text{ V}$, $V_{DD\pm} = \pm 1.5\text{ V}$, $R_S = 50\ \Omega$			25°C to 70°C	2		$\mu\text{V}/^\circ\text{C}$
	Input offset voltage long-term drift ⁽²⁾				25°C	0.003		$\mu\text{V}/\text{MO}$
I_{IO}	Input offset current				25°C	0.5	60	pA
					Full Range		150	
I_{IB}	Input bias current				25°C	1	60	pA
					Full Range		150	
V_{ICR}	Common-mode input voltage range	$ V_{IO} \leq 5\text{ mV}$, $R_S = 50\ \Omega$			25°C	0 to 2.5	–0.25 to 2.75	V
					Full range	0 to 2.2		V
V_{OH}	High-level output voltage	$I_{OH} = -100\ \mu\text{A}$			25°C	2.98		V
		$I_{OH} = -3\text{ mA}$			25°C	2.5		
					Full range	2.25		
V_{OL}	Low-level output voltage	$V_{IC} = 1.5\text{ V}$, $I_{OL} = 100\ \mu\text{A}$			25°C	0.02		V
		$V_{IC} = 1.5\text{ V}$, $I_{OL} = 3\text{ mA}$			25°C	0.83		
					Full range		1	
A_{VD}	Large-signal differential voltage amplification	$V_{IC} = 2.5\text{ V}$, $V_O = 1\text{ V to } 2\text{ V}$	$R_L = 2\text{ k}\Omega^{(3)}$	25°C	1.5	2.5		V/mV
				Full range	1			
			$R_L = 1\text{ M}\Omega^{(3)}$	Full range		750		
$r_{i(d)}$	Differential input resistance			25°C		1000		G_Ω
$r_{i(c)}$	Common-mode input resistance			25°C		1000		G_Ω
$c_{i(c)}$	Common-mode input capacitance			25°C		8		pF
Z_o	Closed-loop output impedance			25°C		130		Ω
CMRR	Common-mode rejection ratio	$V_{IC} = 0\text{ V to } 2.5\text{ V}$, $V_O = 1.5\text{ V}$, $R_S = 50\ \Omega$			25°C	63	83	dB
					Full range	63		
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD} / \Delta V_{IO}$)	$V_{DD} = 2.7\text{ V to } 8\text{ V}$, $V_{IC} = V_{DD}/2$, no load			25°C	80	95	dB
					Full range	80		
I_{DD}	Supply current (per channel)	$V_O = 1.5\text{ V}$, no load			25°C	115	150	μA
					Full range		175	

- (1) Full range for C suffix is 0°C to 70°C. Full range for dual I suffix is –40°C to +85°C. Full range for quad I suffix is –40°C to +125°C.
(2) Typical values are based on the input offset voltage shift observed through 500 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.
(3) Referenced to 2.5 V.

4.5 Operating Characteristics, $V_{DD} = 3\text{ V}$, I and C Suffixes

at specified free-air temperature, $V_{DD} = 3\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T_A ⁽¹⁾	TLV243xC, TLV243xI, TLV243xAC, TLV243xAI			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1\text{ V to }2\text{ V}$, $R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C	0.15	0.25		V/ μs
				Full range	0.1			
V_n	Equivalent input noise voltage	$f = 10\text{ Hz}$		25°C		120		nV/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		25°C		22		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		25°C		2.7		μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		25°C		4		
I_n	Equivalent input noise current			25°C		0.6		fA/ $\sqrt{\text{Hz}}$
THD + N	Total harmonic distortion plus noise	$V_O = 0.5\text{ V to }2.5\text{ V}$, $f = 1\text{ kHz}$, $R_L = 2\text{ k}\Omega$ ⁽²⁾	$A_V = 1$	25°C		0.065%		
			$A_V = 10$	25°C		0.5%		
	Gain-bandwidth product	$f = 10\text{ kHz}$, $R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C		0.5		MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 1\text{ V}$, $A_V = 1$, $R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C		220		kHz
t_s	Settling time	$A_V = -1$, step = $0.5\text{ V to }2.5\text{ V}$, $R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾	To 0.1%	25°C		6.4		μs
			To 0.01%	25°C		14.1		
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C		62°		
	Gain margin	$R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C		11		dB

(1) Full range for C suffix is 0°C to 70°C. Full range for dual I suffix is –40°C to 85°C. Full range for quad I suffix is –40°C to 125°C.

(2) Referenced to 2.5 V.

4.6 Electrical Characteristics, $V_{DD} = 3\text{ V}$, Q Suffix

at specified free-air temperature, $V_{DD} = 3\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T _A	TLV243xQ, TLV243xAQ			UNIT	
					MIN	TYP	MAX		
V _{IO}	Input offset voltage	V _{IC} = 0 V, V _O = 0 V, R _S = 50 Ω, V _{DD±} = ±1.5 V	TLV243xQ	25°C	300		2000	μV	
				–40°C to +125°C	2500				
			TLV243xAQ	25°C	300		950		
				–40°C to +125°C	2000				
α _{VIO}	Temperature coefficient of input offset voltage	VO = 0 V, VIC = 0 V, VDD± = ±1.5 V, RS = 50 Ω		25°C to 70°C	2			μV/°C	
	Input offset voltage long-term drift ⁽¹⁾			25°C	0.003			μV/MO	
I _{IO}	Input offset current			25°C	0.5		60	pA	
				–40°C to +125°C	150				
I _{IB}	Input bias current			25°C	1		60	pA	
				–40°C to +125°C	300				
V _{ICR}	Common-mode input voltage range			25°C	0 to 2.5	–0.25 to 2.75		V	
				–40°C to +125°C	0 to 2.2			V	
V _{OH}	High-level output voltage			I _{OH} = –100 μA	25°C	2.98		V	
				I _{OH} = –3 mA	25°C	2.5			
					–40°C to +125°C	2.25			
V _{OL}	Low-level output voltage			V _{IC} = 1.5 V, I _{OL} = 100 μA	25°C	0.02		V	
				V _{IC} = 1.5 V, I _{OL} = 3 A	25°C	0.83			
					–40°C to +125°C	1			
A _{VD}	Large-signal differential voltage amplification			V _{IC} = 2.5 V, V _O = 1 V to 2 V	R _L = 2 kΩ ⁽²⁾	25°C	1.5	2.5	V/mV
						–40°C to +125°C	0.5		
		R _L = 1 MΩ ⁽²⁾	–40°C to +125°C		750				
r _{i(d)}	Differential input resistance			25°C	1000		GΩ		
r _{i(c)}	Common-mode input resistance			25°C	1000		GΩ		
c _{i(c)}	Common-mode input capacitance			25°C	8		pF		
z _o	Closed-loop output impedance			25°C	130		Ω		
CMRR	Common-mode rejection ratio	V _{IC} = 0 V to 2.5 V, V _O = 1.5 V, R _S = 50 Ω		25°C	63	83	dB		
				–40°C to +125°C	63				
k _{SVR}	Supply-voltage rejection ratio (ΔV _{DD} /ΔV _{IO})	V _{DD} = 2.7 V to 8 V, V _{IC} = V _{DD} /2, no load		25°C	80	95	dB		
				–40°C to +125°C	80				
I _{DD}	Supply current (per channel)	V _O = 1.5 V, no load		25°C	115	150	μA		
				–40°C to +125°C		175			

(1) Typical values are based on the input offset voltage shift observed through 500 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.

(2) Referenced to 2.5 V.

4.7 Operating Characteristics, $V_{DD} = 3\text{ V}$, Q Suffix

at specified free-air temperature, $V_{DD} = 3\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T_A	TLV243xQ, TLV243xAQ			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1\text{ V to }2\text{ V}$, $R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$		25°C	0.15	0.25		V/ μs
				–40°C to +125°C	0.1			
V_n	Equivalent input noise voltage	$f = 10\text{ Hz}$		25°C		120		nV/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		25°C		22		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		25°C		2.7		μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		25°C		4		
I_n	Equivalent input noise current			25°C		0.6		fA/ $\sqrt{\text{Hz}}$
THD + N	Total harmonic distortion plus noise	$V_O = 0.5\text{ V to }2.5\text{ V}$, $f = 1\text{ kHz}$, $R_L = 2\text{ k}\Omega^{(2)}$	$A_V = 1$	25°C		0.065%		
			$A_V = 10$	25°C		0.5%		
	Gain-bandwidth product	$f = 10\text{ kHz}$, $R_L = 2\text{ k}\Omega^{(2)}$, $C_L = 100\text{ pF}^{(2)}$		25°C		0.5		MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 1\text{ V}$, $A_V = 1$, $R_L = 2\text{ k}\Omega^{(2)}$, $C_L = 100\text{ pF}^{(2)}$		25°C		220		kHz
t_s	Settling time	$A_V = -1$, step = $0.5\text{ V to }2.5\text{ V}$, $R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$	To 0.1%	25°C		6.4		μs
			To 0.01%	25°C		14.1		
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$		25°C		62°		
	Gain margin	$R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$		25°C		11		dB

(1) Referenced to 2.5 V.

4.8 Electrical Characteristics, $V_{DD} = 5\text{ V}$, I and C Suffixes

at specified free-air temperature, $V_{DD} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T _A ⁽¹⁾	TLV243xC, TLV243xI, TLV243xAC, TLV243xAI			UNIT
					MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0 V, V _O = 0 V, R _S = 50 Ω, V _{DD±} = ±2.5 V	TLV243xC, TLV243xI	25°C	300		2000	μV
				Full range	2500			
			TLV243xAC, TLV243xAI	25°C	300		950	
				Full range	1500			
α _{VIO}	Temperature coefficient of input offset voltage	V _O = 0 V, V _{IC} = 0V _{DD±} = ±2.5 V, R _S = 50 Ω	25°C to 70°C		2		μV/°C	
	Input offset voltage long-term drift ⁽²⁾		25°C		0.003		μV/MO	
I _{IO}	Input offset current		25°C		0.5		60	pA
			Full Range		150			
I _{IB}	Input bias current		25°C		1		60	pA
			Full Range		150			
V _{ICR}	Common-mode input voltage range	V _{IO} ≤ 5 mV, R _S = 50 Ω		25°C	0 to 4.5	−0.25 to 4.75	V	
				Full range	0 to 4.2		V	
V _{OH}	High-level output voltage	I _{OH} = −100 μA		25°C	4.97		V	
		I _{OH} = −5 mA		25°C	4	4.35		
				Full range	4			
V _{OL}	Low-level output voltage	V _{IC} = 2.5 V, I _{OL} = 100 μA		25°C	0.01		V	
		V _{IC} = 2.5 V, I _{OL} = 5 mA		25°C	0.8			
				Full range	1.25			
A _{VD}	Large-signal differential voltage amplification	V _{IC} = 2.5 V, V _O = 1 V to 4 V	R _L = 2 kΩ ⁽³⁾	25°C	2.5	3.8	V/mV	
				Full range	1.5			
			R _L = 1 MΩ ⁽³⁾	Full range	950			
r _{I(d)}	Differential input resistance			25°C	1000		G _Ω	
r _{I(c)}	Common-mode input resistance			25°C	1000		G _Ω	
c _{i(c)}	Common-mode input capacitance	f = 10 kHz		25°C	8		pF	
Z _o	Closed-loop output impedance	f = 100 kHz, A _V = 10		25°C	130		Ω	
CMRR	Common-mode rejection ratio	V _{IC} = 0 V to 4.5 V, V _O = 2.5 V, R _S = 50 Ω		25°C	63	90	dB	
				Full range	63			
k _{SVR}	Supply-voltage rejection ratio (ΔV _{DD} /ΔV _{IO})	V _{DD} = 4.4 V to 8 V, V _{IC} = V _{DD} /2, no load		25°C	80	95	dB	
				Full range	80			
I _{DD}	Supply current (per channel)	V _O = 2.5 V, no load		25°C	115	150	μA	
				Full range	175			

- (1) Full range for C suffix is 0°C to 70°C. Full range for dual I suffix is −40°C to +85°C. Full range for quad I suffix is −40°C to +125°C.
(2) Typical values are based on the input offset voltage shift observed through 500 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.
(3) Referenced to 2.5 V.

4.9 Operating Characteristics, $V_{DD} = 5\text{ V}$, C and I Suffixes

at specified free-air temperature, $V_{DD} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T_A ⁽¹⁾	TLV243xC, TLV243xI, TLV243xAC, TLV243xAI			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1.5\text{ V to }3\text{ V}$, $R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C	0.15	0.25		V/ μs
				Full range	0.1			
V_n	Equivalent input noise voltage	$f = 10\text{ Hz}$		25°C		100		nV/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		25°C		18		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		25°C		1.9		μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		25°C		2.8		
I_n	Equivalent input noise current			25°C		0.6		fA/ $\sqrt{\text{Hz}}$
THD + N	Total harmonic distortion plus noise	$V_O = 0.5\text{ V to }3.5\text{ V}$, $f = 1\text{ kHz}$, $R_L = 2\text{ k}\Omega$ ⁽²⁾	$A_V = 1$	25°C		0.045%		
			$A_V = 10$	25°C		0.4%		
	Gain-bandwidth product	$f = 10\text{ kHz}$, $R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C		0.55		MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 2\text{ V}$, $A_V = 1$, $R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C		100		kHz
t_s	Settling time	$A_V = -1$, step = $0.5\text{ V to }3.5\text{ V}$, $R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾	To 0.1%	25°C		6.4		μs
			To 0.01%	25°C		13.1		
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C		66°		
	Gain margin	$R_L = 2\text{ k}\Omega$ ⁽²⁾ , $C_L = 100\text{ pF}$ ⁽²⁾		25°C		11		dB

(1) Full range for C suffix is 0°C to 70°C. Full range for dual I suffix is –40°C to +85°C. Full range for quad I suffix is –40°C to +125°C.

(2) Referenced to 2.5 V.

4.10 Electrical Characteristics, $V_{DD} = 5\text{ V}$, Q Suffix

at specified free-air temperature, $V_{DD} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T_A	TLV243xQ, TLV243xAQ			UNIT
					MIN	TYP	MAX	
V_{IO}	Input offset voltage	$V_{IC} = 0\text{ V}$, $V_O = 0\text{ V}$, $R_S = 50\ \Omega$, $V_{DD\pm} = \pm 2.5\text{ V}$	TLV2453xQ	25°C		300	2000	μV
				–40°C to +125°C			2500	
			TLV2453xAQ	25°C		300	950	
				–40°C to +125°C			2000	
α_{VIO}	Temperature coefficient of input offset voltage			25°C to 70°C		2		$\mu\text{V}/^\circ\text{C}$
	Input offset voltage long-term drift ⁽¹⁾			25°C		0.003		$\mu\text{V}/\text{MO}$
I_{IO}	Input offset current	$V_O = 0\text{ V}$, $V_{IC} = 0\text{ V}$, $V_{DD\pm} = \pm 2.5\text{ V}$, $R_S = 50\ \Omega$		25°C		0.5	60	pA
				–40°C to +125°C			150	
I_{IB}	Input bias current			25°C		1	60	pA
				–40°C to +125°C			300	
V_{ICR}	Common-mode input voltage range	$ V_{IO} \leq 5\text{ mV}$, $R_S = 50\ \Omega$		25°C	0 to 4.5	–0.25 to 4.75		V
				–40°C to +125°C	0 to 4.2			V
V_{OH}	High-level output voltage	$I_{OH} = -100\ \mu\text{A}$		25°C		4.97		V
		$I_{OH} = -5\text{ mA}$		25°C	4	4.35		
				–40°C to +125°C	4			
V_{OL}	Low-level output voltage	$V_{IC} = 2.5\text{ V}$, $I_{OL} = 100\ \mu\text{A}$		25°C		0.01		V
		$V_{IC} = 2.5\text{ V}$, $I_{OL} = 5\text{ mA}$		25°C		0.8		
				–40°C to +125°C			1.25	
A_{VD}	Large-signal differential voltage amplification	$V_{IC} = 2.5\text{ V}$, $V_O = 1\text{ V to }4\text{ V}$	$R_L = 2\text{ k}\Omega^{(2)}$	25°C	2.5	3.8		V/mV
				–40°C to +125°C	1.5			
			$R_L = 1\text{ M}\Omega^{(2)}$	–40°C to +125°C		950		
$r_{i(d)}$	Differential input resistance			25°C		1000		$\text{G}\Omega$
$r_{i(c)}$	Common-mode input resistance			25°C		1000		$\text{G}\Omega$
$c_{i(c)}$	Common-mode input capacitance	$f = 10\text{ kHz}$		25°C		8		pF
z_o	Closed-loop output impedance	$f = 100\text{ kHz}$, $A_V = 10$		25°C		130		Ω
CMRR	Common-mode rejection ratio	$V_{IC} = 0\text{ to }4.5\text{ V}$, $V_O = 2.5\text{ V}$, $R_S = 50\ \Omega$		25°C	63	90		dB
				–40°C to +125°C	63			
k_{SVR}	Supply-voltage rejection ratio ($\Delta V_{DD} / \Delta V_{IO}$)	$V_{DD} = 4.4\text{ V to }8\text{ V}$, $V_{IC} = V_{DD}/2$, no load		25°C	80	95		dB
				–40°C to +125°C	80			
I_{DD}	Supply current (per channel)	$V_O = 2.5\text{ V}$, no load		25°C		115	150	μA
				–40°C to +125°C			175	

(1) Typical values are based on the input offset voltage shift observed through 500 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.

(2) Referenced to 2.5 V.

4.11 Operating Characteristics, $V_{DD} = 5\text{ V}$, Q Suffix

at specified free-air temperature, $V_{DD} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T_A	TLV243xQ, TLV243xAQ			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 1.5\text{ V to }3\text{ V}$, $R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$		25°C	0.15	0.25		V/ μs
				–40°C to +125°C	0.1			
V_n	Equivalent input noise voltage	$f = 10\text{ Hz}$		25°C		100		nV/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		25°C		18		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		25°C		1.9		μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		25°C		2.8		
I_n	Equivalent input noise current			25°C		0.6		fA/ $\sqrt{\text{Hz}}$
THD + N	Total harmonic distortion plus noise	$V_O = 0.5\text{ V to }3.5\text{ V}$, $f = 1\text{ kHz}$, $R_L = 2\text{ k}\Omega^{(1)}$	$A_V = 1$	25°C		0.045%		
			$A_V = 10$	25°C		0.4%		
	Gain-bandwidth product	$f = 10\text{ kHz}$, $R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$		25°C		0.55		MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 2\text{ V}$, $A_V = 1$, $R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$		25°C		100		kHz
t_s	Settling time	$A_V = -1$, step = $0.5\text{ V to }3.5\text{ V}$, $R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$	To 0.1%	25°C		6.4		μs
			To 0.01%	25°C		13.1		
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$		25°C		66°		
	Gain margin	$R_L = 2\text{ k}\Omega^{(1)}$, $C_L = 100\text{ pF}^{(1)}$		25°C		11		dB

(1) Referenced to 2.5 V.

4.12 Typical Characteristics




Figure 4-1.




Figure 4-2.




Figure 4-3.




Figure 4-4.




Figure 4-5.




Figure 4-6.

4.12 Typical Characteristics (continued)




Figure 4-7.




Figure 4-8.




Figure 4-9.




Figure 4-10.




Figure 4-11.




Figure 4-12.

4.12 Typical Characteristics (continued)




Figure 4-13.




Figure 4-14.




Figure 4-15.




Figure 4-16.




Figure 4-17.




Figure 4-18.

4.12 Typical Characteristics (continued)




Figure 4-19.




Figure 4-20.




Figure 4-21.




Figure 4-22.




Figure 4-23.




Figure 4-24.

4.12 Typical Characteristics (continued)




Figure 4-25.




Figure 4-26.




Figure 4-27.




Figure 4-28.




Figure 4-29.




Figure 4-30.

4.12 Typical Characteristics (continued)




Figure 4-31.




Figure 4-32.




Figure 4-33.




Figure 4-34.




Figure 4-35.




Figure 4-36.

4.12 Typical Characteristics (continued)




Figure 4-37.




Figure 4-38.




Figure 4-39.




Figure 4-40.




Figure 4-41.




Figure 4-42.

4.12 Typical Characteristics (continued)




Figure 4-43.




Figure 4-44.




Figure 4-45.




Figure 4-46.




Figure 4-47.





Figure 4-48.

4.12 Typical Characteristics (continued)



5 Detailed Description

5.1 Overview

The other members of the TLV243x and TLV243xA family are the high-power [TLV244x](#)TLV244x, and micro-power [TLV2422](#).

The TLV243x, exhibiting high input impedance and low noise, are excellent for small-signal conditioning for high-impedance sources, such as piezoelectric transducers. As a result of the micropower dissipation levels and low-voltage operation, these devices work well in portable monitoring and remote-sensing applications. In addition, the rail-to-rail output feature with single- or split-supplies makes this family a great choice when interfacing with analog-to-digital converters (ADCs). For precision applications, the TLV243xA are available and have a maximum input offset voltage of 950 μ V.

If the design requires single operational amplifiers, see the [TLV2211](#), [TLV2221](#), and [TLV2231](#). This family of rail-to-rail output operational amplifiers is available in the SOT-23 package. The small size and low power consumption make these devices an excellent choice for high-density, battery-powered equipment.

5.2 Functional Block Diagram




Figure 5-1. Equivalent Schematic (Each Amplifier)

6 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

6.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

6.2 Support Resources

TI E2E™ support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

6.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

6.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

6.5 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

7 Revision History


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision F (Nov 1999) to Revision G (July 2025)	Page
• Deleted obsolete FK, JG, and U packages from data sheet.....	1
• Deleted obsolete M-suffix device from data sheet.....	1
• Updated <i>Features</i> to delete "Macromodel Included" and add link to automotive data sheet.....	1
• Deleted <i>Equivalent Schematic</i>	2
• Changed CMRR minimum value for all temperatures from 70 dB to 63 dB in all <i>Electrical Characteristics</i>	4
• Changed I_{DD} at $T_A = 25^\circ\text{C}$ TYP value from 98 μA to 115 μA , and MAX value from 125 μA to 150 μA	4
• Changed I_{DD} at $T_A = \text{Full range}$ MAX value from 125 μA to 175 μA	4
• Changed I_{DD} at $T_A = 25^\circ\text{C}$ TYP value from 195 μA to 115 μA , and MAX value from 250 μA to 150 μA	6
• Changed I_{DD} at $T_A = \text{Full range}$ from 260 μA to 175 μA	6
• Changed I_{DD} at $T_A = 25^\circ\text{C}$ TYP value from 100 μA to 115 μA , and MAX value from 125 μA to 150 μA	8
• Changed I_{DD} at $T_A = \text{Full range}$ from 125 μA to 175 μA	8
• Changed I_{DD} at $T_A = 25^\circ\text{C}$ TYP value from 200 μA to 115 μA , and MAX value from 250 μA to 150 μA	10
• Changed I_{DD} at $T_A = \text{Full range}$ from 270 μA to 175 μA	10
• Updated functional block diagram.....	21
• Deleted <i>Application Information</i> and <i>Macromodel Information</i> section.....	21


8 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

TAPE AND REEL INFORMATION




QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TLV2432AIDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
TLV2432AIPWR	TSSOP	PW	8	2000	330.0	12.4	7.0	3.6	1.6	8.0	12.0	Q1
TLV2432CDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
TLV2432IDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
TLV2434AIDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLV2434AIPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TLV2434AIPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TLV2434CDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLV2434CPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TLV2434CPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TLV2434IDR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLV2434IDRG4	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
TLV2434IPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1
TLV2434IPWR	TSSOP	PW	14	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1


TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TLV2432AIDR	SOIC	D	8	2500	353.0	353.0	32.0
TLV2432AIPWR	TSSOP	PW	8	2000	353.0	353.0	32.0
TLV2432CDR	SOIC	D	8	2500	353.0	353.0	32.0
TLV2432IDR	SOIC	D	8	2500	353.0	353.0	32.0
TLV2434AIDR	SOIC	D	14	2500	353.0	353.0	32.0
TLV2434AIPWR	TSSOP	PW	14	2000	353.0	353.0	32.0
TLV2434AIPWR	TSSOP	PW	14	2000	353.0	353.0	32.0
TLV2434CDR	SOIC	D	14	2500	353.0	353.0	32.0
TLV2434CPWR	TSSOP	PW	14	2000	353.0	353.0	32.0
TLV2434CPWR	TSSOP	PW	14	2000	353.0	353.0	32.0
TLV2434IDR	SOIC	D	14	2500	353.0	353.0	32.0
TLV2434IDRG4	SOIC	D	14	2500	353.0	353.0	32.0
TLV2434IPWR	TSSOP	PW	14	2000	353.0	353.0	32.0
TLV2434IPWR	TSSOP	PW	14	2000	353.0	353.0	32.0

TUBE




*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (μm)	B (mm)
TLV2432AQD	D	SOIC	8	75	507	8	3940	4.32
TLV2432AQD.A	D	SOIC	8	75	507	8	3940	4.32
TLV2432AQDG4	D	SOIC	8	75	507	8	3940	4.32
TLV2432AQDG4.A	D	SOIC	8	75	507	8	3940	4.32
TLV2432QD	D	SOIC	8	75	507	8	3940	4.32
TLV2432QD.A	D	SOIC	8	75	507	8	3940	4.32

D0014A**PACKAGE OUTLINE****SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT




EXAMPLE BOARD LAYOUT



D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE
SCALE:8X



SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT




SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.




D0008A

PACKAGE OUTLINE

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



4214825/C 02/2019

NOTES:



1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
4. This dimension does not include interlead flash.
5. Reference JEDEC registration MS-012, variation AA.

EXAMPLE BOARD LAYOUT

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE
BASED ON .005 INCH [0.125 MM] THICK STENCIL
SCALE:8X

4214825/C 02/2019

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

EXAMPLE BOARD LAYOUT



PW0014A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



SOLDER MASK DETAILS

4220202/B 12/2023

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

PW0014A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4220202/B 12/2023

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

EXAMPLE BOARD LAYOUT



PW0008A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
SCALE:10X



SOLDER MASK DETAILS
NOT TO SCALE

4221848/A 02/2015

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

PW0008A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:10X

4221848/A 02/2015

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated